

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923905

Luminaire Tested: DFN2DIP-TR4F0-110D070US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923905
REPORT IS A COMBINATION OF REPORTS P901958 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D070US940-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14517.1 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923905

CATALOG NUMBER: DFN2DIP-TR4F0-110D070US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923905

CATALOG NUMBER: DFN2DIP-TR4F0-110D070US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87		75	75	75		63
1	100	96	92	89	93	89	86	83	78	75	73		67	65	63		57
2	92	84	78	73	85	79	74	69	69	65	61		59	56	54		50
3	84	75	68	62	78	70	64	59	61	56	52		53	49	46		45
4	77	66	59	53	72	62	56	50	55	49	45		47	43	40		41
5	71	60	52	46	66	56	49	44	49	44	39		43	39	35		37
6	66	54	46	40	61	51	43	38	45	39	35		39	35	31		34
7	61	49	41	35	57	46	39	34	41	35	31		36	31	28		31
8	57	44	37	32	53	42	35	30	37	32	28		33	28	25		29
9	53	41	33	28	49	38	32	27	34	29	25		30	26	23		27
10	49	37	30	26	46	35	29	25	32	26	23		28	24	21		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3221	3221	3221
5°	3226	3169	3190
10°	3194	3107	3086
15°	3150	3005	2925
20°	3092	2863	2728
25°	3032	2704	2538
30°	2952	2542	2297
35°	2874	2367	2085
40°	2794	2185	1842
45°	2702	1985	1622
50°	2606	1782	1407
55°	2506	1565	1200
60°	2390	1339	988
65°	2257	1108	889
70°	2096	894	804
75°	1893	788	732
80°	1600	660	634
85°	1115	440	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2702 cd/sqm

TEST NUMBER: P923905

CATALOG NUMBER: DFN2DIP-TR4F0-110D070US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.9	2.6
10°-20°	1043.0	7.2
20°-30°	1464.4	10.1
30°-40°	1596.2	11.0
40°-50°	1467.1	10.1
50°-60°	1152.2	7.9
60°-70°	750.0	5.2
70°-80°	386.0	2.7
80°-90°	102.3	0.7
90°-100°	69.5	0.5
100°-110°	259.0	1.8
110°-120°	686.8	4.7
120°-130°	1139.1	7.8
130°-140°	1209.9	8.3
140°-150°	1124.5	7.7
150°-160°	904.1	6.2
160°-170°	582.6	4.0
170°-180°	200.5	1.4
0°-30°	2887.3	19.9
0°-40°	4483.6	30.9
0°-60°	7102.9	48.9
0°-90°	8341.2	57.5
90°-120°	1015.2	7.0
90°-150°	4488.7	30.9
90°-180°	6176.0	42.5
0°-180°	14517.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4054	4054	4054	4054	4054	
5°	4054	4036	3988	4021	4010	384
15°	3856	3815	3691	3621	3584	1087
25°	3500	3382	3140	2990	2935	1610
35°	3016	2829	2506	2275	2194	1888
45°	2466	2220	1834	1574	1486	1904
55°	1875	1588	1192	972	903	1675
65°	1266	968	638	514	502	1255
75°	675	418	294	268	264	714
85°	158	81	70	70	70	181
90°	1	18	30	38	41	14
95°	99	49	59	67	66	117
105°	463	509	93	110	116	495
115°	876	902	940	235	125	863
125°	1239	1259	1288	1299	1303	1105
135°	1534	1558	1572	1587	1584	1185
145°	1779	1777	1803	1814	1806	1113
155°	1959	1945	1963	1972	1960	903
165°	2064	2055	2059	2070	2059	583
175°	2111	2100	2104	2114	2099	201
180°	2107	2107	2107	2107	2107	

TEST NUMBER: P923905

CATALOG NUMBER: DFN2DIP-TR4F0-110D070US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4054.0	4054.0	4054.0	4054.0	4054.0
2.5°	4072.3	4054.0	4013.5	4050.5	4043.1
5°	4054.0	4035.7	3987.8	4020.9	4010.0
7.5°	4020.9	3999.1	3947.7	3962.1	3943.8
10°	3976.9	3951.2	3878.0	3866.7	3845.0
12.5°	3922.0	3888.9	3789.7	3767.8	3727.3
15°	3855.8	3815.4	3690.8	3621.1	3584.5
17.5°	3778.8	3720.0	3565.9	3485.2	3426.5
20°	3690.8	3617.2	3433.9	3342.4	3261.4
22.5°	3595.5	3510.9	3298.1	3173.5	3118.6
25°	3500.1	3382.5	3140.4	2990.2	2934.9
27.5°	3386.4	3261.4	2993.7	2821.2	2736.7
30°	3265.4	3125.6	2832.2	2645.3	2546.0
32.5°	3147.8	2978.8	2678.3	2458.1	2366.2
35°	3015.9	2828.6	2506.0	2274.8	2193.8
37.5°	2887.4	2685.4	2344.4	2091.0	1999.6
40°	2751.6	2531.7	2175.5	1915.0	1819.7
42.5°	2612.2	2377.5	2007.0	1735.3	1643.8
45°	2465.5	2219.5	1834.5	1573.7	1485.8
47.5°	2326.1	2065.7	1669.5	1408.6	1328.1
50°	2171.9	1911.6	1508.0	1254.5	1177.9
52.5°	2021.3	1746.1	1353.8	1111.7	1042.0
55°	1874.6	1588.5	1192.2	972.3	902.7
57.5°	1724.4	1430.8	1049.4	843.9	785.1
60°	1570.2	1276.8	898.8	711.9	653.2
62.5°	1420.0	1126.5	770.3	594.4	565.2
65°	1265.8	968.4	638.4	513.8	502.5
67.5°	1119.1	821.7	513.8	451.1	440.2
70°	964.9	678.9	425.4	388.9	374.1
72.5°	818.1	546.5	355.8	326.5	319.1
75°	674.9	418.0	293.5	267.8	264.3
77.5°	532.1	297.0	231.2	216.4	209.0
80°	399.8	212.9	175.9	161.6	161.6
82.5°	278.7	143.2	121.1	113.7	113.7
85°	157.7	80.6	69.6	69.6	69.6
87.5°	58.8	29.2	29.2	25.7	25.7
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.1	65.5
97.5°	178.3	53.4	77.7	82.4	83.8
100°	269.9	61.0	86.9	99.0	102.1
102.5°	370.3	367.5	90.0	106.6	111.3
105°	463.4	509.2	93.0	109.7	115.8
107.5°	571.6	609.7	96.1	112.8	119.0
110°	675.4	707.2	266.8	114.4	120.4

TEST NUMBER: P923905

CATALOG NUMBER: DFN2DIP-TR4F0-110D070US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	772.9	800.2	774.4	117.3	122.0
115°	876.5	902.3	940.5	234.8	125.1
117.5°	966.4	996.8	1022.9	804.8	405.5
120°	1067.0	1089.8	1117.4	1135.7	929.9
122.5°	1152.3	1176.7	1207.4	1216.4	1218.0
125°	1239.2	1259.1	1288.1	1298.8	1303.2
127.5°	1318.5	1339.8	1362.8	1378.0	1379.5
130°	1393.2	1417.6	1434.3	1451.2	1449.7
132.5°	1469.4	1489.3	1506.0	1519.7	1518.3
135°	1533.5	1557.9	1571.6	1586.9	1583.9
137.5°	1600.4	1618.8	1634.1	1649.4	1644.8
140°	1666.0	1678.3	1695.0	1708.7	1701.1
142.5°	1721.0	1731.7	1751.4	1763.5	1756.0
145°	1779.0	1777.4	1803.2	1813.9	1806.3
147.5°	1829.1	1824.6	1850.5	1858.1	1852.1
150°	1877.9	1867.3	1891.8	1900.8	1893.2
152.5°	1919.0	1906.9	1929.8	1938.9	1928.3
155°	1958.7	1945.1	1963.4	1972.5	1960.3
157.5°	1990.7	1978.6	1992.3	2003.0	1990.7
160°	2018.3	2009.0	2018.3	2027.3	2016.6
162.5°	2042.6	2033.5	2041.0	2051.7	2038.0
165°	2063.9	2054.9	2059.3	2070.0	2059.3
167.5°	2080.7	2071.4	2076.2	2086.9	2073.1
170°	2094.4	2085.3	2088.3	2099.0	2085.3
172.5°	2103.5	2094.4	2097.6	2108.2	2094.4
175°	2111.1	2100.4	2103.5	2114.2	2099.0
177.5°	2114.2	2103.5	2105.1	2115.9	2102.0
180°	2106.6	2106.6	2106.6	2106.6	2106.6

TEST NUMBER: P923905

CATALOG NUMBER: DFN2DIP-TR4F0-110D070US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.87	12.77	12.77	13.68	14.85	7.85	8.74	8.75	9.66	10.82
	3H	13.56	14.36	14.47	15.28	16.47	9.04	9.84	9.95	10.76	11.95
	4H	14.17	14.92	15.09	15.85	17.05	9.50	10.25	10.42	11.18	12.38
	6H	14.59	15.29	15.53	16.22	17.43	9.82	10.52	10.76	11.45	12.66
	8H	14.72	15.38	15.66	16.33	17.54	9.92	10.58	10.86	11.53	12.74
	12H	14.79	15.41	15.73	16.36	17.59	9.96	10.59	10.91	11.53	12.77
4H	2H	11.90	12.66	12.83	13.58	14.78	8.45	9.21	9.38	10.13	11.33
	3H	13.74	14.36	14.68	15.32	16.53	9.81	10.44	10.75	11.39	12.61
	4H	14.43	15.00	15.38	15.96	17.19	10.36	10.93	11.31	11.88	13.12
	6H	14.95	15.44	15.91	16.42	17.66	10.78	11.28	11.75	12.25	13.49
	8H	15.13	15.59	16.09	16.55	17.81	10.91	11.37	11.88	12.34	13.60
	12H	15.22	15.64	16.21	16.62	17.88	10.98	11.40	11.97	12.38	13.64
8H	4H	14.40	14.86	15.37	15.83	17.08	10.64	11.10	11.61	12.07	13.33
	6H	14.97	15.35	15.96	16.36	17.61	11.17	11.55	12.16	12.56	13.81
	8H	15.19	15.52	16.19	16.52	17.79	11.36	11.69	12.36	12.69	13.96
	12H	15.33	15.62	16.33	16.62	17.93	11.48	11.78	12.48	12.77	14.08
12H	4H	14.36	14.77	15.34	15.76	17.02	10.65	11.07	11.64	12.05	13.31
	6H	14.95	15.28	15.95	16.28	17.55	11.22	11.55	12.22	12.55	13.82
	8H	15.17	15.47	16.17	16.46	17.77	11.43	11.73	12.43	12.72	14.03

END OF REPORT