

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920965

Luminaire Tested: DFN2DIP-TR4F0-050D080US935-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P920965  
REPORT IS A COMBINATION OF REPORTS P901964 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-050D080US935-RLLONL  
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10478.4 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 101.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P920965  
CATALOG NUMBER: DFN2DIP-TR4F0-050D080US935-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P920965

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US935-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				35
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36	30				30
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26				26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22				22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19				19
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21	17				17
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18	15				15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14				14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12				12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11				11
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1414	1414	1414
5°	1416	1391	1400
10°	1402	1364	1354
15°	1382	1319	1284
20°	1357	1257	1197
25°	1331	1187	1114
30°	1296	1115	1008
35°	1261	1039	915
40°	1226	959	808
45°	1186	871	712
50°	1144	782	617
55°	1100	687	527
60°	1049	587	433
65°	991	487	390
70°	920	392	353
75°	831	346	321
80°	702	290	278
85°	489	194	209

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1236 cd/sqm



TEST NUMBER: P920965

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US935-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.8	1.6
10°-20°	457.8	4.4
20°-30°	642.7	6.1
30°-40°	700.6	6.7
40°-50°	643.9	6.1
50°-60°	505.7	4.8
60°-70°	329.2	3.1
70°-80°	169.5	1.6
80°-90°	47.4	0.5
90°-100°	76.7	0.7
100°-110°	285.7	2.7
110°-120°	757.9	7.2
120°-130°	1256.9	12.0
130°-140°	1335.2	12.7
140°-150°	1240.9	11.8
150°-160°	997.6	9.5
160°-170°	642.8	6.1
170°-180°	221.3	2.1
0°-30°	1267.2	12.1
0°-40°	1967.8	18.8
0°-60°	3117.4	29.8
0°-90°	3663.3	35.0
90°-120°	1120.2	10.7
90°-150°	4953.3	47.3
90°-180°	6815.0	65.0
0°-180°	10478.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1779	1779	1779	1779	1779	
5°	1779	1771	1750	1765	1760	169
15°	1692	1675	1620	1589	1573	477
25°	1536	1484	1378	1312	1288	706
35°	1324	1242	1100	998	963	828
45°	1082	974	805	691	652	836
55°	823	697	523	427	396	735
65°	556	425	280	226	221	551
75°	296	184	129	118	116	313
85°	69	35	31	31	31	79
90°	2	20	34	42	45	10
95°	109	54	66	74	72	129
105°	511	562	103	121	128	546
115°	967	996	1038	259	138	952
125°	1367	1389	1421	1433	1438	1220
135°	1692	1719	1734	1751	1748	1307
145°	1963	1961	1990	2002	1993	1228
155°	2161	2146	2167	2177	2163	996
165°	2278	2268	2272	2284	2272	643
175°	2330	2318	2321	2333	2316	222
180°	2325	2325	2325	2325	2325	



TEST NUMBER: P920965

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US935-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1779.3	1779.3	1779.3	1779.3	1779.3
2.5°	1787.3	1779.3	1761.5	1777.7	1774.4
5°	1779.3	1771.2	1750.2	1764.7	1760.0
7.5°	1764.7	1755.1	1732.6	1739.0	1730.9
10°	1745.4	1734.1	1702.0	1697.1	1687.5
12.5°	1721.3	1706.8	1663.3	1653.7	1635.9
15°	1692.3	1674.6	1619.9	1589.3	1573.2
17.5°	1658.5	1632.7	1565.0	1529.6	1503.8
20°	1619.9	1587.6	1507.1	1467.0	1431.4
22.5°	1578.0	1540.9	1447.5	1392.8	1368.7
25°	1536.1	1484.5	1378.3	1312.3	1288.1
27.5°	1486.3	1431.4	1313.9	1238.2	1201.2
30°	1433.1	1371.8	1243.0	1161.0	1117.4
32.5°	1381.6	1307.4	1175.5	1078.8	1038.5
35°	1323.6	1241.5	1099.8	998.3	962.9
37.5°	1267.2	1178.6	1029.0	917.7	877.6
40°	1207.6	1111.1	954.8	840.5	798.7
42.5°	1146.5	1043.4	880.8	761.6	721.4
45°	1082.1	974.1	805.1	690.7	652.0
47.5°	1020.9	906.6	732.7	618.3	582.9
50°	953.3	839.0	661.8	550.6	516.9
52.5°	887.2	766.4	594.2	487.9	457.4
55°	822.8	697.1	523.2	426.7	396.1
57.5°	756.8	628.0	460.5	370.4	344.6
60°	689.1	560.3	394.4	312.5	286.6
62.5°	623.2	494.4	338.1	260.9	248.1
65°	555.5	425.1	280.2	225.5	220.6
67.5°	491.1	360.7	225.5	198.0	193.2
70°	423.5	297.9	186.8	170.6	164.2
72.5°	359.1	239.9	156.2	143.4	140.1
75°	296.3	183.5	128.8	117.5	116.0
77.5°	233.5	130.4	101.5	95.0	91.7
80°	175.5	93.4	77.2	70.9	70.9
82.5°	122.3	62.9	53.1	49.9	49.9
85°	69.2	35.4	30.6	30.6	30.6
87.5°	25.8	12.8	12.8	11.3	11.3
90°	1.6	20.1	33.6	42.1	45.4
92.5°	42.1	35.4	40.4	43.7	45.4
95°	109.3	53.7	65.5	74.1	72.3
97.5°	196.7	58.9	85.7	90.9	92.5
100°	297.8	67.3	95.9	109.3	112.6
102.5°	408.7	405.4	99.3	117.6	122.9
105°	511.3	561.9	102.6	121.1	127.9
107.5°	630.8	672.7	106.1	124.4	131.2
110°	745.3	780.4	294.5	126.2	132.9



TEST NUMBER: P920965

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US935-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	852.9	883.0	854.5	129.4	134.7
115°	967.2	995.7	1037.8	259.1	138.0
117.5°	1066.4	1100.0	1128.8	888.0	447.5
120°	1177.5	1202.6	1233.0	1253.2	1026.1
122.5°	1271.5	1298.6	1332.3	1342.3	1344.1
125°	1367.4	1389.4	1421.3	1433.1	1438.1
127.5°	1454.9	1478.5	1503.9	1520.6	1522.2
130°	1537.4	1564.3	1582.8	1601.4	1599.7
132.5°	1621.5	1643.5	1661.9	1677.1	1675.4
135°	1692.2	1719.2	1734.1	1751.2	1747.7
137.5°	1766.2	1786.3	1803.3	1820.1	1815.1
140°	1838.4	1852.0	1870.4	1885.6	1877.1
142.5°	1899.2	1910.9	1932.7	1946.1	1937.7
145°	1963.1	1961.3	1989.9	2001.6	1993.2
147.5°	2018.4	2013.4	2041.9	2050.4	2043.8
150°	2072.3	2060.5	2087.5	2097.5	2089.1
152.5°	2117.7	2104.3	2129.4	2139.7	2127.9
155°	2161.4	2146.5	2166.6	2176.6	2163.3
157.5°	2196.7	2183.4	2198.6	2210.4	2196.7
160°	2227.1	2217.0	2227.1	2237.1	2225.3
162.5°	2253.9	2243.9	2252.3	2264.1	2248.9
165°	2277.5	2267.5	2272.5	2284.2	2272.5
167.5°	2296.0	2285.9	2291.0	2302.8	2287.7
170°	2311.3	2301.0	2304.5	2316.3	2301.0
172.5°	2321.3	2311.3	2314.6	2326.4	2311.3
175°	2329.6	2317.8	2321.3	2333.0	2316.3
177.5°	2333.0	2321.3	2323.0	2334.8	2319.6
180°	2324.6	2324.6	2324.6	2324.6	2324.6



TEST NUMBER: P920965  
 CATALOG NUMBER: DFN2DIP-TR4F0-050D080US935-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.75	7.47	7.83	8.55	10.02	2.73	3.45	3.81	4.53	6.00
	3H	8.42	9.07	9.51	10.15	11.64	3.91	4.55	5.00	5.64	7.13
	4H	9.02	9.64	10.13	10.72	12.22	4.35	4.96	5.45	6.05	7.55
	6H	9.44	10.00	10.55	11.09	12.60	4.67	5.23	5.78	6.32	7.83
	8H	9.56	10.10	10.68	11.20	12.71	4.76	5.29	5.87	6.40	7.90
	12H	9.62	10.13	10.74	11.23	12.75	4.80	5.31	5.92	6.41	7.93
4H	2H	6.76	7.37	7.87	8.46	9.95	3.31	3.92	4.42	5.01	6.50
	3H	8.58	9.08	9.69	10.20	11.71	4.65	5.16	5.76	6.27	7.78
	4H	9.26	9.73	10.38	10.84	12.37	5.19	5.66	6.31	6.76	8.29
	6H	9.77	10.17	10.90	11.30	12.82	5.61	6.01	6.73	7.13	8.66
	8H	9.95	10.32	11.07	11.44	12.98	5.74	6.11	6.86	7.23	8.77
	12H	10.04	10.37	11.18	11.51	13.05	5.80	6.13	6.94	7.26	8.81
8H	4H	9.22	9.60	10.35	10.72	12.25	5.47	5.84	6.59	6.96	8.50
	6H	9.79	10.09	10.93	11.26	12.79	5.98	6.29	7.13	7.45	8.98
	8H	10.00	10.27	11.15	11.41	12.97	6.17	6.44	7.32	7.58	9.14
	12H	10.14	10.37	11.29	11.51	13.10	6.29	6.52	7.44	7.66	9.25
12H	4H	9.17	9.51	10.31	10.64	12.18	5.47	5.80	6.61	6.93	8.48
	6H	9.76	10.03	10.91	11.17	12.73	6.03	6.30	7.18	7.44	9.00
	8H	9.98	10.21	11.13	11.35	12.94	6.24	6.47	7.39	7.61	9.20