

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926376

Luminaire Tested: DFN2DIP-TR4F0-040D060US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926376
REPORT IS A COMBINATION OF REPORTS P900406 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D060US950-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8309.4 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926376

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926376

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39		
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34		
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29		
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25		
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22		
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19		
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17		
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15		
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14		
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12		
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1253	1253	1253
5°	1255	1233	1241
10°	1243	1209	1201
15°	1225	1169	1138
20°	1203	1114	1061
25°	1180	1052	987
30°	1149	989	894
35°	1118	921	811
40°	1087	850	717
45°	1051	772	631
50°	1014	693	547
55°	975	609	467
60°	930	521	384
65°	878	431	346
70°	815	348	313
75°	736	306	285
80°	622	257	247
85°	433	172	185

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1410 cd/sqm

TEST NUMBER: P926376

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	1.8
10°-20°	405.8	4.9
20°-30°	569.7	6.9
30°-40°	621.0	7.5
40°-50°	570.8	6.9
50°-60°	448.2	5.4
60°-70°	291.8	3.5
70°-80°	150.2	1.8
80°-90°	43.5	0.5
90°-100°	112.0	1.3
100°-110°	355.9	4.3
110°-120°	609.1	7.3
120°-130°	801.1	9.6
130°-140°	899.2	10.8
140°-150°	881.7	10.6
150°-160°	739.6	8.9
160°-170°	490.5	5.9
170°-180°	171.4	2.1
0°-30°	1123.3	13.5
0°-40°	1744.3	21.0
0°-60°	2763.3	33.3
0°-90°	3248.8	39.1
90°-120°	1077.0	13.0
90°-150°	3659.0	44.0
90°-180°	5061.0	60.9
0°-180°	8309.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	2	20	54	50	52	8
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	

TEST NUMBER: P926376

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4

TEST NUMBER: P926376

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3

TEST NUMBER: P926376

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.81	7.56	7.86	8.61	10.03	2.79	3.53	3.84	4.59	6.01
	3H	8.48	9.15	9.54	10.21	11.65	3.97	4.64	5.03	5.70	7.14
	4H	9.09	9.72	10.16	10.78	12.23	4.42	5.05	5.49	6.11	7.56
	6H	9.51	10.09	10.59	11.15	12.61	4.73	5.32	5.82	6.38	7.84
	8H	9.63	10.18	10.72	11.27	12.72	4.82	5.38	5.91	6.46	7.91
	12H	9.69	10.21	10.78	11.29	12.77	4.86	5.39	5.95	6.47	7.94
4H	2H	6.82	7.45	7.90	8.52	9.96	3.37	4.00	4.45	5.07	6.51
	3H	8.64	9.17	9.73	10.26	11.72	4.71	5.24	5.80	6.33	7.79
	4H	9.33	9.81	10.42	10.89	12.38	5.26	5.74	6.35	6.82	8.30
	6H	9.84	10.26	10.94	11.36	12.83	5.68	6.09	6.78	7.19	8.67
	8H	10.02	10.40	11.11	11.50	12.99	5.80	6.19	6.90	7.29	8.78
	12H	10.11	10.46	11.22	11.56	13.06	5.87	6.22	6.98	7.32	8.82
8H	4H	9.29	9.68	10.39	10.78	12.27	5.53	5.92	6.63	7.02	8.51
	6H	9.86	10.17	10.98	11.31	12.80	6.05	6.37	7.17	7.51	8.99
	8H	10.07	10.35	11.20	11.47	12.98	6.24	6.52	7.37	7.64	9.15
	12H	10.21	10.45	11.34	11.57	13.11	6.36	6.60	7.49	7.72	9.26
12H	4H	9.24	9.59	10.36	10.70	12.19	5.54	5.88	6.65	6.99	8.49
	6H	9.83	10.11	10.96	11.23	12.74	6.10	6.38	7.23	7.50	9.01
	8H	10.05	10.29	11.18	11.41	12.95	6.31	6.55	7.44	7.67	9.21

END OF REPORT