

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921048

Luminaire Tested: DFN2DIP-TR4F0-070D110US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921048
REPORT IS A COMBINATION OF REPORTS P900502 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D110US935-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13504.7 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 150.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921048
CATALOG NUMBER: DFN2DIP-TR4F0-070D110US935-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P921048
 CATALOG NUMBER: DFN2DIP-TR4F0-070D110US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				38
1	95	91	88	84	87	83	80	77	68	66	64	53	52	51	40	40	39	33				33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21				21
5	67	56	48	43	61	51	45	40	42	37	34	34	30	28	26	24	22	19				19
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	20	16				16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15				15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12				12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1979	1979	1979
5°	1982	1947	1960
10°	1962	1909	1896
15°	1935	1846	1797
20°	1900	1759	1676
25°	1863	1662	1560
30°	1814	1562	1411
35°	1766	1454	1281
40°	1717	1343	1132
45°	1660	1219	997
50°	1601	1095	864
55°	1540	962	738
60°	1469	822	607
65°	1387	681	546
70°	1288	549	494
75°	1163	484	450
80°	983	406	390
85°	685	271	293

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2335 cd/sqm



TEST NUMBER: P921048

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	1.7
10°-20°	640.9	4.7
20°-30°	899.8	6.7
30°-40°	980.8	7.3
40°-50°	901.5	6.7
50°-60°	708.0	5.2
60°-70°	460.8	3.4
70°-80°	237.2	1.8
80°-90°	69.1	0.5
90°-100°	185.3	1.4
100°-110°	588.9	4.4
110°-120°	1007.8	7.5
120°-130°	1325.4	9.8
130°-140°	1487.7	11.0
140°-150°	1458.9	10.8
150°-160°	1223.8	9.1
160°-170°	811.6	6.0
170°-180°	283.7	2.1
0°-30°	1774.1	13.1
0°-40°	2754.9	20.4
0°-60°	4364.3	32.3
0°-90°	5131.4	38.0
90°-120°	1782.1	13.2
90°-150°	6054.2	44.8
90°-180°	8373.0	62.0
0°-180°	13504.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	3	32	88	83	86	13
95°	132	157	162	162	157	147
105°	544	551	556	561	561	574
115°	1011	1026	1021	1019	1011	1000
125°	1471	1494	1486	1478	1476	1315
135°	1903	1931	1936	1933	1926	1471
145°	2310	2328	2342	2345	2335	1443
155°	2641	2648	2657	2669	2661	1216
165°	2873	2871	2871	2889	2876	811
175°	2990	2983	2977	2995	2980	284
180°	2995	2995	2995	2995	2995	



TEST NUMBER: P921048

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	2.7	32.5	88.5	83.1	85.8
92.5°	56.0	75.9	78.5	81.3	81.3
95°	131.8	157.1	161.6	161.6	157.1
97.5°	219.5	242.9	252.9	252.9	252.9
100°	320.5	341.3	348.5	348.5	345.9
102.5°	427.1	442.5	452.5	455.1	452.5
105°	543.6	550.9	556.3	560.8	560.8
107.5°	659.2	670.0	670.0	671.8	659.2
110°	771.2	785.7	785.7	785.7	778.4



TEST NUMBER: P921048

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	892.2	907.5	904.8	897.6	892.2
115°	1011.4	1025.8	1021.3	1018.6	1011.4
117.5°	1129.7	1149.5	1136.9	1129.7	1122.5
120°	1248.9	1268.8	1248.9	1248.9	1240.8
122.5°	1357.3	1382.5	1369.8	1362.6	1357.3
125°	1471.0	1493.6	1486.3	1478.2	1475.5
127.5°	1582.1	1610.1	1600.2	1589.3	1582.1
130°	1685.9	1718.5	1713.9	1708.5	1698.6
132.5°	1802.4	1827.7	1829.5	1816.9	1809.6
135°	1902.6	1930.6	1936.0	1933.4	1926.1
137.5°	2014.6	2037.2	2041.7	2039.9	2029.1
140°	2113.1	2135.6	2148.3	2148.3	2138.4
142.5°	2214.2	2236.8	2244.0	2246.7	2236.8
145°	2309.9	2328.0	2342.4	2345.1	2335.2
147.5°	2395.7	2418.3	2429.1	2433.6	2423.7
150°	2484.2	2499.6	2509.5	2517.6	2509.5
152.5°	2562.8	2578.1	2590.7	2600.7	2590.7
155°	2641.4	2648.5	2656.7	2669.4	2661.2
157.5°	2709.0	2714.5	2718.9	2737.0	2724.4
160°	2769.6	2775.0	2777.7	2793.1	2782.2
162.5°	2825.5	2825.5	2828.3	2845.4	2832.8
165°	2873.4	2870.7	2870.7	2888.7	2876.1
167.5°	2916.7	2908.6	2908.6	2926.7	2914.0
170°	2949.3	2942.0	2939.4	2957.4	2942.0
172.5°	2971.8	2964.6	2961.9	2980.0	2964.6
175°	2989.9	2982.7	2977.2	2995.3	2980.0
177.5°	2999.8	2992.6	2987.1	3002.6	2987.1
180°	2995.3	2995.3	2995.3	2995.3	2995.3



TEST NUMBER: P921048
 CATALOG NUMBER: DFN2DIP-TR4F0-070D110US935-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.28	9.02	9.34	10.08	11.51	4.25	4.99	5.31	6.05	7.48
	3H	9.95	10.61	11.02	11.68	13.13	5.43	6.09	6.50	7.16	8.62
	4H	10.55	11.18	11.63	12.25	13.71	5.88	6.51	6.96	7.58	9.04
	6H	10.97	11.54	12.06	12.62	14.09	6.20	6.77	7.29	7.85	9.32
	8H	11.09	11.64	12.18	12.73	14.20	6.28	6.83	7.38	7.92	9.39
	12H	11.15	11.67	12.25	12.75	14.24	6.33	6.85	7.42	7.93	9.42
4H	2H	8.28	8.91	9.37	9.98	11.44	4.83	5.46	5.92	6.53	7.99
	3H	10.10	10.63	11.20	11.72	13.20	6.18	6.70	7.27	7.80	9.27
	4H	10.79	11.27	11.89	12.36	13.85	6.72	7.20	7.82	8.29	9.78
	6H	11.30	11.71	12.41	12.82	14.31	7.14	7.55	8.24	8.66	10.15
	8H	11.48	11.86	12.58	12.96	14.46	7.26	7.65	8.37	8.75	10.25
	12H	11.57	11.91	12.69	13.03	14.54	7.33	7.67	8.45	8.79	10.30
8H	4H	10.75	11.14	11.86	12.24	13.74	7.00	7.38	8.10	8.48	9.98
	6H	11.32	11.63	12.44	12.78	14.28	7.51	7.83	8.64	8.97	10.47
	8H	11.53	11.81	12.67	12.93	14.45	7.70	7.98	8.84	9.10	10.62
	12H	11.67	11.91	12.80	13.03	14.59	7.82	8.06	8.96	9.18	10.74
12H	4H	10.70	11.05	11.82	12.16	13.67	7.00	7.34	8.12	8.46	9.97
	6H	11.29	11.57	12.43	12.69	14.21	7.56	7.84	8.69	8.96	10.48
	8H	11.51	11.75	12.65	12.87	14.43	7.77	8.01	8.91	9.13	10.69