

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926481

Luminaire Tested: DFN2DIP-TR4F0-070D050US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926481
REPORT IS A COMBINATION OF REPORTS P901914 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D050US950-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10398.6 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926481

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926481

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2193	2193	2193
5°	2196	2158	2172
10°	2174	2115	2101
15°	2145	2045	1992
20°	2105	1949	1857
25°	2064	1841	1728
30°	2010	1730	1564
35°	1957	1611	1420
40°	1902	1488	1254
45°	1839	1351	1104
50°	1774	1213	958
55°	1706	1066	817
60°	1627	911	673
65°	1537	755	605
70°	1427	608	547
75°	1289	536	498
80°	1089	450	432
85°	759	300	324

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1839 cd/sqm

TEST NUMBER: P926481

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.7	2.5
10°-20°	710.1	6.8
20°-30°	997.0	9.6
30°-40°	1086.8	10.5
40°-50°	998.8	9.6
50°-60°	784.4	7.5
60°-70°	510.6	4.9
70°-80°	262.8	2.5
80°-90°	69.9	0.7
90°-100°	53.1	0.5
100°-110°	197.9	1.9
110°-120°	524.8	5.0
120°-130°	870.4	8.4
130°-140°	924.6	8.9
140°-150°	859.3	8.3
150°-160°	690.9	6.6
160°-170°	445.2	4.3
170°-180°	153.2	1.5
0°-30°	1965.7	18.9
0°-40°	3052.5	29.4
0°-60°	4835.8	46.5
0°-90°	5679.1	54.6
90°-120°	775.8	7.5
90°-150°	3430.2	33.0
90°-180°	4719.0	45.4
0°-180°	10398.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2760	2760	2760	2760	2760	
5°	2760	2748	2715	2738	2730	262
15°	2625	2598	2513	2465	2440	740
25°	2383	2303	2138	2036	1998	1096
35°	2053	1926	1706	1549	1494	1285
45°	1679	1511	1249	1071	1012	1296
55°	1276	1082	812	662	615	1140
65°	862	659	435	350	342	854
75°	460	285	200	182	180	486
85°	107	55	47	47	47	123
90°	1	14	23	29	31	10
95°	76	37	45	51	50	90
105°	354	389	71	84	88	378
115°	670	690	719	179	96	659
125°	947	962	984	992	996	845
135°	1172	1191	1201	1213	1210	905
145°	1359	1358	1378	1386	1380	850
155°	1497	1486	1500	1507	1498	690
165°	1577	1570	1574	1582	1574	446
175°	1613	1605	1608	1616	1604	154
180°	1610	1610	1610	1610	1610	

TEST NUMBER: P926481

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2760.0	2760.0	2760.0	2760.0	2760.0
2.5°	2772.4	2760.0	2732.4	2757.6	2752.6
5°	2760.0	2747.5	2715.0	2737.5	2730.1
7.5°	2737.5	2722.6	2687.7	2697.4	2685.0
10°	2707.5	2690.1	2640.2	2632.6	2617.7
12.5°	2670.2	2647.6	2580.1	2565.2	2537.6
15°	2625.1	2597.6	2512.7	2465.3	2440.4
17.5°	2572.7	2532.7	2427.7	2372.8	2332.8
20°	2512.7	2462.7	2337.9	2275.6	2220.4
22.5°	2447.9	2390.3	2245.3	2160.5	2123.2
25°	2382.9	2302.9	2138.0	2035.7	1998.2
27.5°	2305.5	2220.4	2038.1	1920.8	1863.3
30°	2223.1	2128.0	1928.1	1801.0	1733.4
32.5°	2143.1	2028.1	1823.5	1673.5	1610.9
35°	2053.2	1925.7	1706.1	1548.7	1493.6
37.5°	1965.8	1828.2	1596.1	1423.6	1361.4
40°	1873.3	1723.6	1481.1	1303.8	1238.9
42.5°	1778.4	1618.7	1366.3	1181.3	1119.1
45°	1678.6	1511.0	1249.0	1071.4	1011.5
47.5°	1583.6	1406.4	1136.6	959.1	904.2
50°	1478.7	1301.4	1026.6	854.1	801.9
52.5°	1376.1	1188.8	921.7	756.8	709.4
55°	1276.3	1081.5	811.7	662.0	614.6
57.5°	1174.0	974.1	714.5	574.5	534.5
60°	1069.1	869.2	611.9	484.7	444.7
62.5°	966.7	766.9	524.4	404.7	384.7
65°	861.7	659.3	434.6	349.8	342.1
67.5°	761.9	559.4	349.8	307.1	299.7
70°	656.9	462.1	289.6	264.7	254.6
72.5°	557.0	372.1	242.2	222.4	217.3
75°	459.5	284.6	199.8	182.3	179.9
77.5°	362.2	202.2	157.4	147.3	142.3
80°	272.2	144.9	119.8	110.0	110.0
82.5°	189.8	97.5	82.4	77.4	77.4
85°	107.3	54.9	47.4	47.4	47.4
87.5°	40.0	19.8	19.8	17.5	17.5
90°	1.1	13.9	23.3	29.2	31.4
92.5°	29.2	24.5	28.0	30.3	31.4
95°	75.7	37.2	45.4	51.3	50.1
97.5°	136.2	40.8	59.3	63.0	64.0
100°	206.3	46.7	66.4	75.7	78.0
102.5°	283.1	280.8	68.8	81.5	85.1
105°	354.1	389.1	71.1	83.9	88.5
107.5°	436.8	465.8	73.5	86.1	90.9
110°	516.1	540.4	203.9	87.4	92.0

TEST NUMBER: P926481

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	590.6	611.5	591.8	89.7	93.2
115°	669.8	689.6	718.7	179.4	95.6
117.5°	738.5	761.8	781.7	614.9	309.9
120°	815.4	832.8	853.8	867.9	710.5
122.5°	880.5	899.2	922.6	929.6	930.8
125°	946.9	962.2	984.3	992.4	996.0
127.5°	1007.5	1023.8	1041.5	1053.0	1054.2
130°	1064.7	1083.4	1096.1	1108.9	1107.9
132.5°	1123.0	1138.1	1150.8	1161.4	1160.3
135°	1171.9	1190.6	1200.9	1212.7	1210.3
137.5°	1223.0	1237.1	1248.8	1260.4	1257.0
140°	1273.1	1282.6	1295.2	1305.7	1300.0
142.5°	1315.2	1323.4	1338.5	1347.7	1341.9
145°	1359.4	1358.2	1378.0	1386.2	1380.3
147.5°	1397.8	1394.3	1414.1	1419.9	1415.4
150°	1435.1	1427.0	1445.6	1452.6	1446.7
152.5°	1466.5	1457.2	1474.7	1481.8	1473.5
155°	1496.8	1486.4	1500.4	1507.3	1498.1
157.5°	1521.2	1512.0	1522.5	1530.7	1521.2
160°	1542.3	1535.3	1542.3	1549.2	1541.1
162.5°	1560.8	1554.0	1559.7	1567.9	1557.4
165°	1577.2	1570.3	1573.7	1581.8	1573.7
167.5°	1590.0	1583.0	1586.6	1594.7	1584.2
170°	1600.5	1593.5	1595.9	1604.0	1593.5
172.5°	1607.5	1600.5	1602.9	1611.0	1600.5
175°	1613.3	1605.1	1607.5	1615.6	1604.0
177.5°	1615.6	1607.5	1608.7	1616.8	1606.3
180°	1609.8	1609.8	1609.8	1609.8	1609.8

TEST NUMBER: P926481

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.29	11.16	11.21	12.10	13.30	6.26	7.13	7.19	8.07	9.28
	3H	11.97	12.75	12.91	13.69	14.92	7.46	8.23	8.39	9.18	10.41
	4H	12.58	13.32	13.53	14.27	15.51	7.91	8.64	8.86	9.59	10.83
	6H	13.00	13.68	13.97	14.64	15.89	8.23	8.91	9.19	9.87	11.12
	8H	13.13	13.77	14.10	14.75	16.00	8.33	8.97	9.29	9.94	11.19
	12H	13.19	13.81	14.17	14.77	16.05	8.37	8.98	9.34	9.95	11.22
4H	2H	10.31	11.05	11.27	12.00	13.24	6.86	7.60	7.82	8.55	9.79
	3H	12.15	12.76	13.11	13.74	14.99	8.22	8.83	9.18	9.81	11.06
	4H	12.84	13.40	13.81	14.37	15.65	8.77	9.33	9.74	10.30	11.58
	6H	13.36	13.84	14.34	14.83	16.11	9.19	9.67	10.18	10.67	11.95
	8H	13.53	13.98	14.52	14.97	16.26	9.32	9.77	10.31	10.76	12.05
	12H	13.63	14.03	14.64	15.04	16.34	9.39	9.79	10.40	10.80	12.10
8H	4H	12.81	13.26	13.80	14.25	15.54	9.05	9.50	10.04	10.49	11.78
	6H	13.38	13.75	14.39	14.78	16.07	9.57	9.94	10.59	10.98	12.26
	8H	13.59	13.92	14.62	14.94	16.25	9.76	10.09	10.79	11.11	12.42
	12H	13.73	14.02	14.76	15.04	16.39	9.89	10.17	10.91	11.19	12.54
12H	4H	12.76	13.17	13.77	14.18	15.47	9.06	9.46	10.06	10.47	11.77
	6H	13.35	13.68	14.37	14.70	16.01	9.62	9.95	10.64	10.97	12.28
	8H	13.58	13.86	14.60	14.88	16.23	9.84	10.12	10.86	11.14	12.49

END OF REPORT