

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926493

Luminaire Tested: DFN2DIP-TR4F0-070D080US950-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P926493  
REPORT IS A COMBINATION OF REPORTS P901968 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-070D080US950-RLLONL  
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13232.0 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 124.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9977  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926493  
CATALOG NUMBER: DFN2DIP-TR4F0-070D080US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P926493

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43				43
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	44	43	37				37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32				32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27				27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24				24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21				21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22	19				19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17				17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15				15
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14				14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14	12				12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2193	2193	2193
5°	2196	2158	2172
10°	2174	2115	2101
15°	2145	2045	1992
20°	2105	1949	1857
25°	2064	1841	1728
30°	2010	1730	1564
35°	1957	1611	1420
40°	1902	1488	1254
45°	1839	1351	1104
50°	1774	1213	958
55°	1706	1066	817
60°	1627	911	673
65°	1537	755	605
70°	1427	608	547
75°	1289	536	498
80°	1089	450	432
85°	759	300	324

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1839 cd/sqm



TEST NUMBER: P926493

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US950-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.7	2.0
10°-20°	710.1	5.4
20°-30°	997.0	7.5
30°-40°	1086.8	8.2
40°-50°	998.8	7.5
50°-60°	784.4	5.9
60°-70°	510.6	3.9
70°-80°	262.8	2.0
80°-90°	71.6	0.5
90°-100°	84.9	0.6
100°-110°	316.6	2.4
110°-120°	839.7	6.3
120°-130°	1392.7	10.5
130°-140°	1479.4	11.2
140°-150°	1374.9	10.4
150°-160°	1105.4	8.4
160°-170°	712.3	5.4
170°-180°	245.2	1.9
0°-30°	1965.7	14.9
0°-40°	3052.5	23.1
0°-60°	4835.8	36.5
0°-90°	5680.8	42.9
90°-120°	1241.3	9.4
90°-150°	5488.3	41.5
90°-180°	7551.0	57.1
0°-180°	13232.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2760	2760	2760	2760	2760	
5°	2760	2748	2715	2738	2730	262
15°	2625	2598	2513	2465	2440	740
25°	2383	2303	2138	2036	1998	1096
35°	2053	1926	1706	1549	1494	1285
45°	1679	1511	1249	1071	1012	1296
55°	1276	1082	812	662	615	1140
65°	862	659	435	350	342	854
75°	460	285	200	182	180	486
85°	107	55	47	47	47	123
90°	2	22	37	47	50	12
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P926493

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US950-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2760.0	2760.0	2760.0	2760.0	2760.0
2.5°	2772.4	2760.0	2732.4	2757.6	2752.6
5°	2760.0	2747.5	2715.0	2737.5	2730.1
7.5°	2737.5	2722.6	2687.7	2697.4	2685.0
10°	2707.5	2690.1	2640.2	2632.6	2617.7
12.5°	2670.2	2647.6	2580.1	2565.2	2537.6
15°	2625.1	2597.6	2512.7	2465.3	2440.4
17.5°	2572.7	2532.7	2427.7	2372.8	2332.8
20°	2512.7	2462.7	2337.9	2275.6	2220.4
22.5°	2447.9	2390.3	2245.3	2160.5	2123.2
25°	2382.9	2302.9	2138.0	2035.7	1998.2
27.5°	2305.5	2220.4	2038.1	1920.8	1863.3
30°	2223.1	2128.0	1928.1	1801.0	1733.4
32.5°	2143.1	2028.1	1823.5	1673.5	1610.9
35°	2053.2	1925.7	1706.1	1548.7	1493.6
37.5°	1965.8	1828.2	1596.1	1423.6	1361.4
40°	1873.3	1723.6	1481.1	1303.8	1238.9
42.5°	1778.4	1618.7	1366.3	1181.3	1119.1
45°	1678.6	1511.0	1249.0	1071.4	1011.5
47.5°	1583.6	1406.4	1136.6	959.1	904.2
50°	1478.7	1301.4	1026.6	854.1	801.9
52.5°	1376.1	1188.8	921.7	756.8	709.4
55°	1276.3	1081.5	811.7	662.0	614.6
57.5°	1174.0	974.1	714.5	574.5	534.5
60°	1069.1	869.2	611.9	484.7	444.7
62.5°	966.7	766.9	524.4	404.7	384.7
65°	861.7	659.3	434.6	349.8	342.1
67.5°	761.9	559.4	349.8	307.1	299.7
70°	656.9	462.1	289.6	264.7	254.6
72.5°	557.0	372.1	242.2	222.4	217.3
75°	459.5	284.6	199.8	182.3	179.9
77.5°	362.2	202.2	157.4	147.3	142.3
80°	272.2	144.9	119.8	110.0	110.0
82.5°	189.8	97.5	82.4	77.4	77.4
85°	107.3	54.9	47.4	47.4	47.4
87.5°	40.0	19.8	19.8	17.5	17.5
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P926493

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US950-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P926493  
 CATALOG NUMBER: DFN2DIP-TR4F0-070D080US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.17	9.95	10.19	10.97	12.34	5.15	5.92	6.17	6.95	8.32
	3H	10.85	11.54	11.88	12.57	13.96	6.33	7.02	7.36	8.06	9.45
	4H	11.45	12.11	12.50	13.14	14.54	6.78	7.44	7.82	8.47	9.87
	6H	11.87	12.47	12.92	13.51	14.93	7.10	7.70	8.15	8.74	10.15
	8H	11.99	12.57	13.05	13.63	15.03	7.19	7.76	8.25	8.82	10.23
	12H	12.05	12.60	13.12	13.65	15.08	7.23	7.78	8.29	8.83	10.26
4H	2H	9.18	9.84	10.23	10.88	12.28	5.73	6.39	6.78	7.43	8.83
	3H	11.01	11.55	12.07	12.62	14.03	7.08	7.63	8.14	8.69	10.10
	4H	11.70	12.20	12.76	13.25	14.69	7.63	8.13	8.69	9.18	10.62
	6H	12.21	12.64	13.28	13.72	15.15	8.04	8.47	9.12	9.55	10.98
	8H	12.38	12.78	13.46	13.86	15.30	8.17	8.57	9.25	9.64	11.09
	12H	12.48	12.84	13.57	13.92	15.37	8.24	8.60	9.33	9.68	11.13
8H	4H	11.66	12.06	12.74	13.13	14.58	7.90	8.30	8.98	9.37	10.82
	6H	12.23	12.56	13.32	13.67	15.11	8.42	8.75	9.52	9.86	11.31
	8H	12.44	12.73	13.55	13.83	15.29	8.61	8.90	9.72	10.00	11.46
	12H	12.58	12.83	13.68	13.92	15.42	8.73	8.98	9.84	10.08	11.58
12H	4H	11.61	11.97	12.70	13.06	14.51	7.90	8.27	9.00	9.35	10.80
	6H	12.20	12.49	13.30	13.59	15.05	8.47	8.76	9.57	9.86	11.32
	8H	12.42	12.67	13.53	13.77	15.27	8.68	8.93	9.78	10.03	11.53