

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921189

Luminaire Tested: DFN2DIP-TR4F0-110D100US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921189
REPORT IS A COMBINATION OF REPORTS P902012 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D100US935-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16574.3 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921189

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921189

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	40
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	36	42	36	32	35	31	28	29	26	24
7	59	47	39	34	55	44	37	32	38	33	29	32	28	25	27	24	21
8	55	43	35	30	51	40	33	29	35	29	26	30	25	22	25	22	19
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3110	3110	3110
5°	3115	3060	3080
10°	3084	3000	2979
15°	3041	2901	2824
20°	2985	2764	2634
25°	2928	2611	2451
30°	2851	2454	2218
35°	2775	2285	2013
40°	2698	2110	1779
45°	2609	1916	1566
50°	2516	1721	1358
55°	2420	1511	1159
60°	2308	1293	954
65°	2179	1070	858
70°	2024	863	777
75°	1828	761	706
80°	1544	638	612
85°	1076	425	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2609 cd/sqm

TEST NUMBER: P921189

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.9	2.2
10°-20°	1007.1	6.1
20°-30°	1413.9	8.5
30°-40°	1541.3	9.3
40°-50°	1416.6	8.5
50°-60°	1112.5	6.7
60°-70°	724.2	4.4
70°-80°	372.8	2.2
80°-90°	100.3	0.6
90°-100°	95.8	0.6
100°-110°	357.2	2.2
110°-120°	947.3	5.7
120°-130°	1571.2	9.5
130°-140°	1669.0	10.1
140°-150°	1551.1	9.4
150°-160°	1247.1	7.5
160°-170°	803.6	4.8
170°-180°	276.6	1.7
0°-30°	2787.9	16.8
0°-40°	4329.1	26.1
0°-60°	6858.3	41.4
0°-90°	8055.5	48.6
90°-120°	1400.3	8.4
90°-150°	6191.6	37.4
90°-180°	8519.0	51.4
0°-180°	16574.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3914	3914	3914	3914	3914	
5°	3914	3897	3850	3882	3872	371
15°	3723	3684	3564	3496	3461	1049
25°	3380	3266	3032	2887	2834	1554
35°	2912	2731	2420	2196	2118	1823
45°	2381	2143	1771	1520	1435	1838
55°	1810	1534	1151	939	872	1617
65°	1222	935	616	496	485	1212
75°	652	404	283	259	255	689
85°	152	78	67	67	67	175
90°	2	25	42	53	57	16
95°	137	67	82	93	90	162
105°	639	702	128	151	160	683
115°	1209	1245	1297	324	172	1190
125°	1709	1737	1777	1792	1798	1524
135°	2115	2149	2168	2189	2185	1634
145°	2454	2452	2487	2502	2492	1535
155°	2702	2683	2708	2721	2704	1245
165°	2847	2834	2841	2855	2841	804
175°	2912	2897	2902	2916	2895	277
180°	2906	2906	2906	2906	2906	

TEST NUMBER: P921189

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3914.4	3914.4	3914.4	3914.4	3914.4
2.5°	3932.0	3914.4	3875.3	3911.0	3903.9
5°	3914.4	3896.7	3850.5	3882.4	3871.9
7.5°	3882.4	3861.3	3811.7	3825.7	3807.9
10°	3840.0	3815.1	3744.5	3733.5	3712.5
12.5°	3786.9	3755.0	3659.2	3638.1	3599.0
15°	3723.0	3684.0	3563.7	3496.4	3461.0
17.5°	3648.7	3591.9	3443.0	3365.2	3308.5
20°	3563.7	3492.6	3315.6	3227.3	3149.1
22.5°	3471.6	3390.0	3184.5	3064.2	3011.2
25°	3379.5	3266.0	3032.3	2887.2	2833.8
27.5°	3269.8	3149.1	2890.5	2724.0	2642.5
30°	3152.9	3018.0	2734.6	2554.2	2458.3
32.5°	3039.4	2876.2	2586.1	2373.4	2284.7
35°	2912.0	2731.2	2419.7	2196.4	2118.2
37.5°	2788.0	2592.9	2263.6	2019.0	1930.7
40°	2656.8	2444.5	2100.6	1849.1	1757.0
42.5°	2522.2	2295.6	1937.8	1675.5	1587.2
45°	2380.6	2143.0	1771.3	1519.5	1434.6
47.5°	2246.0	1994.6	1612.0	1360.1	1282.4
50°	2097.1	1845.7	1456.0	1211.3	1137.3
52.5°	1951.7	1686.0	1307.2	1073.4	1006.1
55°	1810.0	1533.8	1151.2	938.8	871.6
57.5°	1665.0	1381.6	1013.2	814.8	758.0
60°	1516.1	1232.8	867.8	687.4	630.7
62.5°	1371.1	1087.7	743.8	573.9	545.7
65°	1222.2	935.0	616.4	496.1	485.2
67.5°	1080.6	793.4	496.1	435.6	425.1
70°	931.7	655.5	410.8	375.5	361.2
72.5°	790.0	527.7	343.5	315.3	308.2
75°	651.7	403.6	283.4	258.6	255.2
77.5°	513.8	286.8	223.3	209.0	201.8
80°	386.0	205.6	169.9	156.0	156.0
82.5°	269.1	138.3	116.9	109.8	109.8
85°	152.2	77.8	67.2	67.2	67.2
87.5°	56.7	28.2	28.2	24.8	24.8
90°	2.0	25.2	41.9	52.7	56.7
92.5°	52.7	44.2	50.5	54.7	56.7
95°	136.6	67.2	81.9	92.6	90.4
97.5°	245.9	73.6	107.1	113.6	115.6
100°	372.3	84.1	119.9	136.6	140.9
102.5°	510.8	506.9	124.1	147.1	153.5
105°	639.2	702.3	128.4	151.3	159.8
107.5°	788.5	840.9	132.6	155.6	164.0
110°	931.5	975.5	368.0	157.8	166.0

TEST NUMBER: P921189

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1066.1	1103.8	1068.2	161.8	168.3
115°	1208.9	1244.7	1297.4	323.8	172.5
117.5°	1333.0	1375.0	1410.9	1110.1	559.3
120°	1471.9	1503.3	1541.3	1566.5	1282.6
122.5°	1589.5	1623.2	1665.3	1677.8	1680.1
125°	1709.3	1736.8	1776.8	1791.5	1797.7
127.5°	1818.7	1848.1	1879.8	1900.8	1902.8
130°	1921.7	1955.5	1978.5	2001.6	1999.7
132.5°	2026.9	2054.3	2077.3	2096.3	2094.3
135°	2115.3	2149.0	2167.7	2188.9	2184.7
137.5°	2207.7	2232.9	2254.1	2275.1	2268.8
140°	2298.0	2315.1	2338.0	2357.0	2346.5
142.5°	2373.9	2388.7	2415.9	2432.6	2422.2
145°	2453.8	2451.6	2487.3	2502.1	2491.6
147.5°	2523.0	2516.8	2552.4	2562.9	2554.8
150°	2590.4	2575.7	2609.4	2621.9	2611.4
152.5°	2647.1	2630.3	2661.9	2674.5	2659.8
155°	2701.8	2683.0	2708.3	2720.8	2704.0
157.5°	2746.0	2729.3	2748.2	2762.9	2746.0
160°	2784.0	2771.2	2784.0	2796.4	2781.7
162.5°	2817.4	2804.9	2815.4	2830.1	2811.2
165°	2846.8	2834.3	2840.6	2855.3	2840.6
167.5°	2870.1	2857.3	2863.9	2878.6	2859.5
170°	2889.0	2876.3	2880.6	2895.3	2876.3
172.5°	2901.5	2889.0	2893.3	2908.0	2889.0
175°	2912.0	2897.3	2901.5	2916.3	2895.3
177.5°	2916.3	2901.5	2903.8	2918.5	2899.5
180°	2905.8	2905.8	2905.8	2905.8	2905.8

TEST NUMBER: P921189

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.95	11.77	11.93	12.76	14.05	6.92	7.74	7.90	8.73	10.02
	3H	12.63	13.36	13.61	14.35	15.67	8.11	8.85	9.10	9.84	11.16
	4H	13.24	13.93	14.24	14.93	16.25	8.56	9.26	9.56	10.25	11.58
	6H	13.66	14.29	14.67	15.30	16.63	8.89	9.52	9.90	10.52	11.86
	8H	13.78	14.39	14.80	15.41	16.74	8.98	9.58	9.99	10.60	11.93
	12H	13.84	14.42	14.86	15.43	16.79	9.02	9.60	10.04	10.61	11.96
4H	2H	10.97	11.66	11.97	12.66	13.98	7.52	8.21	8.52	9.21	10.53
	3H	12.80	13.37	13.81	14.40	15.74	8.87	9.44	9.88	10.47	11.81
	4H	13.49	14.01	14.51	15.03	16.39	9.42	9.94	10.44	10.96	12.32
	6H	14.00	14.45	15.04	15.50	16.85	9.84	10.29	10.87	11.33	12.69
	8H	14.18	14.60	15.21	15.63	17.01	9.97	10.39	11.00	11.42	12.79
	12H	14.27	14.65	15.32	15.70	17.08	10.03	10.41	11.08	11.46	12.84
8H	4H	13.46	13.88	14.49	14.91	16.28	9.70	10.12	10.73	11.15	12.52
	6H	14.02	14.37	15.08	15.45	16.82	10.22	10.56	11.27	11.64	13.01
	8H	14.24	14.54	15.30	15.61	16.99	10.41	10.71	11.47	11.78	13.16
	12H	14.38	14.64	15.44	15.70	17.13	10.53	10.80	11.59	11.85	13.28
12H	4H	13.41	13.79	14.46	14.84	16.21	9.70	10.08	10.75	11.13	12.51
	6H	14.00	14.30	15.06	15.36	16.75	10.26	10.57	11.33	11.63	13.02
	8H	14.22	14.49	15.28	15.54	16.97	10.48	10.75	11.54	11.80	13.23