

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926675

Luminaire Tested: DFN2DIP-TR4F0-120D090US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926675
REPORT IS A COMBINATION OF REPORTS P901995 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D090US950-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19833.6 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 193.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926675

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926675

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53
2	91	83	77	72	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	40	38
4	76	65	57	50	70	61	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	24	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3539	3539	3539
5°	3544	3489	3513
10°	3516	3442	3465
15°	3464	3386	3391
20°	3394	3307	3315
25°	3325	3213	3227
30°	3238	3125	3115
35°	3155	3022	2996
40°	3054	2917	2883
45°	2953	2813	2768
50°	2842	2703	2635
55°	2726	2576	2512
60°	2595	2425	2371
65°	2452	2269	2205
70°	2270	2078	2027
75°	2018	1850	1862
80°	1715	1560	1547
85°	1240	1058	1025

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2953 cd/sqm

TEST NUMBER: P926675

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	419.3	2.1
10°-20°	1179.6	5.9
20°-30°	1733.6	8.7
30°-40°	2013.5	10.2
40°-50°	2011.0	10.1
50°-60°	1753.5	8.8
60°-70°	1296.2	6.5
70°-80°	733.4	3.7
80°-90°	198.7	1.0
90°-100°	95.6	0.5
100°-110°	356.2	1.8
110°-120°	944.7	4.8
120°-130°	1566.8	7.9
130°-140°	1664.3	8.4
140°-150°	1546.8	7.8
150°-160°	1243.6	6.3
160°-170°	801.3	4.0
170°-180°	275.8	1.4
0°-30°	3332.5	16.8
0°-40°	5345.9	27.0
0°-60°	9110.4	45.9
0°-90°	11338.6	57.2
90°-120°	1396.4	7.0
90°-150°	6174.3	31.1
90°-180°	8495.0	42.8
0°-180°	19833.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4454	4454	4454	4454	4454	
5°	4454	4438	4390	4424	4416	423
15°	4240	4215	4159	4176	4155	1194
25°	3838	3804	3731	3739	3731	1766
35°	3311	3268	3200	3174	3152	2068
45°	2694	2664	2600	2553	2536	2079
55°	2039	2013	1962	1910	1889	1823
65°	1375	1349	1306	1268	1247	1360
75°	719	711	689	664	673	768
85°	175	171	167	154	150	196
90°	2	25	42	53	56	18
95°	136	67	82	92	90	161
105°	637	700	128	151	159	681
115°	1206	1241	1294	323	172	1187
125°	1704	1732	1772	1786	1793	1520
135°	2109	2143	2162	2183	2179	1629
145°	2447	2445	2480	2495	2485	1530
155°	2694	2676	2701	2713	2696	1242
165°	2839	2826	2833	2847	2833	802
175°	2904	2889	2894	2908	2887	276
180°	2898	2898	2898	2898	2898	

TEST NUMBER: P926675

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4454.5	4454.5	4454.5	4454.5	4454.5
2.5°	4480.4	4459.0	4411.8	4454.5	4446.3
5°	4454.5	4437.6	4390.4	4424.5	4416.3
7.5°	4424.5	4399.0	4351.8	4386.3	4377.7
10°	4377.7	4347.7	4296.3	4330.4	4317.7
12.5°	4313.1	4287.7	4236.3	4257.7	4249.0
15°	4240.4	4215.0	4159.1	4176.3	4155.0
17.5°	4150.5	4125.0	4069.1	4090.5	4069.1
20°	4051.8	4026.4	3966.4	3979.1	3962.3
22.5°	3953.7	3915.0	3859.1	3859.1	3850.5
25°	3837.8	3803.7	3731.0	3739.2	3731.0
27.5°	3709.2	3679.2	3623.8	3611.0	3589.7
30°	3581.0	3546.5	3482.4	3469.7	3452.4
32.5°	3443.7	3418.4	3349.7	3323.8	3306.6
35°	3311.0	3268.4	3199.7	3173.9	3152.5
37.5°	3161.1	3122.5	3053.8	3023.9	3002.5
40°	3007.1	2972.6	2903.9	2865.7	2848.5
42.5°	2857.1	2822.6	2754.4	2711.3	2685.8
45°	2694.4	2664.4	2599.8	2553.1	2535.8
47.5°	2535.8	2505.8	2437.2	2390.0	2364.5
50°	2368.6	2347.2	2287.2	2227.2	2205.8
52.5°	2205.8	2175.9	2120.5	2073.1	2043.2
55°	2039.1	2013.2	1961.8	1910.5	1889.1
57.5°	1871.8	1850.5	1794.6	1743.2	1726.0
60°	1704.6	1687.8	1627.8	1580.6	1567.8
62.5°	1542.0	1511.9	1469.3	1426.5	1409.2
65°	1375.2	1349.2	1306.5	1267.9	1246.6
67.5°	1203.9	1182.0	1143.8	1113.9	1096.6
70°	1045.2	1027.9	989.3	959.3	942.6
72.5°	882.5	865.3	843.9	814.0	801.2
75°	719.4	711.2	689.4	664.0	672.6
77.5°	573.9	556.7	548.1	535.3	522.6
80°	428.5	424.0	415.4	402.7	394.0
82.5°	291.3	291.3	287.2	270.0	270.0
85°	175.4	171.3	167.2	154.1	150.0
87.5°	77.3	68.6	60.0	47.2	42.7
90°	2.0	25.2	41.8	52.6	56.5
92.5°	52.6	44.1	50.3	54.6	56.5
95°	136.2	67.0	81.7	92.3	90.2
97.5°	245.3	73.5	106.8	113.2	115.2
100°	371.2	84.0	119.5	136.2	140.4
102.5°	509.4	505.4	123.7	146.6	153.1
105°	637.4	700.4	127.9	150.9	159.3
107.5°	786.3	838.6	132.2	155.1	163.6
110°	928.9	972.8	367.0	157.3	165.6

TEST NUMBER: P926675

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1063.1	1100.7	1065.1	161.3	167.8
115°	1205.6	1241.2	1293.7	322.9	172.0
117.5°	1329.3	1371.2	1407.0	1107.0	557.7
120°	1467.7	1499.1	1537.0	1562.1	1279.0
122.5°	1585.1	1618.7	1660.7	1673.1	1675.4
125°	1704.5	1731.9	1771.8	1786.5	1792.7
127.5°	1813.6	1842.9	1874.6	1895.5	1897.5
130°	1916.4	1950.1	1973.0	1996.1	1994.1
132.5°	2021.2	2048.6	2071.5	2090.5	2088.5
135°	2109.4	2143.0	2161.7	2182.8	2178.6
137.5°	2201.5	2226.6	2247.8	2268.7	2262.5
140°	2291.6	2308.6	2331.5	2350.4	2340.0
142.5°	2367.4	2382.0	2409.1	2425.8	2415.4
145°	2447.0	2444.7	2480.4	2495.1	2484.6
147.5°	2516.0	2509.8	2545.4	2555.9	2547.6
150°	2583.2	2568.5	2602.1	2614.5	2604.1
152.5°	2639.7	2623.0	2654.4	2667.1	2652.4
155°	2694.3	2675.6	2700.7	2713.2	2696.5
157.5°	2738.4	2721.7	2740.6	2755.2	2738.4
160°	2776.1	2763.5	2776.1	2788.6	2773.9
162.5°	2809.5	2797.0	2807.5	2822.2	2803.3
165°	2838.9	2826.4	2832.7	2847.4	2832.7
167.5°	2862.1	2849.4	2855.8	2870.5	2851.6
170°	2881.0	2868.3	2872.5	2887.2	2868.3
172.5°	2893.5	2881.0	2885.2	2899.9	2881.0
175°	2903.9	2889.2	2893.5	2908.1	2887.2
177.5°	2908.1	2893.5	2895.7	2910.4	2891.5
180°	2897.7	2897.7	2897.7	2897.7	2897.7

TEST NUMBER: P926675

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.29	13.22	13.19	14.14	15.30	11.86	12.79	12.76	13.71	14.87
	3H	13.96	14.79	14.86	15.72	16.91	13.49	14.32	14.39	15.24	16.43
	4H	14.55	15.34	15.47	16.27	17.47	14.08	14.87	15.00	15.79	16.99
	6H	14.95	15.68	15.89	16.61	17.83	14.48	15.21	15.41	16.14	17.35
	8H	15.06	15.75	16.00	16.70	17.91	14.59	15.28	15.52	16.23	17.44
	12H	15.11	15.77	16.06	16.72	17.95	14.63	15.29	15.58	16.23	17.47
4H	2H	12.76	13.55	13.69	14.48	15.68	12.42	13.21	13.35	14.14	15.34
	3H	14.64	15.29	15.57	16.25	17.47	14.24	14.90	15.18	15.86	17.07
	4H	15.35	15.95	16.30	16.91	18.15	14.95	15.55	15.89	16.50	17.74
	6H	15.87	16.39	16.83	17.37	18.61	15.46	15.98	16.42	16.96	18.20
	8H	16.02	16.51	16.99	17.48	18.73	15.61	16.10	16.57	17.07	18.32
	12H	16.10	16.54	17.08	17.52	18.78	15.68	16.12	16.66	17.10	18.36
8H	4H	15.56	16.04	16.52	17.01	18.26	15.20	15.68	16.16	16.65	17.90
	6H	16.19	16.59	17.18	17.60	18.85	15.83	16.23	16.81	17.24	18.49
	8H	16.41	16.77	17.41	17.77	19.04	16.04	16.40	17.04	17.40	18.67
	12H	16.55	16.86	17.55	17.85	19.17	16.16	16.47	17.16	17.47	18.78
12H	4H	15.54	15.98	16.53	16.97	18.23	15.19	15.63	16.17	16.62	17.88
	6H	16.22	16.57	17.22	17.58	18.85	15.87	16.22	16.86	17.22	18.49
	8H	16.47	16.78	17.47	17.77	19.09	16.11	16.42	17.11	17.41	18.73