

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926676

Luminaire Tested: DFN2DIP-TR4F0-120D090US950-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926676
REPORT IS A COMBINATION OF REPORTS P900476 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D090US950-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17329.4 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 193.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926676

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926676

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	100	96	92	88		93	89	86	83		77	75	72		66	64	63		55	54	53
2	91	84	78	73		85	79	73	69		68	64	61		58	56	53		49	47	46
3	84	74	67	62		78	70	63	58		61	56	52		52	49	46		44	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	51	46		66	56	49	43		49	43	39		42	38	35		36	33	30
6	65	53	46	40		61	50	43	38		44	38	34		38	34	31		33	30	27
7	61	48	41	35		56	46	39	34		40	35	30		35	31	27		30	27	24
8	56	44	37	31		52	42	35	30		37	31	27		32	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	28	25		30	25	22		26	23	20
10	49	37	30	25		46	35	29	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3759	3759	3759
5°	3765	3699	3723
10°	3728	3627	3601
15°	3676	3507	3414
20°	3609	3341	3184
25°	3539	3156	2962
30°	3446	2966	2681
35°	3354	2762	2433
40°	3261	2551	2150
45°	3153	2316	1893
50°	3041	2080	1642
55°	2925	1827	1401
60°	2790	1562	1153
65°	2634	1294	1038
70°	2446	1043	939
75°	2209	919	854
80°	1867	771	740
85°	1301	515	556

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3153 cd/sqm

TEST NUMBER: P926676

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.4	2.6
10°-20°	1217.3	7.0
20°-30°	1709.1	9.9
30°-40°	1863.0	10.8
40°-50°	1712.3	9.9
50°-60°	1344.7	7.8
60°-70°	875.3	5.1
70°-80°	450.6	2.6
80°-90°	122.7	0.7
90°-100°	168.0	1.0
100°-110°	533.9	3.1
110°-120°	913.7	5.3
120°-130°	1201.6	6.9
130°-140°	1348.7	7.8
140°-150°	1322.6	7.6
150°-160°	1109.5	6.4
160°-170°	735.8	4.2
170°-180°	257.2	1.5
0°-30°	3369.8	19.4
0°-40°	5232.8	30.2
0°-60°	8289.9	47.8
0°-90°	9738.5	56.2
90°-120°	1615.6	9.3
90°-150°	5488.5	31.7
90°-180°	7591.0	43.8
0°-180°	17329.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4732	4732	4732	4732	4732	
5°	4732	4710	4654	4693	4680	449
15°	4500	4453	4308	4226	4184	1268
25°	4085	3948	3665	3490	3425	1879
35°	3520	3301	2925	2655	2560	2203
45°	2878	2590	2141	1837	1734	2222
55°	2188	1854	1392	1135	1054	1955
65°	1477	1130	745	600	586	1465
75°	788	488	343	312	308	833
85°	184	94	81	81	81	211
90°	2	30	80	75	78	17
95°	120	142	146	146	142	133
105°	493	499	504	508	508	520
115°	917	930	926	924	917	907
125°	1334	1354	1348	1340	1338	1192
135°	1725	1750	1755	1753	1746	1333
145°	2094	2110	2124	2126	2117	1308
155°	2394	2401	2408	2420	2413	1102
165°	2605	2602	2602	2619	2607	735
175°	2710	2704	2699	2716	2702	258
180°	2716	2716	2716	2716	2716	

TEST NUMBER: P926676

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4731.5	4731.5	4731.5	4731.5	4731.5
2.5°	4752.8	4731.5	4684.2	4727.4	4718.7
5°	4731.5	4710.1	4654.2	4692.8	4680.1
7.5°	4692.8	4667.3	4607.4	4624.2	4602.9
10°	4641.5	4611.5	4526.1	4512.9	4487.5
12.5°	4577.4	4538.8	4422.9	4397.6	4350.3
15°	4500.2	4453.0	4307.6	4226.2	4183.6
17.5°	4410.2	4341.7	4161.7	4067.8	3999.2
20°	4307.6	4221.7	4007.8	3901.0	3806.5
22.5°	4196.3	4097.7	3849.2	3703.8	3639.8
25°	4085.0	3947.7	3665.2	3489.8	3425.3
27.5°	3952.3	3806.5	3493.9	3292.7	3194.1
30°	3811.0	3648.0	3305.4	3087.3	2971.5
32.5°	3673.9	3476.7	3126.0	2868.9	2761.6
35°	3519.9	3301.3	2924.7	2654.9	2560.3
37.5°	3369.9	3134.2	2736.2	2440.4	2333.7
40°	3211.4	2954.7	2539.1	2235.1	2123.8
42.5°	3048.7	2774.8	2342.4	2025.2	1918.5
45°	2877.5	2590.4	2141.1	1836.7	1734.0
47.5°	2714.8	2410.9	1948.4	1644.1	1550.1
50°	2535.0	2231.0	1759.9	1464.2	1374.7
52.5°	2359.1	2037.9	1580.0	1297.4	1216.2
55°	2187.9	1854.0	1391.5	1134.8	1053.5
57.5°	2012.5	1670.0	1224.7	984.9	916.3
60°	1832.6	1490.1	1048.9	830.9	762.3
62.5°	1657.3	1314.7	899.0	693.7	659.6
65°	1477.4	1130.3	745.1	599.7	586.5
67.5°	1306.1	959.0	599.7	526.5	513.8
70°	1126.2	792.3	496.6	453.8	436.6
72.5°	955.0	637.8	415.2	381.1	372.5
75°	787.7	487.9	342.6	312.5	308.4
77.5°	621.1	346.6	269.9	252.6	243.9
80°	466.6	248.5	205.3	188.5	188.5
82.5°	325.3	167.1	141.3	132.6	132.6
85°	184.0	94.1	81.3	81.3	81.3
87.5°	68.6	34.1	34.1	30.0	30.0
90°	2.5	29.5	80.2	75.3	77.8
92.5°	50.8	68.8	71.3	73.6	73.6
95°	119.5	142.4	146.5	146.5	142.4
97.5°	198.9	220.2	229.2	229.2	229.2
100°	290.6	309.5	316.0	316.0	313.6
102.5°	387.2	401.2	410.1	412.6	410.1
105°	492.8	499.3	504.3	508.4	508.4
107.5°	597.6	607.4	607.4	609.0	597.6
110°	699.1	712.3	712.3	712.3	705.7

TEST NUMBER: P926676

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	808.8	822.7	820.2	813.8	808.8
115°	916.9	930.0	925.9	923.5	916.9
117.5°	1024.1	1042.1	1030.7	1024.1	1017.5
120°	1132.2	1150.1	1132.2	1132.2	1124.8
122.5°	1230.4	1253.4	1241.9	1235.3	1230.4
125°	1333.6	1354.0	1347.5	1340.1	1337.7
127.5°	1434.2	1459.6	1450.7	1440.8	1434.2
130°	1528.4	1557.9	1553.8	1548.8	1539.9
132.5°	1634.0	1656.9	1658.5	1647.1	1640.6
135°	1724.8	1750.2	1755.2	1752.7	1746.2
137.5°	1826.3	1846.8	1851.0	1849.3	1839.5
140°	1915.6	1936.0	1947.5	1947.5	1938.5
142.5°	2007.3	2027.7	2034.3	2036.8	2027.7
145°	2094.1	2110.4	2123.5	2126.0	2117.0
147.5°	2171.9	2192.3	2202.1	2206.2	2197.3
150°	2252.1	2266.0	2275.0	2282.3	2275.0
152.5°	2323.3	2337.2	2348.7	2357.7	2348.7
155°	2394.5	2401.0	2408.5	2419.9	2412.6
157.5°	2455.9	2460.8	2464.9	2481.3	2469.8
160°	2510.7	2515.7	2518.2	2532.0	2522.2
162.5°	2561.5	2561.5	2564.0	2579.5	2568.1
165°	2604.9	2602.4	2602.4	2618.8	2607.4
167.5°	2644.2	2636.9	2636.9	2653.2	2641.7
170°	2673.7	2667.1	2664.7	2681.0	2667.1
172.5°	2694.1	2687.6	2685.1	2701.5	2687.6
175°	2710.5	2703.9	2699.1	2715.5	2701.5
177.5°	2719.5	2713.0	2708.0	2722.0	2708.0
180°	2715.5	2715.5	2715.5	2715.5	2715.5

TEST NUMBER: P926676

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.30	13.18	13.21	14.11	15.29	8.27	9.16	9.18	10.08	11.26
	3H	13.98	14.77	14.90	15.71	16.91	9.47	10.26	10.39	11.19	12.40
	4H	14.59	15.34	15.53	16.28	17.49	9.92	10.67	10.86	11.61	12.82
	6H	15.02	15.70	15.96	16.65	17.88	10.25	10.93	11.19	11.88	13.11
	8H	15.15	15.80	16.10	16.76	17.99	10.34	10.99	11.29	11.95	13.18
	12H	15.21	15.83	16.17	16.78	18.04	10.38	11.01	11.34	11.96	13.21
4H	2H	12.33	13.07	13.27	14.01	15.23	8.88	9.62	9.82	10.56	11.78
	3H	14.16	14.78	15.11	15.75	16.98	10.23	10.85	11.18	11.82	13.05
	4H	14.85	15.42	15.82	16.38	17.64	10.78	11.35	11.74	12.31	13.57
	6H	15.37	15.86	16.35	16.84	18.10	11.21	11.69	12.18	12.68	13.93
	8H	15.55	16.00	16.52	16.98	18.25	11.34	11.79	12.31	12.77	14.04
	12H	15.65	16.05	16.64	17.05	18.32	11.40	11.81	12.40	12.81	14.08
8H	4H	14.83	15.28	15.80	16.26	17.53	11.07	11.52	12.04	12.50	13.77
	6H	15.39	15.77	16.39	16.79	18.06	11.59	11.96	12.59	12.98	14.25
	8H	15.61	15.94	16.62	16.95	18.24	11.78	12.11	12.79	13.12	14.41
	12H	15.75	16.04	16.76	17.05	18.38	11.90	12.19	12.91	13.20	14.53
12H	4H	14.78	15.19	15.77	16.19	17.46	11.07	11.48	12.07	12.48	13.75
	6H	15.37	15.70	16.38	16.71	18.00	11.64	11.97	12.65	12.98	14.26
	8H	15.59	15.88	16.60	16.89	18.22	11.85	12.14	12.86	13.15	14.48