

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332074-927

Luminaire Tested: **S123DIP-S1165D1025U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332074-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6820.4 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57		57
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	53	49		49
2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41		41
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35		35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30		30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	26		26
6	65	53	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26	23		23
7	60	48	40	34	56	45	37	32	39	34	29	34	30	26	30	26	23	21		21
8	56	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21	19		19
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17		17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15		15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13832	13832	13832	13832
5°	16495	13891	12310	13891
10°	20647	13821	11119	13821
15°	25324	13710	10351	13710
20°	30166	13536	9856	13536
25°	32033	13324	9745	13324
30°	27455	13170	9797	13170
35°	19094	12951	9900	12951
40°	14383	12694	9868	12694
45°	11942	12310	9742	12310
50°	10697	11531	9656	11531
55°	10001	10691	9533	10691
60°	9382	9810	9436	9810
65°	8818	8945	9133	8945
70°	8271	7956	8699	7956
75°	7407	6966	7977	6966
80°	6484	5709	6868	5709
85°	5076	4150	4619	4150

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	1.9
10°-20°	405.9	6.0
20°-30°	681.2	10.0
30°-40°	771.4	11.3
40°-50°	691.7	10.1
50°-60°	558.2	8.2
60°-70°	389.0	5.7
70°-80°	204.5	3.0
80°-90°	53.0	0.8
90°-100°	217.4	3.2
100°-110°	615.6	9.0
110°-120°	605.5	8.9
120°-130°	483.0	7.1
130°-140°	380.8	5.6
140°-150°	284.2	4.2
150°-160°	198.1	2.9
160°-170°	116.4	1.7
170°-180°	37.9	0.6
0°-30°	1213.7	17.8
0°-40°	1985.1	29.1
0°-60°	3235.0	47.4
0°-90°	3881.5	56.9
90°-120°	1438.5	21.1
90°-150°	2586.5	37.9
90°-180°	2939.0	43.1
0°-180°	6820.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1285	1285	1285	1285	1285	
5°	1527	1286	1139	1286	1527	158
15°	2272	1230	929	1230	2272	656
25°	2697	1122	820	1122	2697	1183
35°	1453	986	753	986	1453	944
45°	784	809	640	809	784	621
55°	533	570	508	570	533	478
65°	346	351	359	351	346	345
75°	178	168	192	168	178	191
85°	41	34	37	34	41	49
90°	23	2	23	2	23	14
95°	92	27	92	27	92	165
105°	1006	92	1006	92	1006	992
115°	1223	162	1223	162	1223	1189
125°	965	225	965	225	965	874
135°	782	264	782	264	782	607
145°	611	301	611	301	611	389
155°	507	342	507	342	507	236
165°	442	374	442	374	442	126
175°	398	390	398	390	398	39
180°	391	391	391	391	391	

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1363.7	1362.7	1360.3	1362.2	1358.3	1352.7	1352.3	1347.3	1332.8	1331.8	1327.9
5°	1526.6	1521.6	1521.0	1520.4	1511.6	1499.8	1477.4	1475.5	1445.7	1430.7	1412.7
7.5°	1737.5	1740.1	1731.1	1723.1	1696.5	1678.9	1654.9	1624.1	1587.4	1550.1	1525.3
10°	1889.0	1909.5	1884.0	1866.5	1850.4	1819.8	1784.4	1740.1	1695.9	1644.3	1605.0
12.5°	2051.4	2061.4	2056.3	2039.9	2014.7	1968.3	1905.4	1856.7	1816.0	1730.0	1695.2
15°	2272.5	2310.5	2286.2	2230.2	2231.3	2187.1	2105.0	2014.7	1966.8	1891.4	1788.7
17.5°	2508.0	2512.8	2502.4	2455.8	2424.6	2363.9	2288.1	2201.5	2104.4	2013.3	1904.2
20°	2633.5	2629.8	2608.0	2583.8	2530.2	2482.9	2400.1	2303.6	2179.1	2089.5	1970.5
22.5°	2703.3	2697.1	2686.8	2666.4	2621.9	2571.0	2496.7	2391.3	2272.7	2149.2	2011.8
25°	2697.1	2705.1	2706.4	2700.8	2685.3	2654.8	2596.2	2512.2	2393.9	2235.1	2091.9
27.5°	2453.0	2464.5	2497.8	2527.2	2560.3	2593.8	2589.3	2547.7	2460.1	2323.0	2147.9
30°	2208.9	2184.0	2245.7	2323.5	2376.5	2469.8	2522.1	2525.2	2476.0	2358.4	2187.8
32.5°	1870.3	1897.7	1924.9	2020.7	2136.4	2241.2	2345.3	2429.1	2438.7	2360.4	2211.2
35°	1453.1	1487.4	1537.2	1587.0	1711.5	1818.6	2001.6	2161.0	2288.1	2304.9	2213.3
37.5°	1171.0	1187.9	1219.4	1269.3	1350.8	1477.8	1619.4	1820.8	2004.9	2141.7	2147.7
40°	1023.6	1028.5	1064.0	1102.0	1168.0	1272.6	1400.2	1578.3	1798.6	1989.8	2069.5
42.5°	913.0	923.9	939.0	975.5	1028.0	1106.8	1225.4	1372.5	1574.5	1794.5	1950.4
45°	784.5	796.9	806.3	830.5	867.9	920.8	1003.6	1138.1	1291.9	1519.1	1728.9
47.5°	699.6	700.5	707.5	725.8	751.2	790.9	849.5	935.9	1077.1	1261.4	1476.8
50°	638.8	648.7	651.3	665.5	685.5	714.7	763.3	836.8	952.6	1114.4	1312.4
52.5°	596.0	599.0	605.9	616.2	633.7	656.5	698.5	756.1	847.0	984.9	1167.0
55°	532.9	532.9	539.8	547.9	557.9	578.4	606.4	648.7	717.9	824.9	975.6
57.5°	474.7	477.8	482.6	485.1	493.6	507.2	530.6	562.7	614.3	696.6	816.5
60°	435.8	441.4	440.8	445.8	453.3	463.8	483.8	509.9	556.0	621.9	722.9
62.5°	402.0	401.6	401.5	407.4	414.9	425.0	437.9	460.6	499.7	558.3	644.1
65°	346.2	344.9	349.3	353.0	355.5	363.0	373.0	392.8	419.0	462.6	529.2
67.5°	296.6	293.0	295.3	296.6	300.9	306.7	316.0	328.4	349.1	384.1	434.4
70°	262.8	259.6	259.0	260.2	264.0	268.3	275.2	287.0	306.3	334.3	371.1
72.5°	227.8	225.8	225.6	228.4	230.1	233.0	237.8	248.7	264.0	285.0	319.2
75°	178.1	178.1	178.1	178.7	180.5	183.1	186.8	192.3	204.2	219.1	242.2
77.5°	133.5	133.3	132.6	132.5	135.2	136.3	137.2	142.4	149.0	159.1	175.9
80°	104.6	101.5	102.7	104.6	105.8	106.5	108.4	109.6	115.2	120.8	132.6
82.5°	77.7	75.1	75.3	78.2	78.4	79.1	81.0	82.7	84.8	89.9	96.3
85°	41.1	41.1	41.7	41.7	42.3	41.7	43.6	44.2	44.2	47.3	51.0
87.5°	19.6	18.7	19.0	19.4	19.0	19.3	19.6	19.9	20.2	20.9	20.9
90°	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8	19.0	19.8	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5	91.7	121.6	133.8
95°	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6	380.3	468.9	417.5
97.5°	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6	777.4	726.7	532.0
100°	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3	904.6	748.8	506.0
102.5°	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3	910.9	707.7	468.1
105°	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9	862.7	635.7	421.4
107.5°	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7	778.2	572.2	391.7
110°	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2	725.1	536.1	380.3

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3	678.9	512.1	374.0
115°	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4	623.1	486.3	371.6
117.5°	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0	589.4	471.1	373.0
120°	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2	571.7	464.1	375.6
122.5°	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8	557.1	459.7	380.0
125°	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7	538.5	453.9	386.7
127.5°	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4	522.0	451.1	394.3
130°	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4	513.2	449.2	399.3
132.5°	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5	504.9	448.5	403.1
135°	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2	494.2	447.6	408.8
137.5°	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8	484.9	445.8	412.6
140°	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3	479.2	445.2	415.1
142.5°	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6	474.1	443.9	417.0
145°	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7	467.3	442.0	418.3
147.5°	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0	460.7	439.0	418.3
150°	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4	456.2	436.5	418.3
152.5°	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5	451.2	433.3	416.4
155°	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0	443.6	427.8	414.3
157.5°	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0	435.1	422.9	411.7
160°	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7	429.4	419.1	410.4
162.5°	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1	423.7	415.3	407.9
165°	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2	415.9	409.6	404.1
167.5°	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7	408.5	403.9	400.3
170°	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1	404.1	400.1	397.8
172.5°	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0	399.7	397.0	395.9
175°	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2	394.6	393.0	393.0
177.5°	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1324.8	1320.9	1316.9	1310.0	1303.9	1295.5	1293.0	1290.0	1281.0	1273.1	1267.1
5°	1405.8	1390.8	1369.0	1349.2	1333.0	1311.2	1298.7	1285.6	1266.9	1250.1	1236.4
7.5°	1490.5	1461.1	1427.2	1390.6	1356.5	1323.7	1297.1	1273.4	1247.3	1222.5	1203.2
10°	1557.7	1515.4	1468.1	1417.1	1373.4	1331.1	1295.6	1264.5	1230.9	1201.6	1177.3
12.5°	1634.4	1571.7	1506.4	1444.4	1392.9	1334.1	1291.1	1251.6	1213.5	1178.2	1151.0
15°	1725.2	1645.5	1568.3	1483.0	1404.5	1331.1	1280.1	1230.3	1186.1	1149.9	1115.1
17.5°	1807.9	1717.6	1615.9	1512.1	1417.5	1330.4	1258.9	1202.6	1147.3	1103.1	1068.3
20°	1854.7	1752.0	1636.8	1529.1	1424.5	1327.4	1249.0	1181.7	1121.9	1075.2	1036.0
22.5°	1895.1	1774.9	1655.7	1540.6	1424.0	1319.4	1230.5	1161.3	1096.5	1050.8	1009.1
25°	1936.9	1793.1	1673.6	1538.4	1408.3	1300.0	1200.4	1121.9	1057.2	1003.6	960.7
27.5°	1972.8	1791.8	1650.0	1504.7	1383.6	1275.1	1168.7	1084.6	1015.8	957.7	914.1
30°	1996.6	1794.3	1625.6	1481.8	1359.8	1247.7	1144.3	1059.6	987.5	928.3	887.2
32.5°	2011.6	1792.8	1603.1	1449.9	1321.9	1222.7	1117.9	1030.2	956.1	897.9	858.3
35°	2020.3	1781.9	1564.6	1384.0	1260.8	1164.3	1076.5	985.6	907.8	853.6	808.7
37.5°	2002.9	1758.8	1519.7	1320.5	1185.6	1090.5	1016.7	939.2	864.7	805.2	766.5
40°	1975.5	1743.9	1484.9	1275.7	1133.8	1042.2	979.4	903.4	829.9	773.2	737.1
42.5°	1923.2	1713.5	1446.5	1225.9	1080.0	988.4	930.5	867.0	797.6	744.3	708.3
45°	1795.6	1647.3	1389.0	1151.2	1000.5	905.9	854.8	808.7	745.8	694.2	663.1
47.5°	1618.5	1547.9	1305.8	1072.4	917.6	826.6	773.5	736.4	690.5	648.7	618.9
50°	1495.5	1466.2	1249.5	1018.6	862.3	773.2	722.2	688.6	655.6	613.9	586.5
52.5°	1353.5	1371.6	1183.8	962.7	806.0	718.5	670.4	643.7	613.8	579.5	555.6
55°	1153.7	1219.0	1070.2	869.1	722.2	638.8	593.3	569.7	552.2	526.7	506.2
57.5°	966.5	1049.7	947.5	772.6	639.9	567.9	524.3	498.6	487.4	474.0	457.9
60°	855.5	937.6	859.8	707.9	584.6	516.1	477.5	455.7	444.5	435.2	421.5
62.5°	756.3	839.5	774.1	642.1	530.3	466.8	433.2	411.9	403.2	398.3	386.7
65°	620.1	691.7	648.1	539.8	452.7	396.6	366.1	351.2	343.0	341.2	333.7
67.5°	504.7	559.2	527.4	447.7	379.1	330.7	304.8	292.2	285.9	285.3	279.6
70°	429.0	480.0	455.7	383.5	324.4	286.4	264.0	252.8	249.1	248.4	245.3
72.5°	370.2	405.8	386.5	326.2	280.5	246.1	229.6	217.9	213.7	214.5	212.5
75°	273.9	300.7	289.5	247.8	211.0	188.6	174.9	167.5	163.7	165.6	163.1
77.5°	197.1	214.0	204.0	175.1	152.4	136.3	126.1	121.5	118.2	118.0	116.9
80°	148.8	158.8	153.1	135.7	117.1	103.4	95.2	92.1	90.3	89.7	89.0
82.5°	106.0	114.5	107.8	95.9	83.2	74.9	70.3	66.2	64.9	65.3	64.6
85°	53.6	56.6	54.2	46.7	41.7	37.9	35.5	33.6	32.4	33.0	31.8
87.5°	21.5	21.5	19.5	17.2	15.8	13.9	13.5	12.3	11.6	11.9	11.9
90°	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6	3.2	4.8	7.1
92.5°	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8	14.6	21.2	27.3
95°	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9	29.2	37.9	51.4
97.5°	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9	46.7	53.5	65.1
100°	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5	59.3	64.9	75.9
102.5°	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8	73.2	78.1	88.6
105°	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7	94.1	98.9	108.4
107.5°	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9	115.3	119.9	129.2
110°	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1	130.5	134.4	143.1

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0	144.4	148.4	157.0
115°	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1	165.2	170.0	177.9
117.5°	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2	185.8	189.8	197.0
120°	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1	198.4	202.4	210.3
122.5°	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1	210.5	214.4	223.0
125°	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4	227.0	231.7	240.3
127.5°	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5	240.8	246.7	255.6
130°	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7	249.1	256.2	265.7
132.5°	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0	256.0	263.8	275.2
135°	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1	267.3	276.0	287.8
137.5°	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6	277.9	286.4	299.0
140°	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5	285.4	293.3	306.0
142.5°	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1	292.4	301.0	312.4
145°	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3	303.6	310.8	322.7
147.5°	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6	315.1	322.0	332.2
150°	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9	322.7	328.9	339.2
152.5°	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0	330.2	336.5	345.5
155°	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4	342.4	347.1	355.1
157.5°	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2	352.8	356.6	363.6
160°	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8	359.8	363.0	369.2
162.5°	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5	365.5	368.0	373.0
165°	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0	373.2	374.8	378.7
167.5°	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5	379.5	380.3	383.3
170°	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3	382.7	383.5	385.9
172.5°	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8	385.9	386.0	387.8
175°	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8	389.0	388.2	389.8
177.5°	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3	390.6	390.0	390.6
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1263.6	1260.1	1255.1	1247.7	1241.7	1232.2	1232.2	1233.7	1233.7	1233.3	1232.2
5°	1225.3	1215.9	1204.8	1191.7	1178.0	1164.3	1161.7	1156.7	1153.0	1150.6	1147.5
7.5°	1184.8	1168.2	1151.9	1133.6	1116.9	1103.1	1093.5	1085.5	1080.5	1075.0	1071.0
10°	1157.4	1136.9	1117.5	1098.3	1077.1	1060.3	1049.7	1042.2	1036.6	1031.7	1029.1
12.5°	1125.1	1101.5	1080.2	1061.9	1038.7	1021.4	1011.4	1007.8	1001.2	990.8	985.3
15°	1077.7	1055.9	1030.4	1002.3	991.2	970.0	958.1	952.6	948.8	940.7	938.3
17.5°	1037.2	1008.7	980.1	959.2	938.3	921.1	914.6	907.6	902.6	896.0	894.1
20°	1004.9	979.4	953.2	930.8	908.9	890.3	884.7	879.7	874.7	871.6	869.1
22.5°	972.0	946.5	924.8	903.9	880.6	868.4	862.3	856.8	853.3	851.2	848.7
25°	925.8	903.4	879.1	860.4	841.8	833.6	829.9	826.8	824.3	821.2	820.5
27.5°	884.5	860.1	840.3	822.9	809.5	802.8	799.2	797.6	798.2	799.3	800.0
30°	853.6	831.2	815.0	800.0	787.6	781.3	780.7	780.7	783.2	783.9	785.1
32.5°	825.2	806.8	790.6	776.1	766.7	762.4	764.8	764.8	766.8	768.4	770.6
35°	783.9	767.6	755.2	742.8	734.7	736.5	737.8	739.0	742.1	745.8	748.4
37.5°	744.3	730.3	717.3	707.7	703.9	707.3	710.3	712.9	716.4	719.4	721.8
40°	716.0	705.4	692.9	684.2	685.5	687.4	689.8	692.9	696.1	697.9	700.4
42.5°	689.6	678.5	669.1	661.8	663.5	665.9	667.4	669.1	672.6	676.0	677.5
45°	649.4	640.6	631.9	627.6	628.8	630.1	631.3	633.2	636.3	638.8	639.4
47.5°	604.2	598.1	592.2	588.0	589.9	589.5	591.1	595.1	596.0	597.5	601.0
50°	575.3	569.7	562.8	561.6	561.6	561.6	562.2	567.2	567.2	569.7	572.2
52.5°	543.4	539.8	535.4	533.2	532.2	532.2	534.8	537.3	538.3	541.8	544.3
55°	496.2	492.5	488.7	486.9	485.6	486.9	491.9	493.1	496.2	498.0	499.9
57.5°	447.0	444.2	441.2	440.1	439.9	441.6	444.3	448.0	448.8	454.5	457.3
60°	414.6	410.3	407.8	407.8	406.5	412.2	410.9	417.2	418.4	422.2	426.5
62.5°	381.3	375.4	374.5	374.5	376.2	377.8	379.5	382.3	385.5	390.2	393.6
65°	327.5	324.4	328.8	328.1	326.9	330.6	330.6	333.7	337.5	341.8	348.6
67.5°	276.6	275.0	275.3	275.3	277.2	279.3	281.1	283.8	288.3	292.9	297.4
70°	242.2	244.1	241.0	243.4	245.3	245.9	247.2	250.9	255.9	259.0	264.0
72.5°	208.8	208.7	209.1	210.1	211.9	213.0	214.3	218.6	224.0	226.6	230.6
75°	160.7	160.0	161.8	161.8	165.0	166.2	167.5	169.4	174.4	178.1	181.2
77.5°	117.3	118.0	117.6	119.8	118.9	119.1	123.0	124.9	125.4	132.8	134.4
80°	88.4	89.7	90.3	90.9	91.5	90.3	94.7	96.5	96.5	100.8	103.9
82.5°	63.5	64.2	65.9	66.5	66.6	67.9	68.2	69.6	71.1	73.0	77.1
85°	31.8	33.6	34.2	33.6	34.2	33.0	34.9	35.5	36.1	36.1	36.1
87.5°	11.7	12.5	12.5	13.5	13.5	14.4	14.3	13.4	13.5	15.2	13.5
90°	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8	20.6	21.4	22.9
92.5°	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5	52.8	46.7	42.5
95°	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6	193.0	151.1	122.6
97.5°	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6	568.4	466.4	371.8
100°	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3	868.2	775.7	663.5
102.5°	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3	1004.2	950.3	879.2
105°	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9	1107.1	1122.0	1101.5
107.5°	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7	1094.1	1163.3	1191.5
110°	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2	1051.7	1151.3	1206.7

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3	996.0	1107.6	1178.8
115°	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4	907.0	1023.2	1109.4
117.5°	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0	831.7	936.0	1023.5
120°	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2	790.0	884.9	964.7
122.5°	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8	756.5	844.4	918.5
125°	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7	714.9	790.8	854.0
127.5°	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4	678.3	746.8	804.3
130°	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4	655.5	719.5	773.3
132.5°	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5	634.0	693.6	744.9
135°	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2	603.3	654.7	699.8
137.5°	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8	573.8	618.1	657.1
140°	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3	556.7	594.6	628.7
142.5°	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6	540.3	573.1	602.7
145°	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7	518.7	544.0	567.0
147.5°	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0	502.7	523.2	539.5
150°	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4	492.7	509.2	524.3
152.5°	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5	483.2	497.9	510.3
155°	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0	469.7	481.6	491.1
157.5°	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0	456.5	465.7	473.2
160°	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7	448.4	456.2	461.8
162.5°	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1	439.5	446.8	451.7
165°	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2	427.0	432.5	436.5
167.5°	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7	417.3	420.5	423.3
170°	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1	410.4	413.5	415.1
172.5°	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0	404.7	407.3	408.2
175°	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2	397.0	398.5	398.5
177.5°	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9	392.5	393.2	393.2
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1228.8	1228.3	1231.8	1229.2	1231.8	1228.3	1228.8	1232.2	1233.3	1233.7	1233.7
5°	1143.7	1145.6	1139.3	1139.3	1139.3	1145.6	1143.7	1147.5	1150.6	1153.0	1156.7
7.5°	1068.0	1065.2	1065.5	1062.2	1065.5	1065.2	1068.0	1071.0	1075.0	1080.5	1085.5
10°	1021.7	1018.0	1016.7	1017.3	1016.7	1018.0	1021.7	1029.1	1031.7	1036.6	1042.2
12.5°	983.3	982.5	974.4	974.5	974.4	982.5	983.3	985.3	990.8	1001.2	1007.8
15°	938.3	926.5	925.2	928.9	925.2	926.5	938.3	938.3	940.7	948.8	952.6
17.5°	893.0	886.8	887.2	885.3	887.2	886.8	893.0	894.1	896.0	902.6	907.6
20°	869.1	865.4	864.7	860.4	864.7	865.4	869.1	869.1	871.6	874.7	879.7
22.5°	847.2	846.0	846.4	841.5	846.4	846.0	847.2	848.7	851.2	853.3	856.8
25°	820.0	823.1	820.5	820.5	820.5	823.1	820.0	820.5	821.2	824.3	826.8
27.5°	801.5	801.4	800.2	800.2	800.2	801.4	801.5	800.0	799.3	798.2	797.6
30°	787.6	787.0	788.2	788.2	788.2	787.0	787.6	785.1	783.9	783.2	780.7
32.5°	773.6	774.5	774.8	775.2	774.8	774.5	773.6	770.6	768.4	766.8	764.8
35°	752.1	752.7	754.6	753.4	754.6	752.7	752.1	748.4	745.8	742.1	739.0
37.5°	722.9	725.8	725.2	726.2	725.2	725.8	722.9	721.8	719.4	716.4	712.9
40°	701.0	702.9	702.3	702.3	702.3	702.9	701.0	700.4	697.9	696.1	692.9
42.5°	678.7	680.0	678.3	677.4	678.3	680.0	678.7	677.5	676.0	672.6	669.1
45°	641.9	640.6	642.5	640.0	642.5	640.6	641.9	639.4	638.8	636.3	633.2
47.5°	600.8	602.1	602.5	604.4	602.5	602.1	600.8	601.0	597.5	596.0	595.1
50°	573.4	577.1	577.1	576.6	577.1	577.1	573.4	572.2	569.7	567.2	567.2
52.5°	546.5	548.3	550.7	550.6	550.7	548.3	546.5	544.3	541.8	538.3	537.3
55°	504.9	506.2	507.4	508.0	507.4	506.2	504.9	499.9	498.0	496.2	493.1
57.5°	461.8	461.4	464.3	465.2	464.3	461.4	461.8	457.3	454.5	448.8	448.0
60°	431.4	431.4	436.4	438.3	436.4	431.4	431.4	426.5	422.2	418.4	417.2
62.5°	399.1	401.1	406.1	403.5	406.1	401.1	399.1	393.6	390.2	385.5	382.3
65°	351.7	356.7	356.1	358.6	356.1	356.7	351.7	348.6	341.8	337.5	333.7
67.5°	302.3	305.5	309.9	310.3	309.9	305.5	302.3	297.4	292.9	288.3	283.8
70°	268.9	272.0	274.6	276.4	274.6	272.0	268.9	264.0	259.0	255.9	250.9
72.5°	236.6	238.2	244.2	241.5	244.2	238.2	236.6	230.6	226.6	224.0	218.6
75°	185.5	189.9	193.6	191.8	193.6	189.9	185.5	181.2	178.1	174.4	169.4
77.5°	137.2	141.6	143.3	141.7	143.3	141.6	137.2	134.4	132.8	125.4	124.9
80°	108.4	107.7	111.5	110.8	111.5	107.7	108.4	103.9	100.8	96.5	96.5
82.5°	79.5	78.8	80.6	81.0	80.6	78.8	79.5	77.1	73.0	71.1	69.6
85°	38.6	40.5	37.9	37.4	37.9	40.5	38.6	36.1	36.1	36.1	35.5
87.5°	13.4	13.5	13.2	12.5	13.2	13.5	13.4	13.5	15.2	13.5	13.4
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5
95°	107.6	100.4	94.9	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6
97.5°	313.5	277.9	256.5	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6
100°	583.6	525.9	495.0	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3
102.5°	817.0	771.3	745.5	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3
105°	1065.1	1035.1	1009.8	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9
107.5°	1192.2	1182.0	1173.5	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7
110°	1228.8	1235.2	1233.6	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1219.3	1238.9	1244.9	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3
115°	1168.7	1203.5	1219.3	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4
117.5°	1085.4	1125.2	1148.0	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0
120°	1027.1	1071.4	1090.4	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2
122.5°	974.1	1013.9	1034.7	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8
125°	904.6	939.4	959.2	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7
127.5°	849.4	879.2	897.0	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4
130°	815.2	843.8	860.3	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4
132.5°	784.3	812.7	827.4	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5
135°	738.6	762.2	776.5	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2
137.5°	689.7	713.8	725.7	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8
140°	658.7	680.8	693.5	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3
142.5°	628.4	647.9	659.3	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6
145°	586.7	603.3	609.7	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7
147.5°	554.4	565.7	571.7	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0
150°	536.1	544.8	549.5	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4
152.5°	519.7	527.8	530.6	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5
155°	498.2	504.5	506.0	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0
157.5°	479.3	484.1	485.4	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0
160°	467.3	472.1	472.1	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7
162.5°	455.3	459.4	459.4	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1
165°	439.7	442.8	442.0	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2
167.5°	424.8	427.0	426.2	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7
170°	415.9	417.5	416.7	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1
172.5°	408.4	410.0	408.5	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0
175°	398.5	399.3	398.5	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2
177.5°	392.5	393.2	391.9	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1232.2	1232.2	1241.7	1247.7	1255.1	1260.1	1263.6	1267.1	1273.1	1281.0	1290.0
5°	1161.7	1164.3	1178.0	1191.7	1204.8	1215.9	1225.3	1236.4	1250.1	1266.9	1285.6
7.5°	1093.5	1103.1	1116.9	1133.6	1151.9	1168.2	1184.8	1203.2	1222.5	1247.3	1273.4
10°	1049.7	1060.3	1077.1	1098.3	1117.5	1136.9	1157.4	1177.3	1201.6	1230.9	1264.5
12.5°	1011.4	1021.4	1038.7	1061.9	1080.2	1101.5	1125.1	1151.0	1178.2	1213.5	1251.6
15°	958.1	970.0	991.2	1002.3	1030.4	1055.9	1077.7	1115.1	1149.9	1186.1	1230.3
17.5°	914.6	921.1	938.3	959.2	980.1	1008.7	1037.2	1068.3	1103.1	1147.3	1202.6
20°	884.7	890.3	908.9	930.8	953.2	979.4	1004.9	1036.0	1075.2	1121.9	1181.7
22.5°	862.3	868.4	880.6	903.9	924.8	946.5	972.0	1009.1	1050.8	1096.5	1161.3
25°	829.9	833.6	841.8	860.4	879.1	903.4	925.8	960.7	1003.6	1057.2	1121.9
27.5°	799.2	802.8	809.5	822.9	840.3	860.1	884.5	914.1	957.7	1015.8	1084.6
30°	780.7	781.3	787.6	800.0	815.0	831.2	853.6	887.2	928.3	987.5	1059.6
32.5°	764.8	762.4	766.7	776.1	790.6	806.8	825.2	858.3	897.9	956.1	1030.2
35°	737.8	736.5	734.7	742.8	755.2	767.6	783.9	808.7	853.6	907.8	985.6
37.5°	710.3	707.3	703.9	707.7	717.3	730.3	744.3	766.5	805.2	864.7	939.2
40°	689.8	687.4	685.5	684.2	692.9	705.4	716.0	737.1	773.2	829.9	903.4
42.5°	667.4	665.9	663.5	661.8	669.1	678.5	689.6	708.3	744.3	797.6	867.0
45°	631.3	630.1	628.8	627.6	631.9	640.6	649.4	663.1	694.2	745.8	808.7
47.5°	591.1	589.5	589.9	588.0	592.2	598.1	604.2	618.9	648.7	690.5	736.4
50°	562.2	561.6	561.6	561.6	562.8	569.7	575.3	586.5	613.9	655.6	688.6
52.5°	534.8	532.2	532.2	533.2	535.4	539.8	543.4	555.6	579.5	613.8	643.7
55°	491.9	486.9	485.6	486.9	488.7	492.5	496.2	506.2	526.7	552.2	569.7
57.5°	444.3	441.6	439.9	440.1	441.2	444.2	447.0	457.9	474.0	487.4	498.6
60°	410.9	412.2	406.5	407.8	407.8	410.3	414.6	421.5	435.2	444.5	455.7
62.5°	379.5	377.8	376.2	374.5	374.5	375.4	381.3	386.7	398.3	403.2	411.9
65°	330.6	330.6	326.9	328.1	328.8	324.4	327.5	333.7	341.2	343.0	351.2
67.5°	281.1	279.3	277.2	275.3	275.3	275.0	276.6	279.6	285.3	285.9	292.2
70°	247.2	245.9	245.3	243.4	241.0	244.1	242.2	245.3	248.4	249.1	252.8
72.5°	214.3	213.0	211.9	210.1	209.1	208.7	208.8	212.5	214.5	213.7	217.9
75°	167.5	166.2	165.0	161.8	161.8	160.0	160.7	163.1	165.6	163.7	167.5
77.5°	123.0	119.1	118.9	119.8	117.6	118.0	117.3	116.9	118.0	118.2	121.5
80°	94.7	90.3	91.5	90.9	90.3	89.7	88.4	89.0	89.7	90.3	92.1
82.5°	68.2	67.9	66.6	66.5	65.9	64.2	63.5	64.6	65.3	64.9	66.2
85°	34.9	33.0	34.2	33.6	34.2	33.6	31.8	31.8	33.0	32.4	33.6
87.5°	14.3	14.4	13.5	13.5	12.5	12.5	11.7	11.9	11.9	11.6	12.3
90°	19.0	19.8	17.4	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6
92.5°	91.7	121.6	133.8	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8
95°	380.3	468.9	417.5	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9
97.5°	777.4	726.7	532.0	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9
100°	904.6	748.8	506.0	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5
102.5°	910.9	707.7	468.1	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8
105°	862.7	635.7	421.4	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7
107.5°	778.2	572.2	391.7	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9
110°	725.1	536.1	380.3	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	678.9	512.1	374.0	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0
115°	623.1	486.3	371.6	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1
117.5°	589.4	471.1	373.0	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2
120°	571.7	464.1	375.6	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1
122.5°	557.1	459.7	380.0	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1
125°	538.5	453.9	386.7	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4
127.5°	522.0	451.1	394.3	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5
130°	513.2	449.2	399.3	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7
132.5°	504.9	448.5	403.1	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0
135°	494.2	447.6	408.8	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1
137.5°	484.9	445.8	412.6	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6
140°	479.2	445.2	415.1	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5
142.5°	474.1	443.9	417.0	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1
145°	467.3	442.0	418.3	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3
147.5°	460.7	439.0	418.3	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6
150°	456.2	436.5	418.3	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9
152.5°	451.2	433.3	416.4	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0
155°	443.6	427.8	414.3	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4
157.5°	435.1	422.9	411.7	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2
160°	429.4	419.1	410.4	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8
162.5°	423.7	415.3	407.9	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5
165°	415.9	409.6	404.1	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0
167.5°	408.5	403.9	400.3	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5
170°	404.1	400.1	397.8	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3
172.5°	399.7	397.0	395.9	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8
175°	394.6	393.0	393.0	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8
177.5°	391.3	390.6	391.3	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1293.0	1295.5	1303.9	1310.0	1316.9	1320.9	1324.8	1327.9	1331.8	1332.8	1347.3
5°	1298.7	1311.2	1333.0	1349.2	1369.0	1390.8	1405.8	1412.7	1430.7	1445.7	1475.5
7.5°	1297.1	1323.7	1356.5	1390.6	1427.2	1461.1	1490.5	1525.3	1550.1	1587.4	1624.1
10°	1295.6	1331.1	1373.4	1417.1	1468.1	1515.4	1557.7	1605.0	1644.3	1695.9	1740.1
12.5°	1291.1	1334.1	1392.9	1444.4	1506.4	1571.7	1634.4	1695.2	1730.0	1816.0	1856.7
15°	1280.1	1331.1	1404.5	1483.0	1568.3	1645.5	1725.2	1788.7	1891.4	1966.8	2014.7
17.5°	1258.9	1330.4	1417.5	1512.1	1615.9	1717.6	1807.9	1904.2	2013.3	2104.4	2201.5
20°	1249.0	1327.4	1424.5	1529.1	1636.8	1752.0	1854.7	1970.5	2089.5	2179.1	2303.6
22.5°	1230.5	1319.4	1424.0	1540.6	1655.7	1774.9	1895.1	2011.8	2149.2	2272.7	2391.3
25°	1200.4	1300.0	1408.3	1538.4	1673.6	1793.1	1936.9	2091.9	2235.1	2393.9	2512.2
27.5°	1168.7	1275.1	1383.6	1504.7	1650.0	1791.8	1972.8	2147.9	2323.0	2460.1	2547.7
30°	1144.3	1247.7	1359.8	1481.8	1625.6	1794.3	1996.6	2187.8	2358.4	2476.0	2525.2
32.5°	1117.9	1222.7	1321.9	1449.9	1603.1	1792.8	2011.6	2211.2	2360.4	2438.7	2429.1
35°	1076.5	1164.3	1260.8	1384.0	1564.6	1781.9	2020.3	2213.3	2304.9	2288.1	2161.0
37.5°	1016.7	1090.5	1185.6	1320.5	1519.7	1758.8	2002.9	2147.7	2141.7	2004.9	1820.8
40°	979.4	1042.2	1133.8	1275.7	1484.9	1743.9	1975.5	2069.5	1989.8	1798.6	1578.3
42.5°	930.5	988.4	1080.0	1225.9	1446.5	1713.5	1923.2	1950.4	1794.5	1574.5	1372.5
45°	854.8	905.9	1000.5	1151.2	1389.0	1647.3	1795.6	1728.9	1519.1	1291.9	1138.1
47.5°	773.5	826.6	917.6	1072.4	1305.8	1547.9	1618.5	1476.8	1261.4	1077.1	935.9
50°	722.2	773.2	862.3	1018.6	1249.5	1466.2	1495.5	1312.4	1114.4	952.6	836.8
52.5°	670.4	718.5	806.0	962.7	1183.8	1371.6	1353.5	1167.0	984.9	847.0	756.1
55°	593.3	638.8	722.2	869.1	1070.2	1219.0	1153.7	975.6	824.9	717.9	648.7
57.5°	524.3	567.9	639.9	772.6	947.5	1049.7	966.5	816.5	696.6	614.3	562.7
60°	477.5	516.1	584.6	707.9	859.8	937.6	855.5	722.9	621.9	556.0	509.9
62.5°	433.2	466.8	530.3	642.1	774.1	839.5	756.3	644.1	558.3	499.7	460.6
65°	366.1	396.6	452.7	539.8	648.1	691.7	620.1	529.2	462.6	419.0	392.8
67.5°	304.8	330.7	379.1	447.7	527.4	559.2	504.7	434.4	384.1	349.1	328.4
70°	264.0	286.4	324.4	383.5	455.7	480.0	429.0	371.1	334.3	306.3	287.0
72.5°	229.6	246.1	280.5	326.2	386.5	405.8	370.2	319.2	285.0	264.0	248.7
75°	174.9	188.6	211.0	247.8	289.5	300.7	273.9	242.2	219.1	204.2	192.3
77.5°	126.1	136.3	152.4	175.1	204.0	214.0	197.1	175.9	159.1	149.0	142.4
80°	95.2	103.4	117.1	135.7	153.1	158.8	148.8	132.6	120.8	115.2	109.6
82.5°	70.3	74.9	83.2	95.9	107.8	114.5	106.0	96.3	89.9	84.8	82.7
85°	35.5	37.9	41.7	46.7	54.2	56.6	53.6	51.0	47.3	44.2	44.2
87.5°	13.5	13.9	15.8	17.2	19.5	21.5	21.5	20.9	20.9	20.2	19.9
90°	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8
92.5°	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5
95°	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6
97.5°	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6
100°	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3
102.5°	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3
105°	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9
107.5°	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7
110°	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3
115°	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4
117.5°	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0
120°	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2
122.5°	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8
125°	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7
127.5°	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4
130°	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4
132.5°	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5
135°	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2
137.5°	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8
140°	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3
142.5°	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6
145°	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7
147.5°	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0
150°	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4
152.5°	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5
155°	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0
157.5°	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0
160°	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7
162.5°	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1
165°	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2
167.5°	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7
170°	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1
172.5°	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0
175°	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2
177.5°	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1352.3	1352.7	1358.3	1362.2	1360.3	1362.7	1363.7
5°	1477.4	1499.8	1511.6	1520.4	1521.0	1521.6	1526.6
7.5°	1654.9	1678.9	1696.5	1723.1	1731.1	1740.1	1737.5
10°	1784.4	1819.8	1850.4	1866.5	1884.0	1909.5	1889.0
12.5°	1905.4	1968.3	2014.7	2039.9	2056.3	2061.4	2051.4
15°	2105.0	2187.1	2231.3	2230.2	2286.2	2310.5	2272.5
17.5°	2288.1	2363.9	2424.6	2455.8	2502.4	2512.8	2508.0
20°	2400.1	2482.9	2530.2	2583.8	2608.0	2629.8	2633.5
22.5°	2496.7	2571.0	2621.9	2666.4	2686.8	2697.1	2703.3
25°	2596.2	2654.8	2685.3	2700.8	2706.4	2705.1	2697.1
27.5°	2589.3	2593.8	2560.3	2527.2	2497.8	2464.5	2453.0
30°	2522.1	2469.8	2376.5	2323.5	2245.7	2184.0	2208.9
32.5°	2345.3	2241.2	2136.4	2020.7	1924.9	1897.7	1870.3
35°	2001.6	1818.6	1711.5	1587.0	1537.2	1487.4	1453.1
37.5°	1619.4	1477.8	1350.8	1269.3	1219.4	1187.9	1171.0
40°	1400.2	1272.6	1168.0	1102.0	1064.0	1028.5	1023.6
42.5°	1225.4	1106.8	1028.0	975.5	939.0	923.9	913.0
45°	1003.6	920.8	867.9	830.5	806.3	796.9	784.5
47.5°	849.5	790.9	751.2	725.8	707.5	700.5	699.6
50°	763.3	714.7	685.5	665.5	651.3	648.7	638.8
52.5°	698.5	656.5	633.7	616.2	605.9	599.0	596.0
55°	606.4	578.4	557.9	547.9	539.8	532.9	532.9
57.5°	530.6	507.2	493.6	485.1	482.6	477.8	474.7
60°	483.8	463.8	453.3	445.8	440.8	441.4	435.8
62.5°	437.9	425.0	414.9	407.4	401.5	401.6	402.0
65°	373.0	363.0	355.5	353.0	349.3	344.9	346.2
67.5°	316.0	306.7	300.9	296.6	295.3	293.0	296.6
70°	275.2	268.3	264.0	260.2	259.0	259.6	262.8
72.5°	237.8	233.0	230.1	228.4	225.6	225.8	227.8
75°	186.8	183.1	180.5	178.7	178.1	178.1	178.1
77.5°	137.2	136.3	135.2	132.5	132.6	133.3	133.5
80°	108.4	106.5	105.8	104.6	102.7	101.5	104.6
82.5°	81.0	79.1	78.4	78.2	75.3	75.1	77.7
85°	43.6	41.7	42.3	41.7	41.7	41.1	41.1
87.5°	19.6	19.3	19.0	19.4	19.0	18.7	19.6
90°	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0

TEST NUMBER: P332074-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)