

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332274-927

Luminaire Tested: **S123RDIP-S560D365U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332274-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2678.7 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332274-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332274-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	48	45	43	39
4	78	67	59	53	73	63	56	51	56	50	46	50	45	42	43	40	37	34
5	71	60	52	46	67	57	49	44	50	45	40	45	40	36	39	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	38	30	25	47	36	29	25	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332274-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	2.6
10°-20°	195.5	7.3
20°-30°	281.5	10.5
30°-40°	317.1	11.8
40°-50°	303.3	11.3
50°-60°	248.4	9.3
60°-70°	167.6	6.3
70°-80°	84.3	3.1
80°-90°	23.4	0.9
90°-100°	23.2	0.9
100°-110°	69.5	2.6
110°-120°	118.2	4.4
120°-130°	155.5	5.8
130°-140°	174.7	6.5
140°-150°	171.8	6.4
150°-160°	144.6	5.4
160°-170°	96.3	3.6
170°-180°	33.7	1.3
0°-30°	547.2	20.4
0°-40°	864.3	32.3
0°-60°	1416.1	52.9
0°-90°	1691.3	63.1
90°-120°	210.9	7.9
90°-150°	712.8	26.6
90°-180°	987.0	36.8
0°-180°	2678.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	0	3	7	8	8	3
95°	17	18	21	22	22	19
105°	63	64	66	66	67	67
115°	119	120	119	120	119	118
125°	174	175	174	173	172	155
135°	226	228	227	226	226	174
145°	274	275	275	275	274	171
155°	314	314	314	315	313	144
165°	342	341	341	342	341	96
175°	356	354	354	356	354	34
180°	356	356	356	356	356	



TEST NUMBER: P332274-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.7	10.6	9.6	8.6	7.4	7.0	7.2	7.4	7.5	7.7	7.6
90°	0.3	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0
92.5°	6.8	7.2	7.6	8.1	8.5	8.9	9.3	9.8	10.3	10.8	10.9
95°	16.6	17.0	17.3	17.8	18.2	18.7	19.3	19.7	20.2	20.8	21.0
97.5°	29.3	29.6	30.0	30.3	30.7	31.0	31.4	31.7	32.1	32.4	32.7
100°	38.1	38.4	38.8	39.2	39.5	39.9	40.2	40.6	40.9	41.1	41.4
102.5°	48.2	48.4	48.6	48.8	49.0	49.4	49.7	50.2	50.6	51.0	51.2
105°	63.0	63.1	63.2	63.4	63.5	63.8	64.4	65.0	65.5	66.1	66.1
107.5°	80.2	80.3	80.4	80.5	80.6	80.6	80.9	81.1	81.4	81.6	81.8
110°	91.0	91.1	91.3	91.3	91.5	91.6	91.7	91.9	92.0	92.1	92.4



TEST NUMBER: P332274-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.2	102.3	102.3	102.4	102.5	102.5	102.6	102.6	102.6	102.7	102.9
115°	119.0	119.1	119.4	119.5	119.7	119.8	119.6	119.5	119.4	119.2	119.3
117.5°	135.9	136.0	136.2	136.3	136.4	136.3	136.2	136.0	135.9	135.7	135.7
120°	146.4	146.8	147.2	147.5	147.9	147.9	147.7	147.3	147.0	146.7	146.6
122.5°	157.4	157.6	158.0	158.2	158.5	158.5	158.4	158.2	158.0	157.9	157.7
125°	174.1	174.3	174.5	174.7	174.9	174.9	174.8	174.7	174.5	174.4	174.1
127.5°	189.6	190.0	190.4	190.8	191.2	191.3	191.2	191.0	190.9	190.8	190.4
130°	199.9	200.3	200.9	201.4	201.8	202.0	201.8	201.7	201.5	201.3	201.1
132.5°	210.2	210.7	211.2	211.7	212.1	212.4	212.2	212.1	211.9	211.8	211.5
135°	225.9	226.3	226.6	227.0	227.4	227.6	227.5	227.4	227.4	227.4	227.0
137.5°	240.5	240.8	241.1	241.4	241.7	241.9	242.1	242.2	242.4	242.6	242.3
140°	250.6	250.9	251.2	251.5	251.8	252.0	252.1	252.1	252.2	252.2	252.2
142.5°	259.8	260.1	260.4	260.7	260.9	261.2	261.3	261.4	261.5	261.7	261.6
145°	274.1	274.2	274.3	274.4	274.6	274.7	274.9	275.1	275.3	275.4	275.4
147.5°	286.6	286.8	287.1	287.3	287.5	287.7	287.9	288.0	288.2	288.4	288.4
150°	295.3	295.5	295.6	295.7	295.9	296.0	296.1	296.2	296.4	296.4	296.4
152.5°	302.5	302.7	302.9	303.0	303.2	303.3	303.4	303.5	303.6	303.6	303.7
155°	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9	314.0	314.1	314.3
157.5°	323.4	323.4	323.3	323.2	323.1	323.1	323.2	323.2	323.3	323.4	323.6
160°	329.5	329.4	329.2	329.2	329.0	328.9	328.9	328.9	328.9	328.9	329.2
162.5°	334.9	334.7	334.5	334.4	334.1	334.1	334.1	334.2	334.3	334.3	334.6
165°	341.8	341.7	341.4	341.3	341.0	341.0	341.0	341.0	341.0	341.0	341.4
167.5°	347.4	347.1	346.9	346.6	346.3	346.3	346.3	346.3	346.4	346.5	346.8
170°	350.5	350.2	350.0	349.7	349.5	349.4	349.4	349.4	349.4	349.4	349.8
172.5°	353.0	352.7	352.4	352.2	352.0	351.8	351.8	351.8	351.8	351.8	352.2
175°	355.5	355.3	355.1	354.8	354.6	354.4	354.4	354.4	354.4	354.4	354.8
177.5°	356.6	356.4	356.2	356.0	355.8	355.7	355.7	355.7	355.7	355.7	356.0
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332274-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	7.5	7.4	7.4	7.4	7.3	7.2	7.1	7.1
90°	7.2	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.2	11.3	11.6	11.6	11.6	11.5	11.4	11.3
95°	21.2	21.5	21.7	21.9	21.9	21.9	21.9	21.9
97.5°	33.0	33.3	33.6	33.7	33.7	33.7	33.6	33.6
100°	41.5	41.7	41.9	42.1	42.1	42.3	42.5	42.5
102.5°	51.4	51.6	51.7	51.8	51.8	51.8	51.7	51.7
105°	66.1	66.1	66.1	66.1	66.2	66.4	66.5	66.6
107.5°	82.0	82.1	82.4	82.5	82.4	82.3	82.2	82.1
110°	92.6	92.8	93.1	93.2	93.0	92.9	92.8	92.7



TEST NUMBER: P332274-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	103.2	103.5	103.9	103.9	103.9	103.9	103.9	103.9
115°	119.4	119.5	119.5	119.5	119.5	119.4	119.3	119.2
117.5°	135.7	135.7	135.7	135.5	135.4	135.2	135.1	134.9
120°	146.6	146.5	146.5	146.3	146.2	146.1	146.0	145.8
122.5°	157.6	157.4	157.2	157.1	156.9	156.7	156.5	156.4
125°	173.9	173.6	173.4	173.2	172.9	172.7	172.4	172.1
127.5°	190.0	189.7	189.3	189.0	188.8	188.5	188.2	187.9
130°	200.8	200.5	200.3	199.9	199.6	199.1	198.7	198.2
132.5°	211.2	210.9	210.6	210.3	209.9	209.6	209.3	209.0
135°	226.8	226.6	226.3	226.2	226.0	225.9	225.8	225.6
137.5°	242.1	241.9	241.5	241.3	241.1	240.8	240.6	240.3
140°	252.1	252.1	252.0	251.8	251.3	250.9	250.4	250.0
142.5°	261.5	261.4	261.4	261.2	260.9	260.5	260.2	259.8
145°	275.4	275.3	275.2	275.0	274.8	274.6	274.3	274.1
147.5°	288.4	288.4	288.4	288.2	287.9	287.5	287.1	286.7
150°	296.4	296.4	296.4	296.3	295.9	295.6	295.2	294.8
152.5°	303.8	304.0	304.0	303.9	303.6	303.2	302.9	302.6
155°	314.6	314.8	315.1	315.0	314.6	314.1	313.7	313.2
157.5°	323.8	324.2	324.4	324.3	324.0	323.7	323.3	323.0
160°	329.5	329.9	330.2	330.2	329.9	329.7	329.5	329.2
162.5°	334.9	335.3	335.6	335.5	335.1	334.7	334.3	333.9
165°	341.7	342.1	342.5	342.5	342.0	341.6	341.1	340.7
167.5°	347.2	347.6	348.0	348.0	347.6	347.2	346.8	346.5
170°	350.2	350.7	351.1	351.1	350.7	350.2	349.8	349.4
172.5°	352.6	353.0	353.4	353.4	352.9	352.5	352.0	351.6
175°	355.1	355.5	355.9	355.8	355.5	355.0	354.6	354.1
177.5°	356.3	356.6	356.9	356.9	356.6	356.2	355.8	355.5
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4

(END OF REPORT)