

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332326-927

Luminaire Tested: **S123RDIP-S775D1195U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332326-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5836.5 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	89	85	88	84	81	78	70	67	65	56	54	53	43	42	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	31	29	27
5	68	57	49	43	62	52	46	41	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	1.6
10°-20°	297.7	5.1
20°-30°	467.6	8.0
30°-40°	487.9	8.4
40°-50°	417.5	7.2
50°-60°	318.2	5.5
60°-70°	204.0	3.5
70°-80°	98.1	1.7
80°-90°	29.5	0.5
90°-100°	253.0	4.3
100°-110°	716.5	12.3
110°-120°	704.8	12.1
120°-130°	562.2	9.6
130°-140°	443.3	7.6
140°-150°	330.8	5.7
150°-160°	230.6	4.0
160°-170°	135.5	2.3
170°-180°	44.1	0.8
0°-30°	860.6	14.7
0°-40°	1348.4	23.1
0°-60°	2084.2	35.7
0°-90°	2415.8	41.4
90°-120°	1674.3	28.7
90°-150°	3010.6	51.6
90°-180°	3421.0	58.6
0°-180°	5836.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	27	2	27	2	27	15
95°	107	31	107	31	107	192
105°	1171	107	1171	107	1171	1155
115°	1424	189	1424	189	1424	1383
125°	1123	262	1123	262	1123	1018
135°	910	307	910	307	910	706
145°	712	351	712	351	712	452
155°	590	398	590	398	590	275
165°	514	435	514	435	514	147
175°	463	454	463	454	463	45
180°	455	455	455	455	455	

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	8.6	9.5	8.6	8.8	9.0	9.0	8.8	8.6	9.0	9.0	8.7
90°	26.7	27.6	26.7	25.7	26.7	24.9	23.9	23.0	22.1	23.0	20.3
92.5°	44.4	46.0	45.1	47.8	49.5	54.3	61.5	77.5	106.8	141.6	155.7
95°	106.8	110.4	116.9	125.2	142.7	175.8	224.6	331.4	442.7	545.8	486.0
97.5°	290.7	298.6	323.4	364.9	432.8	542.9	661.6	825.9	904.9	845.8	619.2
100°	577.1	576.2	612.0	679.2	772.2	902.9	1010.6	1085.1	1053.0	871.6	589.1
102.5°	846.6	867.8	897.8	950.9	1023.3	1106.1	1168.9	1171.3	1060.3	823.8	544.9
105°	1170.8	1175.4	1204.8	1239.8	1282.1	1306.1	1288.6	1196.5	1004.2	740.0	490.6
107.5°	1357.4	1365.9	1375.8	1387.6	1386.9	1354.1	1273.4	1123.9	905.9	666.0	456.0
110°	1434.0	1435.8	1437.7	1430.3	1404.5	1340.1	1224.2	1054.8	844.0	624.0	442.7

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1449.5	1449.1	1442.1	1419.3	1372.1	1289.3	1159.4	986.3	790.3	596.0	435.4
115°	1423.9	1419.3	1400.8	1360.3	1291.3	1191.0	1055.7	895.6	725.2	566.0	432.6
117.5°	1342.5	1336.3	1309.7	1263.4	1191.4	1089.6	968.0	829.8	686.0	548.3	434.3
120°	1274.8	1269.2	1247.1	1195.6	1122.9	1029.9	919.5	795.2	665.4	540.3	437.2
122.5°	1211.4	1204.4	1180.1	1133.8	1069.1	982.8	880.4	767.9	648.5	535.1	442.4
125°	1122.9	1116.4	1093.4	1053.0	994.0	920.4	832.0	731.7	626.8	528.3	450.0
127.5°	1050.0	1044.1	1023.3	988.7	936.2	869.2	789.5	700.1	607.7	525.0	458.9
130°	1008.8	1001.4	982.1	949.0	900.2	837.6	763.0	680.2	597.3	522.8	464.8
132.5°	968.3	963.1	945.9	912.8	867.0	807.4	738.0	661.8	587.8	522.0	469.2
135°	910.3	903.8	887.2	859.7	814.5	762.1	702.3	636.9	575.3	520.9	475.9
137.5°	849.0	844.7	830.8	802.8	764.9	719.4	667.8	614.3	564.4	518.9	480.3
140°	806.3	807.2	792.5	766.7	731.7	692.1	647.9	601.0	557.8	518.2	483.2
142.5°	766.5	767.4	754.2	731.3	701.6	667.1	628.8	588.5	551.8	516.7	485.4
145°	711.5	709.6	702.3	682.9	659.9	633.3	603.8	573.4	544.0	514.5	486.9
147.5°	666.1	665.4	658.5	645.4	627.9	609.0	585.2	561.1	536.2	511.0	486.9
150°	639.7	639.7	634.1	624.0	610.2	592.7	573.4	552.2	531.1	508.0	486.9
152.5°	617.6	617.6	614.3	604.9	594.1	579.5	562.4	544.2	525.2	504.4	484.7
155°	589.9	589.1	587.2	579.9	571.6	560.5	546.7	532.0	516.3	498.0	482.3
157.5°	564.7	564.9	563.5	557.9	550.7	542.1	531.5	519.1	506.4	492.3	479.2
160°	548.6	549.5	549.5	544.0	537.5	531.1	521.9	511.7	499.8	487.8	477.7
162.5°	533.9	534.7	534.7	530.0	525.7	520.0	511.6	502.9	493.1	483.4	474.8
165°	514.5	514.5	515.4	511.7	508.0	503.4	497.0	491.5	484.1	476.7	470.3
167.5°	496.1	496.1	497.0	494.4	492.8	489.5	485.8	481.6	475.5	470.2	465.9
170°	485.1	485.1	486.0	484.1	483.2	481.3	477.7	474.9	470.3	465.7	463.0
172.5°	474.8	475.5	477.1	475.3	475.1	474.0	471.0	469.1	465.2	462.0	460.7
175°	463.0	463.9	464.8	463.9	463.9	463.9	462.0	461.1	459.3	457.4	457.4
177.5°	456.1	456.1	457.6	456.9	457.6	457.6	456.9	456.1	455.4	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	8.8	7.9	8.0	7.7	8.3	8.1	9.7	11.0	11.7	10.7	11.2
90°	17.5	14.7	12.0	10.1	8.3	5.5	3.6	1.8	3.6	5.5	8.3
92.5°	116.9	77.3	53.2	39.6	31.8	24.6	17.0	11.4	17.0	24.6	31.8
95°	335.0	197.9	119.6	83.7	59.8	44.2	34.1	31.3	34.1	44.2	59.8
97.5°	367.6	213.0	138.2	99.4	75.8	62.2	54.3	53.4	54.3	62.2	75.8
100°	347.0	210.8	146.3	110.4	88.3	75.5	69.0	68.1	69.0	75.5	88.3
102.5°	329.3	213.7	155.9	122.9	103.1	90.9	85.2	83.6	85.2	90.9	103.1
105°	316.6	221.8	172.1	143.5	126.1	115.0	109.6	106.8	109.6	115.0	126.1
107.5°	315.7	236.9	193.3	166.8	150.4	139.5	134.2	131.4	134.2	139.5	150.4
110°	319.4	249.5	208.0	182.2	166.6	156.5	151.9	149.1	151.9	156.5	166.6

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.8	262.0	223.5	198.4	182.8	172.7	168.1	165.3	168.1	172.7	182.8
115°	338.7	282.6	247.6	222.8	207.1	197.9	192.3	188.7	192.3	197.9	207.1
117.5°	354.5	304.4	269.9	246.8	229.3	220.9	216.3	212.1	216.3	220.9	229.3
120°	366.3	318.5	285.3	262.3	244.9	235.6	231.0	228.2	231.0	235.6	244.9
122.5°	377.4	333.2	300.8	276.3	259.5	249.6	245.0	242.2	245.0	249.6	259.5
125°	394.8	354.3	322.1	297.3	279.8	269.7	264.2	262.3	264.2	269.7	279.8
127.5°	409.2	372.7	341.7	316.8	297.5	287.2	280.4	277.6	280.4	287.2	297.5
130°	418.7	383.8	353.4	328.6	309.3	298.2	289.9	287.2	289.9	298.2	309.3
132.5°	427.6	393.4	363.8	339.6	320.3	307.0	298.0	294.5	298.0	307.0	320.3
135°	439.0	407.7	379.2	354.3	335.0	321.2	311.1	307.4	311.1	321.2	335.0
137.5°	447.5	417.6	390.2	367.3	348.1	333.4	323.4	319.6	323.4	333.4	348.1
140°	451.9	424.3	397.6	374.6	356.2	341.4	332.2	327.6	332.2	341.4	356.2
142.5°	456.3	429.4	403.5	382.0	363.5	350.3	340.4	336.5	340.4	350.3	363.5
145°	461.1	436.3	412.3	391.2	375.5	361.7	353.4	350.7	353.4	361.7	375.5
147.5°	464.1	441.8	419.9	401.9	386.7	374.8	366.7	365.0	366.7	374.8	386.7
150°	464.8	445.4	424.3	407.7	394.8	382.9	375.5	374.6	375.5	382.9	394.8
152.5°	466.3	447.7	429.4	413.6	402.2	391.7	384.4	384.2	384.4	391.7	402.2
155°	466.7	451.9	436.3	423.3	413.3	404.1	398.5	398.5	398.5	404.1	413.3
157.5°	467.5	454.3	441.8	431.8	423.2	415.1	410.7	410.0	410.7	415.1	423.2
160°	467.5	456.5	445.4	436.3	429.8	422.5	418.7	418.7	418.7	422.5	429.8
162.5°	466.8	457.2	447.7	440.0	434.3	428.3	425.4	425.4	425.4	428.3	434.3
165°	464.8	458.4	451.0	444.6	440.8	436.3	434.4	435.4	434.4	436.3	440.8
167.5°	463.3	458.2	452.8	448.8	446.2	442.7	441.8	442.9	441.8	442.7	446.2
170°	461.1	457.4	452.8	451.0	449.2	446.4	445.4	447.3	445.4	446.4	449.2
172.5°	460.4	457.4	453.6	452.5	451.4	449.3	449.2	450.3	449.2	449.3	451.4
175°	458.4	456.5	454.7	453.8	453.8	451.9	452.8	453.8	452.8	451.9	453.8
177.5°	456.9	455.4	454.7	454.7	454.7	453.9	454.7	455.4	454.7	453.9	454.7
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	11.3	12.7	13.5	14.4	15.4	15.5	15.7	15.8	16.4	16.6	17.0
90°	10.1	12.0	14.7	17.5	20.3	23.0	22.1	23.0	23.9	24.9	26.7
92.5°	39.6	53.2	77.3	116.9	155.7	141.6	106.8	77.5	61.5	54.3	49.5
95°	83.7	119.6	197.9	335.0	486.0	545.8	442.7	331.4	224.6	175.8	142.7
97.5°	99.4	138.2	213.0	367.6	619.2	845.8	904.9	825.9	661.6	542.9	432.8
100°	110.4	146.3	210.8	347.0	589.1	871.6	1053.0	1085.1	1010.6	902.9	772.2
102.5°	122.9	155.9	213.7	329.3	544.9	823.8	1060.3	1171.3	1168.9	1106.1	1023.3
105°	143.5	172.1	221.8	316.6	490.6	740.0	1004.2	1196.5	1288.6	1306.1	1282.1
107.5°	166.8	193.3	236.9	315.7	456.0	666.0	905.9	1123.9	1273.4	1354.1	1386.9
110°	182.2	208.0	249.5	319.4	442.7	624.0	844.0	1054.8	1224.2	1340.1	1404.5

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.4	223.5	262.0	326.8	435.4	596.0	790.3	986.3	1159.4	1289.3	1372.1
115°	222.8	247.6	282.6	338.7	432.6	566.0	725.2	895.6	1055.7	1191.0	1291.3
117.5°	246.8	269.9	304.4	354.5	434.3	548.3	686.0	829.8	968.0	1089.6	1191.4
120°	262.3	285.3	318.5	366.3	437.2	540.3	665.4	795.2	919.5	1029.9	1122.9
122.5°	276.3	300.8	333.2	377.4	442.4	535.1	648.5	767.9	880.4	982.8	1069.1
125°	297.3	322.1	354.3	394.8	450.0	528.3	626.8	731.7	832.0	920.4	994.0
127.5°	316.8	341.7	372.7	409.2	458.9	525.0	607.7	700.1	789.5	869.2	936.2
130°	328.6	353.4	383.8	418.7	464.8	522.8	597.3	680.2	763.0	837.6	900.2
132.5°	339.6	363.8	393.4	427.6	469.2	522.0	587.8	661.8	738.0	807.4	867.0
135°	354.3	379.2	407.7	439.0	475.9	520.9	575.3	636.9	702.3	762.1	814.5
137.5°	367.3	390.2	417.6	447.5	480.3	518.9	564.4	614.3	667.8	719.4	764.9
140°	374.6	397.6	424.3	451.9	483.2	518.2	557.8	601.0	647.9	692.1	731.7
142.5°	382.0	403.5	429.4	456.3	485.4	516.7	551.8	588.5	628.8	667.1	701.6
145°	391.2	412.3	436.3	461.1	486.9	514.5	544.0	573.4	603.8	633.3	659.9
147.5°	401.9	419.9	441.8	464.1	486.9	511.0	536.2	561.1	585.2	609.0	627.9
150°	407.7	424.3	445.4	464.8	486.9	508.0	531.1	552.2	573.4	592.7	610.2
152.5°	413.6	429.4	447.7	466.3	484.7	504.4	525.2	544.2	562.4	579.5	594.1
155°	423.3	436.3	451.9	466.7	482.3	498.0	516.3	532.0	546.7	560.5	571.6
157.5°	431.8	441.8	454.3	467.5	479.2	492.3	506.4	519.1	531.5	542.1	550.7
160°	436.3	445.4	456.5	467.5	477.7	487.8	499.8	511.7	521.9	531.1	537.5
162.5°	440.0	447.7	457.2	466.8	474.8	483.4	493.1	502.9	511.6	520.0	525.7
165°	444.6	451.0	458.4	464.8	470.3	476.7	484.1	491.5	497.0	503.4	508.0
167.5°	448.8	452.8	458.2	463.3	465.9	470.2	475.5	481.6	485.8	489.5	492.8
170°	451.0	452.8	457.4	461.1	463.0	465.7	470.3	474.9	477.7	481.3	483.2
172.5°	452.5	453.6	457.4	460.4	460.7	462.0	465.2	469.1	471.0	474.0	475.1
175°	453.8	454.7	456.5	458.4	457.4	457.4	459.3	461.1	462.0	463.9	463.9
177.5°	454.7	454.7	455.4	456.9	455.4	454.7	455.4	456.1	456.9	457.6	457.6
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	17.4	17.0	17.1	17.3	17.1	17.0	17.4	17.0	16.6	16.4	15.8
90°	25.7	26.7	27.6	26.7	27.6	26.7	25.7	26.7	24.9	23.9	23.0
92.5°	47.8	45.1	46.0	44.4	46.0	45.1	47.8	49.5	54.3	61.5	77.5
95°	125.2	116.9	110.4	106.8	110.4	116.9	125.2	142.7	175.8	224.6	331.4
97.5°	364.9	323.4	298.6	290.7	298.6	323.4	364.9	432.8	542.9	661.6	825.9
100°	679.2	612.0	576.2	577.1	576.2	612.0	679.2	772.2	902.9	1010.6	1085.1
102.5°	950.9	897.8	867.8	846.6	867.8	897.8	950.9	1023.3	1106.1	1168.9	1171.3
105°	1239.8	1204.8	1175.4	1170.8	1175.4	1204.8	1239.8	1282.1	1306.1	1288.6	1196.5
107.5°	1387.6	1375.8	1365.9	1357.4	1365.9	1375.8	1387.6	1386.9	1354.1	1273.4	1123.9
110°	1430.3	1437.7	1435.8	1434.0	1435.8	1437.7	1430.3	1404.5	1340.1	1224.2	1054.8

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1419.3	1442.1	1449.1	1449.5	1449.1	1442.1	1419.3	1372.1	1289.3	1159.4	986.3
115°	1360.3	1400.8	1419.3	1423.9	1419.3	1400.8	1360.3	1291.3	1191.0	1055.7	895.6
117.5°	1263.4	1309.7	1336.3	1342.5	1336.3	1309.7	1263.4	1191.4	1089.6	968.0	829.8
120°	1195.6	1247.1	1269.2	1274.8	1269.2	1247.1	1195.6	1122.9	1029.9	919.5	795.2
122.5°	1133.8	1180.1	1204.4	1211.4	1204.4	1180.1	1133.8	1069.1	982.8	880.4	767.9
125°	1053.0	1093.4	1116.4	1122.9	1116.4	1093.4	1053.0	994.0	920.4	832.0	731.7
127.5°	988.7	1023.3	1044.1	1050.0	1044.1	1023.3	988.7	936.2	869.2	789.5	700.1
130°	949.0	982.1	1001.4	1008.8	1001.4	982.1	949.0	900.2	837.6	763.0	680.2
132.5°	912.8	945.9	963.1	968.3	963.1	945.9	912.8	867.0	807.4	738.0	661.8
135°	859.7	887.2	903.8	910.3	903.8	887.2	859.7	814.5	762.1	702.3	636.9
137.5°	802.8	830.8	844.7	849.0	844.7	830.8	802.8	764.9	719.4	667.8	614.3
140°	766.7	792.5	807.2	806.3	807.2	792.5	766.7	731.7	692.1	647.9	601.0
142.5°	731.3	754.2	767.4	766.5	767.4	754.2	731.3	701.6	667.1	628.8	588.5
145°	682.9	702.3	709.6	711.5	709.6	702.3	682.9	659.9	633.3	603.8	573.4
147.5°	645.4	658.5	665.4	666.1	665.4	658.5	645.4	627.9	609.0	585.2	561.1
150°	624.0	634.1	639.7	639.7	639.7	634.1	624.0	610.2	592.7	573.4	552.2
152.5°	604.9	614.3	617.6	617.6	617.6	614.3	604.9	594.1	579.5	562.4	544.2
155°	579.9	587.2	589.1	589.9	589.1	587.2	579.9	571.6	560.5	546.7	532.0
157.5°	557.9	563.5	564.9	564.7	564.9	563.5	557.9	550.7	542.1	531.5	519.1
160°	544.0	549.5	549.5	548.6	549.5	549.5	544.0	537.5	531.1	521.9	511.7
162.5°	530.0	534.7	534.7	533.9	534.7	534.7	530.0	525.7	520.0	511.6	502.9
165°	511.7	515.4	514.5	514.5	514.5	515.4	511.7	508.0	503.4	497.0	491.5
167.5°	494.4	497.0	496.1	496.1	496.1	497.0	494.4	492.8	489.5	485.8	481.6
170°	484.1	486.0	485.1	485.1	485.1	486.0	484.1	483.2	481.3	477.7	474.9
172.5°	475.3	477.1	475.5	474.8	475.5	477.1	475.3	475.1	474.0	471.0	469.1
175°	463.9	464.8	463.9	463.0	463.9	464.8	463.9	463.9	463.9	462.0	461.1
177.5°	456.9	457.6	456.1	456.1	456.1	457.6	456.9	457.6	457.6	456.9	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	15.7	15.5	15.4	14.4	13.5	12.7	11.3	11.2	10.7	11.7	11.0
90°	22.1	23.0	20.3	17.5	14.7	12.0	10.1	8.3	5.5	3.6	1.8
92.5°	106.8	141.6	155.7	116.9	77.3	53.2	39.6	31.8	24.6	17.0	11.4
95°	442.7	545.8	486.0	335.0	197.9	119.6	83.7	59.8	44.2	34.1	31.3
97.5°	904.9	845.8	619.2	367.6	213.0	138.2	99.4	75.8	62.2	54.3	53.4
100°	1053.0	871.6	589.1	347.0	210.8	146.3	110.4	88.3	75.5	69.0	68.1
102.5°	1060.3	823.8	544.9	329.3	213.7	155.9	122.9	103.1	90.9	85.2	83.6
105°	1004.2	740.0	490.6	316.6	221.8	172.1	143.5	126.1	115.0	109.6	106.8
107.5°	905.9	666.0	456.0	315.7	236.9	193.3	166.8	150.4	139.5	134.2	131.4
110°	844.0	624.0	442.7	319.4	249.5	208.0	182.2	166.6	156.5	151.9	149.1

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	790.3	596.0	435.4	326.8	262.0	223.5	198.4	182.8	172.7	168.1	165.3
115°	725.2	566.0	432.6	338.7	282.6	247.6	222.8	207.1	197.9	192.3	188.7
117.5°	686.0	548.3	434.3	354.5	304.4	269.9	246.8	229.3	220.9	216.3	212.1
120°	665.4	540.3	437.2	366.3	318.5	285.3	262.3	244.9	235.6	231.0	228.2
122.5°	648.5	535.1	442.4	377.4	333.2	300.8	276.3	259.5	249.6	245.0	242.2
125°	626.8	528.3	450.0	394.8	354.3	322.1	297.3	279.8	269.7	264.2	262.3
127.5°	607.7	525.0	458.9	409.2	372.7	341.7	316.8	297.5	287.2	280.4	277.6
130°	597.3	522.8	464.8	418.7	383.8	353.4	328.6	309.3	298.2	289.9	287.2
132.5°	587.8	522.0	469.2	427.6	393.4	363.8	339.6	320.3	307.0	298.0	294.5
135°	575.3	520.9	475.9	439.0	407.7	379.2	354.3	335.0	321.2	311.1	307.4
137.5°	564.4	518.9	480.3	447.5	417.6	390.2	367.3	348.1	333.4	323.4	319.6
140°	557.8	518.2	483.2	451.9	424.3	397.6	374.6	356.2	341.4	332.2	327.6
142.5°	551.8	516.7	485.4	456.3	429.4	403.5	382.0	363.5	350.3	340.4	336.5
145°	544.0	514.5	486.9	461.1	436.3	412.3	391.2	375.5	361.7	353.4	350.7
147.5°	536.2	511.0	486.9	464.1	441.8	419.9	401.9	386.7	374.8	366.7	365.0
150°	531.1	508.0	486.9	464.8	445.4	424.3	407.7	394.8	382.9	375.5	374.6
152.5°	525.2	504.4	484.7	466.3	447.7	429.4	413.6	402.2	391.7	384.4	384.2
155°	516.3	498.0	482.3	466.7	451.9	436.3	423.3	413.3	404.1	398.5	398.5
157.5°	506.4	492.3	479.2	467.5	454.3	441.8	431.8	423.2	415.1	410.7	410.0
160°	499.8	487.8	477.7	467.5	456.5	445.4	436.3	429.8	422.5	418.7	418.7
162.5°	493.1	483.4	474.8	466.8	457.2	447.7	440.0	434.3	428.3	425.4	425.4
165°	484.1	476.7	470.3	464.8	458.4	451.0	444.6	440.8	436.3	434.4	435.4
167.5°	475.5	470.2	465.9	463.3	458.2	452.8	448.8	446.2	442.7	441.8	442.9
170°	470.3	465.7	463.0	461.1	457.4	452.8	451.0	449.2	446.4	445.4	447.3
172.5°	465.2	462.0	460.7	460.4	457.4	453.6	452.5	451.4	449.3	449.2	450.3
175°	459.3	457.4	457.4	458.4	456.5	454.7	453.8	453.8	451.9	452.8	453.8
177.5°	455.4	454.7	455.4	456.9	455.4	454.7	454.7	454.7	453.9	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.7	8.1	8.3	7.7	8.0	7.9	8.8	8.7	9.0	9.0	8.6
90°	3.6	5.5	8.3	10.1	12.0	14.7	17.5	20.3	23.0	22.1	23.0
92.5°	17.0	24.6	31.8	39.6	53.2	77.3	116.9	155.7	141.6	106.8	77.5
95°	34.1	44.2	59.8	83.7	119.6	197.9	335.0	486.0	545.8	442.7	331.4
97.5°	54.3	62.2	75.8	99.4	138.2	213.0	367.6	619.2	845.8	904.9	825.9
100°	69.0	75.5	88.3	110.4	146.3	210.8	347.0	589.1	871.6	1053.0	1085.1
102.5°	85.2	90.9	103.1	122.9	155.9	213.7	329.3	544.9	823.8	1060.3	1171.3
105°	109.6	115.0	126.1	143.5	172.1	221.8	316.6	490.6	740.0	1004.2	1196.5
107.5°	134.2	139.5	150.4	166.8	193.3	236.9	315.7	456.0	666.0	905.9	1123.9
110°	151.9	156.5	166.6	182.2	208.0	249.5	319.4	442.7	624.0	844.0	1054.8

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.1	172.7	182.8	198.4	223.5	262.0	326.8	435.4	596.0	790.3	986.3
115°	192.3	197.9	207.1	222.8	247.6	282.6	338.7	432.6	566.0	725.2	895.6
117.5°	216.3	220.9	229.3	246.8	269.9	304.4	354.5	434.3	548.3	686.0	829.8
120°	231.0	235.6	244.9	262.3	285.3	318.5	366.3	437.2	540.3	665.4	795.2
122.5°	245.0	249.6	259.5	276.3	300.8	333.2	377.4	442.4	535.1	648.5	767.9
125°	264.2	269.7	279.8	297.3	322.1	354.3	394.8	450.0	528.3	626.8	731.7
127.5°	280.4	287.2	297.5	316.8	341.7	372.7	409.2	458.9	525.0	607.7	700.1
130°	289.9	298.2	309.3	328.6	353.4	383.8	418.7	464.8	522.8	597.3	680.2
132.5°	298.0	307.0	320.3	339.6	363.8	393.4	427.6	469.2	522.0	587.8	661.8
135°	311.1	321.2	335.0	354.3	379.2	407.7	439.0	475.9	520.9	575.3	636.9
137.5°	323.4	333.4	348.1	367.3	390.2	417.6	447.5	480.3	518.9	564.4	614.3
140°	332.2	341.4	356.2	374.6	397.6	424.3	451.9	483.2	518.2	557.8	601.0
142.5°	340.4	350.3	363.5	382.0	403.5	429.4	456.3	485.4	516.7	551.8	588.5
145°	353.4	361.7	375.5	391.2	412.3	436.3	461.1	486.9	514.5	544.0	573.4
147.5°	366.7	374.8	386.7	401.9	419.9	441.8	464.1	486.9	511.0	536.2	561.1
150°	375.5	382.9	394.8	407.7	424.3	445.4	464.8	486.9	508.0	531.1	552.2
152.5°	384.4	391.7	402.2	413.6	429.4	447.7	466.3	484.7	504.4	525.2	544.2
155°	398.5	404.1	413.3	423.3	436.3	451.9	466.7	482.3	498.0	516.3	532.0
157.5°	410.7	415.1	423.2	431.8	441.8	454.3	467.5	479.2	492.3	506.4	519.1
160°	418.7	422.5	429.8	436.3	445.4	456.5	467.5	477.7	487.8	499.8	511.7
162.5°	425.4	428.3	434.3	440.0	447.7	457.2	466.8	474.8	483.4	493.1	502.9
165°	434.4	436.3	440.8	444.6	451.0	458.4	464.8	470.3	476.7	484.1	491.5
167.5°	441.8	442.7	446.2	448.8	452.8	458.2	463.3	465.9	470.2	475.5	481.6
170°	445.4	446.4	449.2	451.0	452.8	457.4	461.1	463.0	465.7	470.3	474.9
172.5°	449.2	449.3	451.4	452.5	453.6	457.4	460.4	460.7	462.0	465.2	469.1
175°	452.8	451.9	453.8	453.8	454.7	456.5	458.4	457.4	457.4	459.3	461.1
177.5°	454.7	453.9	454.7	454.7	454.7	455.4	456.9	455.4	454.7	455.4	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	8.8	9.0	9.0	8.8	8.6	9.5	8.6
90°	23.9	24.9	26.7	25.7	26.7	27.6	26.7
92.5°	61.5	54.3	49.5	47.8	45.1	46.0	44.4
95°	224.6	175.8	142.7	125.2	116.9	110.4	106.8
97.5°	661.6	542.9	432.8	364.9	323.4	298.6	290.7
100°	1010.6	902.9	772.2	679.2	612.0	576.2	577.1
102.5°	1168.9	1106.1	1023.3	950.9	897.8	867.8	846.6
105°	1288.6	1306.1	1282.1	1239.8	1204.8	1175.4	1170.8
107.5°	1273.4	1354.1	1386.9	1387.6	1375.8	1365.9	1357.4
110°	1224.2	1340.1	1404.5	1430.3	1437.7	1435.8	1434.0

TEST NUMBER: P332326-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1159.4	1289.3	1372.1	1419.3	1442.1	1449.1	1449.5
115°	1055.7	1191.0	1291.3	1360.3	1400.8	1419.3	1423.9
117.5°	968.0	1089.6	1191.4	1263.4	1309.7	1336.3	1342.5
120°	919.5	1029.9	1122.9	1195.6	1247.1	1269.2	1274.8
122.5°	880.4	982.8	1069.1	1133.8	1180.1	1204.4	1211.4
125°	832.0	920.4	994.0	1053.0	1093.4	1116.4	1122.9
127.5°	789.5	869.2	936.2	988.7	1023.3	1044.1	1050.0
130°	763.0	837.6	900.2	949.0	982.1	1001.4	1008.8
132.5°	738.0	807.4	867.0	912.8	945.9	963.1	968.3
135°	702.3	762.1	814.5	859.7	887.2	903.8	910.3
137.5°	667.8	719.4	764.9	802.8	830.8	844.7	849.0
140°	647.9	692.1	731.7	766.7	792.5	807.2	806.3
142.5°	628.8	667.1	701.6	731.3	754.2	767.4	766.5
145°	603.8	633.3	659.9	682.9	702.3	709.6	711.5
147.5°	585.2	609.0	627.9	645.4	658.5	665.4	666.1
150°	573.4	592.7	610.2	624.0	634.1	639.7	639.7
152.5°	562.4	579.5	594.1	604.9	614.3	617.6	617.6
155°	546.7	560.5	571.6	579.9	587.2	589.1	589.9
157.5°	531.5	542.1	550.7	557.9	563.5	564.9	564.7
160°	521.9	531.1	537.5	544.0	549.5	549.5	548.6
162.5°	511.6	520.0	525.7	530.0	534.7	534.7	533.9
165°	497.0	503.4	508.0	511.7	515.4	514.5	514.5
167.5°	485.8	489.5	492.8	494.4	497.0	496.1	496.1
170°	477.7	481.3	483.2	484.1	486.0	485.1	485.1
172.5°	471.0	474.0	475.1	475.3	477.1	475.5	474.8
175°	462.0	463.9	463.9	463.9	464.8	463.9	463.0
177.5°	456.9	457.6	457.6	456.9	457.6	456.1	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7

(END OF REPORT)