

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332042-830

Luminaire Tested: **S123DIP-S1000D1195U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332042-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1195U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8381.1 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332042-830

CATALOG NUMBER: S123DIP-S1000D1195U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot



TEST NUMBER: P332042-830

CATALOG NUMBER: S123DIP-S1000D1195U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	47	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595

TEST NUMBER: P332042-830

CATALOG NUMBER: S123DIP-S1000D1195U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	1.7
10°-20°	396.8	4.7
20°-30°	586.2	7.0
30°-40°	684.7	8.2
40°-50°	688.4	8.2
50°-60°	604.7	7.2
60°-70°	450.5	5.4
70°-80°	256.7	3.1
80°-90°	77.8	0.9
90°-100°	53.6	0.6
100°-110°	255.4	3.0
110°-120°	613.5	7.3
120°-130°	781.2	9.3
130°-140°	834.7	10.0
140°-150°	780.5	9.3
150°-160°	629.6	7.5
160°-170°	406.3	4.8
170°-180°	140.0	1.7
0°-30°	1123.5	13.4
0°-40°	1808.2	21.6
0°-60°	3101.3	37.0
0°-90°	3886.3	46.4
90°-120°	922.4	11.0
90°-150°	3318.8	39.6
90°-180°	4495.0	53.6
0°-180°	8381.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	12	26	31	33	7
95°	67	25	34	41	42	83
105°	326	332	240	57	48	346
115°	612	619	629	639	644	604
125°	863	871	876	878	880	770
135°	1074	1081	1085	1088	1085	827
145°	1240	1247	1249	1252	1252	776
155°	1366	1364	1364	1369	1363	629
165°	1440	1437	1436	1443	1437	407
175°	1474	1469	1470	1476	1468	140
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P332042-830

CATALOG NUMBER: S123DIP-S1000D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.9	26.7	26.5	26.3	26.1	26.2	26.6	27.1	27.4	27.8	27.8
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	20.4	19.7	19.0	18.3	17.6	18.5	20.9	23.3	25.6	28.0	29.6
95°	66.8	56.8	46.8	36.9	26.9	23.3	25.9	28.6	31.3	33.9	35.6
97.5°	134.2	129.8	125.3	120.8	116.3	105.4	87.8	70.3	52.8	35.3	37.2
100°	185.0	189.9	194.8	199.6	204.5	187.9	150.1	112.1	74.1	36.1	38.1
102.5°	242.9	246.4	249.9	253.4	256.9	237.9	196.4	155.0	113.5	72.0	66.0
105°	326.3	329.0	331.7	334.3	337.1	327.4	305.5	283.6	261.7	239.8	196.7
107.5°	414.3	416.5	418.7	420.8	422.9	425.7	429.2	432.6	436.1	439.6	407.9
110°	473.1	475.0	476.9	478.9	480.9	483.1	485.9	488.5	491.2	493.9	485.9

TEST NUMBER: P332042-830

CATALOG NUMBER: S123DIP-S1000D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.1	530.8	532.6	534.4	536.1	538.4	541.0	543.8	546.4	549.0	549.2
115°	612.2	613.6	615.0	616.5	617.9	619.8	622.0	624.2	626.4	628.6	631.0
117.5°	692.5	694.3	696.1	698.0	699.7	701.2	702.3	703.4	704.6	705.7	707.6
120°	742.4	744.6	746.9	749.0	751.2	752.7	753.4	754.1	754.9	755.5	757.5
122.5°	793.2	795.0	796.8	798.6	800.5	801.8	802.8	803.7	804.6	805.5	806.9
125°	862.9	864.9	866.8	868.7	870.7	872.1	873.1	874.1	875.1	876.0	876.6
127.5°	930.4	932.3	934.2	936.2	938.1	939.7	940.8	942.1	943.2	944.3	945.2
130°	972.4	974.4	976.3	978.3	980.1	981.7	982.6	983.6	984.6	985.5	986.6
132.5°	1012.7	1014.6	1016.6	1018.5	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0
135°	1074.2	1075.7	1077.1	1078.6	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9
137.5°	1126.8	1128.7	1130.5	1132.4	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7
140°	1161.9	1163.3	1164.8	1166.2	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7
142.5°	1194.3	1195.7	1197.2	1198.6	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9
145°	1239.6	1241.3	1243.0	1244.7	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9
147.5°	1282.3	1283.5	1284.6	1285.6	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1
150°	1308.6	1309.3	1310.0	1310.8	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6
152.5°	1332.3	1332.6	1332.9	1333.2	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0
155°	1365.6	1365.1	1364.5	1364.0	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6
157.5°	1391.4	1391.3	1391.3	1391.2	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6
160°	1407.1	1406.9	1406.7	1406.5	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5
162.5°	1422.0	1421.4	1420.8	1420.1	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8
165°	1440.0	1439.3	1438.5	1437.8	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6
167.5°	1454.1	1453.0	1452.1	1451.1	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6
170°	1461.9	1460.9	1460.0	1459.0	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4
172.5°	1467.2	1466.0	1464.8	1463.7	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7
175°	1473.9	1472.7	1471.5	1470.3	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3
177.5°	1475.7	1474.7	1473.8	1472.8	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

TEST NUMBER: P332042-830

CATALOG NUMBER: S123DIP-S1000D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	27.8	27.7	27.7	27.7	27.8	27.9	28.0	28.1
90°	28.2	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	31.1	32.7	34.3	35.2	35.4	35.8	36.1	36.4
95°	37.3	39.0	40.7	41.6	41.6	41.6	41.6	41.6
97.5°	39.1	41.1	43.1	44.1	44.4	44.7	44.9	45.1
100°	40.1	41.9	43.9	45.1	45.2	45.5	45.7	46.0
102.5°	59.9	53.9	47.9	45.1	45.5	46.0	46.5	46.8
105°	153.6	110.6	67.5	46.3	46.8	47.2	47.7	48.2
107.5°	376.4	344.8	313.2	281.2	248.7	216.2	183.8	151.4
110°	477.8	469.8	461.8	440.4	405.6	370.7	335.9	301.1

TEST NUMBER: P332042-830

CATALOG NUMBER: S123DIP-S1000D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	549.3	549.5	549.7	546.0	538.7	531.3	524.0	516.6
115°	633.4	635.8	638.3	640.0	640.9	642.0	642.9	643.9
117.5°	709.5	711.5	713.4	714.5	714.7	714.9	715.1	715.3
120°	759.5	761.4	763.4	764.3	764.3	764.3	764.3	764.3
122.5°	808.2	809.6	811.0	811.7	811.9	812.1	812.4	812.6
125°	877.0	877.5	878.0	878.4	878.9	879.5	880.0	880.4
127.5°	945.9	946.7	947.4	947.6	947.2	946.7	946.2	945.7
130°	987.5	988.4	989.5	989.7	989.2	988.7	988.3	987.8
132.5°	1026.9	1027.9	1028.9	1029.0	1028.3	1027.7	1027.0	1026.2
135°	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2
137.5°	1139.9	1141.0	1142.2	1142.6	1142.1	1141.6	1141.1	1140.6
140°	1173.7	1174.6	1175.6	1175.8	1175.4	1174.9	1174.4	1173.9
142.5°	1205.7	1206.5	1207.2	1207.3	1206.6	1205.9	1205.2	1204.6
145°	1250.5	1250.9	1251.4	1251.6	1251.6	1251.6	1251.6	1251.6
147.5°	1290.5	1291.0	1291.5	1291.2	1290.1	1288.9	1287.8	1286.7
150°	1315.0	1315.5	1316.0	1315.9	1315.1	1314.5	1313.7	1313.0
152.5°	1336.8	1337.8	1338.6	1338.5	1337.4	1336.2	1335.1	1334.0
155°	1366.9	1368.1	1369.3	1369.1	1367.7	1366.3	1364.8	1363.4
157.5°	1393.0	1394.4	1395.9	1395.7	1393.8	1391.9	1390.0	1388.1
160°	1407.9	1409.3	1410.8	1410.7	1409.0	1407.3	1405.5	1403.8
162.5°	1421.4	1423.1	1424.7	1424.7	1423.2	1421.7	1420.2	1418.7
165°	1439.5	1441.4	1443.4	1443.5	1441.8	1440.1	1438.4	1436.7
167.5°	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6
170°	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5
172.5°	1466.7	1468.6	1470.6	1470.5	1468.3	1466.2	1464.1	1461.9
175°	1473.0	1474.7	1476.4	1476.2	1474.3	1472.3	1470.5	1468.5
177.5°	1475.3	1476.9	1478.4	1478.2	1476.3	1474.3	1472.3	1470.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

(END OF REPORT)