

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332262-930

Luminaire Tested: **S123RDIP-S340D1025U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332262-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3931.7 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332262-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot



TEST NUMBER: P332262-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27		
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23		
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	28	26	25	20		
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17		
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15		
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13		
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11		
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	14	13	10		
8	51	39	32	27	45	35	29	25	28	24	20	22	18	16	15	13	12	9		
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	10	8		
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	10	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223

TEST NUMBER: P332262-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.1
10°-20°	122.4	3.1
20°-30°	176.2	4.5
30°-40°	198.5	5.0
40°-50°	189.9	4.8
50°-60°	155.5	4.0
60°-70°	104.9	2.7
70°-80°	52.8	1.3
80°-90°	17.0	0.4
90°-100°	67.5	1.7
100°-110°	202.0	5.1
110°-120°	343.6	8.7
120°-130°	451.9	11.5
130°-140°	508.0	12.9
140°-150°	499.3	12.7
150°-160°	420.4	10.7
160°-170°	279.8	7.1
170°-180°	98.0	2.5
0°-30°	342.6	8.7
0°-40°	541.1	13.8
0°-60°	886.5	22.5
0°-90°	1061.2	27.0
90°-120°	613.1	15.6
90°-150°	2072.3	52.7
90°-180°	2870.0	73.0
0°-180°	3931.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	1	9	20	23	24	4
95°	48	54	60	63	64	54
105°	183	185	192	192	194	196
115°	346	348	347	347	347	342
125°	506	508	507	504	500	451
135°	657	661	661	658	656	506
145°	797	798	801	800	797	497
155°	912	912	913	916	911	420
165°	994	991	991	996	990	280
175°	1034	1030	1030	1035	1030	98
180°	1036	1036	1036	1036	1036	

TEST NUMBER: P332262-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.4	7.1	6.7	6.3	6.0	6.0	6.4	6.9	7.4	7.8	7.9
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	19.7	21.0	22.2	23.4	24.6	25.9	27.2	28.5	29.9	31.2	31.8
95°	48.0	49.2	50.5	51.9	53.1	54.5	55.8	57.3	58.8	60.3	61.0
97.5°	85.3	86.3	87.2	88.1	89.0	90.0	91.1	92.1	93.2	94.2	95.1
100°	110.7	111.8	112.8	113.9	115.0	116.0	116.9	117.8	118.7	119.6	120.2
102.5°	140.0	140.6	141.3	141.9	142.6	143.5	144.7	145.9	147.1	148.3	148.8
105°	183.1	183.4	183.8	184.2	184.6	185.6	187.2	188.8	190.5	192.1	192.1
107.5°	233.3	233.5	233.7	233.9	234.2	234.6	235.2	235.9	236.5	237.2	237.7
110°	264.5	264.9	265.2	265.5	266.0	266.3	266.7	267.0	267.4	267.7	268.5

TEST NUMBER: P332262-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.0	297.3	297.5	297.7	297.9	298.1	298.2	298.2	298.3	298.3	299.2
115°	345.8	346.4	347.0	347.5	348.1	348.1	347.8	347.4	347.1	346.7	346.9
117.5°	395.0	395.4	395.7	396.2	396.5	396.4	396.0	395.5	395.0	394.5	394.5
120°	425.7	426.7	427.8	428.9	430.0	430.1	429.2	428.3	427.4	426.5	426.2
122.5°	457.5	458.4	459.1	459.9	460.7	460.9	460.4	459.9	459.5	459.0	458.5
125°	506.2	506.8	507.3	507.8	508.3	508.5	508.1	507.8	507.4	507.0	506.3
127.5°	551.1	552.3	553.4	554.6	555.8	556.1	555.7	555.4	555.0	554.6	553.5
130°	581.1	582.5	584.0	585.4	586.9	587.3	586.8	586.2	585.7	585.1	584.4
132.5°	611.1	612.5	613.9	615.4	616.9	617.3	616.9	616.5	616.1	615.7	614.9
135°	656.8	657.9	658.9	660.0	661.1	661.5	661.4	661.2	661.0	660.8	660.1
137.5°	699.1	700.0	700.9	701.8	702.7	703.4	703.8	704.3	704.8	705.2	704.5
140°	728.4	729.3	730.2	731.1	732.0	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	755.0	755.9	756.9	757.8	758.7	759.3	759.6	759.9	760.3	760.6	760.4
145°	796.7	797.1	797.4	797.9	798.2	798.7	799.2	799.7	800.3	800.8	800.6
147.5°	833.2	833.9	834.5	835.2	835.8	836.4	836.9	837.4	837.9	838.5	838.5
150°	858.6	859.0	859.3	859.7	860.1	860.4	860.8	861.1	861.5	861.9	861.9
152.5°	879.5	880.0	880.4	880.9	881.4	881.8	882.1	882.2	882.5	882.7	883.0
155°	912.3	912.3	912.3	912.3	912.3	912.4	912.6	912.7	913.0	913.1	913.9
157.5°	940.3	940.1	939.9	939.6	939.5	939.4	939.6	939.7	939.9	940.0	940.8
160°	957.9	957.5	957.2	956.8	956.4	956.3	956.3	956.3	956.3	956.3	957.2
162.5°	973.5	973.0	972.5	972.0	971.5	971.3	971.4	971.6	971.8	971.9	972.8
165°	993.7	993.1	992.6	992.1	991.6	991.2	991.2	991.2	991.2	991.2	992.3
167.5°	1009.8	1009.1	1008.4	1007.6	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4
170°	1019.0	1018.2	1017.5	1016.8	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9
172.5°	1026.1	1025.4	1024.7	1023.9	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9
175°	1033.6	1032.8	1032.1	1031.4	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4
177.5°	1036.7	1036.1	1035.5	1034.9	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

TEST NUMBER: P332262-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	8.0	8.1	8.2	8.2	8.2	8.2	8.2	8.2
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	32.4	33.0	33.6	33.8	33.5	33.3	33.1	32.9
95°	61.6	62.4	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	95.9	96.8	97.6	97.9	97.9	97.8	97.8	97.7
100°	120.7	121.2	121.8	122.3	122.6	122.9	123.4	123.7
102.5°	149.4	149.9	150.4	150.7	150.6	150.5	150.5	150.4
105°	192.1	192.1	192.1	192.2	192.6	193.0	193.3	193.7
107.5°	238.3	238.9	239.5	239.6	239.5	239.2	239.0	238.8
110°	269.2	269.9	270.7	270.8	270.4	270.1	269.8	269.4

TEST NUMBER: P332262-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.1	300.9	301.8	302.2	302.1	302.1	302.0	301.9
115°	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7
117.5°	394.4	394.4	394.4	394.1	393.6	393.1	392.6	392.1
120°	426.1	425.9	425.7	425.4	425.1	424.8	424.4	424.0
122.5°	458.0	457.6	457.1	456.6	456.2	455.6	455.1	454.6
125°	505.6	504.8	504.1	503.4	502.7	502.0	501.2	500.5
127.5°	552.5	551.5	550.5	549.6	548.8	547.9	547.1	546.3
130°	583.7	582.9	582.3	581.2	580.0	578.7	577.5	576.2
132.5°	614.0	613.2	612.3	611.4	610.4	609.4	608.5	607.5
135°	659.4	658.7	657.9	657.4	657.0	656.6	656.3	656.0
137.5°	703.8	703.0	702.2	701.5	700.8	700.1	699.4	698.8
140°	732.9	732.7	732.5	731.8	730.6	729.3	728.1	726.8
142.5°	760.3	760.1	759.9	759.3	758.3	757.3	756.4	755.4
145°	800.5	800.3	800.1	799.6	798.9	798.2	797.4	796.7
147.5°	838.5	838.5	838.5	837.9	836.8	835.7	834.6	833.6
150°	861.9	861.9	861.9	861.3	860.2	859.2	858.0	857.0
152.5°	883.3	883.5	883.9	883.5	882.6	881.7	880.7	879.8
155°	914.6	915.3	916.0	915.7	914.5	913.2	911.9	910.7
157.5°	941.5	942.2	943.1	942.9	941.9	940.9	939.9	938.8
160°	958.1	959.0	959.9	959.9	959.3	958.5	957.8	957.1
162.5°	973.7	974.6	975.5	975.3	974.2	973.1	971.9	970.8
165°	993.4	994.5	995.6	995.5	994.3	993.0	991.7	990.4
167.5°	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2
170°	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7
172.5°	1025.1	1026.2	1027.3	1027.3	1026.0	1024.7	1023.4	1022.1
175°	1032.5	1033.6	1034.7	1034.5	1033.3	1032.0	1030.8	1029.5
177.5°	1035.8	1036.7	1037.5	1037.5	1036.5	1035.4	1034.5	1033.4
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

(END OF REPORT)