

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332015

Luminaire Tested: **S123DIP-S1000D585U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332015
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6462.1 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332015

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot



TEST NUMBER: P332015

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91		79	79	79		69
1	101	96	92	89	94	91	87	84	80	77	75		70	68	66		61
2	92	84	78	72	86	79	74	69	70	66	62		61	58	55		53
3	84	74	66	60	78	70	63	58	62	56	52		54	50	47		47
4	77	65	57	51	72	62	54	49	55	49	44		48	44	40		42
5	70	58	50	44	66	55	48	42	49	43	38		43	38	35		38
6	65	52	44	38	61	50	42	37	44	38	33		39	34	30		35
7	60	47	39	34	56	45	37	32	40	34	30		36	31	27		32
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29
9	52	39	32	27	49	37	30	26	34	28	24		30	25	22		27
10	49	36	29	24	46	35	28	23	31	25	21		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17038	17038	17038
5°	17117	16883	17001
10°	17004	16736	16840
15°	16805	16547	16577
20°	16573	16276	16292
25°	16262	15954	15922
30°	15918	15597	15478
35°	15559	15219	15023
40°	15185	14802	14573
45°	14772	14420	14067
50°	14359	13949	13561
55°	13818	13461	13052
60°	13272	12893	12482
65°	12791	12271	11889
70°	12079	11566	11050
75°	11038	10643	10189
80°	9955	9534	9447
85°	8744	8410	8065

TEST NUMBER: P332015

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.1	2.3
10°-20°	421.0	6.5
20°-30°	621.9	9.6
30°-40°	726.5	11.2
40°-50°	730.4	11.3
50°-60°	641.5	9.9
60°-70°	478.0	7.4
70°-80°	272.3	4.2
80°-90°	80.3	1.2
90°-100°	27.9	0.4
100°-110°	133.0	2.1
110°-120°	319.5	4.9
120°-130°	406.9	6.3
130°-140°	434.7	6.7
140°-150°	406.5	6.3
150°-160°	327.9	5.1
160°-170°	211.6	3.3
170°-180°	72.9	1.1
0°-30°	1192.0	18.4
0°-40°	1918.5	29.7
0°-60°	3290.4	50.9
0°-90°	4121.0	63.8
90°-120°	480.5	7.4
90°-150°	1728.6	26.8
90°-180°	2341.0	36.2
0°-180°	6462.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1584	1577	1562	1575	1573	150
15°	1508	1502	1485	1495	1488	425
25°	1369	1360	1343	1344	1341	630
35°	1184	1175	1158	1150	1143	740
45°	970	964	947	932	924	749
55°	736	734	717	703	696	659
65°	502	495	482	471	467	495
75°	265	260	256	249	245	284
85°	71	68	68	65	65	78
90°	1	6	14	16	17	6
95°	35	13	18	21	22	43
105°	170	173	125	30	25	180
115°	319	322	327	333	335	315
125°	449	454	456	457	459	401
135°	560	563	565	567	565	431
145°	646	650	651	652	652	404
155°	711	710	711	713	710	328
165°	750	748	748	752	748	212
175°	768	765	765	769	765	73
180°	768	768	768	768	768	

TEST NUMBER: P332015

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1588.3	1587.4	1586.4	1585.4	1584.5	1582.6	1580.0	1577.3	1574.7	1572.0	1574.4
5°	1584.2	1582.7	1581.2	1579.7	1578.2	1575.8	1572.5	1569.1	1565.8	1562.5	1565.5
7.5°	1568.7	1567.2	1565.7	1564.2	1562.7	1560.2	1556.8	1553.3	1549.9	1546.4	1549.1
10°	1555.7	1554.2	1552.6	1551.1	1549.6	1546.9	1543.0	1539.0	1535.1	1531.2	1533.9
12.5°	1538.2	1537.0	1535.7	1534.4	1533.2	1530.7	1527.0	1523.3	1519.6	1515.9	1517.9
15°	1508.0	1506.8	1505.6	1504.4	1503.2	1500.6	1496.7	1492.8	1488.8	1484.9	1487.3
17.5°	1472.9	1471.3	1469.8	1468.2	1466.6	1463.9	1459.9	1456.0	1452.1	1448.1	1449.8
20°	1446.8	1445.0	1443.2	1441.3	1439.5	1436.6	1432.7	1428.8	1424.9	1420.9	1422.1
22.5°	1417.4	1415.6	1413.8	1411.9	1410.1	1407.3	1403.3	1399.4	1395.5	1391.5	1392.5
25°	1369.2	1367.4	1365.6	1363.8	1361.9	1359.1	1355.1	1351.2	1347.3	1343.3	1343.6
27.5°	1317.8	1316.0	1314.2	1312.5	1310.7	1307.7	1303.5	1299.3	1295.0	1290.8	1291.0
30°	1280.7	1279.2	1277.7	1276.2	1274.7	1271.8	1267.6	1263.3	1259.1	1254.9	1254.9
32.5°	1243.7	1241.7	1239.7	1237.7	1235.7	1233.1	1229.8	1226.6	1223.3	1220.0	1218.3
35°	1184.1	1182.3	1180.5	1178.7	1176.8	1174.0	1170.0	1166.1	1162.2	1158.2	1156.4
37.5°	1123.1	1120.8	1118.5	1116.2	1113.9	1110.8	1106.8	1102.8	1098.8	1094.8	1092.6
40°	1080.7	1078.8	1077.0	1075.2	1073.4	1070.4	1066.1	1061.9	1057.7	1053.4	1051.0
42.5°	1038.2	1036.1	1034.1	1032.0	1030.0	1026.8	1022.6	1018.4	1014.1	1009.9	1007.5
45°	970.4	969.2	968.0	966.8	965.6	963.0	959.1	955.1	951.2	947.3	943.7
47.5°	903.2	901.4	899.7	897.9	896.2	893.4	889.8	886.1	882.4	878.7	875.1
50°	857.5	855.9	854.4	852.9	851.4	848.7	844.7	840.8	836.9	833.0	829.6
52.5°	809.5	808.5	807.5	806.5	805.4	802.8	798.7	794.5	790.3	786.1	783.3
55°	736.3	736.0	735.7	735.4	735.1	733.0	729.1	725.1	721.2	717.3	713.9
57.5°	666.6	665.6	664.6	663.6	662.5	660.4	657.3	654.1	651.0	647.9	644.9
60°	616.5	616.2	615.9	615.6	615.3	613.4	609.7	606.1	602.5	598.9	596.1
62.5°	571.9	571.1	570.3	569.5	568.8	566.6	562.9	559.3	555.7	552.0	549.3
65°	502.2	500.7	499.2	497.7	496.2	493.9	490.9	487.9	484.8	481.8	479.4
67.5°	428.5	427.1	425.8	424.5	423.1	421.3	419.0	416.7	414.4	412.1	410.0
70°	383.8	382.0	380.2	378.4	376.6	374.7	372.9	371.1	369.3	367.5	365.4
72.5°	337.0	335.7	334.3	333.0	331.7	330.0	327.9	325.9	323.8	321.7	319.9
75°	265.4	264.2	263.0	261.8	260.6	259.5	258.6	257.7	256.8	255.9	254.4
77.5°	202.0	201.3	200.6	200.0	199.3	198.4	197.4	196.3	195.2	194.1	193.1
80°	160.6	159.7	158.8	157.9	157.0	156.2	155.6	155.0	154.4	153.8	153.5
82.5°	120.3	120.1	120.0	119.8	119.6	119.4	119.3	119.2	119.1	119.0	118.4
85°	70.8	70.2	69.6	69.0	68.4	68.1	68.1	68.1	68.1	68.1	67.4
87.5°	28.4	28.0	27.5	27.0	26.5	26.3	26.4	26.5	26.6	26.7	26.6
90°	0.6	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2
92.5°	10.6	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4
95°	34.8	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6
97.5°	69.9	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4
100°	96.4	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8
102.5°	126.5	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4
105°	170.0	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5
107.5°	215.8	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5
110°	246.4	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0

TEST NUMBER: P332015

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1
115°	318.8	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7
117.5°	360.7	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6
120°	386.7	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6
122.5°	413.2	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3
125°	449.4	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5
127.5°	484.6	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3
130°	506.5	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8
132.5°	527.5	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4
135°	559.5	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6
137.5°	586.9	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1
140°	605.1	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8
142.5°	622.0	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6
145°	645.6	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0
147.5°	667.9	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9
150°	681.6	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7
152.5°	693.9	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8
155°	711.2	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3
157.5°	724.7	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8
160°	732.9	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5
162.5°	740.7	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5
165°	750.0	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8
167.5°	757.3	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1
170°	761.4	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2
172.5°	764.2	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9
175°	767.7	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3
177.5°	768.6	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P332015

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1576.8	1579.3	1581.7	1582.8	1582.5	1582.3	1582.0	1581.8
5°	1568.5	1571.5	1574.6	1575.8	1575.2	1574.6	1574.0	1573.4
7.5°	1551.9	1554.6	1557.3	1558.5	1558.1	1557.8	1557.4	1557.0
10°	1536.6	1539.3	1542.1	1543.1	1542.5	1541.9	1541.3	1540.7
12.5°	1519.9	1521.9	1523.9	1524.7	1524.4	1524.0	1523.6	1523.3
15°	1489.7	1492.1	1494.6	1494.9	1493.1	1491.2	1489.4	1487.6
17.5°	1451.5	1453.2	1454.9	1455.4	1454.8	1454.1	1453.4	1452.8
20°	1423.3	1424.6	1425.8	1425.9	1425.0	1424.1	1423.2	1422.3
22.5°	1393.5	1394.4	1395.4	1395.3	1394.2	1393.0	1391.9	1390.7
25°	1343.9	1344.3	1344.6	1344.3	1343.3	1342.4	1341.5	1340.6
27.5°	1291.3	1291.5	1291.8	1291.3	1290.2	1289.0	1287.9	1286.7
30°	1254.9	1254.9	1254.9	1253.8	1251.7	1249.6	1247.5	1245.3
32.5°	1216.6	1215.0	1213.3	1211.8	1210.7	1209.5	1208.4	1207.2
35°	1154.6	1152.8	1151.0	1149.3	1147.8	1146.3	1144.8	1143.3
37.5°	1090.5	1088.3	1086.1	1084.5	1083.6	1082.6	1081.6	1080.7
40°	1048.6	1046.2	1043.8	1041.9	1040.7	1039.5	1038.3	1037.1
42.5°	1005.0	1002.6	1000.2	998.4	997.2	996.0	994.8	993.6
45°	940.0	936.4	932.8	930.2	928.7	927.2	925.7	924.1
47.5°	871.5	868.0	864.4	862.0	860.6	859.3	858.0	856.6
50°	826.3	823.0	819.6	817.1	815.3	813.4	811.6	809.8
52.5°	780.4	777.6	774.8	772.4	770.6	768.8	767.0	765.2
55°	710.6	707.3	704.0	701.5	700.0	698.5	697.0	695.5
57.5°	641.9	639.0	636.0	633.6	631.9	630.1	628.4	626.6
60°	593.4	590.7	588.0	585.9	584.3	582.8	581.3	579.8
62.5°	546.6	543.9	541.1	539.3	538.2	537.2	536.2	535.2
65°	477.0	474.5	472.1	470.5	469.6	468.7	467.7	466.8
67.5°	407.9	405.8	403.7	402.0	400.7	399.4	398.1	396.9
70°	363.2	361.1	359.0	357.2	355.7	354.2	352.7	351.1
72.5°	318.0	316.1	314.2	312.9	312.1	311.3	310.6	309.8
75°	252.9	251.3	249.8	248.6	247.7	246.8	245.9	245.0
77.5°	192.0	191.0	190.0	189.5	189.5	189.5	189.5	189.5
80°	153.2	152.9	152.6	152.4	152.4	152.4	152.4	152.4
82.5°	117.9	117.3	116.8	116.4	116.1	115.9	115.7	115.4
85°	66.8	66.2	65.6	65.3	65.3	65.3	65.3	65.3
87.5°	26.4	26.3	26.1	26.1	26.1	26.2	26.2	26.3
90°	14.7	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	16.2	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	19.5	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	20.4	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	20.8	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	31.2	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	80.0	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	196.0	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	248.9	244.7	240.5	229.3	211.2	193.1	175.0	156.8

TEST NUMBER: P332015

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	286.1	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	329.9	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	369.6	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	395.6	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.0	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	456.8	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	492.7	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.3	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	534.9	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	593.7	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.3	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.0	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.3	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.2	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	684.9	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.3	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	711.9	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	725.5	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	733.3	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	740.3	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	749.8	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	763.9	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	767.2	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	768.4	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)