

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332044-935

Luminaire Tested: **S123DIP-S1000D1195U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332044-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1195U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7268.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332044-935

CATALOG NUMBER: S123DIP-S1000D1195U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P332044-935

CATALOG NUMBER: S123DIP-S1000D1195U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46			41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39			34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33			29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	29			25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25			22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22			19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19			17
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17			15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16			14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941

TEST NUMBER: P332044-935

CATALOG NUMBER: S123DIP-S1000D1195U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.8
10°-20°	362.5	5.0
20°-30°	535.5	7.4
30°-40°	625.5	8.6
40°-50°	628.8	8.7
50°-60°	552.4	7.6
60°-70°	411.5	5.7
70°-80°	234.5	3.2
80°-90°	71.1	1.0
90°-100°	275.0	3.8
100°-110°	778.7	10.7
110°-120°	766.1	10.5
120°-130°	611.0	8.4
130°-140°	481.8	6.6
140°-150°	359.6	4.9
150°-160°	250.6	3.4
160°-170°	147.2	2.0
170°-180°	47.9	0.7
0°-30°	1026.3	14.1
0°-40°	1651.8	22.7
0°-60°	2833.0	39.0
0°-90°	3550.1	48.8
90°-120°	1819.8	25.0
90°-150°	3272.2	45.0
90°-180°	3718.0	51.2
0°-180°	7268.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	2	12	25	28	29	6
95°	34	110	593	173	116	37
105°	116	172	804	1406	1272	123
115°	205	256	615	1349	1548	203
125°	285	337	574	1040	1220	253
135°	334	399	566	857	989	258
145°	381	437	559	703	773	239
155°	433	467	541	615	641	199
165°	473	487	518	550	559	133
175°	493	494	497	504	503	47
180°	494	494	494	494	494	

TEST NUMBER: P332044-935

CATALOG NUMBER: S123DIP-S1000D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.8	24.5	24.4	24.3	24.1	24.0	24.5	24.9	25.2	25.7	25.2
90°	2.0	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0
92.5°	12.4	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1
95°	34.0	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1
97.5°	58.0	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5
100°	74.0	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4
102.5°	90.8	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4
105°	116.1	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4
107.5°	142.8	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6
110°	162.0	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3

TEST NUMBER: P332044-935

CATALOG NUMBER: S123DIP-S1000D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.7	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9
115°	205.1	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2
117.5°	230.5	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6
120°	248.1	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2
122.5°	263.3	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8
125°	285.1	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2
127.5°	301.7	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5
130°	312.1	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2
132.5°	320.1	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9
135°	334.2	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3
137.5°	347.3	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4
140°	356.1	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2
142.5°	365.8	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8
145°	381.2	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2
147.5°	396.7	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8
150°	407.2	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2
152.5°	417.6	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8
155°	433.2	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2
157.5°	445.6	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4
160°	455.1	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2
162.5°	462.4	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0
165°	473.2	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2
167.5°	481.4	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8
170°	486.2	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2
172.5°	489.4	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6
175°	493.2	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2
177.5°	495.0	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332044-935

CATALOG NUMBER: S123DIP-S1000D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	25.2	25.2	25.2	25.5	25.3	25.5	25.7	25.5
90°	25.0	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	84.2	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	360.2	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	897.7	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1179.4	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1273.1	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1300.5	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1221.6	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1146.4	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6

TEST NUMBER: P332044-935

CATALOG NUMBER: S123DIP-S1000D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1071.9	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	973.4	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	901.9	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	864.3	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	834.7	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	795.3	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	760.9	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	739.3	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	719.3	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	692.2	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	667.6	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	653.2	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	639.6	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	623.2	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	609.8	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	600.2	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	591.4	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	578.2	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	564.2	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	556.2	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	546.6	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	534.2	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	523.4	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	516.2	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	509.8	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	501.2	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	495.8	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)