

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923822

Luminaire Tested: DFN2DIP-TR4F0-090D050US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923822
REPORT IS A COMBINATION OF REPORTS P900397 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D050US940-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11891.0 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 125.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923822
CATALOG NUMBER: DFN2DIP-TR4F0-090D050US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P923822

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				67
1	102	97	93	90	96	92	88	85	81	79	76	72	70	68	63	62	61	56				56
2	93	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47				47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40				40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	37	34				34
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	40	36	33	30				30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26				26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23				23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	30	26	23	21				21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19				19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17				17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2481	2481	2481
5°	2485	2446	2463
10°	2465	2413	2429
15°	2428	2373	2377
20°	2380	2318	2324
25°	2331	2252	2262
30°	2270	2191	2183
35°	2212	2118	2100
40°	2141	2045	2021
45°	2070	1972	1941
50°	1992	1895	1847
55°	1911	1806	1761
60°	1819	1700	1662
65°	1719	1590	1546
70°	1591	1457	1421
75°	1415	1297	1305
80°	1202	1093	1085
85°	870	742	718

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2070 cd/sqm



TEST NUMBER: P923822

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.9	2.5
10°-20°	827.0	7.0
20°-30°	1215.3	10.2
30°-40°	1411.5	11.9
40°-50°	1409.7	11.9
50°-60°	1229.3	10.3
60°-70°	908.7	7.6
70°-80°	514.1	4.3
80°-90°	139.7	1.2
90°-100°	87.3	0.7
100°-110°	277.2	2.3
110°-120°	474.5	4.0
120°-130°	624.0	5.2
130°-140°	700.4	5.9
140°-150°	686.8	5.8
150°-160°	576.1	4.8
160°-170°	382.1	3.2
170°-180°	133.5	1.1
0°-30°	2336.2	19.6
0°-40°	3747.7	31.5
0°-60°	6386.7	53.7
0°-90°	7949.2	66.9
90°-120°	838.9	7.1
90°-150°	2850.1	24.0
90°-180°	3942.0	33.2
0°-180°	11891.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3123	3123	3123	3123	3123	
5°	3123	3111	3078	3102	3096	296
15°	2973	2955	2916	2928	2913	837
25°	2690	2666	2616	2621	2616	1238
35°	2321	2291	2243	2225	2210	1449
45°	1889	1868	1823	1790	1778	1458
55°	1430	1411	1375	1339	1324	1278
65°	964	946	916	889	874	953
75°	504	499	483	466	472	538
85°	123	120	117	108	105	137
90°	1	15	42	39	40	11
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	



TEST NUMBER: P923822

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3122.7	3122.7	3122.7	3122.7	3122.7
2.5°	3140.9	3125.9	3092.8	3122.7	3117.0
5°	3122.7	3110.9	3077.8	3101.7	3095.9
7.5°	3101.7	3083.9	3050.7	3075.0	3068.9
10°	3068.9	3047.9	3011.8	3035.7	3026.8
12.5°	3023.6	3005.8	2969.8	2984.7	2978.8
15°	2972.7	2954.9	2915.6	2927.8	2912.8
17.5°	2909.6	2891.7	2852.6	2867.6	2852.6
20°	2840.5	2822.6	2780.5	2789.4	2777.7
22.5°	2771.6	2744.6	2705.4	2705.4	2699.3
25°	2690.4	2666.5	2615.6	2621.3	2615.6
27.5°	2600.2	2579.2	2540.4	2531.5	2516.5
30°	2510.4	2486.2	2441.2	2432.3	2420.3
32.5°	2414.2	2396.4	2348.2	2330.1	2318.0
35°	2321.2	2291.2	2243.1	2225.0	2210.0
37.5°	2216.1	2189.0	2140.8	2119.9	2104.9
40°	2108.0	2083.8	2035.7	2008.9	1996.9
42.5°	2002.9	1978.7	1930.9	1900.7	1882.8
45°	1888.8	1867.9	1822.6	1789.8	1777.7
47.5°	1777.7	1756.7	1708.5	1675.4	1657.6
50°	1660.5	1645.5	1603.4	1561.4	1546.4
52.5°	1546.4	1525.4	1486.5	1453.4	1432.4
55°	1429.5	1411.3	1375.3	1339.3	1324.4
57.5°	1312.2	1297.3	1258.1	1222.1	1210.0
60°	1195.0	1183.2	1141.1	1108.0	1099.1
62.5°	1080.9	1059.9	1029.9	1000.1	987.9
65°	964.0	945.8	915.9	888.9	873.9
67.5°	843.9	828.7	801.8	780.9	768.7
70°	732.7	720.6	693.6	672.5	660.8
72.5°	618.7	606.5	591.6	570.6	561.7
75°	504.4	498.6	483.3	465.5	471.5
77.5°	402.3	390.3	384.2	375.3	366.4
80°	300.4	297.2	291.1	282.2	276.3
82.5°	204.2	204.2	201.3	189.2	189.2
85°	123.0	120.1	117.3	108.0	105.1
87.5°	54.1	48.1	42.1	33.2	30.0
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4



TEST NUMBER: P923822

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1



TEST NUMBER: P923822
 CATALOG NUMBER: DFN2DIP-TR4F0-090D050US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.85	12.88	12.65	13.71	14.71	11.42	12.45	12.21	13.27	14.28
	3H	13.52	14.45	14.33	15.28	16.32	13.05	13.98	13.86	14.81	15.85
	4H	14.12	15.00	14.94	15.83	16.88	13.64	14.52	14.47	15.36	16.41
	6H	14.53	15.34	15.37	16.18	17.24	14.05	14.86	14.89	15.71	16.77
	8H	14.63	15.41	15.48	16.27	17.33	14.16	14.93	15.01	15.80	16.86
	12H	14.69	15.43	15.54	16.28	17.37	14.21	14.95	15.06	15.80	16.89
4H	2H	12.33	13.21	13.16	14.05	15.10	11.99	12.87	12.82	13.70	14.75
	3H	14.21	14.95	15.06	15.82	16.88	13.82	14.55	14.66	15.42	16.49
	4H	14.93	15.60	15.79	16.47	17.56	14.53	15.20	15.39	16.07	17.16
	6H	15.46	16.04	16.33	16.93	18.02	15.05	15.63	15.92	16.52	17.61
	8H	15.61	16.15	16.49	17.04	18.15	15.20	15.74	16.08	16.63	17.74
	12H	15.69	16.18	16.59	17.09	18.20	15.27	15.76	16.17	16.67	17.78
8H	4H	15.14	15.68	16.02	16.57	17.68	14.78	15.32	15.66	16.21	17.32
	6H	15.78	16.23	16.69	17.16	18.27	15.42	15.87	16.32	16.80	17.90
	8H	16.01	16.40	16.92	17.32	18.45	15.64	16.03	16.55	16.96	18.08
	12H	16.14	16.49	17.06	17.41	18.59	15.76	16.11	16.68	17.02	18.20
12H	4H	15.14	15.63	16.03	16.53	17.65	14.79	15.27	15.68	16.18	17.29
	6H	15.81	16.21	16.73	17.13	18.26	15.46	15.86	16.38	16.78	17.91
	8H	16.06	16.41	16.98	17.33	18.51	15.71	16.06	16.62	16.97	18.15