

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331918-935

Luminaire Tested: **S123DIP-S560D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331918-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3127.9 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331918-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P331918-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36
5	70	58	50	44	66	55	48	42	49	43	38	43	39	35	38	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	32	28	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	39	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915

TEST NUMBER: P331918-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	2.3
10°-20°	204.0	6.5
20°-30°	301.4	9.6
30°-40°	352.0	11.3
40°-50°	353.9	11.3
50°-60°	310.9	9.9
60°-70°	231.6	7.4
70°-80°	132.0	4.2
80°-90°	39.0	1.2
90°-100°	83.7	2.7
100°-110°	236.9	7.6
110°-120°	233.0	7.4
120°-130°	185.8	5.9
130°-140°	146.5	4.7
140°-150°	109.4	3.5
150°-160°	76.2	2.4
160°-170°	44.8	1.4
170°-180°	14.6	0.5
0°-30°	577.6	18.5
0°-40°	929.7	29.7
0°-60°	1594.5	51.0
0°-90°	1997.1	63.8
90°-120°	553.5	17.7
90°-150°	995.3	31.8
90°-180°	1131.0	36.2
0°-180°	3127.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	4	8	8	9	3
95°	10	34	180	53	35	11
105°	35	52	245	428	387	38
115°	62	78	187	410	471	62
125°	87	102	175	316	371	77
135°	102	121	172	261	301	79
145°	116	133	170	214	235	73
155°	132	142	165	187	195	61
165°	144	148	158	167	170	41
175°	150	150	151	153	153	14
180°	150	150	150	150	150	

TEST NUMBER: P331918-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	13.6	13.3	13.2	13.0	12.8	12.9	13.0	13.1	13.1	12.9
90°	0.6	1.2	1.8	2.8	3.4	4.0	4.9	5.8	6.7	7.6	7.3
92.5°	3.8	5.6	8.2	10.5	13.1	17.6	25.6	38.7	51.5	46.8	35.3
95°	10.3	11.3	14.6	19.8	27.7	39.5	65.4	110.7	160.7	180.5	146.4
97.5°	17.7	17.9	20.6	25.1	32.9	45.7	70.4	121.5	204.7	279.7	299.1
100°	22.6	22.8	25.0	29.2	36.5	48.4	69.7	114.7	194.8	288.2	348.1
102.5°	27.6	28.2	30.0	34.1	40.6	51.6	70.7	108.8	180.1	272.3	350.5
105°	35.3	36.2	38.1	41.7	47.4	56.9	73.4	104.7	162.2	244.6	331.9
107.5°	43.5	44.3	46.1	49.7	55.1	63.9	78.4	104.4	150.8	220.2	299.5
110°	49.2	50.2	51.7	55.1	60.3	68.8	82.5	105.6	146.4	206.3	279.1

TEST NUMBER: P331918-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.7	55.5	57.1	60.4	65.6	73.9	86.6	108.1	143.9	197.0	261.2
115°	62.3	63.6	65.4	68.4	73.6	81.9	93.4	111.9	143.0	187.1	239.8
117.5°	70.1	71.5	73.0	75.9	81.6	89.2	100.7	117.2	143.5	181.2	226.8
120°	75.4	76.4	77.9	80.9	86.7	94.3	105.3	121.1	144.6	178.6	220.0
122.5°	80.1	81.0	82.5	85.8	91.4	99.4	110.1	124.8	146.2	176.9	214.4
125°	86.7	87.3	89.1	92.5	98.2	106.5	117.2	130.5	148.8	174.6	207.2
127.5°	91.8	92.6	95.0	98.3	104.7	113.0	123.2	135.3	151.7	173.6	200.9
130°	95.0	95.8	98.6	102.2	108.7	116.8	126.9	138.4	153.7	172.8	197.4
132.5°	97.4	98.5	101.5	105.9	112.3	120.3	130.0	141.4	155.2	172.5	194.3
135°	101.6	102.8	106.2	110.7	117.2	125.4	134.7	145.2	157.3	172.2	190.2
137.5°	105.6	106.9	110.2	115.0	121.4	129.0	138.1	147.9	158.8	171.5	186.6
140°	108.3	109.9	112.9	117.8	123.8	131.5	140.3	149.4	159.7	171.3	184.3
142.5°	111.2	112.5	115.8	120.2	126.3	133.4	142.0	150.8	160.5	170.8	182.4
145°	115.9	116.8	119.6	124.2	129.3	136.3	144.2	152.4	160.9	170.0	179.8
147.5°	120.7	121.2	123.9	127.9	132.9	138.8	146.0	153.4	160.9	168.9	177.3
150°	123.8	124.2	126.6	130.5	134.7	140.3	147.2	153.7	160.9	168.0	175.6
152.5°	127.0	127.1	129.5	132.9	136.7	142.0	148.0	154.1	160.2	166.8	173.6
155°	131.7	131.7	133.5	136.6	140.0	144.2	149.4	154.3	159.5	164.6	170.7
157.5°	135.5	135.8	137.2	139.9	142.8	146.0	150.2	154.5	158.4	162.7	167.4
160°	138.4	138.4	139.7	142.1	144.2	147.2	150.9	154.5	157.9	161.3	165.2
162.5°	140.6	140.6	141.6	143.5	145.4	148.0	151.2	154.3	157.0	159.8	163.0
165°	143.9	143.6	144.2	145.8	147.0	149.1	151.5	153.7	155.5	157.6	160.1
167.5°	146.4	146.0	146.4	147.5	148.4	149.7	151.4	153.2	154.0	155.4	157.2
170°	147.8	147.2	147.6	148.4	149.1	149.7	151.2	152.4	153.1	153.9	155.5
172.5°	148.9	148.4	148.5	149.2	149.6	149.9	151.2	152.2	152.3	152.7	153.8
175°	150.0	149.7	149.4	150.0	150.0	150.3	150.9	151.5	151.2	151.2	151.8
177.5°	150.6	150.3	150.1	150.3	150.3	150.3	150.6	151.0	150.6	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P331918-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	12.9	12.8	12.7	12.8	12.7	12.8	12.9	12.8
90°	7.6	7.9	8.2	8.8	8.5	8.8	9.1	8.8
92.5°	25.7	20.3	17.9	16.4	15.8	14.9	15.2	14.6
95°	109.5	74.2	58.1	47.2	41.4	38.7	36.5	35.3
97.5°	273.0	218.7	179.4	143.1	120.6	106.9	98.7	96.1
100°	358.7	334.1	298.5	255.3	224.5	202.3	190.5	190.8
102.5°	387.2	386.4	365.7	338.3	314.4	296.8	286.9	279.8
105°	395.5	425.9	431.7	423.9	409.8	398.3	388.6	387.0
107.5°	371.5	420.9	447.6	458.5	458.7	454.8	451.5	448.8
110°	348.7	404.7	443.0	464.3	472.9	475.3	474.7	474.1

TEST NUMBER: P331918-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.1	383.2	426.2	453.6	469.2	476.7	479.1	479.1
115°	296.0	349.0	393.7	426.9	449.7	463.0	469.2	470.7
117.5°	274.3	320.0	360.2	393.8	417.7	433.0	441.7	443.8
120°	262.9	303.9	340.4	371.2	395.2	412.2	419.6	421.4
122.5°	253.9	291.0	324.9	353.4	374.8	390.1	398.1	400.5
125°	241.9	275.1	304.3	328.6	348.1	361.4	369.1	371.2
127.5°	231.4	261.0	287.3	309.5	326.8	338.3	345.2	347.1
130°	224.8	252.3	276.9	297.6	313.7	324.7	331.1	333.5
132.5°	218.8	243.9	266.9	286.6	301.8	312.7	318.4	320.1
135°	210.5	232.1	251.9	269.2	284.2	293.3	298.8	300.9
137.5°	203.0	220.8	237.8	252.9	265.4	274.7	279.2	280.7
140°	198.7	214.2	228.8	241.9	253.5	262.0	266.8	266.6
142.5°	194.6	207.8	220.5	231.9	241.8	249.3	253.7	253.4
145°	189.6	199.6	209.3	218.2	225.8	232.1	234.6	235.2
147.5°	185.5	193.5	201.3	207.6	213.4	217.7	220.0	220.2
150°	182.5	189.6	196.0	201.7	206.3	209.7	211.5	211.5
152.5°	179.9	185.9	191.6	196.4	199.9	203.0	204.1	204.1
155°	175.9	180.7	185.3	188.9	191.7	194.2	194.8	195.0
157.5°	171.6	175.6	179.2	182.1	184.4	186.2	186.8	186.7
160°	169.2	172.5	175.6	177.7	179.8	181.7	181.7	181.3
162.5°	166.3	169.1	171.9	173.8	175.2	176.8	176.8	176.5
165°	162.5	164.3	166.4	168.0	169.2	170.4	170.0	170.0
167.5°	159.2	160.6	161.8	162.9	163.4	164.3	164.0	164.0
170°	157.0	157.9	159.1	159.7	160.1	160.7	160.3	160.3
172.5°	155.1	155.8	156.7	157.0	157.1	157.7	157.2	157.0
175°	152.4	152.7	153.3	153.3	153.3	153.7	153.3	153.1
177.5°	150.8	151.0	151.3	151.3	151.0	151.3	150.8	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

(END OF REPORT)