

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332033-840

Luminaire Tested: **S123DIP-S1000D1025U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332033-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8300.7 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332033-840

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot



TEST NUMBER: P332033-840

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50		
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47	42		
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35		
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34	30		
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29	26		
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22		
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19		
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17		
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15		
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139

TEST NUMBER: P332033-840

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	1.8
10°-20°	425.2	5.1
20°-30°	628.0	7.6
30°-40°	733.6	8.8
40°-50°	737.6	8.9
50°-60°	647.9	7.8
60°-70°	482.7	5.8
70°-80°	275.0	3.3
80°-90°	82.7	1.0
90°-100°	49.3	0.6
100°-110°	235.1	2.8
110°-120°	564.7	6.8
120°-130°	719.1	8.7
130°-140°	768.3	9.3
140°-150°	718.5	8.7
150°-160°	579.5	7.0
160°-170°	374.0	4.5
170°-180°	128.9	1.6
0°-30°	1203.8	14.5
0°-40°	1937.4	23.3
0°-60°	3322.8	40.0
0°-90°	4163.3	50.2
90°-120°	849.1	10.2
90°-150°	3055.0	36.8
90°-180°	4137.0	49.8
0°-180°	8300.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	1	11	24	28	30	7
95°	62	23	31	38	38	76
105°	300	306	221	52	44	318
115°	564	570	579	588	593	556
125°	794	802	806	808	810	709
135°	989	995	999	1002	999	761
145°	1141	1148	1150	1152	1152	714
155°	1257	1255	1256	1260	1255	579
165°	1326	1323	1322	1329	1322	374
175°	1357	1352	1353	1359	1352	129
180°	1357	1357	1357	1357	1357	

TEST NUMBER: P332033-840

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.8	28.5	28.2	28.0	27.7	27.7	28.0	28.4	28.7	29.0	29.0
90°	1.0	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0
92.5°	18.8	18.1	17.5	16.9	16.3	17.1	19.2	21.4	23.6	25.9	27.3
95°	61.5	52.3	43.1	33.9	24.7	21.4	23.8	26.4	28.8	31.2	32.8
97.5°	123.6	119.5	115.3	111.2	107.0	96.9	80.9	64.7	48.6	32.4	34.2
100°	170.4	174.8	179.4	183.8	188.2	173.0	138.0	103.1	68.2	33.2	35.0
102.5°	223.6	226.8	230.0	233.3	236.5	219.0	180.9	142.7	104.5	66.3	60.8
105°	300.3	302.9	305.3	307.8	310.2	301.3	281.2	261.1	241.0	220.8	181.1
107.5°	381.4	383.4	385.4	387.4	389.3	391.9	395.1	398.3	401.4	404.7	375.6
110°	435.5	437.3	439.0	440.8	442.6	444.7	447.2	449.7	452.1	454.6	447.2

TEST NUMBER: P332033-840

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.1	488.7	490.3	491.9	493.5	495.5	498.1	500.5	502.9	505.4	505.5
115°	563.5	564.8	566.1	567.5	568.9	570.6	572.5	574.5	576.5	578.6	580.9
117.5°	637.4	639.1	640.8	642.5	644.1	645.4	646.4	647.5	648.5	649.5	651.4
120°	683.4	685.4	687.4	689.4	691.5	692.9	693.5	694.2	694.9	695.5	697.3
122.5°	730.2	731.8	733.5	735.2	736.8	738.1	738.9	739.8	740.6	741.4	742.8
125°	794.3	796.1	797.9	799.7	801.4	802.8	803.8	804.6	805.5	806.4	806.9
127.5°	856.4	858.2	860.0	861.7	863.5	864.9	866.1	867.2	868.2	869.3	870.0
130°	895.1	896.9	898.7	900.5	902.3	903.6	904.5	905.4	906.3	907.2	908.1
132.5°	932.2	934.0	935.7	937.6	939.4	940.6	941.3	942.0	942.8	943.5	944.4
135°	988.9	990.2	991.5	992.9	994.2	995.3	996.2	997.1	998.0	999.0	999.6
137.5°	1037.2	1038.9	1040.7	1042.4	1044.0	1045.1	1045.6	1046.1	1046.6	1047.1	1048.1
140°	1069.4	1070.9	1072.2	1073.5	1074.9	1075.9	1076.5	1077.2	1077.9	1078.5	1079.4
142.5°	1099.3	1100.7	1102.0	1103.4	1104.7	1105.7	1106.4	1107.0	1107.7	1108.4	1109.1
145°	1141.0	1142.7	1144.2	1145.8	1147.3	1148.3	1148.8	1149.2	1149.6	1150.1	1150.5
147.5°	1180.3	1181.4	1182.5	1183.5	1184.5	1185.2	1185.7	1186.1	1186.6	1187.0	1187.5
150°	1204.6	1205.3	1205.9	1206.6	1207.2	1207.8	1208.2	1208.7	1209.1	1209.6	1210.0
152.5°	1226.3	1226.7	1227.0	1227.3	1227.6	1227.9	1228.1	1228.4	1228.7	1228.9	1229.7
155°	1257.0	1256.5	1256.1	1255.7	1255.2	1255.1	1255.3	1255.5	1255.8	1256.0	1257.1
157.5°	1280.7	1280.7	1280.7	1280.6	1280.6	1280.4	1280.2	1280.0	1279.8	1279.5	1280.9
160°	1295.3	1295.1	1294.8	1294.6	1294.3	1294.1	1293.9	1293.7	1293.4	1293.2	1294.6
162.5°	1309.0	1308.4	1307.8	1307.3	1306.7	1306.3	1306.1	1305.8	1305.6	1305.4	1306.9
165°	1325.5	1324.8	1324.1	1323.5	1322.8	1322.4	1322.1	1321.9	1321.7	1321.5	1323.2
167.5°	1338.4	1337.6	1336.7	1335.7	1334.8	1334.3	1334.3	1334.3	1334.3	1334.3	1336.2
170°	1345.6	1344.7	1343.9	1343.0	1342.1	1341.6	1341.6	1341.6	1341.6	1341.6	1343.4
172.5°	1350.5	1349.5	1348.4	1347.3	1346.3	1345.7	1345.9	1346.2	1346.3	1346.5	1348.3
175°	1356.8	1355.6	1354.5	1353.4	1352.3	1351.8	1352.0	1352.3	1352.5	1352.7	1354.3
177.5°	1358.4	1357.5	1356.6	1355.6	1354.8	1354.4	1354.6	1354.8	1354.9	1355.1	1356.6
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8

TEST NUMBER: P332033-840

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	28.9	28.9	28.8	28.8	28.9	29.0	29.1	29.2
90°	26.0	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	28.7	30.1	31.5	32.4	32.6	32.9	33.2	33.4
95°	34.3	36.0	37.6	38.3	38.3	38.3	38.3	38.3
97.5°	36.1	37.9	39.6	40.6	40.9	41.1	41.3	41.5
100°	36.9	38.7	40.4	41.4	41.7	41.9	42.1	42.3
102.5°	55.2	49.7	44.1	41.5	41.9	42.3	42.7	43.1
105°	141.5	101.8	62.2	42.5	43.0	43.4	43.9	44.3
107.5°	346.5	317.4	288.3	258.8	228.9	199.0	169.2	139.3
110°	439.8	432.4	425.1	405.4	373.2	341.2	309.2	277.2

TEST NUMBER: P332033-840

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	505.6	505.8	505.9	502.6	495.8	489.1	482.3	475.5
115°	583.1	585.3	587.5	589.2	590.0	590.9	591.8	592.7
117.5°	653.2	654.9	656.7	657.7	657.9	658.0	658.2	658.4
120°	699.1	700.8	702.7	703.6	703.6	703.6	703.6	703.6
122.5°	744.0	745.3	746.5	747.2	747.4	747.6	747.7	747.9
125°	807.3	807.7	808.2	808.6	809.1	809.5	810.0	810.4
127.5°	870.7	871.4	872.1	872.3	871.8	871.4	870.9	870.5
130°	909.0	909.9	910.8	911.0	910.6	910.1	909.7	909.2
132.5°	945.2	946.1	947.1	947.2	946.5	945.9	945.3	944.7
135°	1000.3	1001.0	1001.6	1001.6	1001.0	1000.3	999.6	999.0
137.5°	1049.2	1050.4	1051.4	1051.7	1051.3	1050.9	1050.4	1050.0
140°	1080.4	1081.3	1082.2	1082.4	1081.9	1081.5	1081.1	1080.6
142.5°	1109.8	1110.5	1111.3	1111.3	1110.6	1110.0	1109.4	1108.8
145°	1151.0	1151.4	1152.0	1152.2	1152.2	1152.2	1152.2	1152.2
147.5°	1187.9	1188.3	1188.8	1188.5	1187.5	1186.5	1185.4	1184.4
150°	1210.5	1210.9	1211.4	1211.2	1210.6	1209.9	1209.2	1208.6
152.5°	1230.5	1231.3	1232.1	1232.0	1231.0	1230.0	1229.0	1227.9
155°	1258.2	1259.3	1260.4	1260.3	1259.0	1257.7	1256.3	1255.0
157.5°	1282.2	1283.5	1285.0	1284.8	1282.9	1281.2	1279.5	1277.8
160°	1296.0	1297.3	1298.6	1298.5	1297.0	1295.4	1293.8	1292.2
162.5°	1308.4	1309.9	1311.4	1311.5	1310.1	1308.7	1307.4	1306.0
165°	1325.0	1326.9	1328.7	1328.8	1327.2	1325.6	1324.0	1322.5
167.5°	1338.0	1339.8	1341.5	1341.5	1339.8	1338.0	1336.2	1334.3
170°	1345.2	1347.1	1348.8	1348.8	1347.1	1345.2	1343.4	1341.6
172.5°	1350.1	1351.8	1353.6	1353.5	1351.6	1349.6	1347.7	1345.6
175°	1355.8	1357.5	1359.0	1358.9	1357.1	1355.3	1353.5	1351.7
177.5°	1358.0	1359.5	1360.9	1360.7	1358.9	1357.2	1355.3	1353.5
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8

(END OF REPORT)