

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332008-840

Luminaire Tested: **S123DIP-S1000D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332008-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5487.2 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332008-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P332008-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	80	80	76
1	103	99	95	91	98	94	91	87	86	83	80	78	76	74	70	69	67	67	67	64
2	94	86	80	74	89	82	77	72	75	70	66	68	65	61	62	59	57	57	57	53
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	48	48	45
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	42	42	42	39
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	36	36	34
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	36	32	32	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	28	28	26
8	58	45	37	31	55	43	35	30	40	33	29	37	31	27	34	29	25	25	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	23	23	21
10	50	38	30	25	48	36	29	24	34	28	23	31	26	22	29	24	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139

TEST NUMBER: P332008-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	2.7
10°-20°	425.2	7.7
20°-30°	628.0	11.4
30°-40°	733.6	13.4
40°-50°	737.6	13.4
50°-60°	647.9	11.8
60°-70°	482.7	8.8
70°-80°	275.0	5.0
80°-90°	80.3	1.5
90°-100°	98.1	1.8
100°-110°	277.8	5.1
110°-120°	273.3	5.0
120°-130°	218.0	4.0
130°-140°	171.9	3.1
140°-150°	128.3	2.3
150°-160°	89.4	1.6
160°-170°	52.5	1.0
170°-180°	17.1	0.3
0°-30°	1203.8	21.9
0°-40°	1937.4	35.3
0°-60°	3322.8	60.6
0°-90°	4160.8	75.8
90°-120°	649.2	11.8
90°-150°	1167.3	21.3
90°-180°	1326.0	24.2
0°-180°	5487.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	1	4	9	10	10	5
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	219	481	552	72
125°	102	120	205	371	435	90
135°	119	142	202	306	353	92
145°	136	156	199	251	276	85
155°	154	167	193	219	229	71
165°	169	174	185	196	199	48
175°	176	176	177	180	180	17
180°	176	176	176	176	176	

TEST NUMBER: P332008-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.8	28.2	27.6	27.1	26.5	26.1	26.1	26.1	26.1	26.0	25.7
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.8	6.8	7.9	8.9	8.6
92.5°	4.4	6.6	9.6	12.3	15.3	20.6	30.0	45.3	60.4	54.8	41.4
95°	12.1	13.2	17.2	23.2	32.5	46.4	76.7	129.9	188.4	211.7	171.7
97.5°	20.7	21.0	24.1	29.4	38.6	53.6	82.6	142.5	240.1	328.0	350.8
100°	26.5	26.8	29.3	34.2	42.8	56.8	81.7	134.5	228.4	338.0	408.3
102.5°	32.4	33.0	35.2	40.0	47.7	60.5	82.9	127.6	211.3	319.4	411.1
105°	41.4	42.5	44.6	48.9	55.6	66.8	86.0	122.8	190.3	286.9	389.3
107.5°	51.0	52.0	54.1	58.3	64.6	74.9	91.9	122.4	176.8	258.2	351.2
110°	57.8	58.9	60.7	64.6	70.7	80.7	96.7	123.8	171.7	242.0	327.3

TEST NUMBER: P332008-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.1	65.1	67.0	70.9	77.0	86.6	101.6	126.7	168.7	231.1	306.4
115°	73.1	74.6	76.7	80.3	86.3	96.0	109.6	131.3	167.7	219.4	281.2
117.5°	82.2	83.8	85.6	89.0	95.7	104.6	118.1	137.4	168.3	212.6	266.0
120°	88.5	89.6	91.4	94.9	101.7	110.6	123.5	142.0	169.6	209.4	258.0
122.5°	93.9	95.0	96.7	100.7	107.1	116.6	129.2	146.3	171.5	207.5	251.5
125°	101.7	102.4	104.5	108.5	115.2	124.9	137.4	153.1	174.5	204.8	243.1
127.5°	107.7	108.7	111.4	115.3	122.8	132.5	144.5	158.6	177.9	203.6	235.6
130°	111.4	112.4	115.6	119.9	127.4	137.0	148.9	162.4	180.3	202.7	231.6
132.5°	114.2	115.5	119.1	124.2	131.7	141.1	152.5	165.8	182.0	202.4	227.9
135°	119.2	120.6	124.5	129.9	137.4	147.0	158.0	170.3	184.5	202.0	223.1
137.5°	123.9	125.4	129.3	134.9	142.4	151.3	162.0	173.5	186.2	201.2	218.8
140°	127.0	128.9	132.4	138.1	145.2	154.2	164.5	175.2	187.3	201.0	216.2
142.5°	130.5	132.0	135.8	141.0	148.1	156.4	166.5	176.9	188.2	200.4	214.0
145°	135.9	137.0	140.3	145.6	151.7	159.9	169.2	178.7	188.7	199.4	210.9
147.5°	141.6	142.2	145.3	150.0	155.8	162.8	171.3	180.0	188.7	198.1	207.9
150°	145.2	145.6	148.5	153.1	158.0	164.5	172.7	180.3	188.7	197.0	205.9
152.5°	149.0	149.1	151.9	155.9	160.4	166.5	173.6	180.8	187.9	195.6	203.6
155°	154.5	154.5	156.6	160.3	164.2	169.2	175.2	181.0	187.0	193.1	200.2
157.5°	159.0	159.3	161.0	164.1	167.4	171.3	176.1	181.3	185.8	190.9	196.3
160°	162.4	162.4	163.8	166.6	169.2	172.7	177.0	181.3	185.2	189.1	193.8
162.5°	164.9	164.9	166.1	168.3	170.6	173.6	177.3	181.0	184.1	187.4	191.2
165°	168.7	168.4	169.2	171.0	172.4	174.9	177.7	180.3	182.4	184.9	187.7
167.5°	171.7	171.3	171.7	173.0	174.0	175.6	177.6	179.7	180.7	182.3	184.4
170°	173.4	172.7	173.1	174.1	174.9	175.6	177.3	178.7	179.6	180.6	182.4
172.5°	174.6	174.1	174.2	175.0	175.4	175.8	177.3	178.5	178.6	179.2	180.4
175°	175.9	175.6	175.2	175.9	175.9	176.3	177.0	177.7	177.3	177.3	178.0
177.5°	176.6	176.3	176.0	176.3	176.3	176.3	176.6	177.1	176.6	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P332008-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	25.4	25.3	25.1	25.1	25.0	25.1	25.2	25.1
90°	8.9	9.3	9.6	10.3	10.0	10.3	10.7	10.3
92.5°	30.1	23.8	21.0	19.2	18.6	17.5	17.9	17.2
95°	128.5	87.1	68.2	55.3	48.6	45.3	42.8	41.4
97.5°	320.2	256.5	210.5	167.8	141.5	125.4	115.7	112.7
100°	420.7	391.8	350.1	299.4	263.4	237.3	223.4	223.8
102.5°	454.1	453.2	428.9	396.8	368.7	348.1	336.5	328.2
105°	463.9	499.6	506.3	497.2	480.7	467.2	455.8	453.9
107.5°	435.8	493.7	525.0	537.8	538.1	533.4	529.6	526.3
110°	409.0	474.6	519.6	544.6	554.6	557.4	556.7	556.0

TEST NUMBER: P332008-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.4	449.5	499.9	532.0	550.3	559.2	561.9	562.0
115°	347.2	409.3	461.8	500.7	527.5	543.1	550.3	552.1
117.5°	321.7	375.4	422.4	461.9	489.9	507.9	518.1	520.5
120°	308.3	356.5	399.3	435.4	463.5	483.5	492.1	494.2
122.5°	297.8	341.3	381.0	414.5	439.6	457.6	467.0	469.7
125°	283.7	322.7	356.9	385.5	408.3	423.9	432.9	435.4
127.5°	271.5	306.1	337.0	363.0	383.3	396.8	404.9	407.1
130°	263.7	295.9	324.8	349.0	367.9	380.8	388.3	391.1
132.5°	256.6	286.1	313.1	336.2	354.0	366.8	373.4	375.5
135°	246.9	272.3	295.5	315.8	333.4	344.1	350.4	352.9
137.5°	238.1	258.9	278.9	296.6	311.2	322.1	327.5	329.2
140°	233.1	251.3	268.3	283.7	297.3	307.3	313.0	312.7
142.5°	228.2	243.8	258.6	272.0	283.6	292.5	297.5	297.2
145°	222.4	234.1	245.5	255.9	264.8	272.3	275.2	275.9
147.5°	217.5	226.9	236.1	243.5	250.2	255.3	258.0	258.3
150°	214.1	222.4	229.8	236.6	242.0	245.9	248.0	248.0
152.5°	211.0	218.0	224.7	230.4	234.5	238.1	239.4	239.4
155°	206.3	212.0	217.3	221.6	224.8	227.7	228.4	228.7
157.5°	201.3	206.0	210.2	213.6	216.3	218.4	219.0	218.9
160°	198.4	202.4	205.9	208.4	210.9	213.1	213.1	212.7
162.5°	195.0	198.3	201.7	203.9	205.5	207.3	207.3	207.0
165°	190.6	192.7	195.2	197.0	198.4	199.9	199.4	199.4
167.5°	186.7	188.3	189.8	191.1	191.7	192.7	192.4	192.4
170°	184.1	185.2	186.6	187.3	187.7	188.4	188.0	188.0
172.5°	181.9	182.7	183.8	184.2	184.3	185.0	184.4	184.1
175°	178.7	179.2	179.9	179.9	179.9	180.3	179.9	179.6
177.5°	176.8	177.1	177.4	177.4	177.1	177.4	176.8	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)