

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332089-840

Luminaire Tested: **S123DIP-S1165D1195U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332089-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9169.1 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332089-840

CATALOG NUMBER: S123DIP-S1165D1195U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P332089-840

CATALOG NUMBER: S123DIP-S1165D1195U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52		52
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49	44		44
2	89	82	76	71	82	76	71	66	65	61	57	55	52	49	45	43	41	37		37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35	31		31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27		27
5	68	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26	23		23
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23	20		20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18		18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	18	16		16
9	50	38	31	25	47	36	29	24	31	26	22	27	22	19	23	19	17	15		15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13		13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411

TEST NUMBER: P332089-840

CATALOG NUMBER: S123DIP-S1165D1195U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	1.9
10°-20°	491.0	5.4
20°-30°	725.3	7.9
30°-40°	847.3	9.2
40°-50°	851.8	9.3
50°-60°	748.3	8.2
60°-70°	557.5	6.1
70°-80°	317.6	3.5
80°-90°	95.6	1.0
90°-100°	322.6	3.5
100°-110°	913.4	10.0
110°-120°	898.5	9.8
120°-130°	716.7	7.8
130°-140°	565.1	6.2
140°-150°	421.7	4.6
150°-160°	294.0	3.2
160°-170°	172.7	1.9
170°-180°	56.2	0.6
0°-30°	1390.3	15.2
0°-40°	2237.6	24.4
0°-60°	3837.7	41.9
0°-90°	4808.4	52.4
90°-120°	2134.4	23.3
90°-150°	3837.9	41.9
90°-180°	4361.0	47.6
0°-180°	9169.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	2	14	29	33	34	7
95°	40	130	696	203	136	43
105°	136	201	943	1650	1492	145
115°	240	300	722	1582	1815	238
125°	334	395	674	1220	1432	297
135°	392	468	664	1005	1160	303
145°	447	512	656	824	907	280
155°	508	548	635	722	752	234
165°	555	571	608	645	656	156
175°	578	579	583	591	590	55
180°	580	580	580	580	580	

TEST NUMBER: P332089-840

CATALOG NUMBER: S123DIP-S1165D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.5	33.1	32.7	32.6	32.2	32.1	32.5	32.9	33.4	33.8	33.3
90°	2.3	4.6	7.1	10.6	12.9	15.2	18.8	22.3	25.9	29.3	28.2
92.5°	14.5	21.6	31.4	40.6	50.5	67.9	98.6	149.1	198.5	180.5	136.1
95°	39.9	43.4	56.4	76.2	106.7	152.5	252.3	427.1	619.6	695.8	564.3
97.5°	68.1	69.2	79.3	96.6	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6
100°	86.8	88.0	96.2	112.6	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3
102.5°	106.5	108.7	115.9	131.4	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6
105°	136.1	139.7	146.6	160.8	183.0	219.4	282.8	403.6	625.4	943.3	1280.1
107.5°	167.5	171.1	177.8	191.7	212.6	246.4	302.1	402.4	581.3	849.0	1154.8
110°	190.1	193.6	199.4	212.4	232.3	265.2	318.0	407.2	564.3	795.5	1075.9

TEST NUMBER: P332089-840

CATALOG NUMBER: S123DIP-S1165D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.8	214.3	220.2	233.0	253.0	284.9	334.0	416.6	555.0	759.8	1007.4
115°	240.5	245.2	252.3	264.0	284.0	315.6	360.2	431.8	551.5	721.5	924.5
117.5°	270.3	275.7	281.6	292.4	314.7	344.1	388.1	451.9	553.6	699.0	874.5
120°	290.9	294.5	300.3	312.1	334.4	363.8	406.0	467.0	557.3	688.7	848.3
122.5°	308.8	312.4	318.2	330.8	352.2	383.4	424.7	481.1	563.9	682.2	826.7
125°	334.4	336.8	343.8	356.7	379.0	410.6	451.7	503.3	573.7	673.5	799.0
127.5°	353.9	357.4	366.1	379.2	403.8	435.6	475.1	521.7	585.0	669.2	774.7
130°	366.1	369.6	380.1	394.3	418.9	450.5	489.3	533.8	592.5	666.4	761.4
132.5°	375.5	379.9	391.4	408.3	432.9	463.7	501.5	545.1	598.1	665.5	749.3
135°	391.9	396.6	409.5	427.1	451.7	483.4	519.8	559.7	606.6	664.1	733.4
137.5°	407.4	412.3	425.0	443.7	468.2	497.5	532.4	570.5	612.3	661.5	719.4
140°	417.7	423.5	435.3	454.0	477.6	506.9	540.9	576.1	616.0	660.6	711.0
142.5°	429.0	433.9	446.6	463.4	487.0	514.4	547.4	581.7	618.8	658.7	703.5
145°	447.1	450.5	461.1	478.7	498.7	525.6	556.1	587.8	620.7	655.9	693.5
147.5°	465.3	467.5	477.8	493.0	512.3	535.2	563.2	591.6	620.7	651.5	683.6
150°	477.6	478.7	488.1	503.3	519.8	540.9	567.8	592.5	620.7	647.6	677.0
152.5°	489.8	490.0	499.4	512.7	527.3	547.4	570.7	594.4	617.8	643.0	669.5
155°	508.1	508.1	515.1	526.8	539.7	556.1	576.1	594.9	614.8	634.8	658.2
157.5°	522.6	523.5	529.2	539.5	550.5	563.2	579.2	596.0	610.9	627.5	645.5
160°	533.8	533.8	538.6	548.0	556.1	567.8	582.0	596.0	608.9	621.9	637.1
162.5°	542.3	542.3	546.0	553.6	560.9	570.7	582.9	595.1	605.2	616.2	628.6
165°	555.0	553.8	556.1	562.0	566.7	574.9	584.3	592.5	599.6	607.7	617.1
167.5°	564.6	563.2	564.3	568.9	572.1	577.2	584.1	590.7	593.9	599.4	606.1
170°	570.3	567.8	569.1	572.6	574.9	577.2	583.1	587.8	590.2	593.7	599.6
172.5°	574.0	572.6	572.8	575.4	576.8	578.2	583.1	586.9	587.3	589.0	593.0
175°	578.5	577.2	576.1	578.5	578.5	579.7	582.0	584.3	583.1	583.1	585.5
177.5°	580.6	579.7	578.7	579.7	579.7	579.7	580.6	582.4	580.6	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

TEST NUMBER: P332089-840

CATALOG NUMBER: S123DIP-S1165D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	33.2	33.2	33.1	33.4	33.2	33.4	33.7	33.4
90°	29.3	30.5	31.7	34.0	32.8	34.0	35.2	34.0
92.5°	98.8	78.4	69.2	63.1	61.0	57.5	58.7	56.6
95°	422.4	286.3	224.1	181.9	159.6	149.1	140.8	136.1
97.5°	1052.9	843.3	692.1	551.7	465.1	412.3	380.6	370.5
100°	1383.3	1288.3	1151.0	984.4	865.9	780.2	734.5	735.7
102.5°	1493.2	1490.1	1410.1	1304.4	1212.2	1144.5	1106.2	1079.2
105°	1525.3	1642.6	1665.0	1634.5	1580.4	1535.9	1498.3	1492.5
107.5°	1432.8	1623.4	1726.2	1768.0	1768.9	1753.8	1741.2	1730.4
110°	1344.6	1560.5	1708.4	1790.5	1823.3	1832.7	1830.4	1828.1

TEST NUMBER: P332089-840

CATALOG NUMBER: S123DIP-S1165D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1257.3	1477.9	1643.6	1749.2	1809.3	1838.4	1847.2	1847.8
115°	1141.7	1345.7	1518.2	1646.2	1734.1	1785.7	1809.3	1815.1
117.5°	1057.8	1234.1	1389.0	1518.7	1610.5	1669.6	1703.4	1711.4
120°	1013.7	1172.2	1312.9	1431.5	1524.1	1589.8	1618.0	1625.1
122.5°	979.0	1122.4	1252.8	1362.9	1445.3	1504.4	1535.4	1544.3
125°	932.8	1060.7	1173.3	1267.2	1342.3	1393.9	1423.2	1431.5
127.5°	892.4	1006.4	1108.0	1193.5	1260.4	1304.4	1331.0	1338.5
130°	867.1	972.7	1067.7	1147.5	1209.7	1251.9	1276.6	1286.0
132.5°	843.6	940.8	1029.3	1105.3	1163.7	1205.9	1227.8	1234.4
135°	811.9	895.2	971.5	1038.3	1095.9	1131.0	1152.2	1160.4
137.5°	783.0	851.3	917.1	975.0	1023.4	1059.0	1076.8	1082.3
140°	766.2	826.0	882.3	932.8	977.3	1010.3	1029.0	1027.8
142.5°	750.2	801.6	850.4	894.3	932.3	961.4	978.3	977.1
145°	730.9	769.7	807.3	841.2	870.6	895.2	904.6	907.0
147.5°	715.3	746.0	776.3	800.4	822.7	839.4	848.3	849.2
150°	704.0	730.9	755.6	777.9	795.5	808.4	815.5	815.5
152.5°	693.7	716.9	738.7	757.3	771.1	783.0	787.3	787.3
155°	678.1	696.9	714.6	728.6	739.2	748.6	750.9	752.0
157.5°	661.8	677.5	691.1	702.1	711.2	718.3	720.1	719.9
160°	652.4	665.3	677.0	685.2	693.5	700.4	700.4	699.3
162.5°	641.1	652.2	662.9	670.1	675.6	681.7	681.7	680.5
165°	626.5	633.6	641.8	647.6	652.4	657.0	655.9	655.9
167.5°	613.9	619.2	624.0	628.2	630.3	633.6	632.4	632.4
170°	605.4	608.9	613.6	616.0	617.1	619.6	618.3	618.3
172.5°	597.9	600.5	604.3	605.6	605.9	608.2	606.1	605.2
175°	587.8	589.0	591.4	591.4	591.4	592.5	591.4	590.2
177.5°	581.5	582.4	583.4	583.4	582.4	583.4	581.5	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

(END OF REPORT)