

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923850

Luminaire Tested: DFN2DIP-TR4F0-090D120US940-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P923850  
REPORT IS A COMBINATION OF REPORTS P900523 AND P897293  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-090D120US940-FLLFLL  
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17415.1 lumens  
Efficiency: N/A  
Efficacy: 97.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 178.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.099  
Total Harmonic Distortion (THDi): 0.979  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923850  
CATALOG NUMBER: DFN2DIP-TR4F0-090D120US940-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P923850  
 CATALOG NUMBER: DFN2DIP-TR4F0-090D120US940-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46	46
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44	38	38	38	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37	32	32	32	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32	27	27	27	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23	23	23	23
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	20	20	20	20
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21	18	18	18	18
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16	16	16	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14	14	14	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13	13	13	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12	12	12	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2481	2481	2481
5°	2485	2446	2463
10°	2465	2413	2429
15°	2428	2373	2377
20°	2380	2318	2324
25°	2331	2252	2262
30°	2270	2191	2183
35°	2212	2118	2100
40°	2141	2045	2021
45°	2070	1972	1941
50°	1992	1895	1847
55°	1911	1806	1761
60°	1819	1700	1662
65°	1719	1590	1546
70°	1591	1457	1421
75°	1415	1297	1305
80°	1202	1093	1085
85°	870	742	718

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2637 cd/sqm



TEST NUMBER: P923850

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US940-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	293.9	1.7
10°-20°	827.0	4.7
20°-30°	1215.3	7.0
30°-40°	1411.5	8.1
40°-50°	1409.7	8.1
50°-60°	1229.3	7.1
60°-70°	908.7	5.2
70°-80°	514.1	3.0
80°-90°	145.3	0.8
90°-100°	209.4	1.2
100°-110°	665.4	3.8
110°-120°	1138.7	6.5
120°-130°	1497.5	8.6
130°-140°	1680.9	9.7
140°-150°	1648.3	9.5
150°-160°	1382.7	7.9
160°-170°	917.0	5.3
170°-180°	320.5	1.8
0°-30°	2336.2	13.4
0°-40°	3747.7	21.5
0°-60°	6386.7	36.7
0°-90°	7954.8	45.7
90°-120°	2013.4	11.6
90°-150°	6840.1	39.3
90°-180°	9460.0	54.3
0°-180°	17415.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3123	3123	3123	3123	3123	
5°	3123	3111	3078	3102	3096	296
15°	2973	2955	2916	2928	2913	837
25°	2690	2666	2616	2621	2616	1238
35°	2321	2291	2243	2225	2210	1449
45°	1889	1868	1823	1790	1778	1458
55°	1430	1411	1375	1339	1324	1278
65°	964	946	916	889	874	953
75°	504	499	483	466	472	538
85°	123	120	117	108	105	137
90°	3	37	100	94	97	17
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	



TEST NUMBER: P923850

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US940-FLLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3122.7	3122.7	3122.7	3122.7	3122.7
2.5°	3140.9	3125.9	3092.8	3122.7	3117.0
5°	3122.7	3110.9	3077.8	3101.7	3095.9
7.5°	3101.7	3083.9	3050.7	3075.0	3068.9
10°	3068.9	3047.9	3011.8	3035.7	3026.8
12.5°	3023.6	3005.8	2969.8	2984.7	2978.8
15°	2972.7	2954.9	2915.6	2927.8	2912.8
17.5°	2909.6	2891.7	2852.6	2867.6	2852.6
20°	2840.5	2822.6	2780.5	2789.4	2777.7
22.5°	2771.6	2744.6	2705.4	2705.4	2699.3
25°	2690.4	2666.5	2615.6	2621.3	2615.6
27.5°	2600.2	2579.2	2540.4	2531.5	2516.5
30°	2510.4	2486.2	2441.2	2432.3	2420.3
32.5°	2414.2	2396.4	2348.2	2330.1	2318.0
35°	2321.2	2291.2	2243.1	2225.0	2210.0
37.5°	2216.1	2189.0	2140.8	2119.9	2104.9
40°	2108.0	2083.8	2035.7	2008.9	1996.9
42.5°	2002.9	1978.7	1930.9	1900.7	1882.8
45°	1888.8	1867.9	1822.6	1789.8	1777.7
47.5°	1777.7	1756.7	1708.5	1675.4	1657.6
50°	1660.5	1645.5	1603.4	1561.4	1546.4
52.5°	1546.4	1525.4	1486.5	1453.4	1432.4
55°	1429.5	1411.3	1375.3	1339.3	1324.4
57.5°	1312.2	1297.3	1258.1	1222.1	1210.0
60°	1195.0	1183.2	1141.1	1108.0	1099.1
62.5°	1080.9	1059.9	1029.9	1000.1	987.9
65°	964.0	945.8	915.9	888.9	873.9
67.5°	843.9	828.7	801.8	780.9	768.7
70°	732.7	720.6	693.6	672.5	660.8
72.5°	618.7	606.5	591.6	570.6	561.7
75°	504.4	498.6	483.3	465.5	471.5
77.5°	402.3	390.3	384.2	375.3	366.4
80°	300.4	297.2	291.1	282.2	276.3
82.5°	204.2	204.2	201.3	189.2	189.2
85°	123.0	120.1	117.3	108.0	105.1
87.5°	54.1	48.1	42.1	33.2	30.0
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5



TEST NUMBER: P923850

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US940-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1



TEST NUMBER: P923850  
 CATALOG NUMBER: DFN2DIP-TR4F0-090D120US940-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.01	10.83	11.00	11.84	13.17	9.58	10.40	10.57	11.41	12.74
	3H	11.67	12.40	12.67	13.42	14.77	11.19	11.93	12.20	12.95	14.30
	4H	12.25	12.95	13.27	13.97	15.33	11.78	12.48	12.80	13.50	14.86
	6H	12.65	13.29	13.68	14.32	15.69	12.17	12.82	13.20	13.84	15.21
	8H	12.75	13.37	13.79	14.40	15.77	12.28	12.89	13.31	13.93	15.30
	12H	12.80	13.38	13.84	14.41	15.81	12.32	12.90	13.36	13.93	15.33
4H	2H	10.47	11.17	11.49	12.18	13.54	10.12	10.82	11.14	11.84	13.20
	3H	12.33	12.91	13.36	13.96	15.33	11.94	12.52	12.97	13.56	14.94
	4H	13.04	13.58	14.08	14.61	16.01	12.64	13.17	13.67	14.21	15.60
	6H	13.55	14.01	14.60	15.07	16.47	13.14	13.60	14.19	14.66	16.06
	8H	13.70	14.13	14.75	15.18	16.59	13.29	13.72	14.34	14.77	16.18
	12H	13.77	14.16	14.84	15.23	16.64	13.35	13.74	14.42	14.81	16.22
8H	4H	13.23	13.66	14.28	14.72	16.12	12.87	13.30	13.92	14.36	15.76
	6H	13.86	14.22	14.94	15.31	16.72	13.50	13.86	14.57	14.95	16.36
	8H	14.08	14.40	15.16	15.48	16.90	13.72	14.03	14.80	15.11	16.53
	12H	14.21	14.49	15.30	15.56	17.03	13.83	14.10	14.91	15.18	16.64
12H	4H	13.22	13.61	14.29	14.67	16.09	12.87	13.25	13.93	14.32	15.74
	6H	13.89	14.21	14.97	15.28	16.71	13.54	13.85	14.62	14.93	16.36
	8H	14.13	14.41	15.22	15.48	16.95	13.78	14.05	14.86	15.13	16.59