

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832068

Luminaire Tested: S123RDIP-S340D1195U840-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832068
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U840-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6304.8 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 43.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24		
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21		
2	84	77	72	67	75	69	64	60	53	50	48	39	37	35	26	25	24	18		
3	77	68	62	56	68	61	55	51	48	44	40	35	32	30	23	22	21	16		
4	71	61	53	48	63	54	48	43	42	38	35	31	29	26	21	19	18	14		
5	65	54	47	41	58	49	42	37	38	34	30	28	25	23	19	17	16	12		
6	60	49	41	36	53	44	37	33	34	30	26	26	23	20	18	16	14	11		
7	55	44	37	31	49	40	33	29	31	27	23	23	20	18	16	14	13	10		
8	51	40	33	28	46	36	30	25	29	24	21	22	19	16	15	13	12	9		
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	12	11	9		
10	45	33	27	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	12076	12076	12076	12076	12076
5°	14338	13881	12151	9823	9121
10°	12991	14100	12091	7871	6753
15°	8945	12090	11964	6433	5341
20°	6222	9308	11724	5424	4694
25°	4742	7094	11374	4821	4327
30°	4128	5671	10936	4477	4007
35°	3790	4784	10318	4185	3717
40°	3458	4272	9507	3901	3451
45°	3124	3908	8634	3631	3186
50°	2835	3605	7603	3366	2858
55°	2563	3310	6611	3108	2451
60°	2297	3010	5744	2822	2316
65°	2122	2672	4944	2537	2190
70°	1721	2310	4315	2294	1781
75°	1510	1838	3656	1905	1568
80°	1370	1556	2994	1599	1481
85°	1247	1359	2272	1445	1359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°

Vertical Angle: 45°

Luminance: 9109 cd/sqm

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	1.6
10°-20°	236.6	3.8
20°-30°	271.5	4.3
30°-40°	267.6	4.2
40°-50°	236.0	3.7
50°-60°	181.6	2.9
60°-70°	119.4	1.9
70°-80°	58.0	0.9
80°-90°	17.8	0.3
90°-100°	55.7	0.9
100°-110°	269.2	4.3
110°-120°	659.8	10.5
120°-130°	837.6	13.3
130°-140°	894.8	14.2
140°-150°	836.7	13.3
150°-160°	674.9	10.7
160°-170°	435.5	6.9
170°-180°	150.1	2.4
0°-30°	610.4	9.7
0°-40°	878.0	13.9
0°-60°	1295.5	20.5
0°-90°	1490.6	23.6
90°-120°	984.6	15.6
90°-150°	3553.7	56.4
90°-180°	4814.0	76.4
0°-180°	6304.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1122	1122	1122	1122	1122	
5°	1327	1285	1125	909	844	121
15°	803	1085	1074	577	479	227
25°	399	597	958	406	364	189
35°	288	364	785	318	283	180
45°	205	257	567	238	209	159
55°	137	176	352	166	131	123
65°	83	105	194	100	86	82
75°	36	44	88	46	38	39
85°	10	11	18	12	11	11
90°	35	28	1	28	35	16
95°	45	36	72	36	45	37
105°	52	257	350	257	52	108
115°	690	674	656	674	690	649
125°	943	939	924	939	943	843
135°	1163	1163	1151	1163	1163	897
145°	1341	1339	1328	1339	1341	837
155°	1461	1462	1463	1462	1461	674
165°	1539	1538	1543	1538	1539	435
175°	1573	1574	1579	1574	1573	150
180°	1579	1579	1579	1579	1579	

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1243.3	1239.4	1235.5	1234.4	1233.2	1229.5	1225.8	1217.6	1209.3	1200.8	1192.3
5°	1327.0	1327.5	1328.0	1326.8	1325.7	1320.8	1316.0	1305.9	1295.8	1284.7	1273.7
7.5°	1301.3	1308.6	1316.0	1317.4	1318.8	1322.4	1326.1	1323.8	1321.5	1317.4	1313.2
10°	1188.6	1188.1	1187.7	1195.9	1204.2	1228.8	1253.4	1266.1	1278.7	1290.0	1301.3
12.5°	1004.6	1005.3	1006.0	1033.1	1060.3	1083.5	1106.7	1138.9	1171.1	1205.8	1240.6
15°	802.7	813.9	825.2	849.4	873.5	908.5	943.4	986.7	1029.9	1084.9	1139.8
17.5°	659.1	664.0	668.8	692.0	715.3	748.4	781.5	830.5	879.5	950.3	1021.2
20°	543.2	547.6	552.0	568.8	585.6	617.3	649.0	695.7	742.4	812.6	882.7
22.5°	453.5	462.0	470.6	481.8	493.1	516.1	539.1	586.7	634.3	698.2	762.2
25°	399.3	403.2	407.1	416.7	426.4	448.5	470.6	502.1	533.6	597.3	661.0
27.5°	362.5	363.6	364.8	371.9	379.0	393.3	407.5	436.7	466.0	518.4	570.8
30°	332.1	334.2	336.2	341.8	347.3	357.6	368.0	388.7	409.4	456.3	503.2
32.5°	308.6	309.8	310.9	315.5	320.1	327.7	335.3	351.7	368.0	403.9	439.7
35°	288.4	288.6	288.9	292.3	295.8	303.1	310.5	324.1	337.6	364.1	390.5
37.5°	265.4	267.0	268.6	271.2	273.7	280.1	286.6	297.6	308.6	330.5	352.3
40°	246.1	247.5	248.8	251.8	254.8	259.9	264.9	275.1	285.2	304.0	322.9
42.5°	226.8	227.7	228.6	231.6	234.6	240.8	247.0	255.1	263.1	278.7	294.4
45°	205.2	207.5	209.8	213.0	216.2	221.5	226.8	235.0	243.3	256.7	270.0
47.5°	187.2	188.4	189.5	192.3	195.0	201.5	207.9	215.3	222.6	235.0	247.5
50°	169.3	169.7	170.2	172.7	175.3	181.0	186.8	195.3	203.8	215.3	226.8
52.5°	152.3	153.4	154.6	157.1	159.6	163.5	167.4	176.2	184.9	196.2	207.5
55°	136.6	137.3	138.0	139.8	141.7	146.3	150.9	158.5	166.1	176.4	186.8
57.5°	121.9	122.8	123.7	125.1	126.5	130.6	134.8	141.4	148.1	158.5	168.8
60°	106.7	107.9	109.0	110.6	112.2	115.5	118.7	124.7	130.6	139.8	149.0
62.5°	95.7	95.9	96.1	97.5	98.9	101.2	103.5	108.3	113.2	122.4	131.6
65°	83.3	83.9	84.6	85.3	86.0	87.9	89.7	93.8	98.0	104.9	111.8
67.5°	70.4	71.1	71.8	72.9	74.1	75.7	77.3	80.0	82.8	89.2	95.7
70°	54.7	54.7	54.7	56.6	58.4	61.2	63.9	66.0	68.1	73.4	78.7
72.5°	44.6	44.8	45.1	45.3	45.5	47.1	48.8	52.2	55.7	58.9	62.1
75°	36.3	36.6	36.8	37.0	37.3	37.7	38.2	39.3	40.5	44.2	47.8
77.5°	29.0	29.2	29.4	29.7	29.9	30.4	30.8	31.3	31.7	33.1	34.5
80°	22.1	22.3	22.5	22.8	23.0	23.2	23.5	23.9	24.4	25.1	25.8
82.5°	16.1	16.1	16.1	16.1	16.1	16.6	17.0	17.0	17.0	17.5	17.9
85°	10.1	10.1	10.1	10.3	10.6	10.6	10.6	10.8	11.0	11.0	11.0
87.5°	4.6	4.4	4.1	4.4	4.6	4.6	4.6	4.8	5.1	5.1	5.1
90°	35.2	34.7	34.2	33.6	33.1	32.3	31.3	30.2	29.2	28.2	24.8
92.5°	39.9	39.6	39.4	39.1	38.8	37.8	36.0	34.2	32.3	30.5	28.2
95°	44.6	44.6	44.6	44.6	44.6	43.7	41.8	40.0	38.2	36.4	33.5
97.5°	48.1	47.8	47.6	47.3	47.1	45.9	43.8	41.7	39.6	37.5	50.8
100°	49.3	49.0	48.8	48.5	48.2	47.1	45.0	42.9	40.8	38.7	79.4
102.5°	50.5	49.9	49.4	48.9	48.4	52.4	61.0	69.6	78.2	86.8	132.2
105°	51.6	51.1	50.6	50.1	49.5	72.4	118.5	164.6	210.8	256.9	280.4
107.5°	122.0	156.2	190.3	224.5	258.6	295.8	335.9	376.1	416.3	456.4	452.5
110°	322.6	359.9	397.2	434.5	471.8	494.7	503.3	511.9	520.5	529.1	526.3

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	611.3	611.8	612.3	612.8	613.4	612.4	610.1	607.8	605.4	603.1	600.2
115°	689.9	688.8	687.8	686.8	685.7	683.9	681.3	678.7	676.1	673.5	671.1
117.5°	753.2	753.0	752.7	752.5	752.2	751.0	748.9	746.9	744.8	742.7	741.4
120°	818.9	818.9	818.9	818.9	818.9	817.9	815.8	813.7	811.6	809.6	808.8
122.5°	883.5	883.2	883.0	882.7	882.4	881.6	880.3	879.0	877.7	876.4	875.4
125°	943.3	942.8	942.3	941.7	941.2	940.7	940.2	939.7	939.1	938.6	937.6
127.5°	1002.0	1002.5	1003.0	1003.5	1004.1	1003.9	1003.1	1002.4	1001.6	1000.8	999.5
130°	1058.3	1058.8	1059.3	1059.9	1060.4	1060.1	1059.1	1058.0	1057.0	1055.9	1054.9
132.5°	1109.9	1110.7	1111.5	1112.3	1113.0	1112.9	1111.9	1110.8	1109.8	1108.7	1108.0
135°	1162.7	1163.5	1164.3	1165.1	1165.8	1165.8	1165.1	1164.3	1163.5	1162.7	1161.7
137.5°	1213.2	1213.7	1214.2	1214.7	1215.2	1214.9	1213.6	1212.3	1210.9	1209.6	1209.1
140°	1257.7	1258.3	1258.8	1259.3	1259.8	1259.6	1258.5	1257.5	1256.4	1255.4	1254.6
142.5°	1298.8	1299.6	1300.4	1301.2	1301.9	1301.9	1301.2	1300.4	1299.6	1298.8	1298.0
145°	1341.0	1341.0	1341.0	1341.0	1341.0	1340.8	1340.3	1339.7	1339.2	1338.7	1338.2
147.5°	1371.6	1372.9	1374.2	1375.5	1376.8	1377.2	1376.6	1376.1	1375.6	1375.1	1374.6
150°	1406.8	1407.5	1408.3	1409.1	1409.9	1410.0	1409.5	1409.0	1408.4	1407.9	1407.4
152.5°	1434.9	1436.2	1437.5	1438.8	1440.1	1440.3	1439.2	1438.2	1437.1	1436.1	1435.8
155°	1460.7	1462.3	1463.9	1465.4	1467.0	1467.1	1465.8	1464.5	1463.2	1461.9	1461.6
157.5°	1483.0	1485.1	1487.2	1489.3	1491.4	1491.6	1490.1	1488.5	1486.9	1485.4	1485.6
160°	1504.1	1506.0	1507.8	1509.6	1511.4	1511.6	1510.0	1508.4	1506.9	1505.3	1505.6
162.5°	1524.1	1525.6	1527.2	1528.8	1530.3	1530.2	1528.4	1526.6	1524.7	1522.9	1523.2
165°	1539.3	1541.2	1543.0	1544.8	1546.6	1546.5	1544.4	1542.3	1540.2	1538.2	1538.4
167.5°	1551.1	1553.2	1555.2	1557.3	1559.4	1559.4	1557.3	1555.2	1553.2	1551.1	1551.1
170°	1561.6	1563.7	1565.8	1567.9	1570.0	1570.0	1567.9	1565.8	1563.7	1561.6	1561.6
172.5°	1567.5	1569.8	1572.2	1574.5	1576.9	1577.0	1574.9	1572.8	1570.8	1568.7	1568.4
175°	1573.4	1575.4	1577.5	1579.6	1581.7	1581.8	1580.0	1578.2	1576.4	1574.5	1574.3
177.5°	1574.5	1577.1	1579.7	1582.4	1585.0	1585.2	1583.1	1581.0	1579.0	1576.9	1576.6
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1191.1	1190.0	1178.9	1167.9	1157.1	1146.3	1138.2	1130.2	1116.6	1103.0	1094.5
5°	1264.9	1256.2	1238.7	1221.2	1195.0	1168.8	1146.7	1124.6	1096.6	1068.5	1045.1
7.5°	1306.1	1299.0	1277.8	1256.7	1221.9	1187.2	1152.7	1118.2	1076.8	1035.4	1000.0
10°	1307.3	1313.2	1295.8	1278.3	1239.2	1200.1	1153.2	1106.2	1050.6	994.9	949.2
12.5°	1266.3	1292.1	1288.4	1284.7	1244.9	1205.1	1148.1	1091.1	1022.8	954.5	897.2
15°	1189.7	1239.6	1254.4	1269.1	1236.2	1203.3	1138.4	1073.6	993.3	913.1	847.3
17.5°	1091.1	1161.0	1199.9	1238.7	1214.8	1190.9	1119.8	1048.8	958.4	868.0	796.5
20°	974.2	1065.8	1126.7	1187.7	1178.9	1170.2	1096.8	1023.5	925.9	828.4	750.9
22.5°	858.8	955.4	1039.6	1123.7	1132.7	1141.7	1067.6	993.6	886.8	780.1	701.2
25°	759.2	857.4	957.7	1058.0	1078.2	1098.4	1028.1	957.7	847.1	736.4	658.0
27.5°	664.2	757.6	868.0	978.4	1015.2	1052.0	987.6	923.2	808.0	692.7	614.5
30°	586.7	670.2	782.9	895.6	946.9	998.2	939.0	879.9	765.6	651.3	574.7
32.5°	514.5	589.2	702.4	815.5	875.1	934.7	883.6	832.6	722.6	612.7	537.0
35°	457.4	524.4	629.9	735.5	802.2	868.9	827.0	785.2	677.8	570.4	498.8
37.5°	408.5	464.6	563.7	662.8	733.7	804.5	769.5	734.6	633.6	532.7	465.0
40°	368.0	413.1	505.3	597.5	667.0	736.4	706.5	676.6	586.2	495.9	432.6
42.5°	333.3	372.1	454.9	537.7	601.4	665.1	645.4	625.6	543.7	461.8	403.2
45°	302.7	335.3	408.2	481.1	539.8	598.4	582.8	567.2	496.5	425.9	372.1
47.5°	275.5	303.6	368.7	433.8	486.4	539.1	524.6	510.1	451.7	393.3	344.3
50°	250.7	274.6	328.9	383.2	430.5	477.9	466.0	454.0	405.7	357.4	315.1
52.5°	227.2	247.0	295.8	344.5	382.7	420.9	411.7	402.5	365.2	328.0	289.6
55°	204.9	223.1	264.3	305.4	338.1	370.7	361.5	352.3	323.4	294.4	260.6
57.5°	184.7	200.6	233.9	267.2	293.2	319.2	314.9	310.5	286.3	262.2	234.4
60°	163.3	177.6	206.3	235.0	256.0	276.9	271.8	266.8	249.5	232.3	208.4
62.5°	144.2	156.9	179.9	202.9	219.9	236.9	233.2	229.5	216.4	203.3	183.5
65°	124.2	136.6	155.2	173.9	187.2	200.6	197.3	194.1	184.2	174.3	158.5
67.5°	106.0	116.4	132.5	148.6	157.5	166.5	164.7	162.8	155.2	147.7	135.2
70°	87.6	96.6	109.9	123.3	129.5	135.7	136.4	137.1	130.2	123.3	114.1
72.5°	69.2	76.4	88.8	101.2	106.0	110.9	110.6	110.4	106.3	102.1	93.8
75°	53.1	58.4	68.1	77.7	81.9	86.0	86.9	87.9	83.9	80.0	75.4
77.5°	38.2	41.9	49.2	56.6	61.2	65.8	66.2	66.7	64.9	63.0	58.6
80°	26.9	28.1	32.7	37.3	42.1	46.9	47.6	48.3	46.5	44.6	41.9
82.5°	18.6	19.3	20.9	22.5	26.4	30.4	31.3	32.2	31.3	30.4	27.4
85°	11.3	11.5	12.2	12.9	14.7	16.6	17.5	18.4	17.9	17.5	15.9
87.5°	5.1	5.1	5.3	5.5	6.0	6.4	7.6	8.7	8.0	7.4	6.7
90°	21.4	18.0	14.6	11.6	9.0	6.4	3.8	1.2	3.8	6.4	9.0
92.5°	25.8	23.5	21.1	20.7	22.3	23.9	25.4	27.0	25.4	23.9	22.3
95°	30.6	27.8	24.9	28.8	39.5	50.2	60.9	71.6	60.9	50.2	39.5
97.5°	64.1	77.4	90.7	101.0	108.3	115.6	122.9	130.2	122.9	115.6	108.3
100°	120.1	160.7	201.4	219.1	213.9	208.7	203.5	198.3	203.5	208.7	213.9
102.5°	177.6	222.9	268.3	289.3	285.9	282.5	279.1	275.7	279.1	282.5	285.9
105°	303.9	327.3	350.8	361.1	358.2	355.4	352.5	349.6	352.5	355.4	358.2
107.5°	448.6	444.7	440.8	437.6	435.3	432.9	430.6	428.2	430.6	432.9	435.3
110°	523.4	520.5	517.7	515.2	513.1	511.0	508.9	506.9	508.9	511.0	513.1

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	597.3	594.5	591.6	589.2	587.4	585.6	583.8	581.9	583.8	585.6	587.4
115°	668.8	666.4	664.1	662.1	660.6	659.0	657.4	655.9	657.4	659.0	660.6
117.5°	740.1	738.8	737.5	735.9	734.1	732.3	730.4	728.6	730.4	732.3	734.1
120°	808.0	807.2	806.4	804.9	802.5	800.2	797.8	795.5	797.8	800.2	802.5
122.5°	874.3	873.3	872.3	870.8	869.0	867.2	865.4	863.5	865.4	867.2	869.0
125°	936.5	935.5	934.4	932.9	930.8	928.7	926.6	924.5	926.6	928.7	930.8
127.5°	998.2	996.9	995.6	993.9	991.8	989.7	987.6	985.5	987.6	989.7	991.8
130°	1053.9	1052.8	1051.8	1050.2	1048.1	1046.0	1044.0	1041.9	1044.0	1046.0	1048.1
132.5°	1107.2	1106.4	1105.6	1104.2	1102.1	1100.0	1097.9	1095.8	1097.9	1100.0	1102.1
135°	1160.6	1159.6	1158.5	1157.2	1155.7	1154.1	1152.5	1151.0	1152.5	1154.1	1155.7
137.5°	1208.6	1208.1	1207.6	1206.3	1204.2	1202.1	1200.0	1197.9	1200.0	1202.1	1204.2
140°	1253.8	1253.1	1252.3	1251.1	1249.5	1248.0	1246.4	1244.8	1246.4	1248.0	1249.5
142.5°	1297.2	1296.5	1295.7	1294.5	1292.9	1291.4	1289.8	1288.3	1289.8	1291.4	1292.9
145°	1337.7	1337.1	1336.6	1335.4	1333.6	1331.8	1330.0	1328.1	1330.0	1331.8	1333.6
147.5°	1374.0	1373.5	1373.0	1372.1	1370.8	1369.5	1368.2	1366.9	1368.2	1369.5	1370.8
150°	1406.9	1406.4	1405.8	1405.2	1404.4	1403.6	1402.8	1402.1	1402.8	1403.6	1404.4
152.5°	1435.6	1435.3	1435.0	1434.8	1434.5	1434.3	1434.0	1433.7	1434.0	1434.3	1434.5
155°	1461.4	1461.1	1460.9	1461.0	1461.5	1462.0	1462.5	1463.1	1462.5	1462.0	1461.5
157.5°	1485.9	1486.1	1486.4	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
160°	1505.8	1506.1	1506.4	1506.6	1506.9	1507.1	1507.4	1507.7	1507.4	1507.1	1506.9
162.5°	1523.4	1523.7	1523.9	1524.5	1525.3	1526.0	1526.8	1527.6	1526.8	1526.0	1525.3
165°	1538.7	1538.9	1539.2	1539.7	1540.5	1541.3	1542.1	1542.9	1542.1	1541.3	1540.5
167.5°	1551.1	1551.1	1551.1	1551.6	1552.6	1553.7	1554.7	1555.8	1554.7	1553.7	1552.6
170°	1561.6	1561.6	1561.6	1562.1	1563.2	1564.2	1565.3	1566.3	1565.3	1564.2	1563.2
172.5°	1568.1	1567.9	1567.6	1568.1	1569.4	1570.8	1572.1	1573.4	1572.1	1570.8	1569.4
175°	1574.0	1573.7	1573.5	1574.0	1575.3	1576.6	1577.9	1579.2	1577.9	1576.6	1575.3
177.5°	1576.4	1576.1	1575.8	1576.4	1577.7	1579.0	1580.3	1581.6	1580.3	1579.0	1577.7
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1086.0	1072.9	1059.8	1050.4	1040.9	1029.2	1017.5	1017.0	1016.6	1007.8	999.1
5°	1021.6	998.8	976.1	953.8	931.5	909.1	886.8	881.8	876.7	869.1	861.5
7.5°	964.6	928.2	891.9	863.4	834.9	812.6	790.2	775.1	759.9	748.2	736.4
10°	903.4	858.3	813.2	778.7	744.2	720.1	695.9	678.5	661.0	652.7	644.4
12.5°	839.9	790.9	741.9	708.1	674.3	645.4	616.4	600.5	584.6	573.1	561.6
15°	781.5	728.8	676.2	640.3	604.4	577.3	550.1	534.3	518.4	506.9	495.4
17.5°	724.9	671.8	618.7	582.3	546.0	521.4	496.8	481.4	466.0	458.8	451.7
20°	673.4	619.8	566.2	532.0	497.7	473.5	449.4	441.1	432.8	426.2	419.5
22.5°	622.4	570.8	519.3	486.4	453.5	436.1	418.6	411.9	405.2	400.2	395.1
25°	579.6	528.3	477.0	448.2	419.5	405.9	392.4	388.0	383.6	378.6	373.5
27.5°	536.3	487.6	438.8	415.8	392.8	381.8	370.7	365.2	359.7	355.6	351.4
30°	498.2	453.1	408.0	388.9	369.8	360.2	350.5	344.5	338.5	334.6	330.7
32.5°	461.4	421.3	381.3	365.0	348.7	339.2	329.8	324.1	318.3	313.7	309.1
35°	427.3	392.6	357.9	342.9	328.0	318.5	309.1	303.4	297.6	293.0	288.4
37.5°	397.4	365.9	334.4	320.4	306.3	298.1	289.8	283.8	277.8	273.0	268.2
40°	369.4	341.5	313.7	300.1	286.6	277.6	268.6	263.3	258.0	253.7	249.3
42.5°	344.5	319.0	293.5	280.1	266.8	258.3	249.8	243.6	237.3	234.8	232.3
45°	318.3	295.8	273.2	260.3	247.5	238.5	229.5	224.2	218.9	216.6	214.4
47.5°	295.3	274.4	253.4	240.8	228.1	220.1	212.1	207.9	203.8	200.6	197.3
50°	272.8	252.5	232.3	220.1	207.9	201.0	194.1	189.1	184.0	181.7	179.4
52.5°	251.1	232.7	214.4	201.9	189.5	182.8	176.2	171.8	167.4	162.6	157.8
55°	226.8	210.7	194.6	183.5	172.5	165.6	158.7	153.6	148.6	143.5	138.5
57.5°	206.5	190.7	174.8	164.9	155.0	148.3	141.7	136.2	130.6	126.5	122.4
60°	184.5	170.7	156.9	147.2	137.5	131.1	124.7	119.4	114.1	112.0	109.9
62.5°	163.8	150.9	138.0	129.5	121.0	114.8	108.6	105.1	101.7	100.3	98.9
65°	142.6	131.6	120.5	112.7	104.9	99.6	94.3	92.7	91.1	89.9	88.8
67.5°	122.8	113.4	104.0	97.1	90.2	86.5	82.8	81.0	79.1	77.7	76.4
70°	104.9	96.6	88.3	82.3	76.4	72.9	69.5	67.8	66.2	63.7	61.2
72.5°	85.6	79.1	72.7	68.1	63.5	60.5	57.5	54.3	51.1	48.8	46.5
75°	70.8	64.4	58.0	53.6	49.2	45.8	42.3	41.2	40.0	39.3	38.6
77.5°	54.3	48.8	43.2	39.8	36.3	34.7	33.1	32.4	31.7	31.5	31.3
80°	39.1	34.5	29.9	28.1	26.2	25.8	25.3	24.8	24.4	24.1	23.9
82.5°	24.4	22.1	19.8	19.3	18.9	18.6	18.4	18.2	17.9	17.7	17.5
85°	14.3	13.3	12.4	12.2	12.0	11.7	11.5	11.5	11.5	11.5	11.5
87.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.7	5.5
90°	11.6	14.6	18.0	21.4	24.8	28.2	29.2	30.2	31.3	32.3	33.1
92.5°	20.7	21.1	23.5	25.8	28.2	30.5	32.3	34.2	36.0	37.8	38.8
95°	28.8	24.9	27.8	30.6	33.5	36.4	38.2	40.0	41.8	43.7	44.6
97.5°	101.0	90.7	77.4	64.1	50.8	37.5	39.6	41.7	43.8	45.9	47.1
100°	219.1	201.4	160.7	120.1	79.4	38.7	40.8	42.9	45.0	47.1	48.2
102.5°	289.3	268.3	222.9	177.6	132.2	86.8	78.2	69.6	61.0	52.4	48.4
105°	361.1	350.8	327.3	303.9	280.4	256.9	210.8	164.6	118.5	72.4	49.5
107.5°	437.6	440.8	444.7	448.6	452.5	456.4	416.3	376.1	335.9	295.8	258.6
110°	515.2	517.7	520.5	523.4	526.3	529.1	520.5	511.9	503.3	494.7	471.8

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	589.2	591.6	594.5	597.3	600.2	603.1	605.4	607.8	610.1	612.4	613.4
115°	662.1	664.1	666.4	668.8	671.1	673.5	676.1	678.7	681.3	683.9	685.7
117.5°	735.9	737.5	738.8	740.1	741.4	742.7	744.8	746.9	748.9	751.0	752.2
120°	804.9	806.4	807.2	808.0	808.8	809.6	811.6	813.7	815.8	817.9	818.9
122.5°	870.8	872.3	873.3	874.3	875.4	876.4	877.7	879.0	880.3	881.6	882.4
125°	932.9	934.4	935.5	936.5	937.6	938.6	939.1	939.7	940.2	940.7	941.2
127.5°	993.9	995.6	996.9	998.2	999.5	1000.8	1001.6	1002.4	1003.1	1003.9	1004.1
130°	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0	1058.0	1059.1	1060.1	1060.4
132.5°	1104.2	1105.6	1106.4	1107.2	1108.0	1108.7	1109.8	1110.8	1111.9	1112.9	1113.0
135°	1157.2	1158.5	1159.6	1160.6	1161.7	1162.7	1163.5	1164.3	1165.1	1165.8	1165.8
137.5°	1206.3	1207.6	1208.1	1208.6	1209.1	1209.6	1210.9	1212.3	1213.6	1214.9	1215.2
140°	1251.1	1252.3	1253.1	1253.8	1254.6	1255.4	1256.4	1257.5	1258.5	1259.6	1259.8
142.5°	1294.5	1295.7	1296.5	1297.2	1298.0	1298.8	1299.6	1300.4	1301.2	1301.9	1301.9
145°	1335.4	1336.6	1337.1	1337.7	1338.2	1338.7	1339.2	1339.7	1340.3	1340.8	1341.0
147.5°	1372.1	1373.0	1373.5	1374.0	1374.6	1375.1	1375.6	1376.1	1376.6	1377.2	1376.8
150°	1405.2	1405.8	1406.4	1406.9	1407.4	1407.9	1408.4	1409.0	1409.5	1410.0	1409.9
152.5°	1434.8	1435.0	1435.3	1435.6	1435.8	1436.1	1437.1	1438.2	1439.2	1440.3	1440.1
155°	1461.0	1460.9	1461.1	1461.4	1461.6	1461.9	1463.2	1464.5	1465.8	1467.1	1467.0
157.5°	1486.5	1486.4	1486.1	1485.9	1485.6	1485.4	1486.9	1488.5	1490.1	1491.6	1491.4
160°	1506.6	1506.4	1506.1	1505.8	1505.6	1505.3	1506.9	1508.4	1510.0	1511.6	1511.4
162.5°	1524.5	1523.9	1523.7	1523.4	1523.2	1522.9	1524.7	1526.6	1528.4	1530.2	1530.3
165°	1539.7	1539.2	1538.9	1538.7	1538.4	1538.2	1540.2	1542.3	1544.4	1546.5	1546.6
167.5°	1551.6	1551.1	1551.1	1551.1	1551.1	1551.1	1553.2	1555.2	1557.3	1559.4	1559.4
170°	1562.1	1561.6	1561.6	1561.6	1561.6	1561.6	1563.7	1565.8	1567.9	1570.0	1570.0
172.5°	1568.1	1567.6	1567.9	1568.1	1568.4	1568.7	1570.8	1572.8	1574.9	1577.0	1576.9
175°	1574.0	1573.5	1573.7	1574.0	1574.3	1574.5	1576.4	1578.2	1580.0	1581.8	1581.7
177.5°	1576.4	1575.8	1576.1	1576.4	1576.6	1576.9	1579.0	1581.0	1583.1	1585.2	1585.0
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1121.9	1121.9	1121.9	1121.9
2.5°	996.8	994.5	993.6	992.6
5°	854.4	847.3	845.7	844.1
7.5°	733.4	730.4	720.6	710.7
10°	635.2	626.0	621.9	617.8
12.5°	553.1	544.6	543.2	541.9
15°	489.4	483.4	481.4	479.3
17.5°	447.6	443.4	440.9	438.4
20°	416.5	413.5	411.7	409.8
22.5°	392.8	390.5	389.1	387.8
25°	370.1	366.6	365.5	364.3
27.5°	348.4	345.4	344.3	343.1
30°	328.2	325.7	324.1	322.4
32.5°	306.1	303.1	302.2	301.3
35°	286.6	284.7	283.8	282.9
37.5°	265.9	263.6	262.2	260.8
40°	248.2	247.0	246.3	245.6
42.5°	230.2	228.1	227.9	227.7
45°	212.3	210.2	209.8	209.3
47.5°	195.5	193.7	193.4	193.2
50°	176.9	174.3	172.5	170.7
52.5°	155.5	153.2	151.6	150.0
55°	135.9	133.4	132.0	130.6
57.5°	121.2	120.1	119.4	118.7
60°	109.2	108.6	108.1	107.6
62.5°	98.2	97.5	97.5	97.5
65°	88.1	87.4	86.7	86.0
67.5°	75.0	73.6	73.4	73.1
70°	59.1	57.0	56.8	56.6
72.5°	46.2	46.0	45.5	45.1
75°	38.2	37.7	37.7	37.7
77.5°	30.8	30.4	30.4	30.4
80°	23.7	23.5	23.7	23.9
82.5°	17.5	17.5	17.2	17.0
85°	11.3	11.0	11.0	11.0
87.5°	5.5	5.5	5.5	5.5
90°	33.6	34.2	34.7	35.2
92.5°	39.1	39.4	39.6	39.9
95°	44.6	44.6	44.6	44.6
97.5°	47.3	47.6	47.8	48.1
100°	48.5	48.8	49.0	49.3
102.5°	48.9	49.4	49.9	50.5
105°	50.1	50.6	51.1	51.6
107.5°	224.5	190.3	156.2	122.0
110°	434.5	397.2	359.9	322.6

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	612.8	612.3	611.8	611.3
115°	686.8	687.8	688.8	689.9
117.5°	752.5	752.7	753.0	753.2
120°	818.9	818.9	818.9	818.9
122.5°	882.7	883.0	883.2	883.5
125°	941.7	942.3	942.8	943.3
127.5°	1003.5	1003.0	1002.5	1002.0
130°	1059.9	1059.3	1058.8	1058.3
132.5°	1112.3	1111.5	1110.7	1109.9
135°	1165.1	1164.3	1163.5	1162.7
137.5°	1214.7	1214.2	1213.7	1213.2
140°	1259.3	1258.8	1258.3	1257.7
142.5°	1301.2	1300.4	1299.6	1298.8
145°	1341.0	1341.0	1341.0	1341.0
147.5°	1375.5	1374.2	1372.9	1371.6
150°	1409.1	1408.3	1407.5	1406.8
152.5°	1438.8	1437.5	1436.2	1434.9
155°	1465.4	1463.9	1462.3	1460.7
157.5°	1489.3	1487.2	1485.1	1483.0
160°	1509.6	1507.8	1506.0	1504.1
162.5°	1528.8	1527.2	1525.6	1524.1
165°	1544.8	1543.0	1541.2	1539.3
167.5°	1557.3	1555.2	1553.2	1551.1
170°	1567.9	1565.8	1563.7	1561.6
172.5°	1574.5	1572.2	1569.8	1567.5
175°	1579.6	1577.5	1575.4	1573.4
177.5°	1582.4	1579.7	1577.1	1574.5
180°	1579.2	1579.2	1579.2	1579.2

TEST NUMBER: P832068

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.19	6.83	7.35	7.98	9.58	10.85	11.50	12.02	12.64	14.25
	3H	7.40	7.97	8.57	9.12	10.75	12.34	12.92	13.51	14.07	15.69
	4H	7.77	8.32	8.95	9.47	11.09	12.82	13.37	14.00	14.52	16.15
	6H	8.04	8.54	9.23	9.70	11.33	13.12	13.63	14.31	14.78	16.42
	8H	8.12	8.60	9.31	9.77	11.40	13.20	13.68	14.38	14.84	16.47
	12H	8.17	8.62	9.36	9.79	11.44	13.22	13.68	14.41	14.84	16.49
4H	2H	6.89	7.44	8.08	8.59	10.21	10.83	11.37	12.01	12.53	14.15
	3H	8.24	8.70	9.43	9.88	11.51	12.47	12.92	13.66	14.10	15.74
	4H	8.69	9.11	9.88	10.28	11.93	13.07	13.49	14.26	14.65	16.31
	6H	9.05	9.41	10.24	10.60	12.24	13.50	13.86	14.69	15.04	16.69
	8H	9.17	9.51	10.36	10.68	12.35	13.63	13.96	14.82	15.14	16.80
	12H	9.24	9.54	10.45	10.73	12.40	13.68	13.98	14.89	15.17	16.84
8H	4H	8.99	9.33	10.19	10.51	12.17	13.02	13.36	14.22	14.54	16.20
	6H	9.45	9.73	10.66	10.95	12.61	13.51	13.79	14.73	15.01	16.67
	8H	9.65	9.88	10.86	11.08	12.76	13.70	13.94	14.92	15.14	16.82
	12H	9.78	9.99	11.00	11.18	12.89	13.81	14.02	15.03	15.21	16.92
12H	4H	9.00	9.30	10.20	10.49	12.15	12.97	13.27	14.17	14.46	16.12
	6H	9.51	9.75	10.73	10.95	12.63	13.49	13.73	14.70	14.93	16.60
	8H	9.72	9.93	10.94	11.13	12.84	13.67	13.88	14.89	15.08	16.79

END OF REPORT