

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332060-940

Luminaire Tested: **S123DIP-S1165D585U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332060-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6331.4 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332060-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot



TEST NUMBER: P332060-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	102	97	93	89	95	92	88	85	81	79	76	72	70	68	63	62	60	56		
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	56	53	51	47		
3	84	74	67	61	79	70	64	58	63	57	53	56	52	48	49	46	43	40		
4	77	66	58	52	72	62	55	49	56	50	45	50	45	41	44	40	37	34		
5	71	59	50	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26		
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23		
8	56	44	36	30	53	41	34	29	38	31	27	34	29	25	30	26	23	21		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19		
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17546	17546	17546
5°	17629	17386	17507
10°	17511	17235	17343
15°	17307	17041	17072
20°	17068	16763	16778
25°	16747	16431	16397
30°	16394	16063	15940
35°	16025	15674	15471
40°	15638	15244	15008
45°	15213	14850	14487
50°	14788	14364	13966
55°	14230	13863	13440
60°	13670	13276	12854
65°	13173	12638	12246
70°	12441	11909	11383
75°	11366	10959	10493
80°	10253	9819	9732
85°	9003	8657	8312

TEST NUMBER: P332060-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.6	2.4
10°-20°	433.6	6.8
20°-30°	640.5	10.1
30°-40°	748.2	11.8
40°-50°	752.2	11.9
50°-60°	660.7	10.4
60°-70°	492.2	7.8
70°-80°	280.4	4.4
80°-90°	82.4	1.3
90°-100°	24.9	0.4
100°-110°	118.6	1.9
110°-120°	284.9	4.5
120°-130°	362.8	5.7
130°-140°	387.7	6.1
140°-150°	362.5	5.7
150°-160°	292.4	4.6
160°-170°	188.7	3.0
170°-180°	65.0	1.0
0°-30°	1227.6	19.4
0°-40°	1975.8	31.2
0°-60°	3388.7	53.5
0°-90°	4243.8	67.0
90°-120°	428.4	6.8
90°-150°	1541.4	24.3
90°-180°	2088.0	33.0
0°-180°	6331.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1630	1630	1630	1630	1630	
5°	1632	1624	1609	1622	1620	155
15°	1553	1547	1529	1539	1532	438
25°	1410	1401	1384	1385	1381	649
35°	1220	1211	1193	1185	1177	763
45°	999	993	976	959	952	771
55°	758	756	739	724	716	679
65°	517	510	496	485	481	510
75°	273	268	264	257	252	292
85°	73	70	70	67	67	80
90°	0	6	12	14	15	5
95°	31	12	16	19	19	38
105°	152	154	111	26	22	161
115°	284	287	292	297	299	281
125°	401	405	407	408	409	358
135°	499	502	504	505	504	384
145°	576	579	580	581	581	360
155°	634	633	634	636	633	292
165°	669	667	667	670	667	189
175°	685	682	682	686	682	65
180°	685	685	685	685	685	

TEST NUMBER: P332060-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1635.8	1634.8	1633.8	1632.8	1631.7	1629.9	1627.2	1624.4	1621.7	1618.9	1621.4
5°	1631.6	1630.0	1628.4	1626.9	1625.3	1622.8	1619.4	1616.0	1612.6	1609.1	1612.2
7.5°	1615.6	1614.0	1612.5	1610.9	1609.4	1606.8	1603.2	1599.7	1596.2	1592.6	1595.4
10°	1602.1	1600.5	1599.0	1597.4	1595.9	1593.1	1589.0	1585.0	1580.9	1576.9	1579.7
12.5°	1584.2	1582.9	1581.5	1580.3	1579.0	1576.4	1572.6	1568.8	1565.0	1561.2	1563.3
15°	1553.1	1551.8	1550.6	1549.3	1548.1	1545.4	1541.4	1537.3	1533.3	1529.2	1531.7
17.5°	1516.9	1515.3	1513.7	1512.1	1510.4	1507.6	1503.5	1499.5	1495.4	1491.4	1493.2
20°	1490.0	1488.1	1486.2	1484.3	1482.6	1479.5	1475.5	1471.5	1467.4	1463.4	1464.6
22.5°	1459.7	1457.9	1456.0	1454.1	1452.2	1449.3	1445.2	1441.2	1437.2	1433.1	1434.0
25°	1410.1	1408.2	1406.3	1404.4	1402.7	1399.6	1395.6	1391.6	1387.5	1383.5	1383.8
27.5°	1357.1	1355.3	1353.5	1351.7	1349.9	1346.8	1342.5	1338.1	1333.7	1329.4	1329.6
30°	1319.0	1317.4	1315.9	1314.3	1312.8	1309.8	1305.5	1301.1	1296.7	1292.4	1292.4
32.5°	1280.9	1278.8	1276.8	1274.7	1272.6	1269.9	1266.6	1263.2	1259.8	1256.5	1254.7
35°	1219.5	1217.6	1215.8	1213.9	1212.0	1209.1	1205.0	1201.0	1196.9	1192.8	1191.0
37.5°	1156.6	1154.3	1151.9	1149.6	1147.2	1144.0	1139.9	1135.8	1131.7	1127.5	1125.2
40°	1112.9	1111.1	1109.2	1107.3	1105.5	1102.3	1098.0	1093.6	1089.2	1084.9	1082.4
42.5°	1069.2	1067.1	1065.0	1062.8	1060.7	1057.5	1053.1	1048.7	1044.4	1040.1	1037.6
45°	999.4	998.2	996.9	995.7	994.4	991.8	987.7	983.6	979.6	975.5	971.9
47.5°	930.1	928.4	926.6	924.7	922.9	920.2	916.3	912.5	908.7	904.9	901.3
50°	883.1	881.5	879.9	878.4	876.8	874.1	870.0	865.9	861.8	857.8	854.4
52.5°	833.7	832.7	831.6	830.5	829.5	826.8	822.5	818.2	814.0	809.6	806.6
55°	758.3	758.0	757.7	757.4	757.1	754.9	750.8	746.8	742.7	738.7	735.3
57.5°	686.5	685.5	684.4	683.4	682.3	680.2	676.9	673.7	670.5	667.2	664.1
60°	635.0	634.6	634.4	634.0	633.7	631.7	627.9	624.2	620.5	616.7	613.9
62.5°	589.0	588.2	587.4	586.6	585.8	583.4	579.7	576.0	572.3	568.6	565.7
65°	517.2	515.7	514.1	512.6	511.0	508.6	505.5	502.4	499.3	496.2	493.7
67.5°	441.2	439.9	438.5	437.1	435.8	433.9	431.5	429.2	426.8	424.5	422.2
70°	395.3	393.4	391.6	389.7	387.8	385.9	384.1	382.2	380.3	378.4	376.3
72.5°	347.1	345.7	344.3	343.0	341.6	339.8	337.7	335.6	333.5	331.4	329.4
75°	273.3	272.1	270.8	269.6	268.3	267.2	266.4	265.4	264.5	263.5	262.0
77.5°	208.0	207.3	206.6	206.0	205.3	204.4	203.2	202.2	201.0	199.9	198.9
80°	165.4	164.4	163.5	162.6	161.7	160.9	160.2	159.6	159.0	158.4	158.1
82.5°	123.9	123.7	123.5	123.3	123.1	123.0	122.9	122.8	122.6	122.5	122.0
85°	72.9	72.2	71.6	71.0	70.4	70.1	70.1	70.1	70.1	70.1	69.5
87.5°	29.2	28.7	28.2	27.7	27.2	26.9	27.0	27.0	27.1	27.1	26.9
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	9.5	9.2	8.8	8.5	8.2	8.6	9.7	10.8	11.9	13.0	13.7
95°	31.0	26.4	21.8	17.1	12.5	10.8	12.0	13.3	14.5	15.8	16.6
97.5°	62.3	60.3	58.2	56.1	54.0	49.0	40.8	32.6	24.5	16.4	17.3
100°	86.0	88.2	90.5	92.7	95.0	87.3	69.6	52.1	34.4	16.8	17.7
102.5°	112.8	114.4	116.1	117.7	119.3	110.5	91.2	72.0	52.7	33.4	30.7
105°	151.6	152.8	154.1	155.2	156.5	152.0	141.9	131.7	121.5	111.4	91.4
107.5°	192.4	193.4	194.5	195.5	196.4	197.7	199.3	200.9	202.5	204.1	189.5
110°	219.7	220.6	221.5	222.4	223.3	224.4	225.6	226.9	228.1	229.3	225.6

TEST NUMBER: P332060-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.6	247.4	248.2	249.0	250.0	251.3	252.5	253.8	255.0	255.1
115°	284.3	285.0	285.6	286.3	287.0	287.8	288.9	289.9	290.9	291.9	293.1
117.5°	321.6	322.4	323.3	324.1	324.9	325.7	326.2	326.7	327.3	327.7	328.7
120°	344.8	345.8	346.9	347.9	348.9	349.6	349.9	350.3	350.6	350.9	351.9
122.5°	368.5	369.3	370.1	371.0	371.8	372.4	372.8	373.3	373.7	374.2	374.8
125°	400.7	401.7	402.6	403.5	404.4	405.1	405.6	406.0	406.4	406.9	407.1
127.5°	432.1	433.0	433.9	434.8	435.7	436.4	436.9	437.6	438.1	438.6	439.0
130°	451.7	452.5	453.4	454.3	455.2	455.9	456.4	456.8	457.3	457.7	458.2
132.5°	470.4	471.3	472.2	473.1	473.9	474.6	474.9	475.3	475.6	476.1	476.5
135°	498.9	499.6	500.2	501.0	501.7	502.2	502.7	503.1	503.5	504.0	504.4
137.5°	523.3	524.2	525.0	525.9	526.7	527.4	527.5	527.8	528.1	528.3	528.9
140°	539.6	540.3	541.0	541.6	542.3	542.9	543.1	543.5	543.9	544.2	544.7
142.5°	554.6	555.4	556.1	556.7	557.4	557.9	558.2	558.6	558.9	559.3	559.6
145°	575.7	576.5	577.3	578.1	578.9	579.4	579.6	579.9	580.1	580.3	580.5
147.5°	595.6	596.1	596.6	597.1	597.6	598.0	598.2	598.4	598.7	599.0	599.1
150°	607.8	608.1	608.4	608.8	609.1	609.4	609.7	609.8	610.1	610.3	610.6
152.5°	618.8	618.9	619.0	619.2	619.4	619.6	619.6	619.8	619.9	620.1	620.5
155°	634.2	634.0	633.7	633.6	633.3	633.3	633.4	633.5	633.6	633.7	634.3
157.5°	646.2	646.2	646.1	646.1	646.1	646.0	646.0	645.9	645.7	645.6	646.3
160°	653.5	653.4	653.4	653.2	653.1	653.0	652.8	652.7	652.6	652.6	653.2
162.5°	660.5	660.1	659.9	659.6	659.2	659.1	659.0	658.9	658.7	658.6	659.4
165°	668.8	668.4	668.2	667.8	667.4	667.2	667.1	667.0	666.9	666.7	667.7
167.5°	675.3	674.8	674.4	674.0	673.5	673.2	673.2	673.2	673.2	673.2	674.2
170°	678.9	678.5	678.1	677.6	677.2	676.9	676.9	676.9	676.9	676.9	677.9
172.5°	681.4	680.9	680.3	679.8	679.2	679.0	679.1	679.2	679.3	679.4	680.3
175°	684.6	684.0	683.4	682.9	682.3	682.1	682.2	682.3	682.4	682.5	683.3
177.5°	685.4	684.9	684.5	684.0	683.6	683.4	683.5	683.6	683.7	683.8	684.5
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6

TEST NUMBER: P332060-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1623.9	1626.4	1628.9	1630.0	1629.8	1629.5	1629.2	1629.1
5°	1615.3	1618.5	1621.6	1622.8	1622.2	1621.6	1621.0	1620.3
7.5°	1598.2	1601.0	1603.8	1605.0	1604.6	1604.3	1603.9	1603.6
10°	1582.5	1585.3	1588.1	1589.2	1588.6	1588.0	1587.3	1586.7
12.5°	1565.3	1567.4	1569.4	1570.3	1569.9	1569.5	1569.1	1568.8
15°	1534.2	1536.7	1539.2	1539.5	1537.7	1535.8	1533.9	1532.0
17.5°	1494.9	1496.6	1498.3	1498.9	1498.3	1497.5	1496.8	1496.2
20°	1465.9	1467.1	1468.4	1468.5	1467.6	1466.6	1465.7	1464.7
22.5°	1435.1	1436.1	1437.1	1437.0	1435.8	1434.6	1433.4	1432.3
25°	1384.1	1384.4	1384.7	1384.4	1383.5	1382.5	1381.6	1380.6
27.5°	1329.9	1330.1	1330.3	1329.9	1328.7	1327.5	1326.3	1325.2
30°	1292.4	1292.4	1292.4	1291.3	1289.1	1286.9	1284.7	1282.5
32.5°	1252.9	1251.2	1249.5	1248.0	1246.9	1245.6	1244.5	1243.3
35°	1189.1	1187.2	1185.4	1183.7	1182.1	1180.5	1178.9	1177.4
37.5°	1123.0	1120.8	1118.6	1117.0	1115.9	1114.9	1113.9	1112.9
40°	1080.0	1077.5	1075.0	1073.1	1071.8	1070.6	1069.3	1068.1
42.5°	1035.1	1032.6	1030.1	1028.2	1027.0	1025.7	1024.5	1023.2
45°	968.1	964.4	960.6	958.0	956.4	954.8	953.3	951.7
47.5°	897.6	893.9	890.2	887.7	886.4	884.9	883.6	882.3
50°	851.0	847.6	844.1	841.5	839.6	837.8	835.9	834.0
52.5°	803.8	800.8	797.9	795.5	793.6	791.8	789.9	788.0
55°	731.8	728.4	725.0	722.5	720.9	719.3	717.8	716.2
57.5°	661.1	658.1	655.0	652.6	650.8	649.0	647.1	645.3
60°	611.2	608.3	605.6	603.3	601.8	600.2	598.7	597.1
62.5°	562.9	560.1	557.3	555.4	554.3	553.2	552.2	551.2
65°	491.2	488.7	486.2	484.6	483.6	482.7	481.7	480.8
67.5°	420.1	417.9	415.7	413.9	412.7	411.3	410.0	408.8
70°	374.1	371.9	369.7	367.8	366.3	364.7	363.2	361.7
72.5°	327.5	325.6	323.6	322.3	321.5	320.7	319.9	319.1
75°	260.4	258.9	257.3	256.0	255.1	254.1	253.2	252.3
77.5°	197.8	196.7	195.6	195.1	195.1	195.1	195.1	195.1
80°	157.7	157.5	157.1	157.0	157.0	157.0	157.0	157.0
82.5°	121.4	120.8	120.3	119.8	119.6	119.4	119.1	118.9
85°	68.8	68.2	67.6	67.3	67.3	67.3	67.3	67.3
87.5°	26.8	26.7	26.5	26.4	26.5	26.5	26.6	26.6
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	14.4	15.2	15.9	16.3	16.5	16.6	16.8	16.9
95°	17.4	18.1	18.9	19.4	19.4	19.4	19.4	19.4
97.5°	18.2	19.1	20.0	20.5	20.6	20.7	20.9	21.0
100°	18.5	19.5	20.4	20.9	21.0	21.1	21.2	21.4
102.5°	27.8	25.1	22.3	21.0	21.1	21.4	21.6	21.8
105°	71.3	51.4	31.4	21.5	21.7	21.9	22.1	22.4
107.5°	174.8	160.2	145.4	130.6	115.5	100.4	85.3	70.3
110°	221.9	218.2	214.5	204.5	188.3	172.2	156.0	139.8

TEST NUMBER: P332060-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.1	255.2	255.3	253.6	250.2	246.7	243.3	240.0
115°	294.2	295.3	296.5	297.2	297.7	298.2	298.6	299.1
117.5°	329.6	330.5	331.4	331.9	332.0	332.1	332.2	332.3
120°	352.8	353.7	354.5	355.0	355.0	355.0	355.0	355.0
122.5°	375.4	376.0	376.7	377.0	377.1	377.2	377.3	377.4
125°	407.3	407.5	407.8	408.0	408.2	408.5	408.7	408.9
127.5°	439.3	439.7	440.1	440.1	439.9	439.7	439.4	439.3
130°	458.6	459.1	459.5	459.7	459.4	459.2	459.0	458.8
132.5°	477.0	477.4	477.9	478.0	477.6	477.2	477.0	476.6
135°	504.7	505.1	505.3	505.3	505.1	504.7	504.4	504.0
137.5°	529.4	529.9	530.5	530.7	530.4	530.2	529.9	529.8
140°	545.1	545.5	546.0	546.1	545.9	545.6	545.5	545.2
142.5°	560.0	560.4	560.7	560.7	560.4	560.1	559.7	559.5
145°	580.8	580.9	581.2	581.3	581.3	581.3	581.3	581.3
147.5°	599.4	599.6	599.9	599.7	599.1	598.6	598.2	597.6
150°	610.7	611.0	611.2	611.2	610.8	610.5	610.1	609.8
152.5°	620.9	621.3	621.7	621.6	621.2	620.6	620.1	619.6
155°	634.8	635.4	636.0	635.9	635.3	634.5	633.9	633.2
157.5°	646.9	647.6	648.4	648.2	647.3	646.5	645.6	644.7
160°	653.9	654.5	655.2	655.1	654.4	653.6	652.8	652.0
162.5°	660.1	660.9	661.7	661.7	661.0	660.3	659.6	659.0
165°	668.6	669.5	670.4	670.5	669.7	668.9	668.1	667.3
167.5°	675.1	676.0	676.9	676.9	676.0	675.1	674.2	673.2
170°	678.8	679.7	680.6	680.6	679.7	678.8	677.9	676.9
172.5°	681.2	682.1	683.0	683.0	682.0	681.0	679.9	678.9
175°	684.1	684.9	685.7	685.6	684.7	683.9	683.0	682.0
177.5°	685.2	685.9	686.6	686.5	685.6	684.7	683.9	683.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6

(END OF REPORT)