

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923909

Luminaire Tested: DFN2DIP-TR4F0-110D080US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923909
REPORT IS A COMBINATION OF REPORTS P901976 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D080US940-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15399.8 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 171.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923909

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923909

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	40	38
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	33
5	70	59	51	45	65	55	48	43	48	43	38	41	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	26	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3221	3221	3221
5°	3226	3169	3190
10°	3194	3107	3086
15°	3150	3005	2925
20°	3092	2863	2728
25°	3032	2704	2538
30°	2952	2542	2297
35°	2874	2367	2085
40°	2794	2185	1842
45°	2702	1985	1622
50°	2606	1782	1407
55°	2506	1565	1200
60°	2390	1339	988
65°	2257	1108	889
70°	2096	894	804
75°	1893	788	732
80°	1600	660	634
85°	1115	440	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2702 cd/sqm

TEST NUMBER: P923909

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.9	2.5
10°-20°	1043.0	6.8
20°-30°	1464.4	9.5
30°-40°	1596.2	10.4
40°-50°	1467.1	9.5
50°-60°	1152.2	7.5
60°-70°	750.0	4.9
70°-80°	386.0	2.5
80°-90°	102.8	0.7
90°-100°	79.4	0.5
100°-110°	295.9	1.9
110°-120°	784.9	5.1
120°-130°	1301.8	8.5
130°-140°	1382.8	9.0
140°-150°	1285.1	8.3
150°-160°	1033.2	6.7
160°-170°	665.8	4.3
170°-180°	229.2	1.5
0°-30°	2887.3	18.7
0°-40°	4483.6	29.1
0°-60°	7102.9	46.1
0°-90°	8341.7	54.2
90°-120°	1160.2	7.5
90°-150°	5129.9	33.3
90°-180°	7058.0	45.8
0°-180°	15399.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4054	4054	4054	4054	4054	
5°	4054	4036	3988	4021	4010	384
15°	3856	3815	3691	3621	3584	1087
25°	3500	3382	3140	2990	2935	1610
35°	3016	2829	2506	2275	2194	1888
45°	2466	2220	1834	1574	1486	1904
55°	1875	1588	1192	972	903	1675
65°	1266	968	638	514	502	1255
75°	675	418	294	268	264	714
85°	158	81	70	70	70	181
90°	2	21	35	44	47	14
95°	113	56	68	77	75	134
105°	530	582	106	125	132	566
115°	1002	1031	1075	268	143	986
125°	1416	1439	1472	1484	1489	1263
135°	1753	1780	1796	1814	1810	1354
145°	2033	2031	2061	2073	2064	1272
155°	2238	2223	2244	2254	2240	1032
165°	2359	2348	2354	2366	2354	666
175°	2413	2400	2404	2416	2399	230
180°	2408	2408	2408	2408	2408	

TEST NUMBER: P923909

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4054.0	4054.0	4054.0	4054.0	4054.0
2.5°	4072.3	4054.0	4013.5	4050.5	4043.1
5°	4054.0	4035.7	3987.8	4020.9	4010.0
7.5°	4020.9	3999.1	3947.7	3962.1	3943.8
10°	3976.9	3951.2	3878.0	3866.7	3845.0
12.5°	3922.0	3888.9	3789.7	3767.8	3727.3
15°	3855.8	3815.4	3690.8	3621.1	3584.5
17.5°	3778.8	3720.0	3565.9	3485.2	3426.5
20°	3690.8	3617.2	3433.9	3342.4	3261.4
22.5°	3595.5	3510.9	3298.1	3173.5	3118.6
25°	3500.1	3382.5	3140.4	2990.2	2934.9
27.5°	3386.4	3261.4	2993.7	2821.2	2736.7
30°	3265.4	3125.6	2832.2	2645.3	2546.0
32.5°	3147.8	2978.8	2678.3	2458.1	2366.2
35°	3015.9	2828.6	2506.0	2274.8	2193.8
37.5°	2887.4	2685.4	2344.4	2091.0	1999.6
40°	2751.6	2531.7	2175.5	1915.0	1819.7
42.5°	2612.2	2377.5	2007.0	1735.3	1643.8
45°	2465.5	2219.5	1834.5	1573.7	1485.8
47.5°	2326.1	2065.7	1669.5	1408.6	1328.1
50°	2171.9	1911.6	1508.0	1254.5	1177.9
52.5°	2021.3	1746.1	1353.8	1111.7	1042.0
55°	1874.6	1588.5	1192.2	972.3	902.7
57.5°	1724.4	1430.8	1049.4	843.9	785.1
60°	1570.2	1276.8	898.8	711.9	653.2
62.5°	1420.0	1126.5	770.3	594.4	565.2
65°	1265.8	968.4	638.4	513.8	502.5
67.5°	1119.1	821.7	513.8	451.1	440.2
70°	964.9	678.9	425.4	388.9	374.1
72.5°	818.1	546.5	355.8	326.5	319.1
75°	674.9	418.0	293.5	267.8	264.3
77.5°	532.1	297.0	231.2	216.4	209.0
80°	399.8	212.9	175.9	161.6	161.6
82.5°	278.7	143.2	121.1	113.7	113.7
85°	157.7	80.6	69.6	69.6	69.6
87.5°	58.8	29.2	29.2	25.7	25.7
90°	1.7	20.9	34.8	43.6	47.0
92.5°	43.6	36.6	41.8	45.3	47.0
95°	113.2	55.6	67.9	76.8	74.9
97.5°	203.8	61.0	88.7	94.2	95.8
100°	308.4	69.7	99.3	113.2	116.6
102.5°	423.3	419.9	102.8	121.8	127.2
105°	529.6	581.9	106.3	125.4	132.4
107.5°	653.3	696.7	109.9	128.9	135.9
110°	771.9	808.2	305.0	130.7	137.6

TEST NUMBER: P923909

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	883.3	914.5	885.0	134.0	139.5
115°	1001.7	1031.3	1074.9	268.3	142.9
117.5°	1104.5	1139.2	1169.0	919.7	463.4
120°	1219.5	1245.5	1277.0	1297.9	1062.7
122.5°	1316.9	1344.9	1379.8	1390.2	1392.0
125°	1416.2	1439.0	1472.0	1484.3	1489.4
127.5°	1506.8	1531.2	1557.6	1574.8	1576.5
130°	1592.2	1620.1	1639.2	1658.5	1656.8
132.5°	1679.4	1702.1	1721.2	1736.9	1735.2
135°	1752.6	1780.5	1796.0	1813.6	1810.1
137.5°	1829.2	1850.0	1867.6	1885.0	1879.8
140°	1904.0	1918.1	1937.2	1952.8	1944.1
142.5°	1966.9	1979.1	2001.6	2015.5	2006.8
145°	2033.1	2031.2	2060.8	2073.0	2064.3
147.5°	2090.4	2085.3	2114.8	2123.5	2116.7
150°	2146.3	2134.0	2162.0	2172.3	2163.6
152.5°	2193.3	2179.3	2205.4	2216.0	2203.8
155°	2238.5	2223.0	2243.9	2254.2	2240.4
157.5°	2275.1	2261.3	2277.0	2289.2	2275.1
160°	2306.6	2296.1	2306.6	2316.9	2304.7
162.5°	2334.3	2324.0	2332.6	2344.8	2329.1
165°	2358.8	2348.4	2353.6	2365.7	2353.6
167.5°	2377.9	2367.4	2372.8	2385.0	2369.3
170°	2393.7	2383.1	2386.7	2398.9	2383.1
172.5°	2404.1	2393.7	2397.2	2409.4	2393.7
175°	2412.7	2400.5	2404.1	2416.2	2398.9
177.5°	2416.2	2404.1	2405.8	2418.1	2402.4
180°	2407.5	2407.5	2407.5	2407.5	2407.5

TEST NUMBER: P923909

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.59	12.45	12.51	13.39	14.61	7.56	8.43	8.49	9.37	10.58
	3H	13.27	14.04	14.21	14.99	16.23	8.75	9.53	9.69	10.48	11.71
	4H	13.88	14.61	14.83	15.56	16.81	9.21	9.94	10.16	10.89	12.14
	6H	14.30	14.97	15.26	15.93	17.19	9.53	10.20	10.49	11.16	12.42
	8H	14.43	15.07	15.40	16.04	17.30	9.62	10.26	10.59	11.24	12.49
	12H	14.49	15.10	15.47	16.07	17.35	9.67	10.27	10.64	11.25	12.53
4H	2H	11.61	12.34	12.57	13.29	14.54	8.16	8.89	9.12	9.85	11.09
	3H	13.44	14.05	14.41	15.03	16.29	9.51	10.12	10.48	11.11	12.37
	4H	14.13	14.69	15.11	15.67	16.95	10.06	10.62	11.04	11.60	12.88
	6H	14.65	15.13	15.64	16.13	17.41	10.49	10.96	11.48	11.96	13.25
	8H	14.83	15.27	15.82	16.27	17.56	10.62	11.06	11.61	12.06	13.35
	12H	14.92	15.33	15.93	16.34	17.64	10.68	11.08	11.69	12.10	13.40
8H	4H	14.11	14.55	15.10	15.55	16.84	10.35	10.79	11.34	11.79	13.08
	6H	14.67	15.04	15.69	16.08	17.37	10.87	11.23	11.88	12.27	13.57
	8H	14.89	15.21	15.91	16.24	17.55	11.06	11.38	12.08	12.41	13.72
	12H	15.03	15.31	16.06	16.33	17.69	11.18	11.47	12.21	12.48	13.84
12H	4H	14.06	14.46	15.07	15.47	16.77	10.35	10.75	11.36	11.77	13.07
	6H	14.65	14.97	15.67	16.00	17.31	10.92	11.24	11.94	12.27	13.58
	8H	14.87	15.16	15.90	16.17	17.53	11.13	11.42	12.16	12.43	13.79

END OF REPORT