

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923915

Luminaire Tested: DFN2DIP-TR4F0-110D100US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923915
REPORT IS A COMBINATION OF REPORTS P902011 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D100US940-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18538.7 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923915

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923915

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	52	50	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42
3	82	72	65	59	75	67	61	55	57	53	48	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3032	3032	3032
5°	3037	2990	3010
10°	3012	2950	2969
15°	2968	2901	2905
20°	2908	2833	2840
25°	2849	2753	2765
30°	2774	2678	2669
35°	2704	2589	2567
40°	2616	2500	2471
45°	2530	2410	2372
50°	2435	2316	2257
55°	2335	2207	2152
60°	2223	2077	2032
65°	2101	1944	1890
70°	1945	1781	1736
75°	1729	1585	1595
80°	1469	1336	1325
85°	1063	907	878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2530 cd/sqm

TEST NUMBER: P923915

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.2	1.9
10°-20°	1010.7	5.5
20°-30°	1485.4	8.0
30°-40°	1725.2	9.3
40°-50°	1723.0	9.3
50°-60°	1502.4	8.1
60°-70°	1110.6	6.0
70°-80°	628.4	3.4
80°-90°	171.2	0.9
90°-100°	99.2	0.5
100°-110°	369.9	2.0
110°-120°	981.1	5.3
120°-130°	1627.2	8.8
130°-140°	1728.5	9.3
140°-150°	1606.5	8.7
150°-160°	1291.5	7.0
160°-170°	832.2	4.5
170°-180°	286.4	1.5
0°-30°	2855.3	15.4
0°-40°	4580.5	24.7
0°-60°	7805.9	42.1
0°-90°	9716.1	52.4
90°-120°	1450.3	7.8
90°-150°	6412.5	34.6
90°-180°	8823.0	47.6
0°-180°	18538.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3817	3817	3817	3817	3817	
5°	3817	3802	3762	3791	3784	362
15°	3633	3611	3564	3578	3560	1023
25°	3288	3259	3197	3204	3197	1513
35°	2837	2800	2742	2719	2701	1772
45°	2309	2283	2228	2188	2173	1782
55°	1747	1725	1681	1637	1619	1562
65°	1178	1156	1120	1086	1068	1165
75°	616	609	591	569	576	658
85°	150	147	143	132	128	168
90°	2	26	43	55	59	17
95°	141	70	85	96	94	168
105°	662	727	133	157	166	707
115°	1252	1289	1344	335	179	1233
125°	1770	1799	1840	1855	1862	1579
135°	2191	2226	2245	2267	2263	1692
145°	2541	2539	2576	2591	2580	1589
155°	2798	2779	2805	2818	2800	1289
165°	2948	2935	2942	2957	2942	833
175°	3016	3001	3005	3020	2999	287
180°	3009	3009	3009	3009	3009	

TEST NUMBER: P923915

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3816.7	3816.7	3816.7	3816.7	3816.7
2.5°	3838.8	3820.5	3780.0	3816.7	3809.7
5°	3816.7	3802.3	3761.8	3790.9	3784.0
7.5°	3790.9	3769.2	3728.7	3758.3	3750.9
10°	3750.9	3725.1	3681.2	3710.3	3699.4
12.5°	3695.6	3673.8	3629.8	3648.1	3640.7
15°	3633.3	3611.4	3563.5	3578.3	3560.1
17.5°	3556.1	3534.4	3486.5	3504.8	3486.5
20°	3471.7	3449.8	3398.5	3409.4	3395.0
22.5°	3387.6	3354.4	3306.6	3306.6	3299.1
25°	3288.3	3259.1	3196.8	3203.8	3196.8
27.5°	3178.1	3152.4	3104.8	3094.0	3075.7
30°	3068.3	3038.7	2983.8	2972.9	2958.1
32.5°	2950.7	2928.9	2870.1	2847.9	2833.1
35°	2837.0	2800.4	2741.6	2719.4	2701.1
37.5°	2708.5	2675.4	2616.6	2590.9	2572.6
40°	2576.5	2546.9	2488.1	2455.4	2440.6
42.5°	2448.0	2418.4	2360.0	2323.0	2301.2
45°	2308.6	2282.9	2227.6	2187.5	2172.7
47.5°	2172.7	2147.1	2088.2	2047.7	2025.9
50°	2029.4	2011.2	1959.7	1908.3	1890.1
52.5°	1890.1	1864.3	1816.9	1776.3	1750.6
55°	1747.1	1724.9	1681.0	1636.9	1618.6
57.5°	1603.8	1585.6	1537.7	1493.6	1478.8
60°	1460.5	1446.2	1394.7	1354.2	1343.4
62.5°	1321.2	1295.5	1258.8	1222.3	1207.5
65°	1178.2	1156.0	1119.5	1086.4	1068.1
67.5°	1031.4	1012.8	980.1	954.4	939.6
70°	895.5	880.7	847.7	822.0	807.5
72.5°	756.2	741.4	723.1	697.4	686.4
75°	616.4	609.4	590.7	568.9	576.3
77.5°	491.8	477.0	469.6	458.7	447.8
80°	367.2	363.3	355.9	345.0	337.6
82.5°	249.6	249.6	246.1	231.3	231.3
85°	150.3	146.8	143.3	132.0	128.5
87.5°	66.2	58.8	51.4	40.5	36.6
90°	2.1	26.1	43.4	54.6	58.7
92.5°	54.6	45.7	52.3	56.6	58.7
95°	141.4	69.6	84.8	95.9	93.6
97.5°	254.7	76.2	110.9	117.6	119.8
100°	385.6	87.1	124.1	141.4	145.9
102.5°	529.1	524.9	128.5	152.3	159.0
105°	662.0	727.4	133.0	156.7	165.5
107.5°	816.6	870.9	137.3	161.1	169.9
110°	964.7	1010.3	381.1	163.5	171.9

TEST NUMBER: P923915

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1104.1	1143.2	1106.3	167.6	174.3
115°	1252.1	1289.1	1343.6	335.4	178.7
117.5°	1380.5	1424.1	1461.2	1149.7	579.3
120°	1524.4	1556.9	1596.3	1622.4	1328.4
122.5°	1646.2	1681.1	1724.7	1737.7	1740.0
125°	1770.3	1798.8	1840.1	1855.4	1861.8
127.5°	1883.6	1914.1	1946.9	1968.6	1970.7
130°	1990.3	2025.3	2049.1	2073.0	2071.0
132.5°	2099.2	2127.6	2151.4	2171.0	2169.0
135°	2190.8	2225.6	2245.1	2267.0	2262.6
137.5°	2286.4	2312.6	2334.5	2356.3	2349.7
140°	2380.0	2397.6	2421.4	2441.1	2430.2
142.5°	2458.6	2473.9	2502.1	2519.3	2508.6
145°	2541.4	2539.1	2576.1	2591.3	2580.4
147.5°	2613.0	2606.6	2643.5	2654.4	2645.9
150°	2682.8	2667.6	2702.5	2715.4	2704.6
152.5°	2741.5	2724.2	2756.8	2769.9	2754.7
155°	2798.2	2778.7	2804.9	2817.8	2800.5
157.5°	2843.9	2826.6	2846.3	2861.5	2843.9
160°	2883.3	2870.1	2883.3	2896.2	2880.9
162.5°	2917.9	2904.9	2915.8	2931.1	2911.4
165°	2948.4	2935.4	2941.9	2957.2	2941.9
167.5°	2972.4	2959.2	2966.0	2981.3	2961.5
170°	2992.0	2978.9	2983.3	2998.6	2978.9
172.5°	3005.0	2992.0	2996.5	3011.8	2992.0
175°	3015.9	3000.6	3005.0	3020.3	2998.6
177.5°	3020.3	3005.0	3007.4	3022.6	3002.9
180°	3009.4	3009.4	3009.4	3009.4	3009.4

TEST NUMBER: P923915

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.34	12.22	12.28	13.18	14.41	10.91	11.79	11.85	12.75	13.98
	3H	13.00	13.80	13.95	14.76	16.02	12.53	13.32	13.48	14.29	15.54
	4H	13.59	14.34	14.55	15.31	16.58	13.12	13.87	14.08	14.83	16.10
	6H	13.99	14.68	14.97	15.66	16.94	13.52	14.21	14.49	15.18	16.46
	8H	14.10	14.76	15.08	15.74	17.02	13.62	14.28	14.60	15.27	16.55
	12H	14.15	14.77	15.13	15.76	17.06	13.67	14.29	14.65	15.28	16.58
4H	2H	11.81	12.56	12.77	13.52	14.79	11.46	12.21	12.43	13.18	14.45
	3H	13.67	14.30	14.65	15.30	16.58	13.28	13.91	14.26	14.90	16.19
	4H	14.39	14.96	15.37	15.95	17.26	13.98	14.56	14.97	15.55	16.85
	6H	14.90	15.40	15.90	16.41	17.72	14.50	14.99	15.49	16.00	17.31
	8H	15.05	15.52	16.05	16.52	17.84	14.64	15.10	15.64	16.11	17.43
	12H	15.13	15.54	16.15	16.57	17.89	14.71	15.12	15.73	16.15	17.47
8H	4H	14.59	15.05	15.59	16.05	17.37	14.23	14.69	15.23	15.69	17.01
	6H	15.22	15.60	16.24	16.65	17.97	14.86	15.24	15.88	16.29	17.60
	8H	15.44	15.78	16.47	16.81	18.15	15.07	15.41	16.10	16.44	17.78
	12H	15.57	15.87	16.61	16.90	18.28	15.19	15.48	16.22	16.51	17.89
12H	4H	14.57	14.99	15.59	16.01	17.34	14.22	14.64	15.24	15.66	16.98
	6H	15.25	15.59	16.28	16.62	17.96	14.90	15.23	15.93	16.27	17.60
	8H	15.49	15.79	16.53	16.82	18.20	15.14	15.43	16.17	16.46	17.84

END OF REPORT