

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331881-940

Luminaire Tested: **S123DIP-S340D585U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331881-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3053.2 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331881-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot



TEST NUMBER: P331881-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41		
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35		
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29		
3	79	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24		
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21		
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	27	24	22	18		
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16		
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14		
8	53	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13		
9	49	37	29	24	45	34	27	23	29	23	20	23	19	17	19	16	14	11		
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470

TEST NUMBER: P331881-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	1.5
10°-20°	128.5	4.2
20°-30°	189.9	6.2
30°-40°	221.8	7.3
40°-50°	223.0	7.3
50°-60°	195.8	6.4
60°-70°	145.9	4.8
70°-80°	83.1	2.7
80°-90°	25.8	0.8
90°-100°	42.2	1.4
100°-110°	126.2	4.1
110°-120°	214.7	7.0
120°-130°	282.4	9.3
130°-140°	317.5	10.4
140°-150°	312.1	10.2
150°-160°	262.7	8.6
160°-170°	174.9	5.7
170°-180°	61.2	2.0
0°-30°	363.9	11.9
0°-40°	585.7	19.2
0°-60°	1004.5	32.9
0°-90°	1259.3	41.2
90°-120°	383.2	12.5
90°-150°	1295.1	42.4
90°-180°	1794.0	58.8
0°-180°	3053.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	0	6	12	14	15	3
95°	30	34	38	40	40	34
105°	114	116	120	120	121	123
115°	216	218	217	217	217	214
125°	316	318	317	315	313	282
135°	410	413	413	411	410	316
145°	498	499	500	500	498	311
155°	570	570	571	572	569	262
165°	621	620	620	622	619	175
175°	646	644	644	647	643	61
180°	648	648	648	648	648	

TEST NUMBER: P331881-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.7	8.7	8.7	8.7	8.7	8.9	9.1	9.3	9.5	9.7	9.8
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	12.3	13.1	13.8	14.6	15.4	16.2	17.0	17.8	18.7	19.5	19.9
95°	30.1	30.8	31.6	32.4	33.2	34.1	35.0	35.8	36.7	37.6	38.1
97.5°	53.3	53.9	54.5	55.1	55.6	56.3	56.9	57.6	58.2	58.9	59.4
100°	69.2	69.8	70.5	71.2	71.9	72.5	73.0	73.7	74.2	74.7	75.1
102.5°	87.5	87.9	88.3	88.7	89.1	89.7	90.4	91.2	91.9	92.6	93.0
105°	114.4	114.7	114.9	115.1	115.4	115.9	117.0	118.0	119.0	120.0	120.0
107.5°	145.8	145.9	146.1	146.2	146.3	146.6	147.0	147.4	147.8	148.2	148.6
110°	165.3	165.5	165.8	165.9	166.2	166.4	166.7	166.9	167.1	167.4	167.8

TEST NUMBER: P331881-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	185.7	185.7	185.9	186.0	186.2	186.3	186.4	186.4	186.5	186.5	187.0
115°	216.2	216.5	216.9	217.2	217.5	217.6	217.3	217.1	216.9	216.7	216.8
117.5°	246.9	247.1	247.4	247.5	247.8	247.7	247.4	247.2	246.9	246.6	246.6
120°	266.0	266.7	267.3	268.0	268.8	268.8	268.2	267.7	267.1	266.5	266.4
122.5°	286.0	286.4	287.0	287.4	287.9	288.0	287.8	287.5	287.1	286.9	286.6
125°	316.4	316.7	317.0	317.4	317.7	317.8	317.5	317.4	317.1	316.9	316.4
127.5°	344.5	345.2	345.9	346.6	347.3	347.6	347.3	347.1	346.8	346.6	346.0
130°	363.2	364.1	365.0	365.9	366.8	367.0	366.8	366.4	366.0	365.7	365.2
132.5°	381.8	382.8	383.7	384.6	385.5	385.8	385.6	385.3	385.0	384.9	384.2
135°	410.5	411.2	411.8	412.5	413.1	413.5	413.3	413.2	413.1	413.0	412.6
137.5°	436.9	437.5	438.0	438.6	439.2	439.6	439.9	440.1	440.5	440.8	440.3
140°	455.2	455.8	456.4	456.9	457.4	457.8	457.9	458.1	458.2	458.3	458.2
142.5°	471.9	472.4	473.1	473.6	474.1	474.6	474.7	474.9	475.2	475.4	475.3
145°	497.9	498.2	498.4	498.6	498.8	499.1	499.4	499.8	500.2	500.5	500.3
147.5°	520.8	521.1	521.6	521.9	522.4	522.7	523.1	523.3	523.7	524.0	524.0
150°	536.6	536.8	537.1	537.3	537.5	537.7	538.0	538.1	538.4	538.6	538.6
152.5°	549.7	549.9	550.3	550.5	550.9	551.1	551.3	551.3	551.5	551.6	551.8
155°	570.2	570.2	570.2	570.2	570.2	570.2	570.3	570.4	570.6	570.7	571.1
157.5°	587.6	587.5	587.4	587.3	587.1	587.1	587.2	587.3	587.4	587.5	587.9
160°	598.6	598.4	598.2	598.0	597.7	597.6	597.6	597.6	597.6	597.6	598.2
162.5°	608.4	608.1	607.8	607.4	607.2	607.1	607.2	607.3	607.3	607.4	608.0
165°	621.0	620.7	620.4	620.0	619.6	619.5	619.5	619.5	619.5	619.5	620.2
167.5°	631.1	630.6	630.2	629.7	629.3	629.1	629.2	629.3	629.4	629.5	630.2
170°	636.8	636.3	635.9	635.4	635.0	634.7	634.7	634.7	634.7	634.7	635.5
172.5°	641.2	640.8	640.3	639.9	639.4	639.3	639.3	639.3	639.3	639.3	640.0
175°	646.0	645.5	645.1	644.6	644.2	643.9	643.9	643.9	643.9	643.9	644.6
177.5°	647.9	647.6	647.2	646.8	646.4	646.2	646.2	646.2	646.2	646.2	646.8
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5

TEST NUMBER: P331881-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	9.8	9.8	9.8	9.8	9.9	9.9	10.0	10.1
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	20.2	20.6	21.0	21.1	21.0	20.8	20.7	20.5
95°	38.5	39.0	39.4	39.7	39.7	39.7	39.7	39.7
97.5°	59.9	60.5	61.0	61.2	61.2	61.1	61.1	61.0
100°	75.4	75.8	76.2	76.4	76.6	76.9	77.0	77.3
102.5°	93.4	93.7	94.0	94.2	94.2	94.1	94.1	94.0
105°	120.0	120.0	120.0	120.1	120.4	120.6	120.8	121.1
107.5°	148.9	149.3	149.6	149.8	149.6	149.5	149.4	149.3
110°	168.3	168.7	169.2	169.2	169.1	168.8	168.6	168.4

TEST NUMBER: P331881-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	187.5	188.1	188.6	188.9	188.9	188.8	188.8	188.7
115°	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7
117.5°	246.6	246.5	246.5	246.3	246.0	245.7	245.4	245.0
120°	266.3	266.2	266.1	265.9	265.6	265.5	265.2	265.0
122.5°	286.2	286.0	285.7	285.3	285.1	284.7	284.5	284.1
125°	315.9	315.5	315.0	314.6	314.1	313.7	313.3	312.8
127.5°	345.3	344.6	344.0	343.5	343.0	342.4	341.9	341.3
130°	364.8	364.4	363.9	363.3	362.5	361.7	360.9	360.1
132.5°	383.7	383.2	382.6	382.1	381.5	380.8	380.2	379.6
135°	412.1	411.6	411.2	410.8	410.6	410.4	410.2	409.9
137.5°	439.8	439.3	438.9	438.5	438.0	437.6	437.1	436.7
140°	458.1	457.9	457.8	457.4	456.6	455.8	455.0	454.2
142.5°	475.1	475.0	474.9	474.6	473.9	473.3	472.7	472.1
145°	500.2	500.2	500.1	499.7	499.3	498.8	498.4	497.9
147.5°	524.0	524.0	524.0	523.6	523.0	522.3	521.7	520.9
150°	538.6	538.6	538.6	538.3	537.6	536.9	536.3	535.6
152.5°	552.1	552.2	552.4	552.1	551.6	551.0	550.5	549.8
155°	571.6	572.0	572.5	572.3	571.5	570.7	570.0	569.2
157.5°	588.4	588.9	589.3	589.2	588.6	588.0	587.4	586.7
160°	598.8	599.3	599.9	599.9	599.5	599.1	598.6	598.2
162.5°	608.5	609.1	609.7	609.6	608.9	608.1	607.4	606.7
165°	620.9	621.5	622.2	622.1	621.3	620.5	619.8	619.0
167.5°	630.9	631.6	632.3	632.3	631.6	630.9	630.2	629.5
170°	636.3	637.1	637.9	637.9	637.1	636.3	635.5	634.7
172.5°	640.6	641.3	642.0	642.0	641.2	640.4	639.6	638.8
175°	645.2	646.0	646.7	646.6	645.8	645.0	644.2	643.4
177.5°	647.4	647.9	648.5	648.4	647.7	647.1	646.5	645.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5

(END OF REPORT)