

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923924

Luminaire Tested: DFN2DIP-TR4F0-110D120US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923924
REPORT IS A COMBINATION OF REPORTS P900528 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D120US940-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17807.4 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 204
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923924

CATALOG NUMBER: DFN2DIP-TR4F0-110D120US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923924

CATALOG NUMBER: DFN2DIP-TR4F0-110D120US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	98	93	90	86	90	86	83	80	72	70	68	59	58	57	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3221	3221	3221
5°	3226	3169	3190
10°	3194	3107	3086
15°	3150	3005	2925
20°	3092	2863	2728
25°	3032	2704	2538
30°	2952	2542	2297
35°	2874	2367	2085
40°	2794	2185	1842
45°	2702	1985	1622
50°	2606	1782	1407
55°	2506	1565	1200
60°	2390	1339	988
65°	2257	1108	889
70°	2096	894	804
75°	1893	788	732
80°	1600	660	634
85°	1115	440	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2702 cd/sqm

TEST NUMBER: P923924

CATALOG NUMBER: DFN2DIP-TR4F0-110D120US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.9	2.1
10°-20°	1043.0	5.9
20°-30°	1464.4	8.2
30°-40°	1596.2	9.0
40°-50°	1467.1	8.2
50°-60°	1152.2	6.5
60°-70°	750.0	4.2
70°-80°	386.0	2.2
80°-90°	108.2	0.6
90°-100°	209.4	1.2
100°-110°	665.4	3.7
110°-120°	1138.7	6.4
120°-130°	1497.5	8.4
130°-140°	1680.9	9.4
140°-150°	1648.3	9.3
150°-160°	1382.7	7.8
160°-170°	917.0	5.1
170°-180°	320.5	1.8
0°-30°	2887.3	16.2
0°-40°	4483.6	25.2
0°-60°	7102.9	39.9
0°-90°	8347.1	46.9
90°-120°	2013.4	11.3
90°-150°	6840.1	38.4
90°-180°	9460.0	53.1
0°-180°	17807.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4054	4054	4054	4054	4054	
5°	4054	4036	3988	4021	4010	384
15°	3856	3815	3691	3621	3584	1087
25°	3500	3382	3140	2990	2935	1610
35°	3016	2829	2506	2275	2194	1888
45°	2466	2220	1834	1574	1486	1904
55°	1875	1588	1192	972	903	1675
65°	1266	968	638	514	502	1255
75°	675	418	294	268	264	714
85°	158	81	70	70	70	181
90°	3	37	100	94	97	18
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	

TEST NUMBER: P923924

CATALOG NUMBER: DFN2DIP-TR4F0-110D120US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4054.0	4054.0	4054.0	4054.0	4054.0
2.5°	4072.3	4054.0	4013.5	4050.5	4043.1
5°	4054.0	4035.7	3987.8	4020.9	4010.0
7.5°	4020.9	3999.1	3947.7	3962.1	3943.8
10°	3976.9	3951.2	3878.0	3866.7	3845.0
12.5°	3922.0	3888.9	3789.7	3767.8	3727.3
15°	3855.8	3815.4	3690.8	3621.1	3584.5
17.5°	3778.8	3720.0	3565.9	3485.2	3426.5
20°	3690.8	3617.2	3433.9	3342.4	3261.4
22.5°	3595.5	3510.9	3298.1	3173.5	3118.6
25°	3500.1	3382.5	3140.4	2990.2	2934.9
27.5°	3386.4	3261.4	2993.7	2821.2	2736.7
30°	3265.4	3125.6	2832.2	2645.3	2546.0
32.5°	3147.8	2978.8	2678.3	2458.1	2366.2
35°	3015.9	2828.6	2506.0	2274.8	2193.8
37.5°	2887.4	2685.4	2344.4	2091.0	1999.6
40°	2751.6	2531.7	2175.5	1915.0	1819.7
42.5°	2612.2	2377.5	2007.0	1735.3	1643.8
45°	2465.5	2219.5	1834.5	1573.7	1485.8
47.5°	2326.1	2065.7	1669.5	1408.6	1328.1
50°	2171.9	1911.6	1508.0	1254.5	1177.9
52.5°	2021.3	1746.1	1353.8	1111.7	1042.0
55°	1874.6	1588.5	1192.2	972.3	902.7
57.5°	1724.4	1430.8	1049.4	843.9	785.1
60°	1570.2	1276.8	898.8	711.9	653.2
62.5°	1420.0	1126.5	770.3	594.4	565.2
65°	1265.8	968.4	638.4	513.8	502.5
67.5°	1119.1	821.7	513.8	451.1	440.2
70°	964.9	678.9	425.4	388.9	374.1
72.5°	818.1	546.5	355.8	326.5	319.1
75°	674.9	418.0	293.5	267.8	264.3
77.5°	532.1	297.0	231.2	216.4	209.0
80°	399.8	212.9	175.9	161.6	161.6
82.5°	278.7	143.2	121.1	113.7	113.7
85°	157.7	80.6	69.6	69.6	69.6
87.5°	58.8	29.2	29.2	25.7	25.7
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5

TEST NUMBER: P923924

CATALOG NUMBER: DFN2DIP-TR4F0-110D120US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1

TEST NUMBER: P923924

CATALOG NUMBER: DFN2DIP-TR4F0-110D120US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.90	11.71	11.89	12.71	14.02	6.88	7.68	7.87	8.68	10.00
	3H	12.58	13.30	13.58	14.31	15.65	8.07	8.79	9.07	9.79	11.13
	4H	13.19	13.87	14.20	14.88	16.22	8.52	9.20	9.53	10.21	11.55
	6H	13.61	14.23	14.63	15.25	16.61	8.84	9.46	9.86	10.48	11.84
	8H	13.73	14.33	14.76	15.36	16.71	8.93	9.52	9.96	10.55	11.91
	12H	13.79	14.36	14.83	15.38	16.76	8.97	9.54	10.00	10.56	11.94
4H	2H	10.92	11.60	11.94	12.61	13.96	7.47	8.15	8.49	9.16	10.51
	3H	12.75	13.31	13.77	14.35	15.71	8.82	9.38	9.85	10.42	11.78
	4H	13.44	13.95	14.47	14.99	16.37	9.37	9.88	10.40	10.91	12.30
	6H	13.95	14.40	15.00	15.45	16.83	9.79	10.23	10.83	11.28	12.66
	8H	14.13	14.54	15.17	15.59	16.98	9.91	10.33	10.96	11.38	12.77
	12H	14.22	14.59	15.28	15.66	17.05	9.98	10.35	11.04	11.41	12.81
8H	4H	13.40	13.82	14.45	14.86	16.26	9.64	10.06	10.69	11.11	12.50
	6H	13.97	14.31	15.04	15.40	16.79	10.16	10.51	11.23	11.59	12.99
	8H	14.18	14.49	15.26	15.56	16.97	10.36	10.66	11.43	11.73	13.14
	12H	14.32	14.59	15.40	15.65	17.11	10.47	10.74	11.55	11.81	13.26
12H	4H	13.35	13.73	14.42	14.79	16.19	9.65	10.02	10.71	11.08	12.48
	6H	13.94	14.24	15.02	15.32	16.73	10.21	10.51	11.29	11.59	13.00
	8H	14.16	14.43	15.24	15.50	16.95	10.42	10.69	11.50	11.76	13.21

END OF REPORT