

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923933

Luminaire Tested: DFN2DIP-TR4F0-120D050US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923933
REPORT IS A COMBINATION OF REPORTS P901924 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D050US940-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13509.4 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 163.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923933

CATALOG NUMBER: DFN2DIP-TR4F0-120D050US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923933

CATALOG NUMBER: DFN2DIP-TR4F0-120D050US940-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	98	94	91	96	93	89	86	83	80	78	73	71	70	65	63	62
2	94	86	80	75	88	82	77	72	73	69	66	65	62	59	58	55	53
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46
4	79	68	61	55	74	65	58	52	58	53	48	52	48	44	47	43	40
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	42	39	36
6	67	55	47	42	63	53	45	40	48	42	37	43	38	34	39	35	32
7	63	50	42	37	59	48	41	36	44	38	33	39	35	31	36	32	28
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26
9	54	42	35	30	51	40	33	29	37	31	27	34	29	25	30	26	23
10	51	39	32	27	48	37	31	26	34	28	25	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3513	3513	3513
5°	3519	3458	3480
10°	3484	3390	3366
15°	3436	3278	3191
20°	3373	3123	2976
25°	3308	2950	2769
30°	3221	2773	2506
35°	3135	2582	2274
40°	3048	2384	2009
45°	2947	2165	1769
50°	2843	1944	1535
55°	2734	1707	1309
60°	2608	1460	1078
65°	2462	1209	970
70°	2286	975	877
75°	2065	859	798
80°	1745	721	692
85°	1216	481	519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2947 cd/sqm

TEST NUMBER: P923933

CATALOG NUMBER: DFN2DIP-TR4F0-120D050US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.5	3.1
10°-20°	1137.8	8.4
20°-30°	1597.5	11.8
30°-40°	1741.4	12.9
40°-50°	1600.5	11.8
50°-60°	1256.9	9.3
60°-70°	818.2	6.1
70°-80°	421.2	3.1
80°-90°	110.2	0.8
90°-100°	49.6	0.4
100°-110°	185.0	1.4
110°-120°	490.6	3.6
120°-130°	813.6	6.0
130°-140°	864.3	6.4
140°-150°	803.2	5.9
150°-160°	645.8	4.8
160°-170°	416.1	3.1
170°-180°	143.2	1.1
0°-30°	3149.8	23.3
0°-40°	4891.2	36.2
0°-60°	7748.6	57.4
0°-90°	9098.1	67.3
90°-120°	725.2	5.4
90°-150°	3206.2	23.7
90°-180°	4411.0	32.7
0°-180°	13509.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4422	4422	4422	4422	4422	
5°	4422	4403	4350	4386	4375	419
15°	4206	4162	4026	3950	3910	1185
25°	3818	3690	3426	3262	3202	1756
35°	3290	3086	2734	2482	2393	2059
45°	2690	2421	2001	1717	1621	2077
55°	2045	1733	1301	1061	985	1827
65°	1381	1056	696	560	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	197
90°	1	13	22	27	29	13
95°	71	35	42	48	47	84
105°	331	364	66	78	83	354
115°	626	644	672	168	89	616
125°	885	899	920	928	931	789
135°	1095	1113	1122	1134	1131	846
145°	1271	1270	1288	1296	1290	795
155°	1399	1389	1402	1409	1400	645
165°	1474	1468	1471	1478	1471	416
175°	1508	1500	1502	1510	1499	144
180°	1505	1505	1505	1505	1505	

TEST NUMBER: P923933

CATALOG NUMBER: DFN2DIP-TR4F0-120D050US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	4442.5	4422.5	4378.4	4418.7	4410.6
5°	4422.5	4402.6	4350.3	4386.4	4374.6
7.5°	4386.4	4362.6	4306.6	4322.3	4302.3
10°	4338.4	4310.4	4230.5	4218.2	4194.5
12.5°	4278.5	4242.5	4134.1	4110.4	4066.3
15°	4206.4	4162.2	4026.3	3950.3	3910.4
17.5°	4122.3	4058.2	3890.0	3802.2	3738.0
20°	4026.3	3946.1	3746.1	3646.3	3557.9
22.5°	3922.3	3830.2	3597.9	3462.0	3402.1
25°	3818.3	3690.0	3425.9	3262.0	3201.7
27.5°	3694.3	3557.9	3265.8	3077.7	2985.5
30°	3562.2	3409.8	3089.6	2885.8	2777.5
32.5°	3434.0	3249.7	2921.9	2681.6	2581.3
35°	3290.1	3085.8	2733.7	2481.5	2393.2
37.5°	3149.9	2929.5	2557.5	2281.1	2181.3
40°	3001.7	2761.8	2373.3	2089.2	1985.1
42.5°	2849.6	2593.6	2189.4	1893.0	1793.2
45°	2689.6	2421.3	2001.3	1716.8	1620.8
47.5°	2537.5	2253.5	1821.2	1536.8	1448.9
50°	2369.5	2085.4	1645.0	1368.6	1285.0
52.5°	2205.1	1904.9	1476.9	1212.7	1136.8
55°	2045.0	1732.9	1300.6	1060.7	984.7
57.5°	1881.1	1560.9	1144.8	920.6	856.5
60°	1713.0	1392.8	980.4	776.7	712.6
62.5°	1549.1	1228.9	840.3	648.5	616.5
65°	1380.9	1056.5	696.4	560.5	548.2
67.5°	1220.8	896.3	560.5	492.1	480.3
70°	1052.7	740.6	464.1	424.2	408.0
72.5°	892.6	596.2	388.1	356.2	348.2
75°	736.3	456.0	320.2	292.1	288.3
77.5°	580.5	324.0	252.3	236.1	228.0
80°	436.1	232.3	191.9	176.2	176.2
82.5°	304.1	156.2	132.1	123.9	123.9
85°	172.0	87.9	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	1.1	13.0	21.8	27.3	29.3
92.5°	27.3	22.9	26.1	28.4	29.3
95°	70.7	34.8	42.4	48.0	46.8
97.5°	127.3	38.2	55.5	58.9	59.8
100°	192.8	43.6	62.1	70.7	72.9
102.5°	264.6	262.4	64.3	76.2	79.5
105°	331.0	363.7	66.4	78.4	82.8
107.5°	408.3	435.4	68.7	80.5	85.0
110°	482.4	505.2	190.6	81.7	86.0

TEST NUMBER: P923933

CATALOG NUMBER: DFN2DIP-TR4F0-120D050US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	571.6	553.1	83.8	87.1
115°	626.1	644.5	671.8	167.7	89.3
117.5°	690.3	712.0	730.7	574.8	289.6
120°	762.1	778.5	798.1	811.2	664.1
122.5°	823.0	840.5	862.4	868.9	870.0
125°	885.1	899.4	920.1	927.6	930.9
127.5°	941.7	957.0	973.5	984.3	985.3
130°	995.1	1012.6	1024.5	1036.5	1035.5
132.5°	1049.6	1063.8	1075.7	1085.6	1084.5
135°	1095.4	1112.9	1122.5	1133.5	1131.3
137.5°	1143.2	1156.3	1167.2	1178.1	1174.9
140°	1190.0	1198.8	1210.7	1220.5	1215.1
142.5°	1229.3	1237.0	1251.1	1259.7	1254.3
145°	1270.7	1269.5	1288.0	1295.7	1290.2
147.5°	1306.5	1303.2	1321.8	1327.2	1322.9
150°	1341.4	1333.8	1351.2	1357.7	1352.3
152.5°	1370.7	1362.1	1378.4	1385.0	1377.3
155°	1399.1	1389.4	1402.4	1408.9	1400.3
157.5°	1421.9	1413.3	1423.1	1430.7	1421.9
160°	1441.6	1435.0	1441.6	1448.0	1440.5
162.5°	1458.9	1452.5	1457.9	1465.5	1455.7
165°	1474.2	1467.8	1471.0	1478.5	1471.0
167.5°	1486.2	1479.6	1483.0	1490.6	1480.8
170°	1496.0	1489.4	1491.7	1499.2	1489.4
172.5°	1502.5	1496.0	1498.3	1505.8	1496.0
175°	1508.0	1500.3	1502.5	1510.1	1499.2
177.5°	1510.1	1502.5	1503.7	1511.3	1501.5
180°	1504.7	1504.7	1504.7	1504.7	1504.7

TEST NUMBER: P923933

CATALOG NUMBER: DFN2DIP-TR4F0-120D050US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.99	13.99	13.79	14.80	15.81	8.97	9.96	9.77	10.78	11.78
	3H	14.68	15.57	15.49	16.40	17.43	10.17	11.06	10.98	11.88	12.92
	4H	15.30	16.14	16.13	16.97	18.01	10.63	11.47	11.46	12.30	13.34
	6H	15.73	16.50	16.57	17.34	18.40	10.96	11.73	11.80	12.57	13.63
	8H	15.86	16.59	16.71	17.45	18.51	11.05	11.79	11.90	12.65	13.70
	12H	15.93	16.63	16.78	17.48	18.56	11.10	11.80	11.96	12.66	13.74
4H	2H	13.03	13.87	13.86	14.70	15.75	9.58	10.42	10.42	11.25	12.30
	3H	14.87	15.57	15.72	16.44	17.50	10.95	11.64	11.79	12.51	13.57
	4H	15.57	16.21	16.43	17.07	18.16	11.50	12.14	12.36	13.00	14.09
	6H	16.10	16.64	16.97	17.53	18.62	11.93	12.48	12.81	13.37	14.46
	8H	16.27	16.78	17.15	17.67	18.77	12.06	12.57	12.94	13.46	14.56
	12H	16.38	16.84	17.27	17.74	18.85	12.14	12.59	13.03	13.50	14.61
8H	4H	15.55	16.06	16.43	16.95	18.05	11.79	12.30	12.67	13.19	14.29
	6H	16.12	16.55	17.03	17.47	18.57	12.32	12.74	13.22	13.67	14.77
	8H	16.34	16.72	17.26	17.64	18.75	12.51	12.88	13.43	13.80	14.92
	12H	16.49	16.82	17.40	17.73	18.90	12.64	12.97	13.56	13.88	15.05
12H	4H	15.51	15.97	16.41	16.87	17.98	11.81	12.26	12.70	13.17	14.28
	6H	16.10	16.47	17.02	17.39	18.51	12.37	12.74	13.28	13.66	14.78
	8H	16.33	16.66	17.25	17.57	18.74	12.59	12.92	13.50	13.83	15.00