

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832113

Luminaire Tested: S123RDIP-S340D365U950-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832113  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D365U950-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2789.3 lumens  
Efficiency: N/A  
Efficacy: 124.5 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 22.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50				
1	99	95	91	88	91	88	85	82	74	72	70	62	61	59	51	50	49	44				
2	91	84	78	73	83	78	73	68	66	63	60	56	53	51	46	44	43	38				
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	42	39	37	34				
4	77	66	59	53	71	62	55	50	53	48	44	45	42	39	38	35	33	30				
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	35	32	30	26				
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	24				
7	61	49	42	36	56	46	39	35	40	35	31	35	31	28	30	26	24	22				
8	57	45	38	33	53	42	36	31	37	32	28	32	28	25	27	24	22	20				
9	53	41	34	29	49	39	33	28	34	29	25	30	26	23	26	23	20	18				
10	50	38	31	27	46	36	30	26	32	27	23	28	24	21	24	21	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	11408	11408	11408	11408	11408
5°	13545	13113	11479	9280	8616
10°	12272	13319	11423	7436	6379
15°	8450	11420	11302	6077	5046
20°	5879	8793	11074	5125	4435
25°	4480	6701	10745	4555	4087
30°	3899	5358	10332	4228	3786
35°	3581	4519	9746	3954	3511
40°	3267	4036	8982	3684	3260
45°	2950	3691	8156	3430	3009
50°	2678	3406	7182	3180	2699
55°	2423	3126	6247	2935	2316
60°	2170	2844	5425	2665	2189
65°	2004	2524	4671	2397	2071
70°	1627	2181	4076	2168	1681
75°	1426	1734	3452	1797	1481
80°	1296	1469	2827	1506	1401
85°	1186	1284	2149	1371	1284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 8605 cd/sqm



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.6	3.5
10°-20°	223.5	8.0
20°-30°	256.5	9.2
30°-40°	252.8	9.1
40°-50°	222.9	8.0
50°-60°	171.5	6.1
60°-70°	112.8	4.0
70°-80°	54.8	2.0
80°-90°	14.7	0.5
90°-100°	16.0	0.6
100°-110°	77.3	2.8
110°-120°	189.6	6.8
120°-130°	240.7	8.6
130°-140°	257.1	9.2
140°-150°	240.4	8.6
150°-160°	193.9	7.0
160°-170°	125.1	4.5
170°-180°	43.1	1.5
0°-30°	576.6	20.7
0°-40°	829.4	29.7
0°-60°	1223.8	43.9
0°-90°	1406.1	50.4
90°-120°	282.9	10.1
90°-150°	1021.1	36.6
90°-180°	1383.0	49.6
0°-180°	2789.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1060	1060	1060	1060	1060	
5°	1254	1214	1062	859	797	115
15°	758	1025	1014	545	453	214
25°	377	564	905	384	344	178
35°	272	344	742	301	267	170
45°	194	242	536	225	198	150
55°	129	167	333	156	123	116
65°	79	99	183	94	81	77
75°	34	42	83	43	36	37
85°	10	10	17	11	10	10
90°	10	8	0	8	10	5
95°	13	10	21	10	13	11
105°	15	74	100	74	15	31
115°	198	194	188	194	198	186
125°	271	270	266	270	271	242
135°	334	334	331	334	334	258
145°	385	385	382	385	385	241
155°	420	420	420	420	420	194
165°	442	442	443	442	442	125
175°	452	452	454	452	452	43
180°	454	454	454	454	454	



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1174.5	1170.8	1167.2	1166.1	1165.0	1161.5	1158.0	1150.2	1142.4	1134.3	1126.3
5°	1253.6	1254.1	1254.5	1253.4	1252.3	1247.8	1243.2	1233.6	1224.1	1213.6	1203.2
7.5°	1229.3	1236.2	1243.2	1244.5	1245.8	1249.3	1252.8	1250.6	1248.4	1244.5	1240.6
10°	1122.8	1122.4	1122.0	1129.8	1137.6	1160.9	1184.1	1196.1	1208.0	1218.6	1229.3
12.5°	949.0	949.7	950.3	976.0	1001.6	1023.5	1045.5	1075.9	1106.3	1139.1	1171.9
15°	758.3	768.9	779.6	802.4	825.2	858.2	891.2	932.1	972.9	1024.8	1076.8
17.5°	622.7	627.2	631.8	653.8	675.7	707.0	738.3	784.5	830.8	897.7	964.7
20°	513.2	517.3	521.4	537.3	553.2	583.1	613.1	657.2	701.3	767.6	833.9
22.5°	428.4	436.5	444.5	455.2	465.8	487.5	509.3	554.2	599.2	659.6	720.0
25°	377.2	380.9	384.6	393.7	402.8	423.7	444.5	474.3	504.1	564.2	624.4
27.5°	342.4	343.5	344.6	351.3	358.1	371.5	385.0	412.6	440.2	489.7	539.3
30°	313.7	315.7	317.6	322.9	328.1	337.8	347.6	367.2	386.7	431.1	475.4
32.5°	291.6	292.7	293.7	298.1	302.4	309.6	316.8	332.2	347.6	381.5	415.4
35°	272.5	272.7	272.9	276.1	279.4	286.4	293.3	306.1	318.9	343.9	368.9
37.5°	250.7	252.2	253.8	256.2	258.5	264.6	270.7	281.1	291.6	312.2	332.9
40°	232.5	233.8	235.1	237.9	240.7	245.5	250.3	259.9	269.4	287.2	305.0
42.5°	214.2	215.1	216.0	218.8	221.6	227.5	233.3	240.9	248.6	263.3	278.1
45°	193.8	196.0	198.1	201.2	204.2	209.2	214.2	222.0	229.9	242.5	255.1
47.5°	176.9	177.9	179.0	181.6	184.2	190.3	196.4	203.4	210.3	222.0	233.8
50°	159.9	160.3	160.8	163.2	165.6	171.0	176.4	184.5	192.5	203.4	214.2
52.5°	143.8	144.9	146.0	148.4	150.8	154.5	158.2	166.4	174.7	185.3	196.0
55°	129.1	129.7	130.4	132.1	133.8	138.2	142.5	149.7	156.9	166.6	176.4
57.5°	115.2	116.0	116.9	118.2	119.5	123.4	127.3	133.6	139.9	149.7	159.5
60°	100.8	101.9	103.0	104.5	106.0	109.1	112.1	117.8	123.4	132.1	140.8
62.5°	90.4	90.6	90.8	92.1	93.4	95.6	97.8	102.3	106.9	115.6	124.3
65°	78.7	79.3	80.0	80.6	81.3	83.0	84.7	88.6	92.6	99.1	105.6
67.5°	66.5	67.1	67.8	68.9	70.0	71.5	73.0	75.6	78.2	84.3	90.4
70°	51.7	51.7	51.7	53.4	55.2	57.8	60.4	62.4	64.3	69.3	74.3
72.5°	42.1	42.4	42.6	42.8	43.0	44.5	46.1	49.3	52.6	55.6	58.7
75°	34.3	34.5	34.8	35.0	35.2	35.6	36.1	37.2	38.2	41.7	45.2
77.5°	27.4	27.6	27.8	28.0	28.2	28.7	29.1	29.5	30.0	31.3	32.6
80°	20.9	21.1	21.3	21.5	21.7	21.9	22.2	22.6	23.0	23.7	24.3
82.5°	15.2	15.2	15.2	15.2	15.2	15.6	16.1	16.1	16.1	16.5	16.9
85°	9.6	9.6	9.6	9.8	10.0	10.0	10.0	10.2	10.4	10.4	10.4
87.5°	4.3	4.1	3.9	4.1	4.3	4.3	4.3	4.6	4.8	4.8	4.8
90°	10.1	10.0	9.8	9.7	9.5	9.3	9.0	8.7	8.4	8.1	7.1
92.5°	11.5	11.4	11.3	11.2	11.2	10.9	10.3	9.8	9.3	8.8	8.1
95°	12.8	12.8	12.8	12.8	12.8	12.5	12.0	11.5	11.0	10.5	9.6
97.5°	13.8	13.7	13.7	13.6	13.5	13.2	12.6	12.0	11.4	10.8	14.6
100°	14.2	14.1	14.0	13.9	13.9	13.5	12.9	12.3	11.7	11.1	22.8
102.5°	14.5	14.3	14.2	14.0	13.9	15.1	17.5	20.0	22.5	24.9	38.0
105°	14.8	14.7	14.5	14.4	14.2	20.8	34.0	47.3	60.6	73.8	80.6
107.5°	35.1	44.9	54.7	64.5	74.3	85.0	96.5	108.1	119.6	131.1	130.0
110°	92.7	103.4	114.1	124.8	135.6	142.1	144.6	147.1	149.6	152.0	151.2



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	175.6	175.8	175.9	176.1	176.2	176.0	175.3	174.6	174.0	173.3	172.5
115°	198.2	197.9	197.6	197.3	197.0	196.5	195.8	195.0	194.3	193.5	192.8
117.5°	216.4	216.4	216.3	216.2	216.1	215.8	215.2	214.6	214.0	213.4	213.0
120°	235.3	235.3	235.3	235.3	235.3	235.0	234.4	233.8	233.2	232.6	232.4
122.5°	253.8	253.8	253.7	253.6	253.5	253.3	252.9	252.6	252.2	251.8	251.5
125°	271.0	270.9	270.7	270.6	270.4	270.3	270.1	270.0	269.8	269.7	269.4
127.5°	287.9	288.0	288.2	288.3	288.5	288.5	288.2	288.0	287.8	287.6	287.2
130°	304.1	304.2	304.4	304.5	304.7	304.6	304.3	304.0	303.7	303.4	303.1
132.5°	318.9	319.1	319.4	319.6	319.8	319.8	319.5	319.2	318.9	318.6	318.3
135°	334.1	334.3	334.5	334.8	335.0	335.0	334.8	334.5	334.3	334.1	333.8
137.5°	348.6	348.7	348.9	349.0	349.2	349.1	348.7	348.3	347.9	347.6	347.4
140°	361.4	361.5	361.7	361.8	362.0	361.9	361.6	361.3	361.0	360.7	360.5
142.5°	373.2	373.4	373.6	373.9	374.1	374.1	373.9	373.6	373.4	373.2	373.0
145°	385.3	385.3	385.3	385.3	385.3	385.2	385.1	384.9	384.8	384.6	384.5
147.5°	394.1	394.5	394.8	395.2	395.6	395.7	395.5	395.4	395.2	395.1	394.9
150°	404.2	404.4	404.6	404.9	405.1	405.1	405.0	404.8	404.7	404.5	404.4
152.5°	412.3	412.7	413.0	413.4	413.8	413.8	413.5	413.2	412.9	412.6	412.6
155°	419.7	420.2	420.6	421.1	421.5	421.5	421.2	420.8	420.4	420.0	420.0
157.5°	426.1	426.7	427.3	427.9	428.5	428.6	428.1	427.7	427.2	426.8	426.9
160°	432.2	432.7	433.2	433.8	434.3	434.3	433.9	433.4	433.0	432.5	432.6
162.5°	437.9	438.4	438.8	439.3	439.7	439.7	439.1	438.6	438.1	437.6	437.6
165°	442.3	442.8	443.3	443.9	444.4	444.4	443.8	443.2	442.6	442.0	442.0
167.5°	445.7	446.3	446.9	447.5	448.1	448.1	447.5	446.9	446.3	445.7	445.7
170°	448.7	449.3	449.9	450.5	451.1	451.1	450.5	449.9	449.3	448.7	448.7
172.5°	450.4	451.1	451.7	452.4	453.1	453.1	452.5	451.9	451.3	450.7	450.6
175°	452.1	452.7	453.3	453.9	454.5	454.5	454.0	453.5	452.9	452.4	452.3
177.5°	452.4	453.2	453.9	454.7	455.4	455.5	454.9	454.3	453.7	453.1	453.0
180°	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1125.2	1124.1	1113.7	1103.3	1093.1	1082.9	1075.3	1067.6	1054.8	1042.0	1034.0
5°	1195.0	1186.7	1170.2	1153.7	1128.9	1104.1	1083.3	1062.4	1035.9	1009.4	987.3
7.5°	1233.9	1227.1	1207.1	1187.1	1154.3	1121.5	1088.9	1056.3	1017.2	978.1	944.7
10°	1234.9	1240.6	1224.1	1207.6	1170.6	1133.7	1089.4	1045.1	992.5	939.9	896.7
12.5°	1196.3	1220.6	1217.1	1213.6	1176.1	1138.5	1084.6	1030.7	966.2	901.7	847.6
15°	1123.9	1171.1	1185.0	1198.9	1167.8	1136.7	1075.5	1014.2	938.4	862.5	800.4
17.5°	1030.7	1096.8	1133.5	1170.2	1147.6	1125.0	1057.9	990.7	905.3	820.0	752.4
20°	920.3	1006.8	1064.4	1122.0	1113.7	1105.5	1036.1	966.8	874.7	782.6	709.4
22.5°	811.3	902.5	982.0	1061.6	1070.0	1078.5	1008.6	938.6	837.8	737.0	662.4
25°	717.2	810.0	904.7	999.4	1018.5	1037.7	971.2	904.7	800.2	695.7	621.6
27.5°	627.5	715.7	820.0	924.3	959.0	993.8	932.9	872.1	763.3	654.4	580.5
30°	554.2	633.1	739.6	846.0	894.5	942.9	887.1	831.3	723.3	615.3	542.9
32.5°	486.0	556.6	663.5	770.4	826.7	883.0	834.7	786.5	682.7	578.8	507.3
35°	432.1	495.4	595.1	694.8	757.8	820.8	781.3	741.7	640.3	538.8	471.3
37.5°	385.9	438.9	532.5	626.2	693.1	760.0	727.0	693.9	598.6	503.2	439.3
40°	347.6	390.2	477.3	564.5	630.1	695.7	667.4	639.2	553.8	468.4	408.7
42.5°	314.8	351.5	429.8	508.0	568.2	628.3	609.6	591.0	513.6	436.3	380.9
45°	285.9	316.8	385.6	454.5	509.9	565.3	550.6	535.8	469.1	402.4	351.5
47.5°	260.3	286.8	348.3	409.8	459.5	509.3	495.6	481.9	426.7	371.5	325.2
50°	236.8	259.4	310.7	362.0	406.7	451.5	440.2	428.9	383.3	337.6	297.7
52.5°	214.7	233.3	279.4	325.5	361.5	397.6	388.9	380.2	345.0	309.8	273.5
55°	193.6	210.7	249.6	288.5	319.4	350.2	341.5	332.9	305.5	278.1	246.2
57.5°	174.5	189.5	221.0	252.5	277.0	301.6	297.4	293.3	270.5	247.7	221.4
60°	154.3	167.7	194.9	222.0	241.8	261.6	256.8	252.0	235.7	219.4	196.8
62.5°	136.2	148.2	169.9	191.6	207.7	223.8	220.3	216.8	204.4	192.1	173.4
65°	117.3	129.1	146.7	164.3	176.9	189.5	186.4	183.4	174.0	164.7	149.7
67.5°	100.2	109.9	125.1	140.4	148.8	157.3	155.6	153.8	146.7	139.5	127.8
70°	82.8	91.3	103.9	116.5	122.3	128.2	128.8	129.5	123.0	116.5	107.8
72.5°	65.4	72.1	83.9	95.6	100.2	104.7	104.5	104.3	100.4	96.5	88.6
75°	50.2	55.2	64.3	73.4	77.3	81.3	82.1	83.0	79.3	75.6	71.3
77.5°	36.1	39.5	46.5	53.4	57.8	62.1	62.6	63.0	61.3	59.5	55.4
80°	25.4	26.5	30.9	35.2	39.8	44.3	45.0	45.6	43.9	42.1	39.5
82.5°	17.6	18.3	19.8	21.3	25.0	28.7	29.5	30.4	29.5	28.7	25.9
85°	10.6	10.9	11.5	12.2	13.9	15.6	16.5	17.4	16.9	16.5	15.0
87.5°	4.8	4.8	5.0	5.2	5.6	6.1	7.2	8.3	7.6	7.0	6.3
90°	6.1	5.2	4.2	3.3	2.6	1.8	1.1	0.3	1.1	1.8	2.6
92.5°	7.4	6.7	6.1	6.0	6.4	6.9	7.3	7.8	7.3	6.9	6.4
95°	8.8	8.0	7.2	8.3	11.3	14.4	17.5	20.6	17.5	14.4	11.3
97.5°	18.4	22.2	26.1	29.0	31.1	33.2	35.3	37.4	35.3	33.2	31.1
100°	34.5	46.2	57.9	63.0	61.5	60.0	58.5	57.0	58.5	60.0	61.5
102.5°	51.0	64.1	77.1	83.1	82.1	81.2	80.2	79.2	80.2	81.2	82.1
105°	87.3	94.1	100.8	103.8	102.9	102.1	101.3	100.5	101.3	102.1	102.9
107.5°	128.9	127.8	126.6	125.7	125.1	124.4	123.7	123.0	123.7	124.4	125.1
110°	150.4	149.6	148.7	148.0	147.4	146.8	146.2	145.6	146.2	146.8	147.4





TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	171.6	170.8	170.0	169.3	168.8	168.3	167.7	167.2	167.7	168.3	168.8
115°	192.2	191.5	190.8	190.2	189.8	189.3	188.9	188.4	188.9	189.3	189.8
117.5°	212.6	212.3	211.9	211.4	210.9	210.4	209.9	209.3	209.9	210.4	210.9
120°	232.2	231.9	231.7	231.3	230.6	229.9	229.2	228.6	229.2	229.9	230.6
122.5°	251.2	250.9	250.6	250.2	249.7	249.2	248.6	248.1	248.6	249.2	249.7
125°	269.1	268.8	268.5	268.0	267.4	266.8	266.2	265.6	266.2	266.8	267.4
127.5°	286.8	286.4	286.1	285.6	285.0	284.4	283.8	283.2	283.8	284.4	285.0
130°	302.8	302.5	302.2	301.8	301.2	300.6	300.0	299.4	300.0	300.6	301.2
132.5°	318.1	317.9	317.7	317.3	316.7	316.1	315.5	314.9	315.5	316.1	316.7
135°	333.5	333.2	332.9	332.5	332.1	331.6	331.2	330.7	331.2	331.6	332.1
137.5°	347.3	347.1	347.0	346.6	346.0	345.4	344.8	344.2	344.8	345.4	346.0
140°	360.3	360.0	359.8	359.5	359.0	358.6	358.1	357.7	358.1	358.6	359.0
142.5°	372.7	372.5	372.3	371.9	371.5	371.1	370.6	370.2	370.6	371.1	371.5
145°	384.3	384.2	384.0	383.7	383.2	382.7	382.1	381.6	382.1	382.7	383.2
147.5°	394.8	394.6	394.5	394.2	393.9	393.5	393.1	392.7	393.1	393.5	393.9
150°	404.2	404.1	403.9	403.8	403.5	403.3	403.1	402.9	403.1	403.3	403.5
152.5°	412.5	412.4	412.3	412.3	412.2	412.1	412.0	412.0	412.0	412.1	412.2
155°	419.9	419.8	419.7	419.8	419.9	420.1	420.2	420.4	420.2	420.1	419.9
157.5°	426.9	427.0	427.1	427.1	427.1	427.1	427.1	427.1	427.1	427.1	427.1
160°	432.7	432.7	432.8	432.9	433.0	433.0	433.1	433.2	433.1	433.0	433.0
162.5°	437.7	437.8	437.9	438.0	438.2	438.5	438.7	438.9	438.7	438.5	438.2
165°	442.1	442.2	442.3	442.4	442.6	442.9	443.1	443.3	443.1	442.9	442.6
167.5°	445.7	445.7	445.7	445.8	446.1	446.4	446.7	447.0	446.7	446.4	446.1
170°	448.7	448.7	448.7	448.8	449.1	449.4	449.7	450.0	449.7	449.4	449.1
172.5°	450.6	450.5	450.4	450.6	450.9	451.3	451.7	452.1	451.7	451.3	450.9
175°	452.3	452.2	452.1	452.3	452.6	453.0	453.4	453.8	453.4	453.0	452.6
177.5°	452.9	452.9	452.8	452.9	453.3	453.7	454.1	454.4	454.1	453.7	453.3
180°	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1025.9	1013.5	1001.2	992.3	983.3	972.3	961.2	960.8	960.3	952.1	943.8
5°	965.1	943.6	922.1	901.0	879.9	858.9	837.8	833.0	828.2	821.0	813.9
7.5°	911.2	876.9	842.6	815.6	788.7	767.6	746.5	732.2	717.8	706.8	695.7
10°	853.4	810.8	768.3	735.7	703.1	680.3	657.4	640.9	624.4	616.6	608.8
12.5°	793.5	747.2	700.9	669.0	637.0	609.6	582.3	567.3	552.3	541.4	530.6
15°	738.3	688.5	638.8	604.9	571.0	545.3	519.7	504.7	489.7	478.9	468.0
17.5°	684.8	634.6	584.4	550.1	515.8	492.5	469.3	454.7	440.2	433.4	426.7
20°	636.2	585.5	534.9	502.5	470.2	447.4	424.5	416.7	408.9	402.6	396.3
22.5°	587.9	539.3	490.6	459.5	428.4	411.9	395.4	389.1	382.8	378.0	373.3
25°	547.5	499.1	450.6	423.5	396.3	383.5	370.7	366.5	362.4	357.6	352.8
27.5°	506.7	460.6	414.5	392.8	371.1	360.7	350.2	345.0	339.8	335.9	332.0
30°	470.6	428.0	385.4	367.4	349.4	340.2	331.1	325.5	319.8	316.1	312.4
32.5°	435.8	398.0	360.2	344.8	329.4	320.5	311.6	306.1	300.7	296.4	292.0
35°	403.7	370.9	338.1	323.9	309.8	300.9	292.0	286.6	281.1	276.8	272.5
37.5°	375.4	345.7	315.9	302.7	289.4	281.6	273.8	268.1	262.5	257.9	253.3
40°	348.9	322.6	296.4	283.5	270.7	262.2	253.8	248.8	243.8	239.6	235.5
42.5°	325.5	301.3	277.2	264.6	252.0	244.0	236.0	230.1	224.2	221.8	219.4
45°	300.7	279.4	258.1	245.9	233.8	225.3	216.8	211.8	206.8	204.7	202.5
47.5°	279.0	259.2	239.4	227.5	215.5	207.9	200.3	196.4	192.5	189.5	186.4
50°	257.7	238.6	219.4	207.9	196.4	189.9	183.4	178.6	173.8	171.6	169.5
52.5°	237.3	219.9	202.5	190.8	179.0	172.7	166.4	162.3	158.2	153.6	149.0
55°	214.2	199.0	183.8	173.4	162.9	156.4	149.9	145.1	140.4	135.6	130.8
57.5°	195.1	180.1	165.1	155.8	146.4	140.1	133.8	128.6	123.4	119.5	115.6
60°	174.2	161.2	148.2	139.1	129.9	123.8	117.8	112.8	107.8	105.8	103.9
62.5°	154.7	142.5	130.4	122.3	114.3	108.4	102.5	99.3	96.0	94.7	93.4
65°	134.7	124.3	113.8	106.5	99.1	94.1	89.1	87.6	86.0	85.0	83.9
67.5°	116.0	107.1	98.2	91.7	85.2	81.7	78.2	76.5	74.7	73.4	72.1
70°	99.1	91.3	83.4	77.8	72.1	68.9	65.6	64.1	62.6	60.2	57.8
72.5°	80.8	74.7	68.7	64.3	60.0	57.1	54.3	51.3	48.2	46.1	43.9
75°	66.9	60.8	54.8	50.6	46.5	43.2	40.0	38.9	37.8	37.2	36.5
77.5°	51.3	46.1	40.8	37.6	34.3	32.8	31.3	30.6	30.0	29.8	29.5
80°	36.9	32.6	28.2	26.5	24.8	24.3	23.9	23.5	23.0	22.8	22.6
82.5°	23.0	20.9	18.7	18.3	17.8	17.6	17.4	17.2	16.9	16.7	16.5
85°	13.5	12.6	11.7	11.5	11.3	11.1	10.9	10.9	10.9	10.9	10.9
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.4	5.2
90°	3.3	4.2	5.2	6.1	7.1	8.1	8.4	8.7	9.0	9.3	9.5
92.5°	6.0	6.1	6.7	7.4	8.1	8.8	9.3	9.8	10.3	10.9	11.2
95°	8.3	7.2	8.0	8.8	9.6	10.5	11.0	11.5	12.0	12.5	12.8
97.5°	29.0	26.1	22.2	18.4	14.6	10.8	11.4	12.0	12.6	13.2	13.5
100°	63.0	57.9	46.2	34.5	22.8	11.1	11.7	12.3	12.9	13.5	13.9
102.5°	83.1	77.1	64.1	51.0	38.0	24.9	22.5	20.0	17.5	15.1	13.9
105°	103.8	100.8	94.1	87.3	80.6	73.8	60.6	47.3	34.0	20.8	14.2
107.5°	125.7	126.6	127.8	128.9	130.0	131.1	119.6	108.1	96.5	85.0	74.3
110°	148.0	148.7	149.6	150.4	151.2	152.0	149.6	147.1	144.6	142.1	135.6



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	169.3	170.0	170.8	171.6	172.5	173.3	174.0	174.6	175.3	176.0	176.2
115°	190.2	190.8	191.5	192.2	192.8	193.5	194.3	195.0	195.8	196.5	197.0
117.5°	211.4	211.9	212.3	212.6	213.0	213.4	214.0	214.6	215.2	215.8	216.1
120°	231.3	231.7	231.9	232.2	232.4	232.6	233.2	233.8	234.4	235.0	235.3
122.5°	250.2	250.6	250.9	251.2	251.5	251.8	252.2	252.6	252.9	253.3	253.5
125°	268.0	268.5	268.8	269.1	269.4	269.7	269.8	270.0	270.1	270.3	270.4
127.5°	285.6	286.1	286.4	286.8	287.2	287.6	287.8	288.0	288.2	288.5	288.5
130°	301.8	302.2	302.5	302.8	303.1	303.4	303.7	304.0	304.3	304.6	304.7
132.5°	317.3	317.7	317.9	318.1	318.3	318.6	318.9	319.2	319.5	319.8	319.8
135°	332.5	332.9	333.2	333.5	333.8	334.1	334.3	334.5	334.8	335.0	335.0
137.5°	346.6	347.0	347.1	347.3	347.4	347.6	347.9	348.3	348.7	349.1	349.2
140°	359.5	359.8	360.0	360.3	360.5	360.7	361.0	361.3	361.6	361.9	362.0
142.5°	371.9	372.3	372.5	372.7	373.0	373.2	373.4	373.6	373.9	374.1	374.1
145°	383.7	384.0	384.2	384.3	384.5	384.6	384.8	384.9	385.1	385.2	385.3
147.5°	394.2	394.5	394.6	394.8	394.9	395.1	395.2	395.4	395.5	395.7	395.6
150°	403.8	403.9	404.1	404.2	404.4	404.5	404.7	404.8	405.0	405.1	405.1
152.5°	412.3	412.3	412.4	412.5	412.6	412.6	412.9	413.2	413.5	413.8	413.8
155°	419.8	419.7	419.8	419.9	420.0	420.0	420.4	420.8	421.2	421.5	421.5
157.5°	427.1	427.1	427.0	426.9	426.9	426.8	427.2	427.7	428.1	428.6	428.5
160°	432.9	432.8	432.7	432.7	432.6	432.5	433.0	433.4	433.9	434.3	434.3
162.5°	438.0	437.9	437.8	437.7	437.6	437.6	438.1	438.6	439.1	439.7	439.7
165°	442.4	442.3	442.2	442.1	442.0	442.0	442.6	443.2	443.8	444.4	444.4
167.5°	445.8	445.7	445.7	445.7	445.7	445.7	446.3	446.9	447.5	448.1	448.1
170°	448.8	448.7	448.7	448.7	448.7	448.7	449.3	449.9	450.5	451.1	451.1
172.5°	450.6	450.4	450.5	450.6	450.6	450.7	451.3	451.9	452.5	453.1	453.1
175°	452.3	452.1	452.2	452.3	452.3	452.4	452.9	453.5	454.0	454.5	454.5
177.5°	452.9	452.8	452.9	452.9	453.0	453.1	453.7	454.3	454.9	455.5	455.4
180°	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8	453.8



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1059.8	1059.8	1059.8	1059.8
2.5°	941.6	939.5	938.6	937.7
5°	807.1	800.4	798.9	797.4
7.5°	692.9	690.0	680.7	671.4
10°	600.1	591.4	587.5	583.6
12.5°	522.5	514.5	513.2	511.9
15°	462.3	456.7	454.7	452.8
17.5°	422.8	418.9	416.5	414.1
20°	393.5	390.6	388.9	387.2
22.5°	371.1	368.9	367.6	366.3
25°	349.6	346.3	345.2	344.1
27.5°	329.2	326.3	325.2	324.2
30°	310.0	307.6	306.1	304.6
32.5°	289.2	286.4	285.5	284.6
35°	270.7	269.0	268.1	267.2
37.5°	251.2	249.0	247.7	246.4
40°	234.4	233.3	232.7	232.0
42.5°	217.5	215.5	215.3	215.1
45°	200.5	198.6	198.1	197.7
47.5°	184.7	182.9	182.7	182.5
50°	167.1	164.7	162.9	161.2
52.5°	146.9	144.7	143.2	141.7
55°	128.4	126.0	124.7	123.4
57.5°	114.5	113.4	112.8	112.1
60°	103.2	102.5	102.1	101.7
62.5°	92.8	92.1	92.1	92.1
65°	83.2	82.6	81.9	81.3
67.5°	70.8	69.5	69.3	69.1
70°	55.8	53.9	53.7	53.4
72.5°	43.7	43.5	43.0	42.6
75°	36.1	35.6	35.6	35.6
77.5°	29.1	28.7	28.7	28.7
80°	22.4	22.2	22.4	22.6
82.5°	16.5	16.5	16.3	16.1
85°	10.6	10.4	10.4	10.4
87.5°	5.2	5.2	5.2	5.2
90°	9.7	9.8	10.0	10.1
92.5°	11.2	11.3	11.4	11.5
95°	12.8	12.8	12.8	12.8
97.5°	13.6	13.7	13.7	13.8
100°	13.9	14.0	14.1	14.2
102.5°	14.0	14.2	14.3	14.5
105°	14.4	14.5	14.7	14.8
107.5°	64.5	54.7	44.9	35.1
110°	124.8	114.1	103.4	92.7



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	176.1	175.9	175.8	175.6
115°	197.3	197.6	197.9	198.2
117.5°	216.2	216.3	216.4	216.4
120°	235.3	235.3	235.3	235.3
122.5°	253.6	253.7	253.8	253.8
125°	270.6	270.7	270.9	271.0
127.5°	288.3	288.2	288.0	287.9
130°	304.5	304.4	304.2	304.1
132.5°	319.6	319.4	319.1	318.9
135°	334.8	334.5	334.3	334.1
137.5°	349.0	348.9	348.7	348.6
140°	361.8	361.7	361.5	361.4
142.5°	373.9	373.6	373.4	373.2
145°	385.3	385.3	385.3	385.3
147.5°	395.2	394.8	394.5	394.1
150°	404.9	404.6	404.4	404.2
152.5°	413.4	413.0	412.7	412.3
155°	421.1	420.6	420.2	419.7
157.5°	427.9	427.3	426.7	426.1
160°	433.8	433.2	432.7	432.2
162.5°	439.3	438.8	438.4	437.9
165°	443.9	443.3	442.8	442.3
167.5°	447.5	446.9	446.3	445.7
170°	450.5	449.9	449.3	448.7
172.5°	452.4	451.7	451.1	450.4
175°	453.9	453.3	452.7	452.1
177.5°	454.7	453.9	453.2	452.4
180°	453.8	453.8	453.8	453.8



TEST NUMBER: P832113

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.24	10.05	10.21	11.02	12.29	13.91	14.72	14.87	15.69	16.96
	3H	10.46	11.18	11.44	12.17	13.46	15.40	16.13	16.38	17.11	18.40
	4H	10.84	11.53	11.83	12.51	13.81	15.89	16.58	16.88	17.56	18.86
	6H	11.12	11.75	12.12	12.74	14.06	16.20	16.83	17.20	17.82	19.14
	8H	11.21	11.81	12.22	12.81	14.12	16.28	16.88	17.29	17.89	19.20
	12H	11.26	11.83	12.27	12.83	14.16	16.31	16.88	17.32	17.88	19.21
4H	2H	9.96	10.65	10.96	11.63	12.93	13.90	14.58	14.89	15.57	16.87
	3H	11.33	11.90	12.33	12.91	14.23	15.56	16.12	16.56	17.14	18.45
	4H	11.78	12.30	12.80	13.31	14.65	16.16	16.68	17.17	17.69	19.03
	6H	12.15	12.60	13.17	13.63	14.96	16.60	17.04	17.62	18.07	19.41
	8H	12.28	12.69	13.30	13.72	15.07	16.73	17.14	17.75	18.17	19.52
	12H	12.35	12.73	13.39	13.77	15.12	16.79	17.16	17.83	18.20	19.56
8H	4H	12.10	12.51	13.12	13.54	14.89	16.13	16.54	17.15	17.57	18.92
	6H	12.56	12.90	13.61	13.97	15.32	16.62	16.97	17.67	18.03	19.38
	8H	12.76	13.06	13.81	14.11	15.47	16.81	17.11	17.86	18.16	19.53
	12H	12.90	13.16	13.95	14.20	15.61	16.92	17.19	17.98	18.23	19.64
12H	4H	12.11	12.48	13.15	13.52	14.88	16.08	16.45	17.12	17.49	18.84
	6H	12.62	12.92	13.68	13.97	15.34	16.60	16.90	17.65	17.95	19.32
	8H	12.84	13.10	13.90	14.15	15.56	16.79	17.05	17.85	18.10	19.51