

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331283-830

Luminaire Tested: **SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331283-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4765.8 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331283-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot



TEST NUMBER: P331283-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	18	16	14
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779

TEST NUMBER: P331283-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	0.9
10°-20°	117.8	2.5
20°-30°	173.2	3.6
30°-40°	201.2	4.2
40°-50°	200.9	4.2
50°-60°	175.2	3.7
60°-70°	129.6	2.7
70°-80°	73.4	1.5
80°-90°	24.9	0.5
90°-100°	82.2	1.7
100°-110°	255.3	5.4
110°-120°	436.4	9.2
120°-130°	573.9	12.0
130°-140°	644.2	13.5
140°-150°	631.6	13.3
150°-160°	529.8	11.1
160°-170°	351.4	7.4
170°-180°	122.8	2.6
0°-30°	332.9	7.0
0°-40°	534.0	11.2
0°-60°	910.2	19.1
0°-90°	1138.1	23.9
90°-120°	774.0	16.2
90°-150°	2623.7	55.1
90°-180°	3628.0	76.1
0°-180°	4765.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	1	15	38	36	37	4
95°	57	67	70	70	68	65
105°	235	239	241	243	243	249
115°	438	444	442	441	438	433
125°	637	646	644	641	639	569
135°	824	836	839	837	834	637
145°	1001	1008	1015	1016	1012	625
155°	1144	1147	1151	1156	1153	526
165°	1245	1244	1244	1251	1246	351
175°	1295	1292	1290	1297	1291	123
180°	1297	1297	1297	1297	1297	



TEST NUMBER: P331283-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.4	6.8	7.3	7.6	8.1	8.8	9.7	10.7	11.5	12.4	12.2
90°	1.1	4.1	7.0	9.9	12.8	16.9	22.2	27.6	33.0	38.4	37.8
92.5°	19.5	21.6	23.8	25.9	28.1	29.8	31.0	32.3	33.6	34.8	34.9
95°	56.9	59.4	61.8	64.2	66.6	68.1	68.6	69.1	69.6	70.0	70.0
97.5°	104.1	106.1	108.3	110.5	112.5	114.1	115.0	115.9	116.9	117.8	117.8
100°	139.0	141.0	143.0	144.9	146.8	148.2	148.9	149.6	150.3	151.1	151.1
102.5°	175.9	177.4	179.0	180.5	182.1	183.3	184.3	185.1	186.1	187.0	187.2
105°	235.4	236.1	236.9	237.6	238.3	238.9	239.4	239.9	240.3	240.8	241.4
107.5°	295.4	296.4	297.6	298.6	299.6	300.2	300.2	300.2	300.2	300.2	300.4
110°	333.9	335.4	336.9	338.3	339.8	340.5	340.5	340.5	340.5	340.5	340.5

TEST NUMBER: P331283-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.0	377.4	378.9	380.3	381.8	382.5	382.2	382.0	381.8	381.6	381.1
115°	437.9	439.4	440.8	442.3	443.7	444.2	443.7	443.3	442.8	442.3	442.1
117.5°	499.6	501.6	503.6	505.5	507.5	507.7	506.4	505.0	503.7	502.3	501.7
120°	540.8	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	540.8
122.5°	578.5	580.9	583.2	585.5	587.9	588.3	587.0	585.6	584.3	582.9	582.3
125°	637.2	639.4	641.6	643.8	645.9	646.7	645.9	645.3	644.5	643.8	643.0
127.5°	694.4	697.1	699.9	702.7	705.4	706.4	705.5	704.6	703.8	702.9	702.0
130°	730.3	733.4	736.6	739.7	742.9	744.2	743.8	743.3	742.8	742.3	741.8
132.5°	770.5	773.2	775.7	778.3	780.9	782.2	782.3	782.4	782.5	782.6	781.6
135°	824.4	827.1	829.8	832.5	835.1	836.7	837.2	837.6	838.2	838.7	838.4
137.5°	881.1	883.4	885.5	887.7	889.9	891.3	891.9	892.6	893.2	893.8	893.6
140°	915.3	917.5	919.6	921.9	924.1	925.8	927.0	928.2	929.4	930.6	930.6
142.5°	950.4	952.5	954.7	956.9	959.0	960.5	961.4	962.2	963.1	963.9	964.1
145°	1000.7	1002.4	1004.1	1005.8	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1
147.5°	1045.6	1047.6	1049.6	1051.7	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7
150°	1076.2	1077.7	1079.1	1080.6	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9
152.5°	1103.3	1104.8	1106.3	1107.8	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2
155°	1144.2	1144.8	1145.6	1146.3	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9
157.5°	1178.9	1179.4	1179.9	1180.3	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8
160°	1200.0	1200.4	1200.9	1201.4	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7
162.5°	1219.2	1219.3	1219.4	1219.5	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4
165°	1244.8	1244.6	1244.3	1244.1	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5
167.5°	1266.3	1265.6	1264.8	1264.1	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5
170°	1277.7	1277.0	1276.2	1275.4	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0
172.5°	1285.5	1284.9	1284.1	1283.4	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9
175°	1295.2	1294.5	1293.7	1293.0	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5
177.5°	1299.1	1298.5	1298.0	1297.4	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

TEST NUMBER: P331283-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	11.8	11.5	11.1	10.9	10.9	10.9	10.9	10.8
90°	37.3	36.9	36.4	36.3	36.5	36.8	36.9	37.2
92.5°	35.0	35.1	35.3	35.3	35.3	35.3	35.4	35.4
95°	70.0	70.0	70.0	69.8	69.4	68.9	68.3	67.9
97.5°	117.8	117.8	117.8	117.8	117.7	117.7	117.6	117.6
100°	151.1	151.1	151.1	151.0	150.7	150.5	150.2	150.0
102.5°	187.4	187.6	187.8	187.8	187.5	187.3	187.0	186.8
105°	241.9	242.3	242.8	243.1	243.1	243.1	243.1	243.1
107.5°	300.6	300.8	301.0	300.5	299.4	298.3	297.2	296.1
110°	340.5	340.5	340.5	340.2	339.4	338.7	337.9	337.2

TEST NUMBER: P331283-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.5	379.9	379.4	378.8	378.2	377.7	377.2	376.6
115°	441.9	441.6	441.3	440.8	440.2	439.4	438.7	437.9
117.5°	501.1	500.6	500.0	499.4	498.6	497.9	497.1	496.4
120°	540.8	540.8	540.8	540.5	539.8	539.0	538.3	537.5
122.5°	581.7	581.2	580.5	580.0	579.5	578.9	578.4	577.9
125°	642.3	641.6	640.8	640.4	640.1	639.9	639.6	639.4
127.5°	701.2	700.2	699.4	698.5	697.8	697.0	696.3	695.4
130°	741.3	740.8	740.4	739.6	738.7	737.6	736.7	735.7
132.5°	780.4	779.4	778.4	777.4	776.7	775.8	775.1	774.3
135°	838.2	837.9	837.6	837.2	836.4	835.8	835.0	834.2
137.5°	893.4	893.2	893.1	892.5	891.5	890.5	889.6	888.5
140°	930.6	930.6	930.6	930.1	929.2	928.2	927.2	926.2
142.5°	964.3	964.5	964.7	964.3	963.3	962.3	961.4	960.4
145°	1015.4	1015.7	1015.9	1015.5	1014.6	1013.6	1012.6	1011.6
147.5°	1060.3	1060.7	1061.3	1061.1	1060.2	1059.2	1058.3	1057.4
150°	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2
152.5°	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2
155°	1153.1	1154.3	1155.6	1155.7	1155.1	1154.3	1153.6	1152.8
157.5°	1186.4	1188.1	1189.7	1190.0	1188.7	1187.6	1186.5	1185.2
160°	1206.2	1207.6	1209.1	1209.3	1208.3	1207.4	1206.4	1205.4
162.5°	1224.1	1225.7	1227.4	1227.6	1226.4	1225.3	1224.1	1222.9
165°	1247.2	1248.9	1250.6	1250.8	1249.6	1248.4	1247.2	1245.9
167.5°	1266.2	1267.9	1269.6	1269.8	1268.6	1267.2	1266.0	1264.8
170°	1276.7	1278.4	1280.1	1280.3	1278.7	1277.3	1275.8	1274.4
172.5°	1284.6	1286.3	1288.0	1288.1	1286.7	1285.2	1283.7	1282.2
175°	1293.2	1294.9	1296.6	1296.7	1295.2	1293.7	1292.3	1290.8
177.5°	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

(END OF REPORT)