

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331744-940

Luminaire Tested: **SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331744-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4992.1 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331744-940

CATALOG NUMBER: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331744-940

CATALOG NUMBER: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20					20				20
RC	80				70				50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	90	95	91	88	85	80	78	75	70	68	66	60	59	58	54
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43	40
4	78	67	60	54	73	64	57	51	56	51	47	50	46	42	44	40	38	34
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	40	36	33	30
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	28	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24380	24380	24380
5°	24473	24076	24209
10°	24287	23682	23481
15°	24008	22980	22318
20°	23622	21978	20874
25°	23225	20838	19475
30°	22676	19669	17682
35°	22141	18398	16109
40°	21602	17081	14286
45°	20970	15602	12638
50°	20321	14109	11017
55°	19657	12504	9464
60°	18887	10811	7857
65°	18010	9085	7156
70°	16966	7482	6581
75°	15689	6818	6138
80°	13845	6100	5588
85°	10893	4798	4798

TEST NUMBER: P331744-940

CATALOG NUMBER: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	2.8
10°-20°	388.1	7.8
20°-30°	545.0	10.9
30°-40°	594.3	11.9
40°-50°	546.4	10.9
50°-60°	429.2	8.6
60°-70°	279.8	5.6
70°-80°	144.3	2.9
80°-90°	39.0	0.8
90°-100°	21.5	0.4
100°-110°	78.7	1.6
110°-120°	210.3	4.2
120°-130°	347.1	7.0
130°-140°	369.2	7.4
140°-150°	343.1	6.9
150°-160°	275.9	5.5
160°-170°	177.8	3.6
170°-180°	61.2	1.2
0°-30°	1074.4	21.5
0°-40°	1668.7	33.4
0°-60°	2644.3	53.0
0°-90°	3107.4	62.2
90°-120°	310.4	6.2
90°-150°	1369.9	27.4
90°-180°	1885.0	37.8
0°-180°	4992.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1510	1510	1510	1510	1510	
5°	1510	1503	1486	1497	1494	143
15°	1436	1419	1375	1350	1335	404
25°	1304	1257	1170	1116	1093	599
35°	1123	1051	933	850	817	703
45°	918	824	683	590	554	709
55°	698	589	444	365	336	624
65°	471	360	238	194	187	467
75°	252	158	109	100	98	266
85°	59	31	26	26	26	69
90°	0	6	9	12	13	4
95°	30	16	18	20	20	37
105°	141	148	28	33	35	151
115°	268	276	287	82	38	263
125°	378	385	393	396	398	337
135°	468	475	480	484	484	361
145°	543	543	550	553	551	340
155°	598	594	599	602	598	275
165°	630	628	629	632	629	178
175°	644	642	642	645	641	61
180°	643	643	643	643	643	

TEST NUMBER: P331744-940

CATALOG NUMBER: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1515.6	1514.3	1513.1	1511.9	1510.6	1508.7	1506.0	1503.4	1500.7	1498.1	1500.5
5°	1510.0	1508.5	1507.0	1505.5	1504.0	1501.3	1497.3	1493.3	1489.4	1485.5	1488.2
7.5°	1494.5	1492.6	1490.8	1488.8	1486.9	1483.7	1479.1	1474.4	1469.9	1465.3	1466.1
10°	1481.4	1479.3	1477.1	1475.0	1472.8	1468.7	1462.7	1456.6	1450.5	1444.5	1443.6
12.5°	1465.0	1462.3	1459.7	1457.1	1454.6	1449.3	1441.5	1433.8	1426.0	1418.3	1416.6
15°	1436.3	1432.9	1429.6	1426.2	1422.9	1416.0	1405.8	1395.4	1385.1	1374.8	1369.0
17.5°	1401.0	1395.9	1390.8	1385.7	1380.6	1371.5	1358.2	1345.0	1331.7	1318.5	1311.6
20°	1374.8	1368.7	1362.6	1356.6	1350.5	1339.9	1324.6	1309.5	1294.3	1279.1	1271.5
22.5°	1346.3	1339.5	1332.8	1326.0	1319.1	1307.2	1290.0	1272.9	1255.8	1238.7	1228.9
25°	1303.7	1294.0	1284.2	1274.5	1264.8	1250.0	1229.9	1209.9	1189.8	1169.7	1157.4
27.5°	1252.3	1241.8	1231.2	1220.7	1210.1	1193.5	1170.9	1148.3	1125.7	1103.1	1088.6
30°	1216.3	1204.7	1193.2	1181.6	1170.1	1152.2	1127.8	1103.6	1079.3	1055.0	1039.5
32.5°	1181.2	1167.8	1154.3	1140.9	1127.3	1108.2	1083.4	1058.6	1033.8	1009.1	991.4
35°	1123.3	1107.9	1092.3	1076.8	1061.4	1040.3	1013.5	986.9	960.1	933.4	914.3
37.5°	1065.4	1048.4	1031.4	1014.3	997.4	974.6	946.1	917.7	889.1	860.7	839.6
40°	1024.9	1006.7	988.5	970.3	952.1	928.2	898.8	869.3	839.8	810.4	788.8
42.5°	983.4	964.2	945.0	925.8	906.6	881.8	851.4	820.9	790.5	760.1	737.8
45°	918.4	898.0	877.6	857.3	837.0	810.8	778.9	747.1	715.2	683.3	661.7
47.5°	854.9	833.4	811.8	790.2	768.7	741.5	708.6	675.6	642.7	609.8	588.4
50°	809.0	787.5	765.9	744.3	722.7	695.3	661.9	628.5	595.0	561.7	540.7
52.5°	764.2	741.6	719.2	696.6	674.0	646.5	613.8	581.1	548.4	515.8	495.5
55°	698.3	674.7	650.9	627.2	603.6	575.3	542.5	509.7	477.0	444.2	425.9
57.5°	630.8	606.5	582.2	557.9	533.6	505.7	474.2	442.6	411.2	379.6	362.9
60°	584.9	560.6	536.3	512.0	487.7	459.9	428.6	397.3	366.0	334.8	319.3
62.5°	540.1	515.8	491.5	467.2	442.9	415.8	386.0	356.1	326.4	296.6	281.8
65°	471.4	446.8	422.3	397.7	373.1	347.1	319.8	292.5	265.1	237.8	227.5
67.5°	405.3	380.9	356.5	332.1	307.6	283.1	258.6	234.0	209.4	184.8	180.0
70°	359.4	335.7	312.0	288.4	264.7	242.4	221.4	200.5	179.5	158.5	155.5
72.5°	315.7	292.9	270.3	247.5	224.8	205.0	188.2	171.4	154.5	137.8	135.2
75°	251.5	230.2	208.9	187.7	166.4	150.6	140.3	130.0	119.7	109.3	107.2
77.5°	188.3	169.7	151.1	132.4	113.7	101.9	96.9	91.9	86.9	82.0	80.8
80°	148.9	133.5	118.0	102.5	87.0	77.8	74.7	71.7	68.7	65.6	64.4
82.5°	112.9	100.8	88.7	76.6	64.6	57.4	55.4	53.3	51.3	49.2	48.5
85°	58.8	52.3	46.0	39.6	33.3	29.6	28.7	27.8	26.8	25.9	25.9
87.5°	17.6	15.9	14.2	12.4	10.7	10.0	10.1	10.3	10.4	10.6	10.4
90°	0.4	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8
92.5°	9.4	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1
95°	30.2	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6
97.5°	60.0	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7
100°	82.4	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4
102.5°	106.9	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4
105°	141.4	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5
107.5°	180.8	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6
110°	206.2	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1

TEST NUMBER: P331744-940

CATALOG NUMBER: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	230.0	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6
115°	267.6	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2
117.5°	301.2	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5
120°	325.7	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3
122.5°	346.6	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8
125°	378.4	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0
127.5°	407.1	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4
130°	425.3	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1
132.5°	444.0	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4
135°	468.1	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8
137.5°	492.7	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6
140°	508.6	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4
142.5°	522.0	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1
145°	543.1	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3
147.5°	561.4	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0
150°	573.3	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1
152.5°	583.4	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5
155°	598.0	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0
157.5°	609.4	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5
160°	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8
162.5°	622.1	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4
165°	630.1	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5
167.5°	636.1	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3
170°	639.4	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3
172.5°	641.7	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5
175°	644.5	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9
177.5°	645.0	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1

TEST NUMBER: P331744-940

CATALOG NUMBER: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1502.9	1505.3	1507.8	1508.7	1508.2	1507.8	1507.3	1506.8
5°	1490.9	1493.7	1496.4	1497.3	1496.4	1495.5	1494.6	1493.7
7.5°	1466.8	1467.6	1468.4	1468.0	1466.4	1464.8	1463.3	1461.7
10°	1442.6	1441.7	1440.8	1439.5	1437.6	1435.8	1434.0	1432.2
12.5°	1415.0	1413.3	1411.7	1409.3	1406.3	1403.3	1400.3	1397.2
15°	1363.2	1357.5	1351.7	1347.3	1344.3	1341.2	1338.2	1335.2
17.5°	1304.8	1297.9	1291.0	1285.0	1279.8	1274.5	1269.3	1264.1
20°	1263.9	1256.3	1248.8	1241.6	1234.9	1228.2	1221.6	1214.9
22.5°	1219.1	1209.3	1199.5	1192.1	1187.2	1182.2	1177.2	1172.2
25°	1144.9	1132.5	1120.0	1111.5	1106.9	1102.3	1097.8	1093.2
27.5°	1074.1	1059.5	1045.0	1034.1	1026.9	1019.7	1012.4	1005.2
30°	1024.0	1008.5	993.0	981.2	973.0	964.8	956.6	948.4
32.5°	973.7	956.1	938.3	925.7	918.0	910.3	902.5	894.8
35°	895.1	876.0	856.8	843.9	837.2	830.5	823.9	817.3
37.5°	818.5	797.5	776.3	762.0	754.4	746.7	739.0	731.4
40°	767.2	745.6	724.2	709.4	701.5	693.6	685.7	677.8
42.5°	715.5	693.2	670.9	655.9	648.3	640.6	633.0	625.4
45°	640.2	618.6	597.0	582.6	575.3	568.0	560.7	553.5
47.5°	566.9	545.5	524.0	510.0	503.4	496.8	490.1	483.5
50°	519.8	498.8	477.9	464.1	457.8	451.4	445.1	438.6
52.5°	475.3	455.0	434.9	421.8	415.9	410.0	404.1	398.2
55°	407.7	389.5	371.2	359.3	353.5	347.7	342.0	336.2
57.5°	346.3	329.5	312.8	302.0	297.2	292.3	287.5	282.6
60°	303.8	288.4	272.9	262.7	257.8	253.0	248.1	243.3
62.5°	267.1	252.3	237.6	228.6	225.8	222.8	219.9	217.0
65°	217.1	206.8	196.4	190.8	189.9	189.0	188.2	187.3
67.5°	175.3	170.6	165.8	162.9	162.0	161.0	160.1	159.1
70°	152.5	149.5	146.4	144.3	143.0	141.8	140.6	139.4
72.5°	132.7	130.1	127.5	125.9	125.2	124.5	123.7	123.0
75°	105.0	103.0	100.9	99.6	99.3	99.0	98.7	98.4
77.5°	79.5	78.4	77.1	76.2	75.8	75.3	74.8	74.4
80°	63.1	62.0	60.7	60.1	60.1	60.1	60.1	60.1
82.5°	47.7	47.0	46.3	45.9	45.9	45.9	45.9	45.9
85°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	10.3	10.2	10.1	10.0	10.1	10.1	10.2	10.2
90°	10.3	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.3	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.2	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.1	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	28.2	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	29.4	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	30.7	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	37.5	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	60.7	50.4	40.0	35.1	35.5	35.9	36.4	36.7

TEST NUMBER: P331744-940

CATALOG NUMBER: SA2XXRDIP-C1005D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	129.9	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	191.4	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	294.9	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	343.6	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	364.5	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	394.7	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	422.5	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	440.1	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	457.4	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	481.9	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	504.6	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	519.3	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.0	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.0	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	568.6	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	578.7	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.1	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	600.7	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.2	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	617.3	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.1	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.0	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.0	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.2	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	643.6	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	643.9	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)