

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926495

Luminaire Tested: DFN2DIP-TR4F0-070D090US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926495
REPORT IS A COMBINATION OF REPORTS P901985 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D090US950-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15111.4 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 133.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926495

CATALOG NUMBER: DFN2DIP-TR4F0-070D090US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926495

CATALOG NUMBER: DFN2DIP-TR4F0-070D090US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	31
4	73	63	55	49	67	58	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2064	2064	2064
5°	2068	2036	2049
10°	2051	2008	2021
15°	2021	1975	1978
20°	1980	1929	1934
25°	1940	1874	1882
30°	1889	1823	1817
35°	1841	1763	1748
40°	1781	1702	1682
45°	1722	1641	1615
50°	1658	1577	1537
55°	1590	1502	1465
60°	1514	1414	1383
65°	1430	1323	1286
70°	1324	1212	1182
75°	1177	1079	1086
80°	1000	910	902
85°	724	618	598

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1722 cd/sqm

TEST NUMBER: P926495

CATALOG NUMBER: DFN2DIP-TR4F0-070D090US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	1.6
10°-20°	688.1	4.6
20°-30°	1011.3	6.7
30°-40°	1174.5	7.8
40°-50°	1173.1	7.8
50°-60°	1022.9	6.8
60°-70°	756.1	5.0
70°-80°	427.8	2.8
80°-90°	118.0	0.8
90°-100°	95.6	0.6
100°-110°	356.2	2.4
110°-120°	944.7	6.3
120°-130°	1566.8	10.4
130°-140°	1664.3	11.0
140°-150°	1546.8	10.2
150°-160°	1243.6	8.2
160°-170°	801.3	5.3
170°-180°	275.8	1.8
0°-30°	1943.9	12.9
0°-40°	3118.5	20.6
0°-60°	5314.4	35.2
0°-90°	6616.4	43.8
90°-120°	1396.4	9.2
90°-150°	6174.3	40.9
90°-180°	8495.0	56.2
0°-180°	15111.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	2	25	42	53	56	14
95°	136	67	82	92	90	161
105°	637	700	128	151	159	681
115°	1206	1241	1294	323	172	1187
125°	1704	1732	1772	1786	1793	1520
135°	2109	2143	2162	2183	2179	1629
145°	2447	2445	2480	2495	2485	1530
155°	2694	2676	2701	2713	2696	1242
165°	2839	2826	2833	2847	2833	802
175°	2904	2889	2894	2908	2887	276
180°	2898	2898	2898	2898	2898	

TEST NUMBER: P926495

CATALOG NUMBER: DFN2DIP-TR4F0-070D090US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	2.0	25.2	41.8	52.6	56.5
92.5°	52.6	44.1	50.3	54.6	56.5
95°	136.2	67.0	81.7	92.3	90.2
97.5°	245.3	73.5	106.8	113.2	115.2
100°	371.2	84.0	119.5	136.2	140.4
102.5°	509.4	505.4	123.7	146.6	153.1
105°	637.4	700.4	127.9	150.9	159.3
107.5°	786.3	838.6	132.2	155.1	163.6
110°	928.9	972.8	367.0	157.3	165.6

TEST NUMBER: P926495

CATALOG NUMBER: DFN2DIP-TR4F0-070D090US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1063.1	1100.7	1065.1	161.3	167.8
115°	1205.6	1241.2	1293.7	322.9	172.0
117.5°	1329.3	1371.2	1407.0	1107.0	557.7
120°	1467.7	1499.1	1537.0	1562.1	1279.0
122.5°	1585.1	1618.7	1660.7	1673.1	1675.4
125°	1704.5	1731.9	1771.8	1786.5	1792.7
127.5°	1813.6	1842.9	1874.6	1895.5	1897.5
130°	1916.4	1950.1	1973.0	1996.1	1994.1
132.5°	2021.2	2048.6	2071.5	2090.5	2088.5
135°	2109.4	2143.0	2161.7	2182.8	2178.6
137.5°	2201.5	2226.6	2247.8	2268.7	2262.5
140°	2291.6	2308.6	2331.5	2350.4	2340.0
142.5°	2367.4	2382.0	2409.1	2425.8	2415.4
145°	2447.0	2444.7	2480.4	2495.1	2484.6
147.5°	2516.0	2509.8	2545.4	2555.9	2547.6
150°	2583.2	2568.5	2602.1	2614.5	2604.1
152.5°	2639.7	2623.0	2654.4	2667.1	2652.4
155°	2694.3	2675.6	2700.7	2713.2	2696.5
157.5°	2738.4	2721.7	2740.6	2755.2	2738.4
160°	2776.1	2763.5	2776.1	2788.6	2773.9
162.5°	2809.5	2797.0	2807.5	2822.2	2803.3
165°	2838.9	2826.4	2832.7	2847.4	2832.7
167.5°	2862.1	2849.4	2855.8	2870.5	2851.6
170°	2881.0	2868.3	2872.5	2887.2	2868.3
172.5°	2893.5	2881.0	2885.2	2899.9	2881.0
175°	2903.9	2889.2	2893.5	2908.1	2887.2
177.5°	2908.1	2893.5	2895.7	2910.4	2891.5
180°	2897.7	2897.7	2897.7	2897.7	2897.7

TEST NUMBER: P926495

CATALOG NUMBER: DFN2DIP-TR4F0-070D090US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.18	9.99	10.19	11.01	12.37	8.75	9.56	9.76	10.58	11.93
	3H	10.84	11.56	11.86	12.59	13.97	10.37	11.09	11.38	12.12	13.49
	4H	11.42	12.11	12.45	13.14	14.52	10.95	11.64	11.98	12.67	14.05
	6H	11.82	12.45	12.86	13.49	14.88	11.34	11.98	12.39	13.01	14.41
	8H	11.92	12.52	12.97	13.58	14.97	11.45	12.05	12.50	13.10	14.49
	12H	11.97	12.54	13.02	13.59	15.00	11.49	12.06	12.54	13.11	14.52
4H	2H	9.64	10.32	10.68	11.35	12.74	9.29	9.98	10.33	11.01	12.39
	3H	11.50	12.07	12.54	13.13	14.53	11.11	11.68	12.15	12.74	14.14
	4H	12.21	12.74	13.26	13.78	15.21	11.80	12.33	12.86	13.38	14.80
	6H	12.72	13.17	13.78	14.25	15.66	12.31	12.76	13.38	13.84	15.25
	8H	12.87	13.29	13.93	14.36	15.79	12.46	12.88	13.52	13.95	15.38
	12H	12.94	13.32	14.02	14.40	15.84	12.52	12.90	13.60	13.98	15.42
8H	4H	12.40	12.82	13.47	13.89	15.32	12.04	12.46	13.11	13.53	14.96
	6H	13.03	13.38	14.12	14.49	15.92	12.67	13.02	13.76	14.12	15.55
	8H	13.25	13.56	14.35	14.65	16.10	12.88	13.19	13.98	14.28	15.73
	12H	13.38	13.65	14.48	14.74	16.22	13.00	13.27	14.09	14.35	15.84
12H	4H	12.39	12.77	13.47	13.85	15.28	12.03	12.41	13.11	13.49	14.93
	6H	13.06	13.37	14.15	14.46	15.91	12.71	13.02	13.80	14.11	15.55
	8H	13.30	13.57	14.40	14.66	16.14	12.94	13.21	14.04	14.30	15.79

END OF REPORT