

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332686-830

Luminaire Tested: **SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332686-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6750.6 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332686-830  
CATALOG NUMBER: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332686-830

CATALOG NUMBER: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	30	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	41	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332686-830

CATALOG NUMBER: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	2.6
10°-20°	498.4	7.4
20°-30°	733.6	10.9
30°-40°	852.8	12.6
40°-50°	852.8	12.6
50°-60°	746.0	11.1
60°-70°	554.0	8.2
70°-80°	314.7	4.7
80°-90°	92.9	1.4
90°-100°	45.8	0.7
100°-110°	135.8	2.0
110°-120°	230.5	3.4
120°-130°	304.0	4.5
130°-140°	341.4	5.1
140°-150°	335.4	5.0
150°-160°	282.1	4.2
160°-170°	187.7	2.8
170°-180°	65.7	1.0
0°-30°	1408.8	20.9
0°-40°	2261.6	33.5
0°-60°	3860.5	57.2
0°-90°	4822.1	71.4
90°-120°	412.2	6.1
90°-150°	1392.9	20.6
90°-180°	1928.0	28.6
0°-180°	6750.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	89
90°	2	7	12	15	16	6
95°	32	37	41	42	42	36
105°	125	126	128	130	131	133
115°	234	234	233	233	232	231
125°	341	341	341	340	339	304
135°	440	443	444	442	441	340
145°	535	537	538	537	536	335
155°	613	613	612	614	612	282
165°	667	666	664	667	666	188
175°	694	691	691	694	691	66
180°	695	695	695	695	695	



TEST NUMBER: P332686-830

CATALOG NUMBER: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	31.7	31.7	31.6	31.6	31.6	31.6	31.5	31.4	31.3	31.3	31.4
90°	1.6	2.9	4.2	5.6	6.9	8.0	9.0	9.9	10.8	11.8	12.5
92.5°	11.5	13.0	14.5	16.0	17.5	18.6	19.3	20.0	20.6	21.3	21.7
95°	32.2	33.4	34.4	35.4	36.6	37.5	38.4	39.2	40.1	40.8	41.2
97.5°	56.4	57.2	58.1	58.9	59.8	60.7	61.6	62.7	63.6	64.7	65.0
100°	75.2	75.8	76.3	76.7	77.2	77.9	79.0	80.1	81.2	82.3	82.5
102.5°	95.0	95.2	95.4	95.6	95.8	96.4	97.4	98.3	99.3	100.3	100.7
105°	125.3	125.4	125.5	125.6	125.7	126.0	126.5	127.0	127.4	127.9	128.3
107.5°	156.9	157.1	157.2	157.4	157.6	157.7	157.7	157.8	157.9	158.0	158.3
110°	178.5	178.7	179.0	179.2	179.5	179.5	179.4	179.3	179.2	179.0	178.8



TEST NUMBER: P332686-830

CATALOG NUMBER: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	200.9	200.9	201.0	201.0	201.0	201.0	200.8	200.5	200.3	200.1	200.0
115°	234.4	234.4	234.4	234.4	234.4	234.2	234.0	233.8	233.6	233.3	233.2
117.5°	266.0	266.1	266.2	266.3	266.4	266.4	266.2	266.0	265.8	265.7	265.2
120°	287.1	287.6	288.0	288.5	289.0	289.1	288.7	288.3	287.9	287.6	287.0
122.5°	309.0	309.2	309.3	309.5	309.7	309.8	309.6	309.4	309.2	309.2	308.7
125°	341.4	341.4	341.4	341.4	341.4	341.3	341.2	341.1	340.9	340.8	340.5
127.5°	370.7	371.1	371.5	371.8	372.1	372.2	372.0	371.8	371.6	371.5	371.3
130°	391.3	391.7	392.1	392.5	392.8	392.9	392.9	392.9	392.9	392.9	392.8
132.5°	412.5	412.7	412.9	413.2	413.5	413.6	413.5	413.4	413.3	413.2	412.9
135°	440.3	441.0	441.7	442.4	443.2	443.5	443.5	443.5	443.5	443.5	443.3
137.5°	470.6	470.9	471.3	471.6	471.9	472.2	472.4	472.6	472.8	473.0	472.7
140°	490.8	491.1	491.3	491.5	491.7	491.9	491.9	491.9	491.9	491.9	491.7
142.5°	509.3	509.5	509.8	510.0	510.3	510.3	510.2	510.1	510.0	509.9	509.9
145°	534.9	535.4	535.8	536.3	536.8	537.1	537.2	537.3	537.4	537.5	537.4
147.5°	560.2	560.8	561.4	561.9	562.6	562.8	562.7	562.6	562.5	562.4	562.3
150°	575.7	576.3	576.7	577.2	577.7	577.9	577.9	577.9	577.9	577.9	577.9
152.5°	590.4	590.7	591.0	591.3	591.5	591.7	591.8	591.9	592.0	592.1	592.4
155°	612.8	612.8	612.8	612.8	612.8	612.7	612.7	612.6	612.5	612.3	612.7
157.5°	631.8	631.5	631.3	631.1	630.9	630.7	630.7	630.7	630.7	630.7	631.0
160°	642.9	642.8	642.7	642.6	642.4	642.3	642.2	642.2	642.0	641.9	642.2
162.5°	653.3	653.0	652.6	652.3	652.1	651.8	651.7	651.6	651.5	651.3	652.0
165°	667.1	666.8	666.4	666.1	665.7	665.4	665.2	665.0	664.7	664.5	665.2
167.5°	677.8	677.3	676.7	676.3	675.8	675.5	675.5	675.6	675.6	675.6	676.4
170°	683.8	683.2	682.6	682.0	681.4	681.2	681.3	681.4	681.6	681.6	682.4
172.5°	688.1	687.6	687.1	686.6	686.1	685.9	685.9	685.9	685.9	686.0	686.7
175°	694.0	693.4	692.9	692.2	691.6	691.3	691.2	691.1	690.9	690.8	691.6
177.5°	696.0	695.5	695.0	694.6	694.0	693.8	693.8	693.8	693.8	693.8	694.5
180°	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1



TEST NUMBER: P332686-830

CATALOG NUMBER: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	31.6	31.7	31.9	32.0	32.0	32.0	32.0	32.1
90°	13.3	13.9	14.7	15.2	15.5	15.6	15.9	16.1
92.5°	22.1	22.6	23.0	23.3	23.5	23.6	23.8	23.8
95°	41.6	41.9	42.3	42.5	42.5	42.5	42.5	42.5
97.5°	65.5	65.9	66.4	66.5	66.5	66.5	66.5	66.5
100°	82.8	82.9	83.2	83.3	83.3	83.3	83.3	83.3
102.5°	100.9	101.3	101.6	101.9	102.0	102.1	102.2	102.3
105°	128.7	129.0	129.4	129.7	130.1	130.4	130.8	131.2
107.5°	158.6	158.9	159.3	159.5	159.4	159.4	159.4	159.4
110°	178.5	178.3	178.0	178.1	178.5	178.8	179.2	179.6





TEST NUMBER: P332686-830

CATALOG NUMBER: SA4XXDIP-C1195D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	200.0	199.9	199.9	199.9	200.0	200.0	200.1	200.2
115°	233.1	233.0	232.8	232.7	232.6	232.4	232.3	232.2
117.5°	264.9	264.5	264.0	263.7	263.4	263.3	263.0	262.8
120°	286.4	285.8	285.2	285.0	285.3	285.5	285.8	286.0
122.5°	308.3	307.9	307.5	307.1	306.6	306.2	305.8	305.4
125°	340.4	340.1	339.9	339.6	339.4	339.1	338.9	338.7
127.5°	371.0	370.8	370.5	370.3	370.1	369.9	369.8	369.6
130°	392.5	392.3	392.0	391.6	391.2	390.7	390.2	389.7
132.5°	412.7	412.5	412.3	412.0	411.8	411.6	411.4	411.2
135°	443.0	442.8	442.5	442.2	441.9	441.5	441.2	440.8
137.5°	472.3	472.0	471.7	471.6	471.6	471.7	471.8	471.9
140°	491.6	491.5	491.4	491.3	491.2	491.1	491.0	490.8
142.5°	509.9	509.9	509.8	509.8	509.8	509.8	509.7	509.7
145°	537.3	537.2	537.1	536.9	536.5	536.1	535.7	535.5
147.5°	562.2	562.1	562.0	561.9	561.8	561.7	561.6	561.5
150°	577.9	577.9	577.9	577.9	577.7	577.6	577.5	577.4
152.5°	592.7	593.0	593.2	593.2	593.0	592.6	592.3	592.0
155°	613.2	613.7	614.3	614.3	613.7	613.2	612.7	612.3
157.5°	631.4	631.8	632.2	632.1	631.7	631.3	630.8	630.5
160°	642.6	642.9	643.3	643.2	642.6	642.0	641.4	640.8
162.5°	652.6	653.3	653.9	653.9	653.4	652.7	652.1	651.6
165°	665.9	666.6	667.3	667.4	666.9	666.5	666.0	665.5
167.5°	677.0	677.8	678.5	678.4	677.8	677.0	676.3	675.5
170°	683.1	683.8	684.5	684.5	683.6	682.8	681.9	681.1
172.5°	687.6	688.4	689.2	689.2	688.3	687.5	686.6	685.9
175°	692.5	693.3	694.1	694.1	693.3	692.5	691.6	690.8
177.5°	695.1	695.8	696.4	696.4	695.7	694.9	694.1	693.3
180°	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1

(END OF REPORT)