

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332606-830

Luminaire Tested: **SA4XXDIP-C795D810U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332606-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5941.1 lumens  
Efficiency: N/A  
Efficacy: 129.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332606-830  
CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332606-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54				54
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	52	50	45				45
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38				38
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	38	36	32				32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28				28
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24				24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21				21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19				19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				17
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15				15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10101	10101	10101
5°	10131	10009	10083
10°	10067	9928	9977
15°	9947	9787	9812
20°	9784	9613	9620
25°	9600	9413	9386
30°	9374	9177	9093
35°	9140	8932	8814
40°	8896	8652	8495
45°	8643	8379	8218
50°	8361	8133	7882
55°	8058	7817	7562
60°	7753	7463	7237
65°	7412	7125	6837
70°	7027	6675	6413
75°	6441	6129	5973
80°	5732	5500	5360
85°	5011	4826	4733



TEST NUMBER: P332606-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.8	2.0
10°-20°	332.0	5.6
20°-30°	488.6	8.2
30°-40°	568.1	9.6
40°-50°	568.1	9.6
50°-60°	496.9	8.4
60°-70°	369.0	6.2
70°-80°	209.7	3.5
80°-90°	62.6	1.1
90°-100°	270.9	4.6
100°-110°	563.9	9.5
110°-120°	505.1	8.5
120°-130°	424.9	7.2
130°-140°	354.3	6.0
140°-150°	270.6	4.6
150°-160°	190.2	3.2
160°-170°	111.9	1.9
170°-180°	36.4	0.6
0°-30°	938.5	15.8
0°-40°	1506.5	25.4
0°-60°	2571.5	43.3
0°-90°	3212.8	54.1
90°-120°	1340.0	22.6
90°-150°	2389.7	40.2
90°-180°	2728.0	45.9
0°-180°	5941.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1250	1246	1235	1245	1244	119
15°	1190	1185	1171	1176	1174	335
25°	1078	1070	1057	1057	1054	496
35°	927	920	906	899	894	580
45°	757	749	734	723	720	583
55°	572	569	555	544	537	513
65°	388	383	373	363	358	384
75°	206	202	196	193	192	219
85°	54	54	52	52	51	60
90°	1	6	13	15	16	4
95°	24	77	601	297	180	27
105°	86	125	483	1041	1037	92
115°	152	191	431	828	996	151
125°	212	251	429	705	794	188
135°	251	299	425	626	710	194
145°	290	332	423	528	580	182
155°	329	356	411	466	486	152
165°	359	370	394	418	424	101
175°	374	375	378	383	382	36
180°	375	375	375	375	375	



TEST NUMBER: P332606-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1254.4	1253.9	1253.3	1252.8	1252.3	1251.0	1249.1	1247.1	1245.1	1243.2	1244.9
5°	1250.2	1249.3	1248.4	1247.5	1246.6	1244.9	1242.5	1240.0	1237.6	1235.1	1237.6
7.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1233.2	1230.5	1227.8	1225.0	1222.3	1224.3
10°	1228.1	1227.3	1226.3	1225.5	1224.6	1222.7	1219.7	1216.9	1214.0	1211.1	1212.9
12.5°	1214.5	1213.6	1212.7	1211.8	1211.0	1208.9	1205.9	1202.8	1199.8	1196.7	1198.6
15°	1190.1	1189.1	1188.3	1187.3	1186.5	1184.4	1181.0	1177.7	1174.3	1171.0	1172.3
17.5°	1160.6	1159.4	1158.3	1157.3	1156.1	1154.0	1150.8	1147.6	1144.4	1141.3	1142.2
20°	1138.9	1137.7	1136.7	1135.6	1134.4	1132.2	1128.9	1125.5	1122.2	1118.9	1119.6
22.5°	1115.7	1114.2	1112.7	1111.3	1109.7	1107.4	1104.0	1100.7	1097.3	1094.0	1095.2
25°	1077.7	1076.2	1074.6	1073.1	1071.5	1069.1	1066.0	1062.9	1059.8	1056.7	1056.9
27.5°	1034.4	1032.8	1031.2	1029.6	1028.0	1025.8	1022.8	1020.0	1017.1	1014.2	1013.6
30°	1005.6	1003.8	1002.0	1000.2	998.4	996.1	993.2	990.3	987.4	984.5	983.6
32.5°	975.1	973.5	971.9	970.3	968.7	966.3	963.3	960.2	957.2	954.0	953.0
35°	927.4	925.8	924.3	922.7	921.1	918.8	915.7	912.6	909.5	906.3	904.7
37.5°	877.0	875.6	874.2	872.8	871.3	868.9	865.6	862.2	858.9	855.5	853.8
40°	844.1	842.4	840.6	838.8	837.0	834.4	831.1	827.7	824.4	821.0	818.9
42.5°	808.9	807.8	806.7	805.7	804.6	802.2	798.5	794.8	791.1	787.4	784.9
45°	757.0	755.4	753.8	752.2	750.7	748.1	744.6	741.0	737.4	733.9	731.4
47.5°	702.6	701.5	700.5	699.4	698.3	696.2	692.9	689.6	686.3	683.0	680.1
50°	665.7	664.8	663.9	663.0	662.1	660.2	657.0	653.9	650.7	647.6	644.5
52.5°	629.6	628.6	627.5	626.4	625.3	623.1	619.8	616.5	613.2	609.9	607.2
55°	572.5	571.7	571.1	570.4	569.8	567.9	564.8	561.7	558.6	555.4	552.7
57.5°	517.9	517.2	516.4	515.7	514.9	512.9	509.9	506.8	503.8	500.7	498.1
60°	480.2	479.1	478.0	476.9	475.8	473.7	470.9	468.0	465.1	462.2	460.1
62.5°	443.4	442.4	441.5	440.5	439.6	437.6	434.5	431.4	428.4	425.3	423.5
65°	388.0	386.9	385.8	384.7	383.5	381.8	379.7	377.4	375.1	373.0	370.7
67.5°	332.2	331.2	330.2	329.1	328.2	326.6	324.4	322.3	320.2	318.0	315.8
70°	297.7	296.2	294.6	293.0	291.5	289.8	288.0	286.3	284.5	282.8	281.0
72.5°	260.9	259.3	257.8	256.2	254.6	253.2	251.8	250.2	248.8	247.4	246.0
75°	206.5	205.4	204.3	203.2	202.1	201.0	199.8	198.7	197.7	196.5	195.6
77.5°	154.6	154.1	153.6	153.2	152.6	151.9	150.9	150.0	148.9	148.0	147.7
80°	123.3	122.6	122.0	121.3	120.6	120.1	119.6	119.2	118.8	118.3	117.8
82.5°	92.8	92.6	92.2	91.9	91.6	91.4	91.3	91.2	91.1	91.0	90.8
85°	54.1	54.1	54.1	54.1	54.1	53.9	53.4	53.1	52.6	52.1	52.1
87.5°	21.0	21.1	21.4	21.4	21.3	21.1	21.9	21.7	21.8	21.9	21.8
90°	0.8	2.2	4.4	5.2	5.9	5.9	10.3	10.3	11.8	13.3	12.5
92.5°	8.4	12.3	19.1	28.2	38.9	54.2	91.7	148.8	204.6	233.8	194.7
95°	24.3	26.5	33.9	43.5	61.2	92.1	156.3	277.1	453.3	600.7	617.6
97.5°	43.6	43.6	50.0	58.8	74.0	99.9	149.3	249.1	424.2	632.6	775.9
100°	56.0	56.0	61.2	70.0	84.0	107.6	151.1	234.4	384.7	592.6	781.2
102.5°	67.8	69.0	73.5	81.8	95.2	117.6	156.9	230.3	358.2	542.4	737.0
105°	86.2	88.4	92.1	100.9	114.2	135.6	171.0	232.1	335.4	483.4	656.7
107.5°	106.6	108.0	111.7	121.1	133.8	155.0	187.4	243.1	331.2	450.4	591.8
110°	120.2	121.6	125.3	134.1	147.4	167.3	199.7	251.3	332.3	439.2	559.4



TEST NUMBER: P332606-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.1	134.6	138.8	147.1	160.3	180.3	211.5	260.1	335.9	433.9	541.1
115°	151.8	154.0	159.2	166.5	180.6	200.5	230.0	274.2	342.7	431.1	524.0
117.5°	171.3	173.3	178.0	186.1	199.2	219.8	247.8	288.4	350.0	430.4	516.3
120°	184.3	185.7	190.9	199.0	211.5	232.1	260.1	298.5	355.2	430.4	512.2
122.5°	196.0	197.6	202.6	210.2	223.9	243.9	271.9	307.9	360.5	429.8	507.5
125°	211.5	214.4	218.9	227.0	241.0	261.6	288.1	322.1	368.5	429.0	499.6
127.5°	225.3	227.6	232.9	242.1	256.7	277.6	303.2	334.3	374.8	427.3	489.2
130°	232.9	235.8	241.8	252.8	266.8	288.1	313.2	342.0	379.6	426.7	482.8
132.5°	240.5	242.9	250.6	261.1	276.3	296.4	321.5	349.6	383.7	426.1	476.8
135°	251.3	254.3	261.6	274.2	289.6	308.8	333.1	359.7	389.8	425.3	468.0
137.5°	262.1	264.9	273.0	284.9	301.0	319.2	342.0	366.7	393.5	425.1	460.3
140°	269.8	271.9	280.0	292.6	308.0	325.7	347.9	371.5	396.5	424.5	456.2
142.5°	278.0	280.2	287.8	299.6	314.5	331.7	353.2	374.9	398.9	424.5	452.7
145°	289.6	291.8	299.3	309.5	323.6	339.8	358.9	378.8	400.2	423.0	446.6
147.5°	302.7	303.5	310.0	320.6	332.2	346.9	364.9	382.2	401.0	420.4	441.2
150°	311.0	311.8	317.6	326.5	337.5	351.6	367.8	384.0	401.0	418.6	437.1
152.5°	318.7	318.9	324.7	333.0	342.9	355.7	370.1	385.1	399.7	415.7	432.3
155°	329.4	330.2	334.6	342.0	350.1	361.1	373.6	386.2	397.9	411.2	425.3
157.5°	339.9	339.9	344.0	349.8	356.8	365.5	376.2	386.2	396.1	406.7	418.0
160°	346.4	346.4	349.3	354.5	360.4	368.5	377.3	386.2	394.3	403.1	412.7
162.5°	352.3	351.7	354.0	358.6	363.9	370.2	378.5	386.2	392.6	399.6	408.0
165°	358.9	358.9	360.4	364.1	367.8	372.2	378.8	384.7	389.2	394.3	400.2
167.5°	365.5	364.9	365.5	368.3	370.4	373.8	378.7	383.0	385.6	389.0	393.1
170°	368.5	367.8	368.5	370.7	372.2	374.4	378.1	381.7	383.2	385.4	388.4
172.5°	371.5	370.7	370.9	372.5	373.3	374.9	377.5	380.6	380.9	381.9	384.3
175°	374.4	373.6	373.6	374.4	375.1	375.1	376.6	378.8	378.1	378.1	379.6
177.5°	375.7	375.1	374.6	375.1	375.1	375.1	375.7	376.9	375.7	375.7	376.3
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332606-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1246.7	1248.5	1250.3	1251.1	1250.9	1250.8	1250.6	1250.4
5°	1240.0	1242.5	1244.9	1245.9	1245.5	1245.1	1244.6	1244.2
7.5°	1226.2	1228.2	1230.1	1231.0	1230.8	1230.5	1230.2	1229.9
10°	1214.7	1216.4	1218.2	1218.9	1218.4	1218.0	1217.6	1217.1
12.5°	1200.6	1202.5	1204.5	1205.1	1204.6	1203.9	1203.2	1202.7
15°	1173.7	1175.0	1176.3	1176.7	1176.0	1175.4	1174.7	1174.0
17.5°	1143.0	1143.9	1144.7	1144.9	1144.4	1144.0	1143.6	1143.1
20°	1120.2	1120.9	1121.5	1121.6	1121.2	1120.8	1120.3	1119.8
22.5°	1096.4	1097.6	1098.8	1099.0	1098.2	1097.4	1096.6	1095.8
25°	1057.2	1057.3	1057.6	1057.2	1056.4	1055.5	1054.6	1053.7
27.5°	1013.1	1012.6	1012.0	1011.3	1010.1	1009.0	1007.9	1006.7
30°	982.7	981.8	980.9	980.0	978.8	977.7	976.6	975.5
32.5°	951.9	950.8	949.8	948.7	947.5	946.4	945.3	944.2
35°	903.2	901.6	900.0	898.7	897.6	896.5	895.4	894.3
37.5°	852.2	850.5	848.9	847.3	845.7	844.3	842.8	841.3
40°	816.6	814.5	812.2	810.5	809.4	808.3	807.2	806.1
42.5°	782.2	779.7	777.0	775.4	774.7	773.9	773.2	772.4
45°	729.0	726.5	724.1	722.6	721.8	721.1	720.5	719.8
47.5°	677.4	674.7	671.8	669.7	668.0	666.3	664.6	662.9
50°	641.4	638.3	635.2	632.9	631.6	630.3	629.0	627.6
52.5°	604.5	601.6	598.9	596.7	595.0	593.3	591.6	589.9
55°	550.1	547.4	544.7	542.7	541.4	540.1	538.7	537.3
57.5°	495.6	493.0	490.5	488.6	487.3	486.0	484.7	483.4
60°	458.2	456.2	454.1	452.6	451.5	450.3	449.2	448.2
62.5°	421.6	419.8	418.0	416.5	415.4	414.2	413.2	412.1
65°	368.5	366.3	364.0	362.4	361.3	360.1	359.0	357.9
67.5°	313.8	311.6	309.4	308.2	307.9	307.6	307.3	307.0
70°	279.2	277.4	275.6	274.4	273.7	273.1	272.4	271.7
72.5°	244.6	243.2	241.8	240.7	240.0	239.3	238.7	238.0
75°	194.7	193.8	192.9	192.4	192.2	191.9	191.7	191.5
77.5°	147.4	147.1	146.9	146.5	145.9	145.3	144.8	144.2
80°	117.4	117.0	116.5	116.2	115.9	115.7	115.6	115.3
82.5°	90.5	90.2	89.9	89.7	89.5	89.3	89.1	88.8
85°	52.1	52.1	52.1	52.0	51.8	51.6	51.4	51.1
87.5°	21.9	22.1	22.2	22.2	22.3	22.5	22.3	22.3
90°	13.3	14.0	14.7	14.7	15.5	16.2	15.5	15.5
92.5°	144.8	109.0	86.7	71.9	63.2	59.3	56.7	56.7
95°	546.1	431.9	333.1	261.6	225.6	202.6	189.5	179.8
97.5°	806.8	764.4	692.3	615.4	562.5	518.1	496.0	480.7
100°	888.8	903.5	867.4	812.9	748.8	703.8	681.7	675.8
102.5°	884.7	957.8	968.3	945.6	906.3	873.6	850.4	845.6
105°	825.5	952.9	1025.9	1056.1	1057.6	1051.7	1041.4	1037.0
107.5°	741.3	877.0	979.8	1045.5	1081.9	1098.7	1106.1	1108.0
110°	690.6	818.0	924.9	1006.0	1058.3	1089.3	1102.6	1109.2





TEST NUMBER: P332606-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	653.5	766.2	867.1	948.2	1007.6	1045.1	1063.7	1074.4
115°	616.1	706.8	793.0	863.7	922.0	966.2	989.8	995.7
117.5°	597.9	672.9	740.6	800.7	850.4	887.5	911.3	916.0
120°	589.6	658.2	717.1	769.4	811.4	843.9	863.0	871.1
122.5°	582.5	648.7	702.4	748.2	783.7	811.4	827.6	835.8
125°	570.4	633.9	684.7	725.2	754.7	776.1	790.0	794.5
127.5°	555.7	616.2	666.9	705.5	735.1	754.1	765.9	770.3
130°	543.9	602.1	652.2	691.3	721.5	740.0	751.8	756.2
132.5°	531.5	586.2	635.2	674.2	703.8	724.6	735.8	740.3
135°	514.4	562.3	607.3	644.1	673.6	694.3	706.1	710.5
137.5°	499.0	539.5	577.4	610.7	638.2	658.6	668.3	673.6
140°	490.1	524.7	557.9	588.9	614.6	630.8	641.2	647.1
142.5°	481.8	512.4	540.8	567.6	590.5	605.5	614.6	618.8
145°	470.2	495.3	517.4	538.0	556.5	568.9	576.4	580.0
147.5°	460.6	480.5	498.2	514.4	528.0	538.8	544.3	545.6
150°	454.7	471.6	486.4	499.6	511.5	521.0	525.5	526.2
152.5°	448.3	462.8	476.4	487.3	497.3	505.1	507.7	508.5
155°	438.5	450.3	461.4	470.2	477.6	483.4	485.7	485.7
157.5°	428.0	437.9	447.2	454.3	459.9	464.3	465.6	465.6
160°	421.6	429.7	437.8	443.7	448.1	452.5	453.3	453.3
162.5°	415.1	422.0	428.4	433.7	436.9	441.3	442.1	441.5
165°	406.0	410.5	415.7	419.3	422.3	425.3	424.5	423.8
167.5°	397.4	400.8	404.9	407.1	408.6	410.5	410.4	409.7
170°	392.1	394.3	397.3	399.4	401.0	401.6	401.0	401.0
172.5°	387.4	389.0	390.8	392.4	393.2	394.0	393.2	392.1
175°	381.1	381.7	383.2	383.2	383.2	384.7	383.2	381.7
177.5°	376.9	377.5	377.5	378.1	377.5	378.1	376.9	375.7
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1

(END OF REPORT)