

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926532

Luminaire Tested: DFN2DIP-TR4F0-080D090US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926532
REPORT IS A COMBINATION OF REPORTS P900468 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-080D090US950-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14085.8 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 142.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926532
CATALOG NUMBER: DFN2DIP-TR4F0-080D090US950-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P926532

CATALOG NUMBER: DFN2DIP-TR4F0-080D090US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46				46
1	97	93	90	86	89	86	83	80	72	70	68	59	57	56	47	46	45	40				40
2	89	82	76	71	82	75	70	66	63	60	57	52	50	47	42	40	39	34				34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33	29				29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	26				26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22				22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20				20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16				16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15				15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2506	2506	2506
5°	2510	2466	2482
10°	2485	2418	2401
15°	2451	2338	2276
20°	2406	2228	2123
25°	2359	2104	1975
30°	2297	1977	1787
35°	2236	1841	1622
40°	2174	1700	1433
45°	2102	1544	1262
50°	2027	1386	1095
55°	1950	1218	934
60°	1860	1042	769
65°	1756	862	692
70°	1631	695	626
75°	1473	613	569
80°	1244	514	493
85°	868	343	370

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2117 cd/sqm



TEST NUMBER: P926532

CATALOG NUMBER: DFN2DIP-TR4F0-080D090US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	2.1
10°-20°	811.5	5.8
20°-30°	1139.4	8.1
30°-40°	1242.0	8.8
40°-50°	1141.5	8.1
50°-60°	896.5	6.4
60°-70°	583.5	4.1
70°-80°	300.4	2.1
80°-90°	84.4	0.6
90°-100°	168.0	1.2
100°-110°	533.9	3.8
110°-120°	913.7	6.5
120°-130°	1201.6	8.5
130°-140°	1348.7	9.6
140°-150°	1322.6	9.4
150°-160°	1109.5	7.9
160°-170°	735.8	5.2
170°-180°	257.2	1.8
0°-30°	2246.6	15.9
0°-40°	3488.6	24.8
0°-60°	5526.6	39.2
0°-90°	6494.9	46.1
90°-120°	1615.6	11.5
90°-150°	5488.5	39.0
90°-180°	7591.0	53.9
0°-180°	14085.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	2	30	80	75	78	14
95°	120	142	146	146	142	133
105°	493	499	504	508	508	520
115°	917	930	926	924	917	907
125°	1334	1354	1348	1340	1338	1192
135°	1725	1750	1755	1753	1746	1333
145°	2094	2110	2124	2126	2117	1308
155°	2394	2401	2408	2420	2413	1102
165°	2605	2602	2602	2619	2607	735
175°	2710	2704	2699	2716	2702	258
180°	2716	2716	2716	2716	2716	



TEST NUMBER: P926532

CATALOG NUMBER: DFN2DIP-TR4F0-080D090US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	2.5	29.5	80.2	75.3	77.8
92.5°	50.8	68.8	71.3	73.6	73.6
95°	119.5	142.4	146.5	146.5	142.4
97.5°	198.9	220.2	229.2	229.2	229.2
100°	290.6	309.5	316.0	316.0	313.6
102.5°	387.2	401.2	410.1	412.6	410.1
105°	492.8	499.3	504.3	508.4	508.4
107.5°	597.6	607.4	607.4	609.0	597.6
110°	699.1	712.3	712.3	712.3	705.7



TEST NUMBER: P926532

CATALOG NUMBER: DFN2DIP-TR4F0-080D090US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	808.8	822.7	820.2	813.8	808.8
115°	916.9	930.0	925.9	923.5	916.9
117.5°	1024.1	1042.1	1030.7	1024.1	1017.5
120°	1132.2	1150.1	1132.2	1132.2	1124.8
122.5°	1230.4	1253.4	1241.9	1235.3	1230.4
125°	1333.6	1354.0	1347.5	1340.1	1337.7
127.5°	1434.2	1459.6	1450.7	1440.8	1434.2
130°	1528.4	1557.9	1553.8	1548.8	1539.9
132.5°	1634.0	1656.9	1658.5	1647.1	1640.6
135°	1724.8	1750.2	1755.2	1752.7	1746.2
137.5°	1826.3	1846.8	1851.0	1849.3	1839.5
140°	1915.6	1936.0	1947.5	1947.5	1938.5
142.5°	2007.3	2027.7	2034.3	2036.8	2027.7
145°	2094.1	2110.4	2123.5	2126.0	2117.0
147.5°	2171.9	2192.3	2202.1	2206.2	2197.3
150°	2252.1	2266.0	2275.0	2282.3	2275.0
152.5°	2323.3	2337.2	2348.7	2357.7	2348.7
155°	2394.5	2401.0	2408.5	2419.9	2412.6
157.5°	2455.9	2460.8	2464.9	2481.3	2469.8
160°	2510.7	2515.7	2518.2	2532.0	2522.2
162.5°	2561.5	2561.5	2564.0	2579.5	2568.1
165°	2604.9	2602.4	2602.4	2618.8	2607.4
167.5°	2644.2	2636.9	2636.9	2653.2	2641.7
170°	2673.7	2667.1	2664.7	2681.0	2667.1
172.5°	2694.1	2687.6	2685.1	2701.5	2687.6
175°	2710.5	2703.9	2699.1	2715.5	2701.5
177.5°	2719.5	2713.0	2708.0	2722.0	2708.0
180°	2715.5	2715.5	2715.5	2715.5	2715.5



TEST NUMBER: P926532
 CATALOG NUMBER: DFN2DIP-TR4F0-080D090US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.96	10.76	10.95	11.76	13.09	5.93	6.73	6.93	7.73	9.06
	3H	11.63	12.35	12.64	13.36	14.71	7.12	7.83	8.12	8.84	10.19
	4H	12.24	12.92	13.26	13.93	15.29	7.57	8.24	8.59	9.26	10.62
	6H	12.66	13.28	13.69	14.30	15.67	7.89	8.51	8.92	9.53	10.90
	8H	12.78	13.38	13.82	14.41	15.78	7.98	8.57	9.01	9.61	10.97
	12H	12.84	13.41	13.88	14.44	15.83	8.02	8.58	9.06	9.61	11.00
4H	2H	9.97	10.65	11.00	11.66	13.02	6.52	7.20	7.55	8.21	9.57
	3H	11.80	12.36	12.83	13.40	14.77	7.87	8.43	8.90	9.48	10.85
	4H	12.49	13.00	13.53	14.04	15.43	8.42	8.93	9.46	9.97	11.36
	6H	13.00	13.44	14.05	14.50	15.89	8.84	9.28	9.89	10.34	11.73
	8H	13.18	13.59	14.23	14.64	16.04	8.96	9.38	10.02	10.43	11.83
	12H	13.27	13.64	14.34	14.71	16.12	9.03	9.40	10.10	10.47	11.88
8H	4H	12.45	12.87	13.51	13.92	15.32	8.70	9.11	9.75	10.16	11.56
	6H	13.02	13.36	14.09	14.45	15.85	9.21	9.55	10.29	10.65	12.05
	8H	13.24	13.53	14.32	14.61	16.03	9.41	9.70	10.49	10.78	12.20
	12H	13.37	13.64	14.46	14.71	16.17	9.52	9.79	10.61	10.86	12.32
12H	4H	12.40	12.78	13.47	13.84	15.25	8.70	9.07	9.77	10.14	11.55
	6H	12.99	13.29	14.08	14.37	15.79	9.26	9.56	10.34	10.64	12.06
	8H	13.21	13.48	14.30	14.55	16.01	9.47	9.74	10.56	10.81	12.27