

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332515-840

Luminaire Tested: **SA4XXDIP-C350D810U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332515-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4366.1 lumens  
Efficiency: N/A  
Efficacy: 139.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332515-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332515-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	29				
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25				
3	78	69	62	56	71	63	57	52	51	46	43	40	36	34	29	27	26	21				
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18				
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16				
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10				
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332515-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.2	1.3
10°-20°	158.3	3.6
20°-30°	233.0	5.3
30°-40°	270.8	6.2
40°-50°	270.9	6.2
50°-60°	236.9	5.4
60°-70°	175.9	4.0
70°-80°	100.0	2.3
80°-90°	31.9	0.7
90°-100°	67.3	1.5
100°-110°	199.5	4.6
110°-120°	338.5	7.8
120°-130°	446.4	10.2
130°-140°	501.3	11.5
140°-150°	492.6	11.3
150°-160°	414.3	9.5
160°-170°	275.7	6.3
170°-180°	96.5	2.2
0°-30°	447.4	10.2
0°-40°	718.3	16.5
0°-60°	1226.1	28.1
0°-90°	1533.9	35.1
90°-120°	605.4	13.9
90°-150°	2045.7	46.9
90°-180°	2832.0	64.9
0°-180°	4366.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	2	11	17	22	24	4
95°	47	54	60	62	62	53
105°	184	185	188	190	193	195
115°	344	344	343	342	341	339
125°	501	501	501	499	497	447
135°	647	651	651	650	647	500
145°	786	789	790	789	786	491
155°	900	900	899	902	899	414
165°	980	977	976	980	977	276
175°	1019	1015	1014	1020	1014	97
180°	1021	1021	1021	1021	1021	



TEST NUMBER: P332515-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.4	10.7	11.0	11.3	11.6	11.9	12.0	12.2	12.4	12.6	12.8
90°	2.3	4.3	6.3	8.2	10.1	11.7	13.1	14.5	16.0	17.4	18.4
92.5°	16.9	19.1	21.3	23.5	25.8	27.4	28.3	29.3	30.3	31.3	31.9
95°	47.4	49.0	50.5	52.1	53.7	55.1	56.4	57.6	58.8	60.0	60.5
97.5°	82.7	84.0	85.2	86.5	87.8	89.2	90.6	92.0	93.4	94.9	95.5
100°	110.6	111.2	111.9	112.6	113.3	114.5	116.0	117.6	119.2	120.8	121.2
102.5°	139.6	139.9	140.2	140.5	140.7	141.6	143.0	144.4	145.9	147.3	147.8
105°	184.0	184.1	184.3	184.5	184.7	185.1	185.8	186.5	187.2	187.9	188.4
107.5°	230.6	230.8	231.0	231.2	231.4	231.6	231.7	231.8	231.9	232.0	232.5
110°	262.2	262.5	262.8	263.2	263.5	263.6	263.5	263.3	263.1	262.9	262.6



TEST NUMBER: P332515-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.0	295.0	295.1	295.2	295.3	295.1	294.8	294.5	294.2	293.9	293.8
115°	344.3	344.3	344.3	344.3	344.3	344.1	343.7	343.4	343.0	342.6	342.4
117.5°	390.6	390.8	390.9	391.0	391.2	391.1	390.9	390.6	390.4	390.2	389.6
120°	421.6	422.3	423.0	423.7	424.4	424.4	423.9	423.4	422.9	422.4	421.5
122.5°	453.8	454.0	454.3	454.6	454.9	454.9	454.7	454.4	454.2	453.9	453.3
125°	501.3	501.3	501.3	501.3	501.3	501.2	501.1	500.9	500.7	500.6	500.2
127.5°	544.4	544.9	545.5	546.0	546.5	546.6	546.3	546.1	545.8	545.5	545.2
130°	574.7	575.3	575.8	576.3	576.8	577.1	577.1	577.1	577.1	577.1	576.7
132.5°	605.7	606.1	606.5	606.8	607.2	607.3	607.2	607.1	606.9	606.8	606.4
135°	646.6	647.6	648.7	649.7	650.9	651.4	651.4	651.4	651.4	651.4	651.0
137.5°	691.2	691.7	692.1	692.6	693.1	693.5	693.8	694.1	694.3	694.6	694.2
140°	720.8	721.1	721.5	721.9	722.3	722.4	722.4	722.4	722.4	722.4	722.3
142.5°	748.0	748.3	748.7	749.0	749.4	749.5	749.3	749.2	749.0	748.9	748.9
145°	785.6	786.3	787.0	787.7	788.4	788.8	789.0	789.1	789.3	789.5	789.3
147.5°	822.8	823.6	824.5	825.4	826.2	826.6	826.4	826.3	826.1	826.0	825.9
150°	845.6	846.3	847.0	847.7	848.4	848.7	848.7	848.7	848.7	848.7	848.7
152.5°	867.1	867.5	867.9	868.3	868.7	869.0	869.1	869.3	869.4	869.6	870.0
155°	900.0	900.0	900.0	900.0	900.0	899.9	899.8	899.6	899.4	899.3	899.9
157.5°	927.9	927.5	927.2	926.9	926.6	926.3	926.3	926.3	926.2	926.2	926.8
160°	944.2	944.0	943.9	943.7	943.5	943.3	943.2	943.0	942.8	942.7	943.2
162.5°	959.4	959.0	958.5	958.1	957.6	957.3	957.0	956.9	956.7	956.5	957.6
165°	979.8	979.3	978.8	978.2	977.7	977.2	976.8	976.5	976.1	975.8	976.8
167.5°	995.4	994.6	993.9	993.2	992.5	992.1	992.1	992.2	992.2	992.2	993.3
170°	1004.2	1003.4	1002.5	1001.6	1000.8	1000.4	1000.6	1000.8	1000.9	1001.1	1002.1
172.5°	1010.6	1009.9	1009.1	1008.4	1007.6	1007.2	1007.3	1007.3	1007.3	1007.4	1008.6
175°	1019.3	1018.3	1017.4	1016.6	1015.7	1015.2	1015.0	1014.8	1014.7	1014.5	1015.7
177.5°	1022.1	1021.4	1020.7	1020.0	1019.3	1019.0	1019.0	1019.0	1019.0	1019.0	1019.9
180°	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8



TEST NUMBER: P332515-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	13.0	13.3	13.5	13.6	13.7	13.7	13.8	13.9
90°	19.5	20.5	21.6	22.3	22.6	23.0	23.3	23.7
92.5°	32.5	33.1	33.8	34.2	34.4	34.6	34.8	35.0
95°	61.1	61.6	62.1	62.4	62.4	62.4	62.4	62.4
97.5°	96.1	96.7	97.5	97.8	97.8	97.8	97.8	97.8
100°	121.5	121.9	122.2	122.4	122.4	122.4	122.4	122.4
102.5°	148.3	148.8	149.3	149.6	149.8	149.9	150.1	150.2
105°	188.9	189.5	190.0	190.6	191.1	191.6	192.1	192.7
107.5°	233.0	233.4	233.9	234.2	234.1	234.1	234.1	234.0
110°	262.2	261.9	261.5	261.6	262.2	262.7	263.2	263.7





TEST NUMBER: P332515-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	293.7	293.7	293.6	293.6	293.7	293.8	293.9	294.0
115°	342.2	342.1	341.9	341.7	341.6	341.4	341.2	341.0
117.5°	389.0	388.4	387.8	387.3	387.0	386.6	386.3	385.9
120°	420.6	419.7	418.9	418.6	419.0	419.3	419.7	420.0
122.5°	452.7	452.2	451.6	451.0	450.3	449.7	449.1	448.5
125°	499.9	499.5	499.2	498.8	498.5	498.1	497.8	497.4
127.5°	544.8	544.5	544.1	543.8	543.5	543.3	543.0	542.7
130°	576.4	576.0	575.7	575.2	574.5	573.8	573.1	572.4
132.5°	606.1	605.7	605.4	605.1	604.8	604.5	604.2	604.0
135°	650.7	650.3	649.9	649.4	648.9	648.4	647.9	647.4
137.5°	693.7	693.3	692.8	692.6	692.7	692.8	692.9	693.1
140°	722.1	721.9	721.6	721.5	721.3	721.1	720.9	720.8
142.5°	748.8	748.8	748.8	748.7	748.7	748.7	748.6	748.6
145°	789.1	789.0	788.8	788.4	787.9	787.4	786.9	786.4
147.5°	825.7	825.6	825.4	825.3	825.1	824.9	824.8	824.6
150°	848.7	848.7	848.7	848.6	848.5	848.3	848.1	847.9
152.5°	870.4	870.8	871.2	871.2	870.8	870.3	869.9	869.4
155°	900.6	901.3	902.0	902.0	901.3	900.6	899.9	899.3
157.5°	927.3	927.9	928.4	928.3	927.8	927.2	926.6	925.9
160°	943.7	944.2	944.7	944.6	943.7	942.8	942.0	941.1
162.5°	958.5	959.4	960.4	960.4	959.5	958.7	957.8	956.8
165°	978.0	979.0	980.1	980.2	979.5	978.8	978.1	977.4
167.5°	994.3	995.4	996.4	996.4	995.3	994.2	993.2	992.1
170°	1003.2	1004.2	1005.3	1005.2	1004.0	1002.8	1001.5	1000.3
172.5°	1009.8	1011.0	1012.2	1012.2	1011.0	1009.7	1008.5	1007.2
175°	1016.9	1018.1	1019.5	1019.5	1018.1	1016.9	1015.7	1014.5
177.5°	1020.9	1021.9	1022.9	1022.8	1021.7	1020.6	1019.5	1018.2
180°	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8

(END OF REPORT)