

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332712-940

Luminaire Tested: **SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332712-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8849.3 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332712-940
CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332712-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	49	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332712-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	1.9
10°-20°	471.5	5.3
20°-30°	694.0	7.8
30°-40°	806.8	9.1
40°-50°	806.8	9.1
50°-60°	705.8	8.0
60°-70°	524.1	5.9
70°-80°	297.8	3.4
80°-90°	89.9	1.0
90°-100°	47.4	0.5
100°-110°	302.1	3.4
110°-120°	577.9	6.5
120°-130°	733.6	8.3
130°-140°	784.9	8.9
140°-150°	734.0	8.3
150°-160°	591.9	6.7
160°-170°	381.8	4.3
170°-180°	131.6	1.5
0°-30°	1332.9	15.1
0°-40°	2139.7	24.2
0°-60°	3652.3	41.3
0°-90°	4564.1	51.6
90°-120°	927.4	10.5
90°-150°	3179.9	35.9
90°-180°	4285.0	48.4
0°-180°	8849.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	3	14	23	29	31	7
95°	57	24	23	29	30	73
105°	312	318	323	330	295	326
115°	582	585	584	586	586	573
125°	818	822	821	824	825	730
135°	1015	1015	1018	1021	1023	782
145°	1171	1174	1174	1175	1177	731
155°	1284	1285	1282	1285	1283	592
165°	1354	1349	1349	1356	1348	383
175°	1385	1379	1380	1388	1377	132
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P332712-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	30.2	30.5	30.8	31.0	31.2	31.5	31.6	31.7	31.7	31.9	32.2
90°	3.1	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2
92.5°	13.0	13.2	13.4	13.5	13.6	14.6	16.4	18.3	20.2	21.9	23.4
95°	57.0	49.1	41.3	33.5	25.7	21.8	22.1	22.3	22.6	22.8	24.2
97.5°	121.0	125.9	130.8	135.6	140.5	130.1	104.4	78.7	53.1	27.4	27.5
100°	170.0	174.1	178.3	182.4	186.5	172.7	140.9	109.1	77.4	45.6	41.6
102.5°	224.6	227.7	230.7	233.7	236.7	236.2	232.1	227.9	223.8	219.6	177.5
105°	311.8	313.3	314.6	316.0	317.4	318.7	319.9	320.9	322.1	323.2	325.4
107.5°	392.9	393.6	394.3	394.9	395.7	396.8	398.3	399.9	401.4	403.1	404.0
110°	447.6	448.3	449.0	449.7	450.4	451.4	452.8	454.1	455.6	456.9	457.4



TEST NUMBER: P332712-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	500.7	501.9	503.1	504.4	505.6	506.6	507.2	507.8	508.5	509.2	509.1
115°	582.3	583.0	583.7	584.3	585.1	585.3	585.1	584.9	584.6	584.3	584.9
117.5°	655.9	656.7	657.7	658.6	659.5	660.2	660.8	661.3	661.8	662.3	662.2
120°	705.6	706.5	707.5	708.4	709.3	709.6	709.4	709.2	708.9	708.7	709.2
122.5°	752.0	752.6	753.1	753.7	754.2	754.7	755.0	755.3	755.6	756.0	756.3
125°	818.5	819.5	820.4	821.3	822.2	822.4	822.0	821.5	821.1	820.6	821.3
127.5°	881.5	881.7	882.0	882.3	882.4	883.1	884.1	885.2	886.3	887.3	887.2
130°	922.1	922.4	922.7	922.8	923.1	923.5	924.3	924.9	925.6	926.3	926.5
132.5°	959.5	959.8	960.3	960.7	961.1	961.8	962.6	963.5	964.4	965.3	965.5
135°	1015.4	1015.2	1014.9	1014.7	1014.5	1014.9	1015.7	1016.6	1017.6	1018.5	1019.0
137.5°	1065.0	1065.1	1065.1	1065.2	1065.3	1065.9	1066.8	1067.9	1068.9	1069.9	1070.4
140°	1097.3	1097.7	1098.1	1098.7	1099.1	1099.6	1100.0	1100.5	1100.9	1101.4	1102.1
142.5°	1126.2	1127.1	1127.9	1128.7	1129.6	1130.2	1130.4	1130.7	1131.0	1131.2	1131.8
145°	1170.8	1171.5	1172.2	1172.9	1173.6	1173.9	1173.9	1173.9	1173.9	1173.9	1174.2
147.5°	1206.2	1207.6	1208.8	1210.1	1211.4	1211.9	1211.7	1211.5	1211.2	1211.0	1211.2
150°	1232.0	1232.9	1233.8	1234.8	1235.6	1236.0	1235.7	1235.6	1235.3	1235.0	1235.0
152.5°	1253.5	1254.3	1255.0	1255.7	1256.4	1256.6	1256.2	1255.8	1255.4	1255.0	1255.4
155°	1283.8	1284.0	1284.2	1284.4	1284.7	1284.4	1283.8	1283.1	1282.4	1281.7	1282.6
157.5°	1309.2	1309.1	1308.9	1308.9	1308.7	1308.2	1307.4	1306.7	1305.9	1305.1	1306.3
160°	1324.2	1323.5	1322.8	1322.1	1321.4	1321.0	1320.7	1320.4	1320.3	1320.0	1321.4
162.5°	1337.4	1336.6	1335.7	1334.8	1333.9	1333.4	1333.1	1332.9	1332.7	1332.5	1333.8
165°	1354.2	1353.1	1351.9	1350.8	1349.6	1349.1	1349.1	1349.1	1349.1	1349.1	1350.9
167.5°	1367.4	1366.3	1365.1	1363.9	1362.7	1362.0	1361.9	1361.7	1361.6	1361.5	1363.5
170°	1374.9	1373.6	1372.2	1370.8	1369.4	1368.9	1369.0	1369.3	1369.5	1369.8	1371.6
172.5°	1379.9	1378.5	1377.2	1375.7	1374.4	1373.8	1374.0	1374.3	1374.5	1374.8	1376.5
175°	1385.3	1383.9	1382.5	1381.2	1379.7	1379.2	1379.4	1379.7	1379.9	1380.1	1382.2
177.5°	1387.8	1386.5	1385.2	1383.9	1382.6	1382.2	1382.5	1382.9	1383.3	1383.7	1385.1
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332712-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	32.5	32.7	33.0	33.2	33.3	33.3	33.4	33.5
90°	25.6	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	24.7	26.1	27.5	28.3	28.4	28.4	28.5	28.6
95°	25.6	26.9	28.4	29.2	29.3	29.6	29.8	30.1
97.5°	27.6	27.7	27.9	28.1	28.4	28.5	28.8	29.0
100°	37.7	33.9	30.0	28.1	28.4	28.5	28.8	29.0
102.5°	135.2	93.0	50.7	29.7	29.7	29.8	29.8	29.9
105°	327.4	329.5	331.5	328.4	320.1	311.8	303.6	295.3
107.5°	405.1	406.1	407.1	408.0	408.9	409.8	410.6	411.5
110°	457.9	458.3	458.8	459.3	460.0	460.7	461.5	462.1



TEST NUMBER: P332712-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	509.0	508.9	508.8	509.2	510.1	511.0	511.8	512.6
115°	585.3	585.8	586.2	586.5	586.5	586.5	586.5	586.5
117.5°	662.1	662.0	661.9	661.8	661.7	661.6	661.6	661.5
120°	709.6	710.1	710.5	710.5	710.1	709.6	709.2	708.7
122.5°	756.5	756.8	757.1	757.0	756.5	756.1	755.5	755.1
125°	822.0	822.7	823.4	823.9	824.0	824.3	824.6	824.7
127.5°	887.1	886.9	886.8	886.6	886.4	886.3	886.1	885.9
130°	926.8	927.0	927.2	927.3	927.3	927.3	927.3	927.3
132.5°	965.7	966.0	966.2	966.2	966.0	965.8	965.6	965.5
135°	1019.4	1019.8	1020.4	1020.8	1021.3	1021.7	1022.2	1022.6
137.5°	1070.9	1071.4	1071.9	1072.1	1072.0	1071.8	1071.7	1071.6
140°	1102.8	1103.5	1104.2	1104.7	1104.8	1105.1	1105.3	1105.5
142.5°	1132.3	1132.7	1133.3	1133.5	1133.6	1133.6	1133.7	1133.7
145°	1174.4	1174.7	1174.8	1175.2	1175.6	1176.1	1176.6	1177.1
147.5°	1211.4	1211.6	1211.7	1211.9	1212.2	1212.5	1212.6	1212.9
150°	1235.0	1235.0	1235.0	1235.2	1235.4	1235.6	1235.9	1236.1
152.5°	1255.7	1256.1	1256.4	1256.5	1256.4	1256.2	1256.2	1256.0
155°	1283.5	1284.4	1285.4	1285.5	1284.8	1284.1	1283.4	1282.7
157.5°	1307.5	1308.7	1309.9	1309.9	1308.7	1307.5	1306.3	1305.1
160°	1322.8	1324.2	1325.5	1325.5	1324.2	1322.8	1321.4	1320.0
162.5°	1335.2	1336.6	1338.0	1337.9	1336.3	1334.8	1333.2	1331.6
165°	1352.7	1354.6	1356.4	1356.3	1354.2	1352.1	1350.1	1348.0
167.5°	1365.6	1367.5	1369.6	1369.4	1367.2	1364.9	1362.5	1360.2
170°	1373.4	1375.3	1377.2	1376.9	1374.6	1372.3	1370.0	1367.7
172.5°	1378.4	1380.3	1382.1	1381.8	1379.3	1376.8	1374.3	1371.8
175°	1384.3	1386.3	1388.4	1388.0	1385.3	1382.5	1379.7	1377.0
177.5°	1386.6	1388.0	1389.6	1389.2	1387.0	1384.7	1382.5	1380.4
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3

(END OF REPORT)