

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904880

Luminaire Tested: DFN2DIP-4P2F0-030D020US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904880
REPORT IS A COMBINATION OF REPORTS P899014 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D020US835-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4320.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 43.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904880

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904880

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3105	3105	3105
5°	3103	3048	3070
10°	3067	2980	2965
15°	3018	2874	2806
20°	2956	2731	2612
25°	2893	2572	2425
30°	2809	2410	2191
35°	2727	2236	1984
40°	2644	2057	1749
45°	2548	1860	1535
50°	2447	1662	1327
55°	2341	1450	1128
60°	2219	1231	923
65°	2079	1009	825
70°	1908	802	740
75°	1692	693	662
80°	1385	559	559
85°	893	344	394

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2548 cd/sqm

TEST NUMBER: P904880

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	2.7
10°-20°	319.0	7.4
20°-30°	447.9	10.4
30°-40°	488.2	11.3
40°-50°	448.7	10.4
50°-60°	352.4	8.2
60°-70°	229.4	5.3
70°-80°	118.1	2.7
80°-90°	31.9	0.7
90°-100°	39.1	0.9
100°-110°	124.4	2.9
110°-120°	212.8	4.9
120°-130°	279.9	6.5
130°-140°	314.2	7.3
140°-150°	308.1	7.1
150°-160°	258.4	6.0
160°-170°	171.4	4.0
170°-180°	59.9	1.4
0°-30°	883.1	20.4
0°-40°	1371.3	31.7
0°-60°	2172.4	50.3
0°-90°	2551.8	59.1
90°-120°	376.3	8.7
90°-150°	1278.5	29.6
90°-180°	1768.0	40.9
0°-180°	4320.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	1	7	19	18	18	4
95°	28	33	34	34	33	31
105°	115	116	118	118	118	121
115°	214	217	216	215	214	211
125°	311	315	314	312	312	278
135°	402	408	409	408	407	311
145°	488	492	495	495	493	305
155°	558	559	561	564	562	257
165°	607	606	606	610	607	171
175°	631	630	629	632	629	60
180°	632	632	632	632	632	

TEST NUMBER: P904880

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	0.6	6.9	18.7	17.5	18.1
92.5°	11.8	16.0	16.6	17.2	17.2
95°	27.8	33.2	34.1	34.1	33.2
97.5°	46.3	51.3	53.4	53.4	53.4
100°	67.7	72.1	73.6	73.6	73.0
102.5°	90.2	93.4	95.5	96.1	95.5
105°	114.8	116.3	117.5	118.4	118.4
107.5°	139.2	141.5	141.5	141.9	139.2
110°	162.9	165.9	165.9	165.9	164.4



TEST NUMBER: P904880

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.4	191.6	191.1	189.5	188.4
115°	213.6	216.6	215.7	215.1	213.6
117.5°	238.6	242.8	240.1	238.6	237.0
120°	263.7	267.9	263.7	263.7	262.0
122.5°	286.6	291.9	289.3	287.8	286.6
125°	310.6	315.4	313.9	312.2	311.6
127.5°	334.1	340.0	337.9	335.6	334.1
130°	356.0	362.9	361.9	360.8	358.7
132.5°	380.6	386.0	386.3	383.7	382.1
135°	401.8	407.7	408.8	408.3	406.7
137.5°	425.4	430.2	431.2	430.8	428.5
140°	446.2	451.0	453.7	453.7	451.6
142.5°	467.6	472.3	473.9	474.4	472.3
145°	487.8	491.6	494.7	495.2	493.1
147.5°	505.9	510.7	513.0	513.9	511.8
150°	524.6	527.8	529.9	531.6	529.9
152.5°	541.2	544.4	547.1	549.2	547.1
155°	557.8	559.3	561.0	563.7	562.0
157.5°	572.1	573.2	574.2	578.0	575.3
160°	584.9	586.0	586.6	589.8	587.5
162.5°	596.7	596.7	597.2	600.9	598.2
165°	606.8	606.2	606.2	610.0	607.4
167.5°	615.9	614.2	614.2	618.0	615.4
170°	622.8	621.3	620.7	624.5	621.3
172.5°	627.6	626.0	625.5	629.3	626.0
175°	631.4	629.9	628.7	632.5	629.3
177.5°	633.5	632.0	630.8	634.0	630.8
180°	632.5	632.5	632.5	632.5	632.5

TEST NUMBER: P904880

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.75	12.66	12.64	13.56	14.70	7.72	8.63	8.60	9.52	10.66
	3H	13.42	14.23	14.31	15.14	16.30	8.89	9.70	9.78	10.61	11.77
	4H	14.01	14.78	14.92	15.69	16.87	9.33	10.10	10.24	11.01	12.18
	6H	14.42	15.13	15.34	16.05	17.23	9.63	10.34	10.56	11.26	12.45
	8H	14.54	15.21	15.47	16.15	17.33	9.72	10.39	10.65	11.33	12.51
	12H	14.59	15.23	15.53	16.16	17.37	9.75	10.39	10.69	11.33	12.54
4H	2H	11.78	12.55	12.69	13.46	14.63	8.31	9.08	9.22	9.99	11.16
	3H	13.59	14.23	14.51	15.17	16.36	9.64	10.28	10.57	11.22	12.41
	4H	14.26	14.85	15.20	15.79	17.00	10.17	10.76	11.11	11.69	12.91
	6H	14.76	15.26	15.71	16.23	17.44	10.58	11.08	11.52	12.04	13.25
	8H	14.93	15.39	15.88	16.35	17.58	10.69	11.16	11.65	12.12	13.35
	12H	15.01	15.43	15.98	16.41	17.64	10.75	11.17	11.72	12.15	13.38
8H	4H	14.23	14.70	15.18	15.66	16.89	10.45	10.91	11.40	11.87	13.10
	6H	14.78	15.16	15.75	16.16	17.39	10.94	11.33	11.92	12.32	13.55
	8H	14.98	15.32	15.96	16.31	17.55	11.12	11.46	12.10	12.44	13.69
	12H	15.10	15.40	16.09	16.38	17.68	11.22	11.52	12.21	12.50	13.79
12H	4H	14.19	14.61	15.16	15.58	16.82	10.45	10.87	11.42	11.85	13.08
	6H	14.75	15.09	15.74	16.08	17.32	10.98	11.32	11.97	12.31	13.56
	8H	14.96	15.26	15.95	16.24	17.53	11.18	11.48	12.17	12.46	13.75

END OF REPORT