

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904935

Luminaire Tested: DFN2DIP-4P3F0-030D050US835-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904935
REPORT IS A COMBINATION OF REPORTS P900581 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D050US835-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 64.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904935
CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P904935
 CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38				38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32				32
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	26				26
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27	22				22
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19				19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17				17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15				15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13				13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12				12
9	48	36	29	24	44	33	27	23	28	23	19	22	19	16	17	15	13	11				11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1330	1330	1330
5°	1332	1311	1320
10°	1320	1292	1302
15°	1300	1270	1273
20°	1273	1240	1244
25°	1246	1204	1211
30°	1212	1170	1169
35°	1180	1130	1124
40°	1141	1090	1081
45°	1102	1050	1037
50°	1059	1007	987
55°	1015	958	940
60°	964	901	887
65°	908	840	823
70°	838	767	755
75°	740	679	692
80°	622	566	572
85°	438	375	375

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1152 cd/sqm



TEST NUMBER: P904935

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	1.4
10°-20°	309.1	3.9
20°-30°	454.3	5.7
30°-40°	527.6	6.7
40°-50°	527.0	6.7
50°-60°	459.5	5.8
60°-70°	339.7	4.3
70°-80°	192.2	2.4
80°-90°	53.7	0.7
90°-100°	55.7	0.7
100°-110°	207.4	2.6
110°-120°	550.1	6.9
120°-130°	912.4	11.5
130°-140°	969.2	12.2
140°-150°	900.8	11.4
150°-160°	724.2	9.1
160°-170°	466.6	5.9
170°-180°	160.6	2.0
0°-30°	873.3	11.0
0°-40°	1400.9	17.7
0°-60°	2387.4	30.1
0°-90°	2973.0	37.5
90°-120°	813.2	10.3
90°-150°	3595.6	45.4
90°-180°	4947.0	62.5
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	51
90°	1	15	24	31	33	7
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P904935

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P904935

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P904935
 CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.95	7.71	8.01	8.77	10.21	6.51	7.27	7.57	8.33	9.77
	3H	8.60	9.28	9.67	10.35	11.81	8.11	8.79	9.18	9.86	11.32
	4H	9.18	9.83	10.26	10.90	12.36	8.69	9.33	9.77	10.41	11.87
	6H	9.57	10.17	10.66	11.24	12.72	9.07	9.67	10.16	10.74	12.22
	8H	9.67	10.24	10.77	11.33	12.80	9.17	9.74	10.26	10.83	12.30
	12H	9.72	10.25	10.81	11.34	12.83	9.21	9.75	10.30	10.83	12.32
4H	2H	7.40	8.04	8.48	9.12	10.58	7.04	7.69	8.13	8.76	10.22
	3H	9.25	9.79	10.34	10.89	12.36	8.84	9.38	9.93	10.48	11.96
	4H	9.96	10.45	11.05	11.54	13.04	9.53	10.03	10.63	11.12	12.61
	6H	10.46	10.89	11.57	12.00	13.49	10.03	10.45	11.14	11.57	13.06
	8H	10.61	11.00	11.71	12.11	13.61	10.17	10.57	11.27	11.67	13.18
	12H	10.67	11.03	11.80	12.15	13.66	10.22	10.58	11.35	11.70	13.21
8H	4H	10.14	10.54	11.25	11.64	13.15	9.76	10.16	10.87	11.26	12.77
	6H	10.76	11.09	11.89	12.24	13.74	10.38	10.71	11.51	11.85	13.35
	8H	10.98	11.26	12.11	12.39	13.92	10.59	10.87	11.72	12.00	13.52
	12H	11.10	11.35	12.24	12.48	14.04	10.69	10.94	11.83	12.07	13.63
12H	4H	10.12	10.48	11.24	11.60	13.11	9.75	10.11	10.87	11.23	12.74
	6H	10.79	11.08	11.92	12.20	13.73	10.42	10.70	11.55	11.83	13.35
	8H	11.02	11.27	12.16	12.40	13.96	10.64	10.89	11.78	12.02	13.58