

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926603

Luminaire Tested: DFN2DIP-TR4F0-100D090US950-FLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P926603  
REPORT IS A COMBINATION OF REPORTS P901991 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-100D090US950-FLLONL  
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17944.7 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 168.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9972  
Total Harmonic Distortion (THDi): 0.128  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926603  
CATALOG NUMBER: DFN2DIP-TR4F0-100D090US950-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P926603  
 CATALOG NUMBER: DFN2DIP-TR4F0-100D090US950-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53			
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	49	44			
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37			
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	40	38	35	31			
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31	27			
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	23			
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23	21			
7	59	46	38	33	54	43	36	31	37	32	27	32	28	24	27	24	21	18			
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16			
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	19	17	15			
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2949	2949	2949
5°	2954	2908	2927
10°	2930	2869	2888
15°	2887	2821	2826
20°	2829	2756	2762
25°	2771	2677	2689
30°	2698	2604	2595
35°	2629	2518	2497
40°	2545	2431	2403
45°	2460	2344	2307
50°	2368	2252	2196
55°	2272	2146	2093
60°	2162	2020	1976
65°	2043	1891	1838
70°	1892	1732	1689
75°	1681	1542	1551
80°	1429	1300	1289
85°	1034	882	854

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2460 cd/sqm



TEST NUMBER: P926603

CATALOG NUMBER: DFN2DIP-TR4F0-100D090US950-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	349.4	1.9
10°-20°	983.0	5.5
20°-30°	1444.7	8.1
30°-40°	1677.9	9.4
40°-50°	1675.8	9.3
50°-60°	1461.2	8.1
60°-70°	1080.2	6.0
70°-80°	611.1	3.4
80°-90°	166.4	0.9
90°-100°	95.6	0.5
100°-110°	356.2	2.0
110°-120°	944.7	5.3
120°-130°	1566.8	8.7
130°-140°	1664.3	9.3
140°-150°	1546.8	8.6
150°-160°	1243.6	6.9
160°-170°	801.3	4.5
170°-180°	275.8	1.5
0°-30°	2777.1	15.5
0°-40°	4454.9	24.8
0°-60°	7592.0	42.3
0°-90°	9449.7	52.7
90°-120°	1396.4	7.8
90°-150°	6174.3	34.4
90°-180°	8495.0	47.3
0°-180°	17944.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3712	3712	3712	3712	3712	
5°	3712	3698	3659	3687	3680	352
15°	3534	3512	3466	3480	3462	995
25°	3198	3170	3109	3116	3109	1472
35°	2759	2724	2666	2645	2627	1723
45°	2245	2220	2166	2128	2113	1733
55°	1699	1678	1635	1592	1574	1519
65°	1146	1124	1089	1057	1039	1133
75°	600	593	574	553	560	640
85°	146	143	139	128	125	163
90°	2	25	42	53	56	17
95°	136	67	82	92	90	161
105°	637	700	128	151	159	681
115°	1206	1241	1294	323	172	1187
125°	1704	1732	1772	1786	1793	1520
135°	2109	2143	2162	2183	2179	1629
145°	2447	2445	2480	2495	2485	1530
155°	2694	2676	2701	2713	2696	1242
165°	2839	2826	2833	2847	2833	802
175°	2904	2889	2894	2908	2887	276
180°	2898	2898	2898	2898	2898	



TEST NUMBER: P926603

CATALOG NUMBER: DFN2DIP-TR4F0-100D090US950-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3712.1	3712.1	3712.1	3712.1	3712.1
2.5°	3733.7	3715.8	3676.4	3712.1	3705.2
5°	3712.1	3698.1	3658.7	3687.1	3680.2
7.5°	3687.1	3665.8	3626.4	3655.3	3648.1
10°	3648.1	3623.1	3580.3	3608.7	3598.1
12.5°	3594.3	3573.1	3530.3	3548.1	3540.9
15°	3533.7	3512.5	3465.9	3480.3	3462.5
17.5°	3458.7	3437.5	3390.9	3408.7	3390.9
20°	3376.5	3355.3	3305.3	3315.9	3301.9
22.5°	3294.7	3262.6	3215.9	3215.9	3208.8
25°	3198.2	3169.8	3109.2	3116.0	3109.2
27.5°	3091.0	3066.0	3019.8	3009.2	2991.4
30°	2984.2	2955.4	2902.0	2891.4	2877.0
32.5°	2869.8	2848.6	2791.4	2769.8	2755.4
35°	2759.3	2723.7	2666.4	2644.9	2627.0
37.5°	2634.3	2602.0	2544.9	2519.9	2502.1
40°	2505.9	2477.1	2419.9	2388.1	2373.7
42.5°	2380.9	2352.1	2295.3	2259.4	2238.2
45°	2245.3	2220.3	2166.5	2127.5	2113.2
47.5°	2113.2	2088.2	2031.0	1991.6	1970.4
50°	1973.8	1956.0	1906.0	1856.0	1838.3
52.5°	1838.3	1813.3	1767.0	1727.7	1702.7
55°	1699.3	1677.7	1634.9	1592.0	1574.3
57.5°	1559.9	1542.0	1495.5	1452.8	1438.3
60°	1420.5	1406.5	1356.5	1317.1	1306.5
62.5°	1284.9	1259.9	1224.4	1188.8	1174.4
65°	1145.9	1124.4	1088.8	1056.6	1038.8
67.5°	1003.2	985.0	953.2	928.2	913.8
70°	871.0	856.6	824.4	799.5	785.4
72.5°	735.4	721.0	703.3	678.3	667.6
75°	599.5	592.7	574.5	553.3	560.5
77.5°	478.3	463.9	456.7	446.1	435.5
80°	357.1	353.4	346.1	335.5	328.4
82.5°	242.8	242.8	239.4	225.0	225.0
85°	146.2	142.8	139.4	128.4	125.0
87.5°	64.4	57.1	50.0	39.4	35.6
90°	2.0	25.2	41.8	52.6	56.5
92.5°	52.6	44.1	50.3	54.6	56.5
95°	136.2	67.0	81.7	92.3	90.2
97.5°	245.3	73.5	106.8	113.2	115.2
100°	371.2	84.0	119.5	136.2	140.4
102.5°	509.4	505.4	123.7	146.6	153.1
105°	637.4	700.4	127.9	150.9	159.3
107.5°	786.3	838.6	132.2	155.1	163.6
110°	928.9	972.8	367.0	157.3	165.6



TEST NUMBER: P926603

CATALOG NUMBER: DFN2DIP-TR4F0-100D090US950-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1063.1	1100.7	1065.1	161.3	167.8
115°	1205.6	1241.2	1293.7	322.9	172.0
117.5°	1329.3	1371.2	1407.0	1107.0	557.7
120°	1467.7	1499.1	1537.0	1562.1	1279.0
122.5°	1585.1	1618.7	1660.7	1673.1	1675.4
125°	1704.5	1731.9	1771.8	1786.5	1792.7
127.5°	1813.6	1842.9	1874.6	1895.5	1897.5
130°	1916.4	1950.1	1973.0	1996.1	1994.1
132.5°	2021.2	2048.6	2071.5	2090.5	2088.5
135°	2109.4	2143.0	2161.7	2182.8	2178.6
137.5°	2201.5	2226.6	2247.8	2268.7	2262.5
140°	2291.6	2308.6	2331.5	2350.4	2340.0
142.5°	2367.4	2382.0	2409.1	2425.8	2415.4
145°	2447.0	2444.7	2480.4	2495.1	2484.6
147.5°	2516.0	2509.8	2545.4	2555.9	2547.6
150°	2583.2	2568.5	2602.1	2614.5	2604.1
152.5°	2639.7	2623.0	2654.4	2667.1	2652.4
155°	2694.3	2675.6	2700.7	2713.2	2696.5
157.5°	2738.4	2721.7	2740.6	2755.2	2738.4
160°	2776.1	2763.5	2776.1	2788.6	2773.9
162.5°	2809.5	2797.0	2807.5	2822.2	2803.3
165°	2838.9	2826.4	2832.7	2847.4	2832.7
167.5°	2862.1	2849.4	2855.8	2870.5	2851.6
170°	2881.0	2868.3	2872.5	2887.2	2868.3
172.5°	2893.5	2881.0	2885.2	2899.9	2881.0
175°	2903.9	2889.2	2893.5	2908.1	2887.2
177.5°	2908.1	2893.5	2895.7	2910.4	2891.5
180°	2897.7	2897.7	2897.7	2897.7	2897.7



TEST NUMBER: P926603  
 CATALOG NUMBER: DFN2DIP-TR4F0-100D090US950-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.27	12.15	12.20	13.10	14.34	10.84	11.72	11.77	12.67	13.91
	3H	12.93	13.72	13.87	14.68	15.94	12.46	13.25	13.40	14.21	15.47
	4H	13.52	14.27	14.48	15.23	16.50	13.04	13.80	14.00	14.76	16.03
	6H	13.92	14.61	14.89	15.58	16.86	13.44	14.14	14.41	15.11	16.38
	8H	14.02	14.68	15.00	15.67	16.95	13.55	14.21	14.53	15.20	16.47
	12H	14.07	14.70	15.06	15.68	16.98	13.59	14.22	14.58	15.20	16.50
4H	2H	11.73	12.48	12.70	13.45	14.71	11.39	12.14	12.35	13.10	14.37
	3H	13.60	14.23	14.57	15.22	16.50	13.21	13.83	14.18	14.83	16.11
	4H	14.31	14.89	15.30	15.88	17.18	13.91	14.48	14.89	15.47	16.77
	6H	14.83	15.33	15.83	16.34	17.64	14.42	14.92	15.42	15.93	17.23
	8H	14.98	15.44	15.98	16.45	17.76	14.57	15.03	15.57	16.04	17.35
	12H	15.06	15.47	16.07	16.49	17.81	14.63	15.05	15.65	16.07	17.39
8H	4H	14.51	14.98	15.51	15.98	17.30	14.15	14.62	15.15	15.62	16.94
	6H	15.15	15.53	16.17	16.57	17.89	14.78	15.17	15.81	16.21	17.53
	8H	15.37	15.70	16.40	16.74	18.07	15.00	15.33	16.03	16.37	17.70
	12H	15.50	15.80	16.53	16.82	18.20	15.12	15.41	16.15	16.44	17.82
12H	4H	14.50	14.92	15.52	15.94	17.26	14.15	14.57	15.17	15.59	16.91
	6H	15.18	15.51	16.21	16.55	17.88	14.82	15.16	15.86	16.19	17.53
	8H	15.42	15.72	16.45	16.74	18.12	15.06	15.36	16.10	16.39	17.76