

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926607

Luminaire Tested: DFN2DIP-TR4F0-100D100US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926607
REPORT IS A COMBINATION OF REPORTS P902009 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D100US950-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18889.2 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 177.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926607

CATALOG NUMBER: DFN2DIP-TR4F0-100D100US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926607

CATALOG NUMBER: DFN2DIP-TR4F0-100D100US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2949	2949	2949
5°	2954	2908	2927
10°	2930	2869	2888
15°	2887	2821	2826
20°	2829	2756	2762
25°	2771	2677	2689
30°	2698	2604	2595
35°	2629	2518	2497
40°	2545	2431	2403
45°	2460	2344	2307
50°	2368	2252	2196
55°	2272	2146	2093
60°	2162	2020	1976
65°	2043	1891	1838
70°	1892	1732	1689
75°	1681	1542	1551
80°	1429	1300	1289
85°	1034	882	854

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2460 cd/sqm

TEST NUMBER: P926607

CATALOG NUMBER: DFN2DIP-TR4F0-100D100US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.4	1.8
10°-20°	983.0	5.2
20°-30°	1444.7	7.6
30°-40°	1677.9	8.9
40°-50°	1675.8	8.9
50°-60°	1461.2	7.7
60°-70°	1080.2	5.7
70°-80°	611.1	3.2
80°-90°	167.0	0.9
90°-100°	106.2	0.6
100°-110°	395.8	2.1
110°-120°	1049.6	5.6
120°-130°	1740.9	9.2
130°-140°	1849.2	9.8
140°-150°	1718.7	9.1
150°-160°	1381.8	7.3
160°-170°	890.4	4.7
170°-180°	306.5	1.6
0°-30°	2777.1	14.7
0°-40°	4454.9	23.6
0°-60°	7592.0	40.2
0°-90°	9450.3	50.0
90°-120°	1551.6	8.2
90°-150°	6860.4	36.3
90°-180°	9439.0	50.0
0°-180°	18889.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3712	3712	3712	3712	3712	
5°	3712	3698	3659	3687	3680	352
15°	3534	3512	3466	3480	3462	995
25°	3198	3170	3109	3116	3109	1472
35°	2759	2724	2666	2645	2627	1723
45°	2245	2220	2166	2128	2113	1733
55°	1699	1678	1635	1592	1574	1519
65°	1146	1124	1089	1057	1039	1133
75°	600	593	574	553	560	640
85°	146	143	139	128	125	163
90°	2	28	46	58	63	17
95°	151	74	91	103	100	179
105°	708	778	142	168	177	757
115°	1340	1379	1438	359	191	1319
125°	1894	1924	1969	1985	1992	1689
135°	2344	2381	2402	2425	2421	1810
145°	2719	2716	2756	2772	2761	1700
155°	2994	2973	3001	3015	2996	1380
165°	3154	3140	3147	3164	3147	891
175°	3226	3210	3215	3231	3208	307
180°	3220	3220	3220	3220	3220	

TEST NUMBER: P926607

CATALOG NUMBER: DFN2DIP-TR4F0-100D100US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3712.1	3712.1	3712.1	3712.1	3712.1
2.5°	3733.7	3715.8	3676.4	3712.1	3705.2
5°	3712.1	3698.1	3658.7	3687.1	3680.2
7.5°	3687.1	3665.8	3626.4	3655.3	3648.1
10°	3648.1	3623.1	3580.3	3608.7	3598.1
12.5°	3594.3	3573.1	3530.3	3548.1	3540.9
15°	3533.7	3512.5	3465.9	3480.3	3462.5
17.5°	3458.7	3437.5	3390.9	3408.7	3390.9
20°	3376.5	3355.3	3305.3	3315.9	3301.9
22.5°	3294.7	3262.6	3215.9	3215.9	3208.8
25°	3198.2	3169.8	3109.2	3116.0	3109.2
27.5°	3091.0	3066.0	3019.8	3009.2	2991.4
30°	2984.2	2955.4	2902.0	2891.4	2877.0
32.5°	2869.8	2848.6	2791.4	2769.8	2755.4
35°	2759.3	2723.7	2666.4	2644.9	2627.0
37.5°	2634.3	2602.0	2544.9	2519.9	2502.1
40°	2505.9	2477.1	2419.9	2388.1	2373.7
42.5°	2380.9	2352.1	2295.3	2259.4	2238.2
45°	2245.3	2220.3	2166.5	2127.5	2113.2
47.5°	2113.2	2088.2	2031.0	1991.6	1970.4
50°	1973.8	1956.0	1906.0	1856.0	1838.3
52.5°	1838.3	1813.3	1767.0	1727.7	1702.7
55°	1699.3	1677.7	1634.9	1592.0	1574.3
57.5°	1559.9	1542.0	1495.5	1452.8	1438.3
60°	1420.5	1406.5	1356.5	1317.1	1306.5
62.5°	1284.9	1259.9	1224.4	1188.8	1174.4
65°	1145.9	1124.4	1088.8	1056.6	1038.8
67.5°	1003.2	985.0	953.2	928.2	913.8
70°	871.0	856.6	824.4	799.5	785.4
72.5°	735.4	721.0	703.3	678.3	667.6
75°	599.5	592.7	574.5	553.3	560.5
77.5°	478.3	463.9	456.7	446.1	435.5
80°	357.1	353.4	346.1	335.5	328.4
82.5°	242.8	242.8	239.4	225.0	225.0
85°	146.2	142.8	139.4	128.4	125.0
87.5°	64.4	57.1	50.0	39.4	35.6
90°	2.2	28.0	46.5	58.4	62.8
92.5°	58.4	48.9	55.9	60.6	62.8
95°	151.3	74.4	90.7	102.7	100.2
97.5°	272.5	81.6	118.7	125.8	128.1
100°	412.5	93.2	132.8	151.3	156.1
102.5°	566.0	561.6	137.5	162.9	170.1
105°	708.2	778.2	142.2	167.6	177.1
107.5°	873.7	931.8	146.9	172.4	181.7
110°	1032.1	1080.9	407.7	174.9	183.9

TEST NUMBER: P926607

CATALOG NUMBER: DFN2DIP-TR4F0-100D100US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1181.2	1223.0	1183.5	179.3	186.5
115°	1339.5	1379.1	1437.5	358.8	191.2
117.5°	1477.0	1523.5	1563.3	1230.0	619.7
120°	1630.9	1665.7	1707.8	1735.7	1421.2
122.5°	1761.2	1798.5	1845.2	1859.1	1861.5
125°	1894.0	1924.4	1968.7	1985.0	1991.9
127.5°	2015.1	2047.8	2082.9	2106.1	2108.3
130°	2129.3	2166.7	2192.2	2217.9	2215.7
132.5°	2245.8	2276.2	2301.7	2322.7	2320.5
135°	2343.8	2381.1	2401.9	2425.4	2420.7
137.5°	2446.2	2474.1	2497.6	2520.8	2513.9
140°	2546.2	2565.1	2590.5	2611.6	2599.9
142.5°	2630.4	2646.7	2676.8	2695.3	2683.8
145°	2718.9	2716.4	2756.0	2772.3	2760.7
147.5°	2795.5	2788.6	2828.1	2839.8	2830.7
150°	2870.2	2853.9	2891.3	2905.1	2893.5
152.5°	2933.0	2914.5	2949.4	2963.4	2947.1
155°	2993.7	2972.9	3000.8	3014.6	2996.1
157.5°	3042.6	3024.1	3045.1	3061.4	3042.6
160°	3084.7	3070.5	3084.7	3098.5	3082.2
162.5°	3121.7	3107.8	3119.5	3135.8	3114.8
165°	3154.3	3140.5	3147.4	3163.8	3147.4
167.5°	3180.1	3165.9	3173.2	3189.5	3168.4
170°	3201.1	3187.0	3191.7	3208.0	3187.0
172.5°	3214.9	3201.1	3205.8	3222.1	3201.1
175°	3226.5	3210.2	3214.9	3231.3	3208.0
177.5°	3231.3	3214.9	3217.5	3233.8	3212.7
180°	3219.7	3219.7	3219.7	3219.7	3219.7

TEST NUMBER: P926607

CATALOG NUMBER: DFN2DIP-TR4F0-100D100US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.03	11.89	11.98	12.86	14.13	10.60	11.46	11.55	12.43	13.70
	3H	12.69	13.46	13.66	14.44	15.73	12.21	12.99	13.18	13.97	15.26
	4H	13.27	14.01	14.26	14.99	16.29	12.80	13.53	13.78	14.52	15.82
	6H	13.67	14.35	14.67	15.34	16.65	13.20	13.87	14.19	14.86	16.18
	8H	13.78	14.42	14.78	15.43	16.74	13.30	13.95	14.30	14.95	16.26
	12H	13.83	14.44	14.83	15.44	16.77	13.35	13.96	14.35	14.96	16.29
4H	2H	11.49	12.22	12.48	13.21	14.51	11.14	11.88	12.13	12.86	14.16
	3H	13.35	13.96	14.35	14.98	16.29	12.96	13.57	13.96	14.59	15.90
	4H	14.07	14.63	15.07	15.63	16.97	13.66	14.22	14.67	15.23	16.57
	6H	14.58	15.06	15.60	16.10	17.43	14.17	14.66	15.19	15.69	17.02
	8H	14.73	15.18	15.75	16.21	17.56	14.32	14.77	15.34	15.79	17.15
	12H	14.81	15.21	15.84	16.25	17.61	14.39	14.79	15.42	15.83	17.19
8H	4H	14.27	14.71	15.28	15.74	17.09	13.91	14.35	14.92	15.38	16.73
	6H	14.90	15.27	15.94	16.33	17.68	14.53	14.91	15.58	15.97	17.32
	8H	15.12	15.44	16.17	16.50	17.86	14.75	15.08	15.80	16.13	17.49
	12H	15.25	15.54	16.30	16.58	17.99	14.87	15.15	15.92	16.20	17.61
12H	4H	14.25	14.66	15.29	15.70	17.05	13.90	14.31	14.94	15.34	16.70
	6H	14.93	15.25	15.98	16.31	17.67	14.58	14.90	15.63	15.95	17.32
	8H	15.17	15.46	16.22	16.50	17.91	14.81	15.10	15.87	16.15	17.56

END OF REPORT