

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926615

Luminaire Tested: DFN2DIP-TR4F0-100D120US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926615
REPORT IS A COMBINATION OF REPORTS P902045 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D120US950-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20778.1 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926615

CATALOG NUMBER: DFN2DIP-TR4F0-100D120US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926615

CATALOG NUMBER: DFN2DIP-TR4F0-100D120US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2949	2949	2949
5°	2954	2908	2927
10°	2930	2869	2888
15°	2887	2821	2826
20°	2829	2756	2762
25°	2771	2677	2689
30°	2698	2604	2595
35°	2629	2518	2497
40°	2545	2431	2403
45°	2460	2344	2307
50°	2368	2252	2196
55°	2272	2146	2093
60°	2162	2020	1976
65°	2043	1891	1838
70°	1892	1732	1689
75°	1681	1542	1551
80°	1429	1300	1289
85°	1034	882	854

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2460 cd/sqm

TEST NUMBER: P926615

CATALOG NUMBER: DFN2DIP-TR4F0-100D120US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.4	1.7
10°-20°	983.0	4.7
20°-30°	1444.7	7.0
30°-40°	1677.9	8.1
40°-50°	1675.8	8.1
50°-60°	1461.2	7.0
60°-70°	1080.2	5.2
70°-80°	611.1	2.9
80°-90°	168.1	0.8
90°-100°	127.4	0.6
100°-110°	474.9	2.3
110°-120°	1259.5	6.1
120°-130°	2089.1	10.1
130°-140°	2219.1	10.7
140°-150°	2062.4	9.9
150°-160°	1658.1	8.0
160°-170°	1068.4	5.1
170°-180°	367.7	1.8
0°-30°	2777.1	13.4
0°-40°	4454.9	21.4
0°-60°	7592.0	36.5
0°-90°	9451.4	45.5
90°-120°	1861.9	9.0
90°-150°	8232.4	39.6
90°-180°	11327.0	54.5
0°-180°	20778.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3712	3712	3712	3712	3712	
5°	3712	3698	3659	3687	3680	352
15°	3534	3512	3466	3480	3462	995
25°	3198	3170	3109	3116	3109	1472
35°	2759	2724	2666	2645	2627	1723
45°	2245	2220	2166	2128	2113	1733
55°	1699	1678	1635	1592	1574	1519
65°	1146	1124	1089	1057	1039	1133
75°	600	593	574	553	560	640
85°	146	143	139	128	125	163
90°	3	34	56	70	75	19
95°	182	89	109	123	120	215
105°	850	934	171	201	212	908
115°	1607	1655	1725	430	229	1582
125°	2273	2309	2362	2382	2390	2027
135°	2812	2857	2882	2910	2905	2173
145°	3263	3260	3307	3327	3313	2041
155°	3592	3567	3601	3618	3595	1655
165°	3785	3769	3777	3796	3777	1069
175°	3872	3852	3858	3878	3850	368
180°	3864	3864	3864	3864	3864	

TEST NUMBER: P926615

CATALOG NUMBER: DFN2DIP-TR4F0-100D120US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3712.1	3712.1	3712.1	3712.1	3712.1
2.5°	3733.7	3715.8	3676.4	3712.1	3705.2
5°	3712.1	3698.1	3658.7	3687.1	3680.2
7.5°	3687.1	3665.8	3626.4	3655.3	3648.1
10°	3648.1	3623.1	3580.3	3608.7	3598.1
12.5°	3594.3	3573.1	3530.3	3548.1	3540.9
15°	3533.7	3512.5	3465.9	3480.3	3462.5
17.5°	3458.7	3437.5	3390.9	3408.7	3390.9
20°	3376.5	3355.3	3305.3	3315.9	3301.9
22.5°	3294.7	3262.6	3215.9	3215.9	3208.8
25°	3198.2	3169.8	3109.2	3116.0	3109.2
27.5°	3091.0	3066.0	3019.8	3009.2	2991.4
30°	2984.2	2955.4	2902.0	2891.4	2877.0
32.5°	2869.8	2848.6	2791.4	2769.8	2755.4
35°	2759.3	2723.7	2666.4	2644.9	2627.0
37.5°	2634.3	2602.0	2544.9	2519.9	2502.1
40°	2505.9	2477.1	2419.9	2388.1	2373.7
42.5°	2380.9	2352.1	2295.3	2259.4	2238.2
45°	2245.3	2220.3	2166.5	2127.5	2113.2
47.5°	2113.2	2088.2	2031.0	1991.6	1970.4
50°	1973.8	1956.0	1906.0	1856.0	1838.3
52.5°	1838.3	1813.3	1767.0	1727.7	1702.7
55°	1699.3	1677.7	1634.9	1592.0	1574.3
57.5°	1559.9	1542.0	1495.5	1452.8	1438.3
60°	1420.5	1406.5	1356.5	1317.1	1306.5
62.5°	1284.9	1259.9	1224.4	1188.8	1174.4
65°	1145.9	1124.4	1088.8	1056.6	1038.8
67.5°	1003.2	985.0	953.2	928.2	913.8
70°	871.0	856.6	824.4	799.5	785.4
72.5°	735.4	721.0	703.3	678.3	667.6
75°	599.5	592.7	574.5	553.3	560.5
77.5°	478.3	463.9	456.7	446.1	435.5
80°	357.1	353.4	346.1	335.5	328.4
82.5°	242.8	242.8	239.4	225.0	225.0
85°	146.2	142.8	139.4	128.4	125.0
87.5°	64.4	57.1	50.0	39.4	35.6
90°	2.7	33.5	55.8	70.0	75.4
92.5°	70.0	58.8	67.1	72.7	75.4
95°	181.5	89.3	108.9	123.2	120.2
97.5°	327.0	98.0	142.4	151.0	153.7
100°	494.9	111.9	159.3	181.5	187.3
102.5°	679.2	673.9	164.9	195.6	204.2
105°	849.8	933.9	170.7	201.2	212.5
107.5°	1048.4	1118.1	176.3	206.8	218.1
110°	1238.6	1297.1	489.3	209.8	220.8

TEST NUMBER: P926615

CATALOG NUMBER: DFN2DIP-TR4F0-100D120US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1417.5	1467.6	1420.2	215.1	223.7
115°	1607.4	1654.9	1724.9	430.5	229.4
117.5°	1772.4	1828.2	1876.0	1475.9	743.6
120°	1957.0	1998.8	2049.3	2082.9	1705.4
122.5°	2113.4	2158.2	2214.3	2230.9	2233.9
125°	2272.7	2309.3	2362.4	2381.9	2390.2
127.5°	2418.1	2457.3	2499.5	2527.3	2530.0
130°	2555.2	2600.0	2630.6	2661.5	2658.8
132.5°	2695.0	2731.5	2762.0	2787.3	2784.6
135°	2812.5	2857.3	2882.2	2910.5	2904.8
137.5°	2935.4	2968.8	2997.1	3024.9	3016.6
140°	3055.6	3078.1	3108.6	3133.9	3120.0
142.5°	3156.4	3176.1	3212.2	3234.4	3220.5
145°	3262.7	3259.7	3307.1	3326.8	3312.8
147.5°	3354.6	3346.3	3393.9	3407.8	3396.8
150°	3444.2	3424.7	3469.5	3486.1	3472.2
152.5°	3519.6	3497.4	3539.2	3556.1	3536.6
155°	3592.3	3567.4	3601.0	3617.6	3595.3
157.5°	3651.1	3628.8	3654.1	3673.7	3651.1
160°	3701.5	3684.6	3701.5	3718.1	3698.6
162.5°	3746.1	3729.5	3743.4	3763.0	3737.8
165°	3785.2	3768.6	3776.9	3796.5	3776.9
167.5°	3816.1	3799.1	3807.8	3827.4	3802.2
170°	3841.3	3824.4	3830.0	3849.6	3824.4
172.5°	3857.9	3841.3	3847.0	3866.6	3841.3
175°	3871.8	3852.3	3857.9	3877.5	3849.6
177.5°	3877.5	3857.9	3860.9	3880.5	3855.3
180°	3863.6	3863.6	3863.6	3863.6	3863.6

TEST NUMBER: P926615

CATALOG NUMBER: DFN2DIP-TR4F0-100D120US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.59	11.41	11.59	12.42	13.75	10.16	10.98	11.16	11.99	13.32
	3H	12.25	12.99	13.25	14.00	15.36	11.78	12.51	12.78	13.53	14.88
	4H	12.83	13.53	13.85	14.55	15.91	12.36	13.06	13.38	14.08	15.44
	6H	13.23	13.88	14.26	14.90	16.27	12.76	13.40	13.79	14.42	15.80
	8H	13.34	13.95	14.37	14.99	16.36	12.86	13.47	13.90	14.51	15.88
	12H	13.38	13.96	14.42	15.00	16.39	12.90	13.48	13.94	14.52	15.91
4H	2H	11.05	11.75	12.07	12.77	14.13	10.70	11.40	11.73	12.42	13.78
	3H	12.91	13.49	13.94	14.54	15.92	12.52	13.10	13.55	14.15	15.52
	4H	13.62	14.16	14.66	15.20	16.59	13.22	13.75	14.26	14.79	16.19
	6H	14.14	14.60	15.19	15.66	17.05	13.73	14.19	14.78	15.25	16.64
	8H	14.29	14.71	15.34	15.77	17.18	13.87	14.30	14.92	15.36	16.77
	12H	14.36	14.74	15.43	15.81	17.23	13.93	14.32	15.00	15.39	16.81
8H	4H	13.82	14.25	14.87	15.30	16.71	13.46	13.89	14.51	14.94	16.35
	6H	14.45	14.80	15.52	15.90	17.30	14.08	14.44	15.16	15.54	16.94
	8H	14.67	14.98	15.75	16.06	17.49	14.30	14.61	15.38	15.69	17.12
	12H	14.80	15.07	15.88	16.15	17.61	14.41	14.69	15.50	15.76	17.23
12H	4H	13.80	14.19	14.87	15.26	16.67	13.45	13.84	14.52	14.91	16.32
	6H	14.48	14.79	15.56	15.87	17.29	14.13	14.44	15.21	15.52	16.94
	8H	14.72	14.99	15.80	16.07	17.53	14.36	14.63	15.45	15.71	17.18

END OF REPORT