

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902396

Luminaire Tested: DFN2DIP-4P4F0-080D030US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902396
REPORT IS A COMBINATION OF REPORTS P899090 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D030US830-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8911.8 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 108.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902396

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902396

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	96	96	96	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	49	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2022	2022	2022
5°	2025	1990	2003
10°	2005	1952	1939
15°	1978	1888	1839
20°	1941	1800	1716
25°	1904	1700	1597
30°	1854	1599	1446
35°	1805	1489	1313
40°	1755	1376	1161
45°	1697	1250	1023
50°	1637	1123	888
55°	1575	988	758
60°	1502	846	625
65°	1419	701	563
70°	1318	566	511
75°	1191	501	467
80°	1008	422	407
85°	704	285	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1697 cd/sqm

TEST NUMBER: P902396

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	3.3
10°-20°	801.8	9.0
20°-30°	1125.7	12.6
30°-40°	1227.1	13.8
40°-50°	1127.8	12.7
50°-60°	885.7	9.9
60°-70°	576.5	6.5
70°-80°	296.8	3.3
80°-90°	78.3	0.9
90°-100°	55.3	0.6
100°-110°	175.8	2.0
110°-120°	300.9	3.4
120°-130°	395.7	4.4
130°-140°	444.2	5.0
140°-150°	435.6	4.9
150°-160°	365.4	4.1
160°-170°	242.3	2.7
170°-180°	84.7	1.0
0°-30°	2219.6	24.9
0°-40°	3446.7	38.7
0°-60°	5460.2	61.3
0°-90°	6411.9	71.9
90°-120°	532.1	6.0
90°-150°	1807.5	20.3
90°-180°	2500.0	28.1
0°-180°	8911.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	1	10	26	25	26	9
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	

TEST NUMBER: P902396

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4

TEST NUMBER: P902396

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3

TEST NUMBER: P902396

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.45	12.50	12.20	13.27	14.19	7.42	8.46	8.17	9.23	10.15
	3H	13.15	14.09	13.92	14.87	15.82	8.62	9.56	9.39	10.34	11.29
	4H	13.78	14.66	14.56	15.45	16.41	9.08	9.97	9.87	10.75	11.72
	6H	14.21	15.03	15.01	15.82	16.80	9.42	10.23	10.21	11.03	12.00
	8H	14.35	15.12	15.15	15.94	16.92	9.51	10.29	10.32	11.10	12.08
	12H	14.42	15.16	15.23	15.96	16.97	9.57	10.30	10.38	11.11	12.12
4H	2H	11.50	12.38	12.28	13.17	14.13	8.04	8.92	8.83	9.71	10.67
	3H	13.35	14.09	14.15	14.91	15.89	9.41	10.15	10.21	10.97	11.95
	4H	14.06	14.73	14.87	15.55	16.55	9.97	10.64	10.78	11.46	12.47
	6H	14.59	15.17	15.42	16.01	17.03	10.40	10.98	11.23	11.82	12.84
	8H	14.77	15.31	15.61	16.15	17.18	10.54	11.07	11.37	11.91	12.94
	12H	14.88	15.37	15.73	16.23	17.26	10.61	11.10	11.46	11.96	12.99
8H	4H	14.04	14.58	14.88	15.42	16.45	10.27	10.81	11.10	11.65	12.67
	6H	14.62	15.07	15.48	15.95	16.98	10.80	11.24	11.66	12.12	13.15
	8H	14.85	15.24	15.72	16.12	17.16	10.99	11.39	11.86	12.26	13.31
	12H	15.00	15.34	15.87	16.21	17.31	11.12	11.47	12.00	12.34	13.44
12H	4H	14.01	14.49	14.86	15.35	16.38	10.29	10.77	11.14	11.63	12.66
	6H	14.60	14.99	15.47	15.87	16.92	10.85	11.24	11.72	12.12	13.17
	8H	14.83	15.18	15.71	16.05	17.15	11.07	11.42	11.95	12.29	13.39