

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926618

Luminaire Tested: DFN2DIP-TR4F0-110D040US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926618
REPORT IS A COMBINATION OF REPORTS P900383 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D040US950-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13766.2 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 143
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926618
CATALOG NUMBER: DFN2DIP-TR4F0-110D040US950-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P926618

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	80	80	80	80	80	80	75
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	70	69	67	67	67	67	64
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	57	57	57	53
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	48	48	48	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	42	42	42	39
5	73	60	52	46	69	58	50	44	53	46	42	48	43	39	44	40	36	36	36	36	34
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32	32	32	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	34	30	37	32	29	29	29	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	26	26	26	23
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	23	23	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3244	3244	3244
5°	3249	3199	3220
10°	3223	3156	3176
15°	3175	3104	3108
20°	3111	3031	3038
25°	3048	2945	2958
30°	2968	2865	2855
35°	2892	2770	2746
40°	2799	2674	2643
45°	2706	2578	2538
50°	2605	2477	2415
55°	2499	2361	2303
60°	2379	2223	2174
65°	2248	2080	2021
70°	2081	1905	1858
75°	1849	1696	1707
80°	1572	1429	1418
85°	1137	970	940

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2706 cd/sqm



TEST NUMBER: P926618

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.3	2.8
10°-20°	1081.3	7.9
20°-30°	1589.1	11.5
30°-40°	1845.7	13.4
40°-50°	1843.4	13.4
50°-60°	1607.4	11.7
60°-70°	1188.2	8.6
70°-80°	672.3	4.9
80°-90°	180.9	1.3
90°-100°	74.7	0.5
100°-110°	237.3	1.7
110°-120°	406.1	2.9
120°-130°	534.0	3.9
130°-140°	599.4	4.4
140°-150°	587.8	4.3
150°-160°	493.1	3.6
160°-170°	327.0	2.4
170°-180°	114.3	0.8
0°-30°	3054.8	22.2
0°-40°	4900.4	35.6
0°-60°	8351.2	60.7
0°-90°	10392.5	75.5
90°-120°	718.0	5.2
90°-150°	2439.3	17.7
90°-180°	3374.0	24.5
0°-180°	13766.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4083	4083	4083	4083	4083	
5°	4083	4068	4024	4056	4048	388
15°	3887	3864	3812	3828	3809	1095
25°	3518	3487	3420	3428	3420	1619
35°	3035	2996	2933	2909	2890	1895
45°	2470	2442	2383	2340	2324	1906
55°	1869	1845	1798	1751	1732	1671
65°	1260	1237	1198	1162	1143	1246
75°	659	652	632	609	617	704
85°	161	157	153	141	138	179
90°	1	13	36	34	34	13
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	



TEST NUMBER: P926618

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4083.3	4083.3	4083.3	4083.3	4083.3
2.5°	4107.0	4087.4	4044.1	4083.3	4075.8
5°	4083.3	4067.9	4024.5	4055.7	4048.3
7.5°	4055.7	4032.5	3989.2	4020.8	4012.9
10°	4012.9	3985.3	3938.3	3969.5	3957.9
12.5°	3953.8	3930.4	3883.4	3902.9	3895.0
15°	3887.1	3863.7	3812.5	3828.3	3808.7
17.5°	3804.6	3781.3	3730.0	3749.6	3730.0
20°	3714.2	3690.8	3635.9	3647.5	3632.2
22.5°	3624.2	3588.8	3537.5	3537.5	3529.6
25°	3518.0	3486.8	3420.1	3427.6	3420.1
27.5°	3400.1	3372.6	3321.7	3310.1	3290.5
30°	3282.6	3250.9	3192.2	3180.5	3164.7
32.5°	3156.8	3133.5	3070.5	3046.8	3031.0
35°	3035.2	2996.0	2933.1	2909.3	2889.8
37.5°	2897.7	2862.3	2799.4	2771.8	2752.3
40°	2756.5	2724.8	2661.9	2626.9	2611.1
42.5°	2619.0	2587.3	2524.9	2485.3	2462.0
45°	2469.9	2442.3	2383.2	2340.4	2324.5
47.5°	2324.5	2297.0	2234.1	2190.8	2167.4
50°	2171.2	2151.7	2096.6	2041.7	2022.1
52.5°	2022.1	1994.5	1943.8	1900.4	1872.9
55°	1869.2	1845.4	1798.4	1751.3	1731.7
57.5°	1715.9	1696.3	1645.1	1597.9	1582.1
60°	1562.6	1547.2	1492.2	1448.8	1437.2
62.5°	1413.4	1386.0	1346.8	1307.6	1291.8
65°	1260.5	1236.8	1197.7	1162.3	1142.7
67.5°	1103.5	1083.6	1048.5	1021.1	1005.2
70°	958.1	942.3	906.9	879.4	863.9
72.5°	809.0	793.2	773.6	746.1	734.4
75°	659.4	652.0	631.9	608.7	616.6
77.5°	526.1	510.3	502.4	490.7	479.1
80°	392.9	388.7	380.7	369.1	361.2
82.5°	267.0	267.0	263.3	247.5	247.5
85°	160.8	157.0	153.3	141.2	137.5
87.5°	70.8	62.9	55.0	43.3	39.1
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7



TEST NUMBER: P926618

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8



TEST NUMBER: P926618
 CATALOG NUMBER: DFN2DIP-TR4F0-110D040US950-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.44	14.59	14.14	15.31	16.16	13.01	14.15	13.71	14.88	15.73
	3H	15.12	16.15	15.83	16.88	17.77	14.65	15.68	15.36	16.41	17.30
	4H	15.72	16.69	16.45	17.44	18.33	15.25	16.22	15.98	16.96	17.86
	6H	16.13	17.03	16.88	17.78	18.70	15.66	16.56	16.41	17.31	18.22
	8H	16.25	17.10	17.00	17.87	18.79	15.77	16.63	16.53	17.40	18.31
	12H	16.30	17.12	17.07	17.89	18.83	15.82	16.64	16.59	17.41	18.35
4H	2H	13.93	14.91	14.67	15.65	16.55	13.59	14.56	14.33	15.30	16.20
	3H	15.82	16.64	16.57	17.42	18.33	15.43	16.25	16.18	17.02	17.94
	4H	16.55	17.29	17.32	18.07	19.01	16.14	16.88	16.91	17.66	18.61
	6H	17.08	17.72	17.87	18.53	19.48	16.67	17.31	17.46	18.12	19.07
	8H	17.24	17.84	18.03	18.64	19.60	16.83	17.43	17.61	18.23	19.19
	12H	17.32	17.86	18.13	18.69	19.66	16.90	17.44	17.71	18.26	19.23
8H	4H	16.77	17.37	17.56	18.17	19.13	16.41	17.01	17.20	17.81	18.77
	6H	17.41	17.91	18.23	18.75	19.72	17.05	17.55	17.87	18.39	19.35
	8H	17.64	18.08	18.47	18.92	19.90	17.27	17.71	18.10	18.55	19.53
	12H	17.78	18.17	18.61	19.00	20.04	17.40	17.79	18.23	18.62	19.66
12H	4H	16.77	17.31	17.58	18.13	19.10	16.42	16.96	17.23	17.78	18.75
	6H	17.44	17.89	18.27	18.73	19.71	17.09	17.54	17.92	18.38	19.36
	8H	17.70	18.09	18.53	18.92	19.96	17.34	17.73	18.18	18.56	19.60