

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926671

Luminaire Tested: DFN2DIP-TR4F0-120D080US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926671
REPORT IS A COMBINATION OF REPORTS P901977 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D080US950-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18889.2 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 184.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926671

CATALOG NUMBER: DFN2DIP-TR4F0-120D080US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926671

CATALOG NUMBER: DFN2DIP-TR4F0-120D080US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65
1	100	96	92	88	93	90	86	83	78	75	73		67	66	64		58
2	91	84	77	72	85	78	73	68	68	64	61		59	56	53		51
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45
4	76	65	57	51	71	61	54	48	54	48	44		47	42	39		40
5	70	58	50	44	65	55	47	42	48	42	38		42	37	34		36
6	64	52	44	38	60	49	42	36	43	37	33		38	33	30		33
7	60	47	39	33	56	44	37	32	39	33	29		35	30	26		30
8	55	43	35	30	52	40	33	28	36	30	26		32	27	23		28
9	52	39	32	26	48	37	30	25	33	27	23		29	24	21		26
10	48	36	29	24	45	34	27	23	30	25	21		27	22	19		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3539	3539	3539
5°	3544	3489	3513
10°	3516	3442	3465
15°	3464	3386	3391
20°	3394	3307	3315
25°	3325	3213	3227
30°	3238	3125	3115
35°	3155	3022	2996
40°	3054	2917	2883
45°	2953	2813	2768
50°	2842	2703	2635
55°	2726	2576	2512
60°	2595	2425	2371
65°	2452	2269	2205
70°	2270	2078	2027
75°	2018	1850	1862
80°	1715	1560	1547
85°	1240	1058	1025

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2953 cd/sqm

TEST NUMBER: P926671

CATALOG NUMBER: DFN2DIP-TR4F0-120D080US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	419.3	2.2
10°-20°	1179.6	6.2
20°-30°	1733.6	9.2
30°-40°	2013.5	10.7
40°-50°	2011.0	10.6
50°-60°	1753.5	9.3
60°-70°	1296.2	6.9
70°-80°	733.4	3.9
80°-90°	198.1	1.0
90°-100°	84.9	0.4
100°-110°	316.6	1.7
110°-120°	839.7	4.4
120°-130°	1392.7	7.4
130°-140°	1479.4	7.8
140°-150°	1374.9	7.3
150°-160°	1105.4	5.9
160°-170°	712.3	3.8
170°-180°	245.2	1.3
0°-30°	3332.5	17.6
0°-40°	5345.9	28.3
0°-60°	9110.4	48.2
0°-90°	11338.1	60.0
90°-120°	1241.3	6.6
90°-150°	5488.3	29.1
90°-180°	7551.0	40.0
0°-180°	18889.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4454	4454	4454	4454	4454	
5°	4454	4438	4390	4424	4416	423
15°	4240	4215	4159	4176	4155	1194
25°	3838	3804	3731	3739	3731	1766
35°	3311	3268	3200	3174	3152	2068
45°	2694	2664	2600	2553	2536	2079
55°	2039	2013	1962	1910	1889	1823
65°	1375	1349	1306	1268	1247	1360
75°	719	711	689	664	673	768
85°	175	171	167	154	150	196
90°	2	22	37	47	50	17
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P926671

CATALOG NUMBER: DFN2DIP-TR4F0-120D080US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4454.5	4454.5	4454.5	4454.5	4454.5
2.5°	4480.4	4459.0	4411.8	4454.5	4446.3
5°	4454.5	4437.6	4390.4	4424.5	4416.3
7.5°	4424.5	4399.0	4351.8	4386.3	4377.7
10°	4377.7	4347.7	4296.3	4330.4	4317.7
12.5°	4313.1	4287.7	4236.3	4257.7	4249.0
15°	4240.4	4215.0	4159.1	4176.3	4155.0
17.5°	4150.5	4125.0	4069.1	4090.5	4069.1
20°	4051.8	4026.4	3966.4	3979.1	3962.3
22.5°	3953.7	3915.0	3859.1	3859.1	3850.5
25°	3837.8	3803.7	3731.0	3739.2	3731.0
27.5°	3709.2	3679.2	3623.8	3611.0	3589.7
30°	3581.0	3546.5	3482.4	3469.7	3452.4
32.5°	3443.7	3418.4	3349.7	3323.8	3306.6
35°	3311.0	3268.4	3199.7	3173.9	3152.5
37.5°	3161.1	3122.5	3053.8	3023.9	3002.5
40°	3007.1	2972.6	2903.9	2865.7	2848.5
42.5°	2857.1	2822.6	2754.4	2711.3	2685.8
45°	2694.4	2664.4	2599.8	2553.1	2535.8
47.5°	2535.8	2505.8	2437.2	2390.0	2364.5
50°	2368.6	2347.2	2287.2	2227.2	2205.8
52.5°	2205.8	2175.9	2120.5	2073.1	2043.2
55°	2039.1	2013.2	1961.8	1910.5	1889.1
57.5°	1871.8	1850.5	1794.6	1743.2	1726.0
60°	1704.6	1687.8	1627.8	1580.6	1567.8
62.5°	1542.0	1511.9	1469.3	1426.5	1409.2
65°	1375.2	1349.2	1306.5	1267.9	1246.6
67.5°	1203.9	1182.0	1143.8	1113.9	1096.6
70°	1045.2	1027.9	989.3	959.3	942.6
72.5°	882.5	865.3	843.9	814.0	801.2
75°	719.4	711.2	689.4	664.0	672.6
77.5°	573.9	556.7	548.1	535.3	522.6
80°	428.5	424.0	415.4	402.7	394.0
82.5°	291.3	291.3	287.2	270.0	270.0
85°	175.4	171.3	167.2	154.1	150.0
87.5°	77.3	68.6	60.0	47.2	42.7
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2

TEST NUMBER: P926671

CATALOG NUMBER: DFN2DIP-TR4F0-120D080US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7

TEST NUMBER: P926671

CATALOG NUMBER: DFN2DIP-TR4F0-120D080US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.53	13.49	13.40	14.38	15.50	12.10	13.06	12.97	13.95	15.07
	3H	14.20	15.06	15.08	15.96	17.11	13.73	14.59	14.61	15.49	16.63
	4H	14.79	15.61	15.69	16.51	17.67	14.32	15.13	15.21	16.04	17.19
	6H	15.20	15.95	16.10	16.86	18.03	14.72	15.47	15.63	16.38	17.55
	8H	15.31	16.02	16.22	16.95	18.12	14.83	15.55	15.75	16.47	17.64
	12H	15.36	16.04	16.28	16.96	18.15	14.88	15.56	15.80	16.48	17.67
4H	2H	13.01	13.82	13.91	14.72	15.88	12.66	13.48	13.56	14.38	15.54
	3H	14.88	15.56	15.79	16.50	17.67	14.49	15.17	15.40	16.10	17.27
	4H	15.60	16.22	16.52	17.15	18.35	15.20	15.82	16.12	16.75	17.94
	6H	16.12	16.66	17.06	17.61	18.81	15.71	16.25	16.65	17.20	18.40
	8H	16.27	16.77	17.21	17.72	18.93	15.86	16.36	16.80	17.31	18.52
	12H	16.35	16.80	17.31	17.77	18.98	15.93	16.38	16.89	17.35	18.56
8H	4H	15.81	16.31	16.74	17.25	18.46	15.45	15.95	16.38	16.89	18.10
	6H	16.44	16.85	17.40	17.84	19.05	16.08	16.49	17.04	17.48	18.69
	8H	16.66	17.03	17.64	18.01	19.24	16.29	16.66	17.27	17.64	18.87
	12H	16.80	17.12	17.77	18.09	19.37	16.41	16.74	17.39	17.71	18.99
12H	4H	15.80	16.25	16.75	17.21	18.43	15.44	15.89	16.40	16.86	18.08
	6H	16.47	16.84	17.44	17.82	19.05	16.12	16.49	17.09	17.47	18.69
	8H	16.72	17.04	17.69	18.01	19.29	16.36	16.68	17.34	17.66	18.93