

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332011-927

Luminaire Tested: **S123DIP-S1000D585U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332011-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5039.2 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71			67
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61			57
2	93	86	80	74	87	81	76	71	72	68	64	64	61	58	57	54	52			48
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	45			41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39			36
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34			31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30			27
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27			24
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24			22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22			20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20			18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11976	11976	11976	11976
5°	14282	12028	10659	12028
10°	17876	11967	9627	11967
15°	21926	11870	8963	11870
20°	26120	11720	8534	11720
25°	27736	11537	8438	11537
30°	23772	11404	8483	11404
35°	16533	11213	8571	11213
40°	12452	10991	8545	10991
45°	10339	10660	8435	10660
50°	9262	9984	8359	9984
55°	8659	9256	8255	9256
60°	8122	8495	8170	8495
65°	7636	7743	7908	7743
70°	7160	6889	7531	6889
75°	6413	6030	6904	6030
80°	5610	4947	5945	4947
85°	4397	3594	3989	3594

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	2.2
10°-20°	351.5	7.0
20°-30°	589.8	11.7
30°-40°	667.9	13.3
40°-50°	598.9	11.9
50°-60°	483.3	9.6
60°-70°	336.8	6.7
70°-80°	177.0	3.5
80°-90°	45.0	0.9
90°-100°	124.2	2.5
100°-110°	351.7	7.0
110°-120°	346.0	6.9
120°-130°	276.0	5.5
130°-140°	217.6	4.3
140°-150°	162.4	3.2
150°-160°	113.2	2.2
160°-170°	66.5	1.3
170°-180°	21.6	0.4
0°-30°	1050.9	20.9
0°-40°	1718.8	34.1
0°-60°	2801.1	55.6
0°-90°	3359.9	66.7
90°-120°	822.0	16.3
90°-150°	1478.0	29.3
90°-180°	1679.0	33.3
0°-180°	5039.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1113	1113	1113	1113	1113	
5°	1322	1113	986	1113	1322	137
15°	1968	1065	804	1065	1968	568
25°	2335	971	710	971	2335	1024
35°	1258	853	652	853	1258	817
45°	679	700	554	700	679	537
55°	461	493	440	493	461	414
65°	300	304	310	304	300	298
75°	154	145	166	145	154	165
85°	36	29	32	29	36	42
90°	13	1	13	1	13	9
95°	52	15	52	15	52	94
105°	575	52	575	52	575	567
115°	699	93	699	93	699	679
125°	551	129	551	129	551	500
135°	447	151	447	151	447	347
145°	349	172	349	172	349	222
155°	290	196	290	196	290	135
165°	252	214	252	214	252	72
175°	227	223	227	223	227	22
180°	223	223	223	223	223	

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1180.7	1180.0	1177.7	1179.5	1176.1	1171.3	1170.8	1166.6	1154.1	1153.2	1149.8
5°	1321.8	1317.5	1316.9	1316.4	1308.8	1298.6	1279.2	1277.6	1251.7	1238.8	1223.1
7.5°	1504.4	1506.7	1498.8	1491.9	1468.9	1453.7	1432.8	1406.2	1374.4	1342.2	1320.7
10°	1635.5	1653.4	1631.3	1616.1	1602.1	1575.7	1545.0	1506.7	1468.5	1423.7	1389.7
12.5°	1776.2	1784.9	1780.4	1766.2	1744.5	1704.2	1649.8	1607.7	1572.4	1497.9	1467.8
15°	1967.6	2000.5	1979.5	1930.9	1932.1	1893.8	1822.6	1744.5	1703.0	1637.7	1548.8
17.5°	2171.6	2175.7	2166.8	2126.3	2099.4	2046.8	1981.1	1906.1	1822.1	1743.1	1648.8
20°	2280.3	2277.0	2258.2	2237.1	2190.8	2149.8	2078.1	1994.6	1886.7	1809.1	1706.2
22.5°	2340.7	2335.3	2326.3	2308.7	2270.2	2226.2	2161.8	2070.4	1967.9	1860.9	1741.9
25°	2335.3	2342.2	2343.4	2338.5	2325.1	2298.6	2247.9	2175.2	2072.7	1935.3	1811.3
27.5°	2123.9	2133.9	2162.7	2188.2	2216.8	2245.9	2242.0	2205.9	2130.1	2011.4	1859.8
30°	1912.6	1891.1	1944.4	2011.8	2057.6	2138.5	2183.8	2186.5	2143.9	2042.0	1894.3
32.5°	1619.4	1643.1	1666.7	1749.6	1849.7	1940.5	2030.7	2103.2	2111.6	2043.8	1914.5
35°	1258.2	1287.9	1330.9	1374.1	1481.9	1574.6	1733.1	1871.1	1981.1	1995.7	1916.4
37.5°	1013.9	1028.6	1055.8	1099.1	1169.6	1279.5	1402.2	1576.6	1735.9	1854.4	1859.6
40°	886.2	890.6	921.3	954.2	1011.3	1101.8	1212.4	1366.5	1557.4	1722.9	1791.9
42.5°	790.5	799.9	813.0	844.6	890.1	958.2	1061.0	1188.4	1363.3	1553.8	1688.8
45°	679.2	690.0	698.1	719.1	751.5	797.3	869.0	985.4	1118.6	1315.3	1497.0
47.5°	605.7	606.6	612.6	628.4	650.5	684.8	735.5	810.3	932.6	1092.2	1278.7
50°	553.1	561.7	563.9	576.2	593.5	618.9	660.9	724.5	824.8	965.0	1136.4
52.5°	516.0	518.6	524.7	533.6	548.7	568.4	604.8	654.7	733.3	852.8	1010.4
55°	461.4	461.4	467.4	474.4	483.0	500.8	525.1	561.7	621.5	714.3	844.7
57.5°	411.0	413.7	417.9	420.0	427.4	439.1	459.4	487.2	531.9	603.2	706.9
60°	377.3	382.2	381.7	386.0	392.4	401.6	418.8	441.5	481.4	538.5	625.9
62.5°	348.0	347.7	347.6	352.8	359.3	368.0	379.2	398.8	432.7	483.3	557.7
65°	299.8	298.7	302.5	305.6	307.8	314.3	322.9	340.2	362.8	400.5	458.2
67.5°	256.8	253.7	255.7	256.8	260.5	265.5	273.6	284.3	302.3	332.6	376.0
70°	227.5	224.8	224.3	225.3	228.5	232.3	238.3	248.5	265.2	289.5	321.3
72.5°	197.3	195.4	195.4	197.7	199.2	201.7	205.9	215.3	228.5	246.8	276.5
75°	154.2	154.2	154.2	154.7	156.3	158.5	161.7	166.6	176.8	189.7	209.7
77.5°	115.6	115.5	114.8	114.7	117.1	118.0	118.8	123.3	129.0	137.8	152.3
80°	90.5	87.9	89.0	90.5	91.7	92.2	93.8	94.9	99.7	104.6	114.8
82.5°	67.3	65.0	65.2	67.7	67.9	68.4	70.1	71.6	73.4	77.9	83.3
85°	35.6	35.6	36.1	36.1	36.7	36.1	37.7	38.3	38.3	41.0	44.2
87.5°	15.5	14.8	15.1	15.4	15.1	15.4	15.7	16.1	16.4	17.0	17.1
90°	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3	10.9	11.3	9.9
92.5°	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0	52.4	69.5	76.4
95°	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6	217.3	267.9	238.6
97.5°	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5	444.3	415.3	304.0
100°	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7	516.9	427.9	289.1
102.5°	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0	520.5	404.4	267.5
105°	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4	493.0	363.3	240.8
107.5°	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8	444.7	326.9	223.9
110°	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8	414.3	306.3	217.3

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2	387.9	292.6	213.7
115°	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7	356.1	277.9	212.4
117.5°	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3	336.8	269.2	213.2
120°	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4	326.7	265.2	214.6
122.5°	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0	318.4	262.7	217.1
125°	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2	307.7	259.4	220.9
127.5°	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6	298.3	257.7	225.3
130°	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9	293.3	256.7	228.1
132.5°	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9	288.5	256.3	230.4
135°	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7	282.4	255.7	233.6
137.5°	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6	277.1	254.8	235.8
140°	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1	273.8	254.4	237.2
142.5°	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9	270.9	253.7	238.3
145°	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5	267.0	252.5	239.0
147.5°	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4	263.2	250.9	239.0
150°	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1	260.7	249.4	239.0
152.5°	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1	257.9	247.6	238.0
155°	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2	253.5	244.5	236.8
157.5°	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8	248.6	241.6	235.2
160°	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2	245.3	239.5	234.5
162.5°	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9	242.1	237.3	233.1
165°	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3	237.7	234.1	230.9
167.5°	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4	233.5	230.8	228.7
170°	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1	230.9	228.6	227.3
172.5°	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3	228.4	226.8	226.2
175°	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4	225.5	224.6	224.6
177.5°	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1147.2	1143.7	1140.3	1134.2	1129.0	1121.7	1119.5	1117.0	1109.2	1102.3	1097.1
5°	1217.2	1204.3	1185.4	1168.2	1154.1	1135.3	1124.5	1113.2	1097.0	1082.4	1070.6
7.5°	1290.5	1265.1	1235.8	1204.0	1174.6	1146.1	1123.1	1102.6	1080.0	1058.5	1041.8
10°	1348.8	1312.1	1271.1	1226.9	1189.2	1152.5	1121.8	1094.9	1065.7	1040.4	1019.4
12.5°	1415.2	1360.8	1304.3	1250.6	1206.0	1155.2	1117.9	1083.6	1050.7	1020.2	996.6
15°	1493.7	1424.7	1358.0	1284.0	1216.2	1152.5	1108.3	1065.2	1026.9	995.7	965.5
17.5°	1565.4	1487.2	1399.1	1309.3	1227.3	1151.9	1090.0	1041.2	993.4	955.1	925.0
20°	1605.9	1516.9	1417.2	1324.0	1233.4	1149.3	1081.4	1023.2	971.4	931.0	897.0
22.5°	1640.8	1536.8	1433.6	1333.9	1233.0	1142.4	1065.4	1005.5	949.4	909.8	873.7
25°	1677.0	1552.5	1449.1	1332.1	1219.4	1125.6	1039.3	971.4	915.4	869.0	831.8
27.5°	1708.1	1551.5	1428.6	1302.8	1198.0	1104.0	1011.9	939.1	879.6	829.2	791.5
30°	1728.8	1553.6	1407.5	1283.0	1177.3	1080.3	990.8	917.5	855.0	803.7	768.2
32.5°	1741.8	1552.3	1388.1	1255.4	1144.5	1058.8	968.0	892.1	827.8	777.4	743.1
35°	1749.3	1542.9	1354.7	1198.3	1091.6	1008.1	932.1	853.3	786.0	739.1	700.3
37.5°	1734.2	1522.9	1315.9	1143.4	1026.5	944.2	880.3	813.3	748.8	697.1	663.7
40°	1710.5	1510.0	1285.7	1104.5	981.7	902.4	848.0	782.2	718.6	669.6	638.3
42.5°	1665.2	1483.6	1252.5	1061.4	935.1	855.8	805.7	750.8	690.5	644.5	613.2
45°	1554.7	1426.4	1202.7	996.7	866.3	784.3	740.1	700.3	645.8	601.0	574.1
47.5°	1401.4	1340.2	1130.7	928.5	794.5	715.7	669.7	637.6	597.9	561.7	535.8
50°	1294.8	1269.6	1081.9	881.9	746.6	669.6	625.3	596.2	567.7	531.6	507.8
52.5°	1172.0	1187.6	1025.0	833.6	697.9	622.1	580.5	557.4	531.4	501.8	481.1
55°	998.9	1055.5	926.7	752.6	625.3	553.1	513.7	493.2	478.2	456.1	438.2
57.5°	836.9	908.9	820.4	669.0	554.1	491.7	454.0	431.7	422.0	410.4	396.4
60°	740.7	811.8	744.5	612.9	506.2	446.9	413.4	394.6	384.9	376.8	365.0
62.5°	654.9	726.9	670.3	556.0	459.1	404.2	375.1	356.6	349.1	344.9	334.8
65°	536.9	598.9	561.2	467.4	391.9	343.4	317.0	304.0	297.1	295.4	288.9
67.5°	437.0	484.2	456.7	387.7	328.3	286.4	264.0	252.9	247.6	247.0	242.2
70°	371.5	415.7	394.6	332.1	280.8	248.0	228.5	218.9	215.6	215.1	212.4
72.5°	320.5	351.3	334.6	282.5	242.9	213.0	198.8	188.7	185.0	185.8	183.9
75°	237.2	260.4	250.6	214.5	182.8	163.3	151.5	145.0	141.8	143.4	141.2
77.5°	170.6	185.4	176.6	151.6	132.0	118.0	109.2	105.2	102.3	102.2	101.2
80°	128.8	137.4	132.6	117.5	101.3	89.5	82.5	79.8	78.2	77.6	77.1
82.5°	91.7	99.1	93.4	83.0	72.0	64.9	60.9	57.4	56.2	56.5	55.9
85°	46.3	49.0	46.9	40.4	36.1	32.9	30.7	29.1	28.0	28.6	27.5
87.5°	17.7	17.8	16.2	14.3	13.3	11.7	11.6	10.5	9.8	10.1	9.9
90°	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9	1.8	2.7	4.0
92.5°	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6	8.3	12.1	15.6
95°	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4	16.7	21.7	29.4
97.5°	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2	26.7	30.6	37.2
100°	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4	33.9	37.1	43.4
102.5°	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0	41.8	44.7	50.6
105°	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4	53.8	56.5	61.9
107.5°	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5	65.9	68.5	73.8
110°	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2	74.5	76.8	81.8

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1	82.5	84.8	89.8
115°	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6	94.4	97.1	101.6
117.5°	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1	106.2	108.4	112.6
120°	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1	113.4	115.7	120.2
122.5°	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9	120.3	122.6	127.4
125°	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8	129.7	132.4	137.4
127.5°	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3	137.6	141.0	146.0
130°	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0	142.4	146.4	151.8
132.5°	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6	146.3	150.8	157.2
135°	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9	152.7	157.7	164.5
137.5°	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9	158.8	163.7	170.9
140°	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9	163.1	167.6	174.8
142.5°	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2	167.1	172.0	178.5
145°	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1	173.5	177.6	184.3
147.5°	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2	180.0	184.0	189.9
150°	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9	184.3	188.0	193.8
152.5°	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6	188.7	192.3	197.5
155°	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7	195.7	198.4	202.9
157.5°	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2	201.6	203.7	207.8
160°	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6	205.6	207.4	211.0
162.5°	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8	208.8	210.3	213.2
165°	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7	213.3	214.2	216.4
167.5°	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5	216.9	217.3	219.0
170°	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6	218.7	219.1	220.5
172.5°	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0	220.5	220.6	221.6
175°	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8	222.3	221.9	222.8
177.5°	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6	223.2	222.8	223.2
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1094.1	1091.1	1086.8	1080.3	1075.1	1066.9	1066.9	1068.3	1068.3	1067.8	1066.9
5°	1060.9	1052.8	1043.1	1031.8	1019.9	1008.1	1005.9	1001.6	998.4	996.2	993.5
7.5°	1025.9	1011.5	997.4	981.5	967.1	955.1	946.8	939.9	935.5	930.7	927.3
10°	1002.1	984.4	967.7	950.9	932.6	918.1	908.9	902.4	897.5	893.3	891.1
12.5°	974.1	953.7	935.3	919.4	899.4	884.4	875.7	872.7	867.0	857.9	853.1
15°	933.1	914.3	892.2	867.9	858.2	839.9	829.7	824.8	821.6	814.5	812.4
17.5°	898.1	873.4	848.6	830.5	812.5	797.6	791.9	785.8	781.6	775.9	774.1
20°	870.1	848.0	825.3	805.9	787.0	770.9	766.0	761.7	757.4	754.7	752.6
22.5°	841.6	819.5	800.7	782.6	762.5	751.9	746.6	741.9	738.9	737.0	734.8
25°	801.6	782.2	761.2	745.0	728.8	721.8	718.6	715.9	713.8	711.1	710.5
27.5°	765.8	744.7	727.6	712.6	700.9	695.1	692.0	690.6	691.1	692.1	692.7
30°	739.1	719.7	705.7	692.7	681.9	676.5	676.0	676.0	678.2	678.7	679.8
32.5°	714.5	698.5	684.5	672.0	663.8	660.1	662.2	662.2	663.9	665.4	667.3
35°	678.7	664.6	653.9	643.1	636.1	637.7	638.8	639.8	642.5	645.8	648.0
37.5°	644.5	632.3	621.2	612.7	609.5	612.4	615.0	617.3	620.4	622.8	625.0
40°	620.0	610.8	600.0	592.5	593.5	595.2	597.3	600.0	602.7	604.3	606.5
42.5°	597.1	587.5	579.3	573.1	574.6	576.6	577.9	579.3	582.4	585.3	586.6
45°	562.3	554.7	547.2	543.4	544.5	545.6	546.6	548.3	551.0	553.1	553.7
47.5°	523.1	517.8	512.8	509.1	510.8	510.4	511.8	515.2	516.1	517.4	520.4
50°	498.1	493.2	487.4	486.2	486.2	486.2	486.8	491.1	491.1	493.2	495.4
52.5°	470.5	467.4	463.6	461.7	460.8	460.8	463.0	465.2	466.1	469.1	471.3
55°	429.7	426.4	423.2	421.5	420.5	421.5	425.9	426.9	429.7	431.3	432.8
57.5°	387.1	384.6	382.0	381.1	380.9	382.3	384.7	387.9	388.6	393.6	396.0
60°	359.0	355.2	353.1	353.1	352.0	356.9	355.8	361.2	362.3	365.5	369.2
62.5°	330.1	325.0	324.2	324.2	325.7	327.1	328.6	331.0	333.8	337.9	340.8
65°	283.5	280.8	284.6	284.1	283.0	286.2	286.2	288.9	292.2	296.0	301.9
67.5°	239.5	238.1	238.4	238.4	240.0	241.9	243.4	245.7	249.6	253.6	257.5
70°	209.7	211.4	208.7	210.8	212.4	212.9	214.0	217.2	221.6	224.3	228.5
72.5°	180.8	180.7	181.0	181.9	183.5	184.5	185.5	189.3	193.9	196.2	199.7
75°	139.1	138.6	140.1	140.1	142.8	143.9	145.0	146.6	150.9	154.2	156.9
77.5°	101.6	102.2	101.9	103.7	103.0	103.1	106.5	108.1	108.6	114.9	116.4
80°	76.5	77.6	78.2	78.7	79.2	78.2	81.9	83.6	83.6	87.3	90.0
82.5°	55.0	55.6	57.0	57.6	57.7	58.8	59.1	60.3	61.6	63.2	66.7
85°	27.5	29.1	29.6	29.1	29.6	28.6	30.2	30.7	31.3	31.3	31.3
87.5°	9.6	10.2	10.1	10.8	10.6	11.3	11.2	10.5	10.5	12.0	10.4
90°	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3	11.7	12.2	13.1
92.5°	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0	30.2	26.7	24.3
95°	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6	110.3	86.3	70.0
97.5°	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5	324.8	266.5	212.5
100°	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7	496.1	443.2	379.1
102.5°	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0	573.9	543.0	502.3
105°	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4	632.6	641.2	629.4
107.5°	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8	625.2	664.7	680.8
110°	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8	600.9	657.9	689.5

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2	569.1	633.0	673.6
115°	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7	518.2	584.7	633.9
117.5°	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3	475.2	534.9	584.9
120°	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4	451.4	505.6	551.3
122.5°	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0	432.2	482.4	524.8
125°	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2	408.4	451.9	488.0
127.5°	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6	387.6	426.7	459.6
130°	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9	374.5	411.1	441.9
132.5°	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9	362.3	396.3	425.6
135°	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7	344.8	374.1	399.9
137.5°	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6	327.9	353.2	375.5
140°	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1	318.1	339.8	359.2
142.5°	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9	308.7	327.5	344.4
145°	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5	296.4	310.9	324.0
147.5°	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4	287.2	299.0	308.2
150°	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1	281.5	291.0	299.6
152.5°	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1	276.1	284.5	291.6
155°	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2	268.4	275.2	280.6
157.5°	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8	260.9	266.2	270.4
160°	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2	256.2	260.7	263.9
162.5°	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9	251.1	255.3	258.1
165°	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3	244.0	247.2	249.4
167.5°	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4	238.4	240.3	241.9
170°	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1	234.5	236.3	237.2
172.5°	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3	231.2	232.7	233.2
175°	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4	226.8	227.8	227.8
177.5°	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9	224.3	224.7	224.7
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1063.9	1063.5	1066.5	1064.4	1066.5	1063.5	1063.9	1066.9	1067.8	1068.3	1068.3
5°	990.3	991.9	986.5	986.5	986.5	991.9	990.3	993.5	996.2	998.4	1001.6
7.5°	924.7	922.3	922.6	919.6	922.6	922.3	924.7	927.3	930.7	935.5	939.9
10°	884.6	881.4	880.3	880.8	880.3	881.4	884.6	891.1	893.3	897.5	902.4
12.5°	851.4	850.8	843.7	843.8	843.7	850.8	851.4	853.1	857.9	867.0	872.7
15°	812.4	802.2	801.1	804.3	801.1	802.2	812.4	812.4	814.5	821.6	824.8
17.5°	773.2	767.9	768.2	766.6	768.2	767.9	773.2	774.1	775.9	781.6	785.8
20°	752.6	749.3	748.8	745.0	748.8	749.3	752.6	752.6	754.7	757.4	761.7
22.5°	733.6	732.5	732.8	728.6	732.8	732.5	733.6	734.8	737.0	738.9	741.9
25°	710.0	712.6	710.5	710.5	710.5	712.6	710.0	710.5	711.1	713.8	715.9
27.5°	694.0	693.9	692.8	692.8	692.8	693.9	694.0	692.7	692.1	691.1	690.6
30°	681.9	681.4	682.5	682.5	682.5	681.4	681.9	679.8	678.7	678.2	676.0
32.5°	669.9	670.6	670.8	671.2	670.8	670.6	669.9	667.3	665.4	663.9	662.2
35°	651.2	651.7	653.4	652.3	653.4	651.7	651.2	648.0	645.8	642.5	639.8
37.5°	626.0	628.4	627.9	628.8	627.9	628.4	626.0	625.0	622.8	620.4	617.3
40°	607.0	608.6	608.1	608.1	608.1	608.6	607.0	606.5	604.3	602.7	600.0
42.5°	587.6	588.7	587.4	586.5	587.4	588.7	587.6	586.6	585.3	582.4	579.3
45°	555.8	554.7	556.3	554.1	556.3	554.7	555.8	553.7	553.1	551.0	548.3
47.5°	520.2	521.3	521.7	523.3	521.7	521.3	520.2	520.4	517.4	516.1	515.2
50°	496.5	499.7	499.7	499.2	499.7	499.7	496.5	495.4	493.2	491.1	491.1
52.5°	473.2	474.7	476.9	476.7	476.9	474.7	473.2	471.3	469.1	466.1	465.2
55°	437.2	438.2	439.3	439.9	439.3	438.2	437.2	432.8	431.3	429.7	426.9
57.5°	399.9	399.4	402.0	402.8	402.0	399.4	399.9	396.0	393.6	388.6	387.9
60°	373.6	373.6	377.9	379.5	377.9	373.6	373.6	369.2	365.5	362.3	361.2
62.5°	345.5	347.3	351.6	349.4	351.6	347.3	345.5	340.8	337.9	333.8	331.0
65°	304.6	308.9	308.3	310.5	308.3	308.9	304.6	301.9	296.0	292.2	288.9
67.5°	261.7	264.4	268.3	268.7	268.3	264.4	261.7	257.5	253.6	249.6	245.7
70°	232.9	235.6	237.7	239.3	237.7	235.6	232.9	228.5	224.3	221.6	217.2
72.5°	204.9	206.3	211.4	209.1	211.4	206.3	204.9	199.7	196.2	193.9	189.3
75°	160.7	164.4	167.6	166.0	167.6	164.4	160.7	156.9	154.2	150.9	146.6
77.5°	118.8	122.6	124.1	122.7	124.1	122.6	118.8	116.4	114.9	108.6	108.1
80°	93.8	93.2	96.5	95.9	96.5	93.2	93.8	90.0	87.3	83.6	83.6
82.5°	68.8	68.3	69.8	70.1	69.8	68.3	68.8	66.7	63.2	61.6	60.3
85°	33.4	35.0	32.9	32.3	32.9	35.0	33.4	31.3	31.3	31.3	30.7
87.5°	10.3	10.4	10.1	9.5	10.1	10.4	10.3	10.4	12.0	10.5	10.5
90°	12.7	13.1	13.5	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3
92.5°	23.5	22.1	22.6	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0
95°	61.5	57.4	54.2	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6
97.5°	179.1	158.8	146.6	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5
100°	333.4	300.5	282.9	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7
102.5°	466.8	440.7	426.0	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0
105°	608.6	591.4	577.0	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4
107.5°	681.2	675.4	670.5	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8
110°	702.2	705.8	704.9	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	696.7	708.0	711.4	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2
115°	667.8	687.7	696.7	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7
117.5°	620.2	642.9	656.0	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3
120°	586.9	612.3	623.1	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4
122.5°	556.6	579.3	591.3	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0
125°	516.9	536.8	548.1	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2
127.5°	485.4	502.3	512.5	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6
130°	465.9	482.1	491.6	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9
132.5°	448.1	464.4	472.8	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9
135°	422.0	435.5	443.7	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7
137.5°	394.1	407.8	414.7	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6
140°	376.4	389.0	396.2	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1
142.5°	359.0	370.3	376.8	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9
145°	335.3	344.8	348.4	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5
147.5°	316.8	323.2	326.7	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4
150°	306.3	311.3	314.0	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1
152.5°	296.9	301.6	303.2	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1
155°	284.6	288.3	289.1	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2
157.5°	273.9	276.6	277.3	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8
160°	267.0	269.7	269.7	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2
162.5°	260.2	262.5	262.5	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9
165°	251.2	253.0	252.5	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3
167.5°	242.7	244.0	243.5	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4
170°	237.7	238.6	238.1	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1
172.5°	233.3	234.2	233.5	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3
175°	227.8	228.1	227.8	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4
177.5°	224.3	224.7	223.9	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1066.9	1066.9	1075.1	1080.3	1086.8	1091.1	1094.1	1097.1	1102.3	1109.2	1117.0
5°	1005.9	1008.1	1019.9	1031.8	1043.1	1052.8	1060.9	1070.6	1082.4	1097.0	1113.2
7.5°	946.8	955.1	967.1	981.5	997.4	1011.5	1025.9	1041.8	1058.5	1080.0	1102.6
10°	908.9	918.1	932.6	950.9	967.7	984.4	1002.1	1019.4	1040.4	1065.7	1094.9
12.5°	875.7	884.4	899.4	919.4	935.3	953.7	974.1	996.6	1020.2	1050.7	1083.6
15°	829.7	839.9	858.2	867.9	892.2	914.3	933.1	965.5	995.7	1026.9	1065.2
17.5°	791.9	797.6	812.5	830.5	848.6	873.4	898.1	925.0	955.1	993.4	1041.2
20°	766.0	770.9	787.0	805.9	825.3	848.0	870.1	897.0	931.0	971.4	1023.2
22.5°	746.6	751.9	762.5	782.6	800.7	819.5	841.6	873.7	909.8	949.4	1005.5
25°	718.6	721.8	728.8	745.0	761.2	782.2	801.6	831.8	869.0	915.4	971.4
27.5°	692.0	695.1	700.9	712.6	727.6	744.7	765.8	791.5	829.2	879.6	939.1
30°	676.0	676.5	681.9	692.7	705.7	719.7	739.1	768.2	803.7	855.0	917.5
32.5°	662.2	660.1	663.8	672.0	684.5	698.5	714.5	743.1	777.4	827.8	892.1
35°	638.8	637.7	636.1	643.1	653.9	664.6	678.7	700.3	739.1	786.0	853.3
37.5°	615.0	612.4	609.5	612.7	621.2	632.3	644.5	663.7	697.1	748.8	813.3
40°	597.3	595.2	593.5	592.5	600.0	610.8	620.0	638.3	669.6	718.6	782.2
42.5°	577.9	576.6	574.6	573.1	579.3	587.5	597.1	613.2	644.5	690.5	750.8
45°	546.6	545.6	544.5	543.4	547.2	554.7	562.3	574.1	601.0	645.8	700.3
47.5°	511.8	510.4	510.8	509.1	512.8	517.8	523.1	535.8	561.7	597.9	637.6
50°	486.8	486.2	486.2	486.2	487.4	493.2	498.1	507.8	531.6	567.7	596.2
52.5°	463.0	460.8	460.8	461.7	463.6	467.4	470.5	481.1	501.8	531.4	557.4
55°	425.9	421.5	420.5	421.5	423.2	426.4	429.7	438.2	456.1	478.2	493.2
57.5°	384.7	382.3	380.9	381.1	382.0	384.6	387.1	396.4	410.4	422.0	431.7
60°	355.8	356.9	352.0	353.1	353.1	355.2	359.0	365.0	376.8	384.9	394.6
62.5°	328.6	327.1	325.7	324.2	324.2	325.0	330.1	334.8	344.9	349.1	356.6
65°	286.2	286.2	283.0	284.1	284.6	280.8	283.5	288.9	295.4	297.1	304.0
67.5°	243.4	241.9	240.0	238.4	238.4	238.1	239.5	242.2	247.0	247.6	252.9
70°	214.0	212.9	212.4	210.8	208.7	211.4	209.7	212.4	215.1	215.6	218.9
72.5°	185.5	184.5	183.5	181.9	181.0	180.7	180.8	183.9	185.8	185.0	188.7
75°	145.0	143.9	142.8	140.1	140.1	138.6	139.1	141.2	143.4	141.8	145.0
77.5°	106.5	103.1	103.0	103.7	101.9	102.2	101.6	101.2	102.2	102.3	105.2
80°	81.9	78.2	79.2	78.7	78.2	77.6	76.5	77.1	77.6	78.2	79.8
82.5°	59.1	58.8	57.7	57.6	57.0	55.6	55.0	55.9	56.5	56.2	57.4
85°	30.2	28.6	29.6	29.1	29.6	29.1	27.5	27.5	28.6	28.0	29.1
87.5°	11.2	11.3	10.6	10.8	10.1	10.2	9.6	9.9	10.1	9.8	10.5
90°	10.9	11.3	9.9	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9
92.5°	52.4	69.5	76.4	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6
95°	217.3	267.9	238.6	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4
97.5°	444.3	415.3	304.0	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2
100°	516.9	427.9	289.1	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4
102.5°	520.5	404.4	267.5	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0
105°	493.0	363.3	240.8	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4
107.5°	444.7	326.9	223.9	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5
110°	414.3	306.3	217.3	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	387.9	292.6	213.7	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1
115°	356.1	277.9	212.4	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6
117.5°	336.8	269.2	213.2	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1
120°	326.7	265.2	214.6	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1
122.5°	318.4	262.7	217.1	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9
125°	307.7	259.4	220.9	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8
127.5°	298.3	257.7	225.3	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3
130°	293.3	256.7	228.1	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0
132.5°	288.5	256.3	230.4	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6
135°	282.4	255.7	233.6	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9
137.5°	277.1	254.8	235.8	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9
140°	273.8	254.4	237.2	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9
142.5°	270.9	253.7	238.3	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2
145°	267.0	252.5	239.0	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1
147.5°	263.2	250.9	239.0	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2
150°	260.7	249.4	239.0	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9
152.5°	257.9	247.6	238.0	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6
155°	253.5	244.5	236.8	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7
157.5°	248.6	241.6	235.2	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2
160°	245.3	239.5	234.5	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6
162.5°	242.1	237.3	233.1	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8
165°	237.7	234.1	230.9	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7
167.5°	233.5	230.8	228.7	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5
170°	230.9	228.6	227.3	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6
172.5°	228.4	226.8	226.2	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0
175°	225.5	224.6	224.6	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8
177.5°	223.6	223.2	223.6	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1119.5	1121.7	1129.0	1134.2	1140.3	1143.7	1147.2	1149.8	1153.2	1154.1	1166.6
5°	1124.5	1135.3	1154.1	1168.2	1185.4	1204.3	1217.2	1223.1	1238.8	1251.7	1277.6
7.5°	1123.1	1146.1	1174.6	1204.0	1235.8	1265.1	1290.5	1320.7	1342.2	1374.4	1406.2
10°	1121.8	1152.5	1189.2	1226.9	1271.1	1312.1	1348.8	1389.7	1423.7	1468.5	1506.7
12.5°	1117.9	1155.2	1206.0	1250.6	1304.3	1360.8	1415.2	1467.8	1497.9	1572.4	1607.7
15°	1108.3	1152.5	1216.2	1284.0	1358.0	1424.7	1493.7	1548.8	1637.7	1703.0	1744.5
17.5°	1090.0	1151.9	1227.3	1309.3	1399.1	1487.2	1565.4	1648.8	1743.1	1822.1	1906.1
20°	1081.4	1149.3	1233.4	1324.0	1417.2	1516.9	1605.9	1706.2	1809.1	1886.7	1994.6
22.5°	1065.4	1142.4	1233.0	1333.9	1433.6	1536.8	1640.8	1741.9	1860.9	1967.9	2070.4
25°	1039.3	1125.6	1219.4	1332.1	1449.1	1552.5	1677.0	1811.3	1935.3	2072.7	2175.2
27.5°	1011.9	1104.0	1198.0	1302.8	1428.6	1551.5	1708.1	1859.8	2011.4	2130.1	2205.9
30°	990.8	1080.3	1177.3	1283.0	1407.5	1553.6	1728.8	1894.3	2042.0	2143.9	2186.5
32.5°	968.0	1058.8	1144.5	1255.4	1388.1	1552.3	1741.8	1914.5	2043.8	2111.6	2103.2
35°	932.1	1008.1	1091.6	1198.3	1354.7	1542.9	1749.3	1916.4	1995.7	1981.1	1871.1
37.5°	880.3	944.2	1026.5	1143.4	1315.9	1522.9	1734.2	1859.6	1854.4	1735.9	1576.6
40°	848.0	902.4	981.7	1104.5	1285.7	1510.0	1710.5	1791.9	1722.9	1557.4	1366.5
42.5°	805.7	855.8	935.1	1061.4	1252.5	1483.6	1665.2	1688.8	1553.8	1363.3	1188.4
45°	740.1	784.3	866.3	996.7	1202.7	1426.4	1554.7	1497.0	1315.3	1118.6	985.4
47.5°	669.7	715.7	794.5	928.5	1130.7	1340.2	1401.4	1278.7	1092.2	932.6	810.3
50°	625.3	669.6	746.6	881.9	1081.9	1269.6	1294.8	1136.4	965.0	824.8	724.5
52.5°	580.5	622.1	697.9	833.6	1025.0	1187.6	1172.0	1010.4	852.8	733.3	654.7
55°	513.7	553.1	625.3	752.6	926.7	1055.5	998.9	844.7	714.3	621.5	561.7
57.5°	454.0	491.7	554.1	669.0	820.4	908.9	836.9	706.9	603.2	531.9	487.2
60°	413.4	446.9	506.2	612.9	744.5	811.8	740.7	625.9	538.5	481.4	441.5
62.5°	375.1	404.2	459.1	556.0	670.3	726.9	654.9	557.7	483.3	432.7	398.8
65°	317.0	343.4	391.9	467.4	561.2	598.9	536.9	458.2	400.5	362.8	340.2
67.5°	264.0	286.4	328.3	387.7	456.7	484.2	437.0	376.0	332.6	302.3	284.3
70°	228.5	248.0	280.8	332.1	394.6	415.7	371.5	321.3	289.5	265.2	248.5
72.5°	198.8	213.0	242.9	282.5	334.6	351.3	320.5	276.5	246.8	228.5	215.3
75°	151.5	163.3	182.8	214.5	250.6	260.4	237.2	209.7	189.7	176.8	166.6
77.5°	109.2	118.0	132.0	151.6	176.6	185.4	170.6	152.3	137.8	129.0	123.3
80°	82.5	89.5	101.3	117.5	132.6	137.4	128.8	114.8	104.6	99.7	94.9
82.5°	60.9	64.9	72.0	83.0	93.4	99.1	91.7	83.3	77.9	73.4	71.6
85°	30.7	32.9	36.1	40.4	46.9	49.0	46.3	44.2	41.0	38.3	38.3
87.5°	11.6	11.7	13.3	14.3	16.2	17.8	17.7	17.1	17.0	16.4	16.1
90°	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3
92.5°	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0
95°	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6
97.5°	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5
100°	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7
102.5°	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0
105°	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4
107.5°	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8
110°	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2
115°	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7
117.5°	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3
120°	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4
122.5°	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0
125°	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2
127.5°	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6
130°	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9
132.5°	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9
135°	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7
137.5°	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6
140°	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1
142.5°	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9
145°	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5
147.5°	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4
150°	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1
152.5°	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1
155°	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2
157.5°	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8
160°	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2
162.5°	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9
165°	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3
167.5°	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4
170°	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1
172.5°	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3
175°	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4
177.5°	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1170.8	1171.3	1176.1	1179.5	1177.7	1180.0	1180.7
5°	1279.2	1298.6	1308.8	1316.4	1316.9	1317.5	1321.8
7.5°	1432.8	1453.7	1468.9	1491.9	1498.8	1506.7	1504.4
10°	1545.0	1575.7	1602.1	1616.1	1631.3	1653.4	1635.5
12.5°	1649.8	1704.2	1744.5	1766.2	1780.4	1784.9	1776.2
15°	1822.6	1893.8	1932.1	1930.9	1979.5	2000.5	1967.6
17.5°	1981.1	2046.8	2099.4	2126.3	2166.8	2175.7	2171.6
20°	2078.1	2149.8	2190.8	2237.1	2258.2	2277.0	2280.3
22.5°	2161.8	2226.2	2270.2	2308.7	2326.3	2335.3	2340.7
25°	2247.9	2298.6	2325.1	2338.5	2343.4	2342.2	2335.3
27.5°	2242.0	2245.9	2216.8	2188.2	2162.7	2133.9	2123.9
30°	2183.8	2138.5	2057.6	2011.8	1944.4	1891.1	1912.6
32.5°	2030.7	1940.5	1849.7	1749.6	1666.7	1643.1	1619.4
35°	1733.1	1574.6	1481.9	1374.1	1330.9	1287.9	1258.2
37.5°	1402.2	1279.5	1169.6	1099.1	1055.8	1028.6	1013.9
40°	1212.4	1101.8	1011.3	954.2	921.3	890.6	886.2
42.5°	1061.0	958.2	890.1	844.6	813.0	799.9	790.5
45°	869.0	797.3	751.5	719.1	698.1	690.0	679.2
47.5°	735.5	684.8	650.5	628.4	612.6	606.6	605.7
50°	660.9	618.9	593.5	576.2	563.9	561.7	553.1
52.5°	604.8	568.4	548.7	533.6	524.7	518.6	516.0
55°	525.1	500.8	483.0	474.4	467.4	461.4	461.4
57.5°	459.4	439.1	427.4	420.0	417.9	413.7	411.0
60°	418.8	401.6	392.4	386.0	381.7	382.2	377.3
62.5°	379.2	368.0	359.3	352.8	347.6	347.7	348.0
65°	322.9	314.3	307.8	305.6	302.5	298.7	299.8
67.5°	273.6	265.5	260.5	256.8	255.7	253.7	256.8
70°	238.3	232.3	228.5	225.3	224.3	224.8	227.5
72.5°	205.9	201.7	199.2	197.7	195.4	195.4	197.3
75°	161.7	158.5	156.3	154.7	154.2	154.2	154.2
77.5°	118.8	118.0	117.1	114.7	114.8	115.5	115.6
80°	93.8	92.2	91.7	90.5	89.0	87.9	90.5
82.5°	70.1	68.4	67.9	67.7	65.2	65.0	67.3
85°	37.7	36.1	36.7	36.1	36.1	35.6	35.6
87.5°	15.7	15.4	15.1	15.4	15.1	14.8	15.5
90°	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	600.9	657.9	689.5	702.2	705.8	704.9	703.9

TEST NUMBER: P332011-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)