

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331936-927

Luminaire Tested: **S123DIP-S560D805U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331936-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4140.6 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331936-927

CATALOG NUMBER: S123DIP-S560D805U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P331936-927

CATALOG NUMBER: S123DIP-S560D805U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	40	38	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	33	31
4	73	62	55	49	67	57	51	45	48	43	39	39	36	33	31	29	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7597	7597	7597
5°	7632	7527	7580
10°	7581	7462	7508
15°	7492	7377	7392
20°	7389	7257	7263
25°	7251	7114	7099
30°	7097	6954	6901
35°	6937	6786	6699
40°	6770	6600	6497
45°	6587	6428	6272
50°	6402	6219	6047
55°	6161	6001	5819
60°	5918	5748	5565
65°	5703	5471	5300
70°	5385	5155	4925
75°	4924	4745	4541
80°	4438	4252	4215
85°	3890	3742	3606

TEST NUMBER: P331936-927

CATALOG NUMBER: S123DIP-S560D805U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.6
10°-20°	187.7	4.5
20°-30°	277.3	6.7
30°-40°	323.9	7.8
40°-50°	325.6	7.9
50°-60°	286.0	6.9
60°-70°	213.1	5.1
70°-80°	121.4	2.9
80°-90°	37.2	0.9
90°-100°	170.3	4.1
100°-110°	482.1	11.6
110°-120°	474.3	11.5
120°-130°	378.3	9.1
130°-140°	298.3	7.2
140°-150°	222.6	5.4
150°-160°	155.2	3.7
160°-170°	91.2	2.2
170°-180°	29.7	0.7
0°-30°	531.5	12.8
0°-40°	855.4	20.7
0°-60°	1467.0	35.4
0°-90°	1838.8	44.4
90°-120°	1126.7	27.2
90°-150°	2025.9	48.9
90°-180°	2302.0	55.6
0°-180°	4140.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	706	706	706	706	706	
5°	706	703	697	702	702	67
15°	672	670	662	666	663	189
25°	610	607	599	599	598	281
35°	528	524	516	513	510	330
45°	433	430	422	415	412	334
55°	328	327	320	313	310	294
65°	224	221	215	210	208	221
75°	118	116	114	111	109	127
85°	32	30	30	29	29	35
90°	1	7	15	17	18	3
95°	21	68	367	107	72	23
105°	72	106	498	871	788	76
115°	127	158	381	835	958	126
125°	176	208	356	644	756	157
135°	207	247	350	530	612	160
145°	236	270	346	435	479	148
155°	268	289	335	381	397	123
165°	293	301	321	340	346	83
175°	305	306	308	312	312	29
180°	306	306	306	306	306	

TEST NUMBER: P331936-927

CATALOG NUMBER: S123DIP-S560D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	708.1	707.7	707.3	706.9	706.5	705.6	704.4	703.2	702.1	700.9	702.0
5°	706.3	705.7	705.0	704.3	703.6	702.6	701.1	699.6	698.2	696.6	698.0
7.5°	699.4	698.8	698.1	697.4	696.7	695.6	694.1	692.5	691.0	689.5	690.7
10°	693.6	692.9	692.3	691.6	690.9	689.7	687.9	686.2	684.4	682.7	683.9
12.5°	685.9	685.2	684.7	684.1	683.6	682.5	680.8	679.1	677.6	675.9	676.8
15°	672.3	671.8	671.3	670.7	670.2	669.1	667.3	665.6	663.8	662.0	663.1
17.5°	656.7	656.0	655.3	654.6	653.9	652.7	650.9	649.2	647.5	645.6	646.4
20°	645.1	644.3	643.4	642.6	641.8	640.6	638.8	637.1	635.3	633.5	634.1
22.5°	631.9	631.1	630.3	629.5	628.7	627.4	625.7	623.9	622.2	620.4	620.8
25°	610.5	609.7	608.9	608.1	607.2	605.9	604.2	602.5	600.7	599.0	599.0
27.5°	587.6	586.8	586.0	585.2	584.4	583.0	581.1	579.3	577.4	575.5	575.6
30°	571.0	570.4	569.7	569.0	568.3	567.0	565.1	563.2	561.4	559.5	559.5
32.5°	554.5	553.7	552.7	551.8	551.0	549.8	548.3	546.8	545.4	544.0	543.2
35°	527.9	527.1	526.3	525.5	524.7	523.4	521.7	519.9	518.2	516.4	515.6
37.5°	500.7	499.7	498.7	497.6	496.6	495.3	493.5	491.7	489.9	488.1	487.2
40°	481.8	481.0	480.2	479.4	478.6	477.2	475.3	473.5	471.6	469.7	468.6
42.5°	462.9	462.0	461.1	460.1	459.2	457.8	455.9	454.1	452.2	450.3	449.2
45°	432.7	432.1	431.6	431.0	430.5	429.4	427.6	425.9	424.1	422.3	420.7
47.5°	402.7	401.9	401.2	400.4	399.6	398.3	396.7	395.1	393.4	391.7	390.1
50°	382.3	381.6	381.0	380.2	379.6	378.4	376.6	374.9	373.1	371.4	369.9
52.5°	360.9	360.4	360.0	359.6	359.1	357.9	356.1	354.3	352.4	350.5	349.3
55°	328.3	328.1	328.0	327.9	327.7	326.8	325.0	323.3	321.5	319.8	318.3
57.5°	297.2	296.8	296.3	295.9	295.4	294.5	293.0	291.7	290.3	288.8	287.6
60°	274.9	274.7	274.6	274.5	274.3	273.5	271.9	270.2	268.6	267.0	265.8
62.5°	255.0	254.6	254.3	254.0	253.6	252.6	251.0	249.4	247.7	246.1	244.9
65°	223.9	223.2	222.6	221.9	221.3	220.2	218.9	217.5	216.2	214.8	213.7
67.5°	191.0	190.4	189.8	189.3	188.6	187.8	186.8	185.8	184.7	183.8	182.8
70°	171.1	170.3	169.5	168.7	167.9	167.1	166.3	165.5	164.6	163.8	162.9
72.5°	150.3	149.6	149.1	148.5	147.9	147.1	146.2	145.3	144.3	143.5	142.6
75°	118.4	117.8	117.2	116.7	116.2	115.7	115.3	114.9	114.5	114.1	113.4
77.5°	90.1	89.8	89.4	89.2	88.9	88.5	88.0	87.5	87.0	86.5	86.1
80°	71.6	71.2	70.8	70.4	69.9	69.6	69.4	69.1	68.8	68.6	68.4
82.5°	53.6	53.6	53.5	53.4	53.3	53.2	53.2	53.2	53.1	53.1	52.8
85°	31.5	31.3	31.1	30.7	30.5	30.3	30.3	30.3	30.3	30.3	30.1
87.5°	12.8	12.8	12.8	12.8	12.7	12.8	13.0	13.2	13.5	13.8	13.5
90°	1.3	2.5	3.7	5.5	6.8	8.1	9.9	11.8	13.6	15.4	14.9
92.5°	7.7	11.4	16.6	21.5	26.6	35.8	52.0	78.7	104.8	95.2	71.9
95°	21.1	22.9	29.7	40.2	56.3	80.5	133.2	225.5	327.0	367.3	297.9
97.5°	35.9	36.5	41.9	51.0	66.9	93.0	143.3	247.4	416.7	569.2	609.0
100°	45.9	46.4	50.8	59.5	74.3	98.5	141.8	233.5	396.4	586.5	708.5
102.5°	56.2	57.4	61.2	69.4	82.8	104.9	143.8	221.6	366.6	554.3	713.5
105°	71.9	73.7	77.4	84.8	96.6	115.8	149.2	213.0	330.1	498.0	675.7
107.5°	88.4	90.3	93.9	101.2	112.3	130.1	159.4	212.5	306.8	448.1	609.6
110°	100.4	102.2	105.3	112.1	122.6	140.0	167.9	214.9	297.9	419.9	567.9

TEST NUMBER: P331936-927

CATALOG NUMBER: S123DIP-S560D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.2	113.1	116.2	123.0	133.6	150.4	176.3	219.8	292.9	401.1	531.8
115°	127.0	129.4	133.2	139.3	149.9	166.6	190.1	227.9	291.1	380.9	488.1
117.5°	142.7	145.5	148.6	154.3	166.1	181.6	204.9	238.6	292.2	369.0	461.7
120°	153.6	155.4	158.5	164.8	176.5	192.0	214.3	246.5	294.2	363.5	447.8
122.5°	163.0	164.9	167.9	174.7	185.9	202.4	224.2	253.9	297.6	360.1	436.4
125°	176.5	177.8	181.5	188.3	200.0	216.7	238.4	265.7	302.9	355.5	421.8
127.5°	186.8	188.6	193.2	200.2	213.2	229.9	250.8	275.4	308.8	353.3	408.9
130°	193.2	195.1	200.7	208.1	221.1	237.8	258.3	281.8	312.8	351.8	402.0
132.5°	198.2	200.6	206.6	215.6	228.5	244.8	264.7	287.7	315.8	351.3	395.5
135°	206.8	209.4	216.2	225.5	238.4	255.2	274.3	295.4	320.2	350.5	387.1
137.5°	215.0	217.6	224.3	234.2	247.1	262.6	281.1	301.1	323.2	349.2	379.8
140°	220.5	223.6	229.8	239.7	252.1	267.5	285.5	304.1	325.2	348.7	375.3
142.5°	226.4	229.0	235.8	244.6	257.1	271.5	289.0	307.0	326.6	347.7	371.4
145°	236.0	237.8	243.4	252.7	263.2	277.5	293.6	310.3	327.6	346.2	366.1
147.5°	245.7	246.8	252.2	260.2	270.4	282.6	297.3	312.3	327.6	343.9	360.8
150°	252.1	252.7	257.6	265.7	274.3	285.5	299.8	312.8	327.6	341.9	357.4
152.5°	258.5	258.6	263.6	270.7	278.3	289.0	301.3	313.8	326.1	339.4	353.4
155°	268.2	268.2	271.9	278.1	284.9	293.6	304.1	314.0	324.6	335.1	347.5
157.5°	275.8	276.3	279.3	284.8	290.6	297.3	305.7	314.7	322.4	331.2	340.8
160°	281.8	281.8	284.3	289.2	293.6	299.8	307.2	314.7	321.5	328.3	336.3
162.5°	286.3	286.3	288.3	292.2	296.0	301.3	307.7	314.1	319.5	325.3	331.8
165°	292.9	292.3	293.6	296.7	299.1	303.5	308.4	312.8	316.5	320.8	325.7
167.5°	298.0	297.3	297.9	300.2	302.0	304.8	308.3	311.8	313.5	316.4	320.0
170°	301.0	299.8	300.4	302.2	303.5	304.8	307.8	310.3	311.6	313.4	316.5
172.5°	303.0	302.2	302.4	303.7	304.4	305.2	307.8	309.8	310.1	310.9	313.0
175°	305.3	304.8	304.1	305.3	305.3	305.9	307.2	308.4	307.8	307.8	309.0
177.5°	306.4	305.9	305.5	305.9	305.9	305.9	306.4	307.4	306.4	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9

TEST NUMBER: P331936-927

CATALOG NUMBER: S123DIP-S560D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	703.1	704.1	705.2	705.7	705.6	705.4	705.4	705.3
5°	699.3	700.7	702.0	702.6	702.3	702.0	701.8	701.5
7.5°	691.9	693.1	694.3	694.8	694.7	694.5	694.3	694.2
10°	685.1	686.3	687.5	688.0	687.8	687.5	687.2	686.9
12.5°	677.6	678.6	679.5	679.8	679.6	679.5	679.3	679.1
15°	664.2	665.3	666.4	666.5	665.7	664.9	664.1	663.3
17.5°	647.2	647.9	648.7	648.9	648.6	648.3	648.0	647.7
20°	634.6	635.2	635.6	635.7	635.3	634.9	634.5	634.1
22.5°	621.3	621.7	622.2	622.1	621.6	621.1	620.6	620.0
25°	599.2	599.4	599.4	599.4	599.0	598.6	598.1	597.7
27.5°	575.8	575.8	575.9	575.8	575.2	574.7	574.2	573.7
30°	559.5	559.5	559.5	559.0	558.1	557.1	556.2	555.2
32.5°	542.5	541.7	540.9	540.3	539.8	539.3	538.8	538.3
35°	514.8	514.0	513.2	512.5	511.7	511.1	510.4	509.8
37.5°	486.2	485.2	484.3	483.5	483.2	482.7	482.3	481.8
40°	467.5	466.4	465.4	464.5	464.0	463.5	463.0	462.4
42.5°	448.1	447.0	445.9	445.1	444.6	444.1	443.5	443.0
45°	419.1	417.5	415.9	414.7	414.1	413.4	412.7	412.0
47.5°	388.6	387.0	385.4	384.3	383.7	383.1	382.5	381.9
50°	368.4	366.9	365.4	364.3	363.5	362.7	361.9	361.1
52.5°	348.0	346.7	345.5	344.4	343.6	342.8	342.0	341.2
55°	316.8	315.4	313.9	312.8	312.1	311.4	310.8	310.1
57.5°	286.2	284.9	283.6	282.5	281.7	281.0	280.2	279.4
60°	264.6	263.4	262.1	261.2	260.5	259.8	259.2	258.5
62.5°	243.7	242.5	241.3	240.4	240.0	239.6	239.1	238.6
65°	212.6	211.6	210.5	209.8	209.4	209.0	208.6	208.1
67.5°	181.9	180.9	180.0	179.2	178.6	178.1	177.5	177.0
70°	161.9	161.1	160.1	159.2	158.6	157.9	157.2	156.5
72.5°	141.8	140.9	140.1	139.5	139.2	138.8	138.5	138.1
75°	112.7	112.1	111.4	110.8	110.4	110.0	109.6	109.2
77.5°	85.6	85.2	84.7	84.4	84.4	84.4	84.4	84.4
80°	68.3	68.1	68.0	68.0	68.0	68.0	68.0	68.0
82.5°	52.5	52.3	52.0	51.9	51.8	51.7	51.6	51.5
85°	29.8	29.5	29.2	29.2	29.2	29.2	29.2	29.2
87.5°	13.5	13.5	13.6	13.8	13.6	13.8	13.9	13.8
90°	15.4	16.1	16.7	18.0	17.3	18.0	18.6	18.0
92.5°	52.1	41.4	36.5	33.4	32.2	30.3	31.0	29.9
95°	223.0	151.1	118.3	96.0	84.2	78.7	74.3	71.9
97.5°	555.8	445.2	365.3	291.2	245.5	217.6	200.9	195.6
100°	730.2	680.0	607.6	519.6	457.1	411.9	387.7	388.3
102.5°	788.1	786.6	744.3	688.6	639.9	604.1	583.9	569.7
105°	805.2	867.0	878.8	862.8	834.2	810.7	790.9	787.8
107.5°	756.4	856.9	911.2	933.2	933.7	925.8	919.1	913.4
110°	709.8	823.7	901.7	945.2	962.4	967.4	966.1	965.0

TEST NUMBER: P331936-927

CATALOG NUMBER: S123DIP-S560D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	663.7	780.1	867.6	923.3	955.1	970.4	975.1	975.3
115°	602.6	710.3	801.5	868.9	915.4	942.6	955.1	958.1
117.5°	558.4	651.4	733.2	801.7	850.1	881.3	899.1	903.4
120°	535.1	618.7	693.1	755.6	804.5	839.2	854.1	857.8
122.5°	516.8	592.5	661.3	719.5	762.9	794.1	810.5	815.2
125°	492.3	559.9	619.3	668.9	708.5	735.8	751.2	755.6
127.5°	471.1	531.2	584.9	630.0	665.3	688.6	702.6	706.5
130°	457.7	513.4	563.6	605.7	638.6	660.8	673.8	678.8
132.5°	445.3	496.6	543.3	583.4	614.3	636.6	648.1	651.6
135°	428.6	472.5	512.8	548.1	578.5	597.1	608.2	612.5
137.5°	413.4	449.4	484.1	514.7	540.2	559.0	568.5	571.3
140°	404.4	436.0	465.7	492.3	515.9	533.2	543.2	542.6
142.5°	396.0	423.1	448.9	472.1	492.1	507.5	516.4	515.8
145°	385.9	406.3	426.1	444.1	459.5	472.5	477.5	478.7
147.5°	377.6	393.8	409.8	422.6	434.3	443.1	447.8	448.3
150°	371.6	385.9	398.9	410.6	419.9	426.7	430.5	430.5
152.5°	366.1	378.4	389.9	399.7	407.0	413.4	415.6	415.6
155°	358.0	367.9	377.2	384.6	390.1	395.1	396.4	397.0
157.5°	349.3	357.6	364.8	370.6	375.4	379.1	380.2	380.0
160°	344.4	351.2	357.4	361.7	366.1	369.7	369.7	369.2
162.5°	338.4	344.2	349.9	353.8	356.6	359.8	359.8	359.3
165°	330.7	334.5	338.8	341.9	344.4	346.8	346.2	346.2
167.5°	324.0	326.9	329.4	331.6	332.7	334.5	333.8	333.8
170°	319.6	321.5	323.9	325.2	325.7	327.0	326.4	326.4
172.5°	315.6	317.0	318.9	319.7	319.8	321.1	320.0	319.5
175°	310.3	310.9	312.1	312.1	312.1	312.8	312.1	311.6
177.5°	307.0	307.4	307.9	307.9	307.4	307.9	307.0	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9

(END OF REPORT)