

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332376-830

Luminaire Tested: **S123RDIP-S1165D805U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332376-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6728.8 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332376-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot



TEST NUMBER: P332376-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90		78	78	78		67
1	101	96	93	89	94	90	87	84	79	77	75		69	67	66		59
2	92	85	79	74	86	80	74	70	70	66	62		61	58	55		53
3	84	75	68	62	79	70	64	59	62	57	53		54	50	47		47
4	77	67	59	53	72	63	56	50	55	50	45		49	44	41		42
5	71	60	51	45	66	56	49	43	50	44	40		44	39	36		38
6	66	54	45	40	61	51	43	38	45	39	35		40	35	31		35
7	61	49	41	35	57	46	39	34	41	35	31		36	32	28		32
8	57	44	36	31	53	42	35	30	38	32	28		33	29	25		29
9	53	41	33	28	49	38	32	27	35	29	25		31	26	23		27
10	49	37	30	25	46	35	29	24	32	26	22		29	24	21		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755

TEST NUMBER: P332376-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	2.5
10°-20°	477.3	7.1
20°-30°	687.3	10.2
30°-40°	774.2	11.5
40°-50°	740.6	11.0
50°-60°	606.5	9.0
60°-70°	409.2	6.1
70°-80°	205.9	3.1
80°-90°	57.2	0.9
90°-100°	61.1	0.9
100°-110°	182.9	2.7
110°-120°	311.1	4.6
120°-130°	409.2	6.1
130°-140°	460.0	6.8
140°-150°	452.1	6.7
150°-160°	380.6	5.7
160°-170°	253.4	3.8
170°-180°	88.7	1.3
0°-30°	1336.1	19.9
0°-40°	2110.3	31.4
0°-60°	3457.4	51.4
0°-90°	4129.7	61.4
90°-120°	555.1	8.3
90°-150°	1876.4	27.9
90°-180°	2599.0	38.6
0°-180°	6728.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	8	18	21	22	7
95°	44	49	55	57	58	49
105°	166	168	174	174	175	178
115°	313	315	314	315	314	310
125°	458	460	459	456	453	409
135°	595	599	598	596	594	458
145°	721	723	725	724	721	450
155°	826	826	827	829	825	380
165°	900	898	898	901	897	254
175°	936	933	933	937	932	89
180°	938	938	938	938	938	

TEST NUMBER: P332376-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.6	26.0	23.5	20.9	18.3	17.2	17.6	18.1	18.5	18.9	18.9
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	17.8	18.9	20.1	21.2	22.2	23.5	24.7	25.9	27.1	28.3	28.8
95°	43.5	44.6	45.8	46.9	48.1	49.3	50.6	51.9	53.3	54.6	55.2
97.5°	77.2	78.0	78.9	79.7	80.7	81.5	82.5	83.4	84.4	85.3	86.1
100°	100.2	101.2	102.2	103.2	104.2	105.1	105.8	106.7	107.5	108.3	108.9
102.5°	126.8	127.3	127.9	128.6	129.1	130.0	131.0	132.1	133.2	134.3	134.8
105°	165.8	166.2	166.5	166.8	167.1	168.1	169.5	171.0	172.5	173.9	173.9
107.5°	211.2	211.4	211.6	211.8	212.0	212.4	213.0	213.6	214.1	214.7	215.3
110°	239.5	239.8	240.2	240.4	240.8	241.1	241.5	241.8	242.1	242.4	243.1

TEST NUMBER: P332376-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.0	269.2	269.4	269.6	269.8	269.8	269.9	270.0	270.1	270.1	271.0
115°	313.2	313.7	314.1	314.6	315.2	315.3	314.9	314.6	314.2	314.0	314.1
117.5°	357.7	358.1	358.4	358.6	359.0	358.9	358.5	358.1	357.7	357.2	357.2
120°	385.4	386.3	387.4	388.3	389.4	389.5	388.6	387.8	387.0	386.2	386.0
122.5°	414.3	415.0	415.8	416.4	417.2	417.4	416.9	416.5	416.0	415.7	415.2
125°	458.4	458.8	459.3	459.9	460.3	460.4	460.1	459.8	459.4	459.1	458.5
127.5°	499.1	500.1	501.1	502.2	503.2	503.6	503.2	502.8	502.5	502.1	501.2
130°	526.1	527.4	528.8	530.1	531.4	531.8	531.3	530.8	530.4	529.8	529.1
132.5°	553.3	554.6	555.9	557.2	558.6	559.0	558.6	558.3	557.9	557.5	556.8
135°	594.7	595.7	596.6	597.7	598.6	599.1	598.9	598.7	598.5	598.4	597.8
137.5°	633.0	633.9	634.6	635.5	636.3	636.9	637.3	637.7	638.2	638.6	637.9
140°	659.5	660.3	661.2	662.0	662.8	663.3	663.5	663.6	663.8	663.9	663.8
142.5°	683.7	684.6	685.3	686.2	687.0	687.6	687.9	688.2	688.4	688.7	688.5
145°	721.4	721.8	722.1	722.5	722.7	723.1	723.7	724.2	724.6	725.1	725.0
147.5°	754.5	755.1	755.6	756.2	756.9	757.3	757.8	758.3	758.7	759.2	759.2
150°	777.4	777.8	778.1	778.4	778.7	779.1	779.4	779.8	780.0	780.4	780.4
152.5°	796.4	796.7	797.2	797.7	798.1	798.5	798.7	798.9	799.1	799.3	799.6
155°	826.0	826.0	826.0	826.0	826.0	826.1	826.3	826.5	826.7	826.8	827.5
157.5°	851.4	851.2	851.0	850.8	850.6	850.6	850.7	850.9	851.0	851.1	851.9
160°	867.3	867.0	866.7	866.4	866.0	865.9	865.9	865.9	865.9	865.9	866.7
162.5°	881.5	881.1	880.6	880.1	879.7	879.5	879.7	879.8	879.9	880.1	880.8
165°	899.8	899.3	898.8	898.3	897.8	897.6	897.6	897.6	897.6	897.6	898.5
167.5°	914.4	913.7	913.0	912.4	911.7	911.5	911.6	911.7	911.9	912.0	913.0
170°	922.7	922.0	921.3	920.7	920.0	919.6	919.6	919.6	919.6	919.6	920.9
172.5°	929.1	928.5	927.8	927.2	926.5	926.1	926.1	926.1	926.1	926.1	927.2
175°	935.9	935.2	934.6	934.0	933.3	932.9	932.9	932.9	932.9	932.9	934.0
177.5°	938.7	938.2	937.6	937.1	936.6	936.3	936.3	936.3	936.3	936.3	937.1
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1

TEST NUMBER: P332376-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	18.7	18.6	18.4	18.3	18.1	17.8	17.6	17.4
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	29.3	29.9	30.3	30.5	30.3	30.2	30.0	29.8
95°	55.8	56.5	57.1	57.5	57.5	57.5	57.5	57.5
97.5°	86.8	87.6	88.3	88.7	88.6	88.6	88.5	88.4
100°	109.3	109.8	110.3	110.7	111.0	111.3	111.7	112.0
102.5°	135.3	135.7	136.2	136.5	136.4	136.3	136.3	136.2
105°	173.9	173.9	173.9	174.1	174.4	174.7	175.0	175.4
107.5°	215.7	216.3	216.9	217.0	216.8	216.6	216.4	216.2
110°	243.7	244.4	245.1	245.2	244.9	244.6	244.2	243.9

TEST NUMBER: P332376-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.7	272.5	273.3	273.6	273.6	273.5	273.4	273.4
115°	314.2	314.4	314.6	314.6	314.4	314.2	314.1	314.0
117.5°	357.2	357.1	357.1	356.8	356.5	356.0	355.5	355.1
120°	385.8	385.7	385.5	385.2	384.9	384.6	384.3	383.9
122.5°	414.8	414.3	414.0	413.5	413.0	412.6	412.1	411.6
125°	457.8	457.1	456.5	455.8	455.2	454.5	453.8	453.2
127.5°	500.3	499.4	498.5	497.7	496.9	496.2	495.4	494.6
130°	528.6	527.9	527.3	526.3	525.2	524.1	522.9	521.7
132.5°	556.0	555.2	554.4	553.6	552.7	551.8	550.9	550.1
135°	597.1	596.4	595.8	595.3	594.9	594.7	594.3	594.0
137.5°	637.3	636.6	635.8	635.2	634.6	634.0	633.4	632.7
140°	663.6	663.5	663.3	662.7	661.5	660.3	659.2	658.1
142.5°	688.4	688.2	688.1	687.6	686.6	685.8	684.9	684.0
145°	724.8	724.6	724.4	724.1	723.4	722.7	722.1	721.4
147.5°	759.2	759.2	759.2	758.7	757.7	756.7	755.7	754.8
150°	780.4	780.4	780.4	780.0	778.9	778.0	776.9	776.0
152.5°	799.7	800.0	800.3	800.0	799.2	798.3	797.5	796.6
155°	828.1	828.8	829.4	829.2	828.0	826.9	825.8	824.6
157.5°	852.5	853.2	853.8	853.8	852.9	852.0	851.0	850.1
160°	867.5	868.4	869.1	869.2	868.6	867.9	867.2	866.6
162.5°	881.7	882.5	883.4	883.2	882.1	881.1	880.1	879.0
165°	899.6	900.5	901.5	901.4	900.3	899.1	898.0	896.8
167.5°	914.1	915.0	916.1	916.1	915.0	914.1	913.0	912.0
170°	922.0	923.1	924.3	924.3	923.1	922.0	920.9	919.6
172.5°	928.2	929.3	930.2	930.2	929.0	927.8	926.7	925.6
175°	934.9	935.9	936.9	936.8	935.7	934.5	933.3	932.2
177.5°	937.9	938.7	939.4	939.4	938.5	937.5	936.7	935.8
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)