

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331917-930

Luminaire Tested: **S123DIP-S560D365U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331917-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2907.3 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331917-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot



TEST NUMBER: P331917-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65			
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59	55			
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50	46			
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39			
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33			
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29			
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25			
7	60	48	39	34	56	45	38	32	41	34	30	36	31	27	32	28	25	22			
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20			
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18			
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705

TEST NUMBER: P331917-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	2.4
10°-20°	193.2	6.6
20°-30°	285.4	9.8
30°-40°	333.3	11.5
40°-50°	335.1	11.5
50°-60°	294.4	10.1
60°-70°	219.3	7.5
70°-80°	124.9	4.3
80°-90°	36.9	1.3
90°-100°	23.9	0.8
100°-110°	71.5	2.5
110°-120°	121.6	4.2
120°-130°	160.0	5.5
130°-140°	179.8	6.2
140°-150°	176.8	6.1
150°-160°	148.8	5.1
160°-170°	99.1	3.4
170°-180°	34.7	1.2
0°-30°	547.0	18.8
0°-40°	880.3	30.3
0°-60°	1509.9	51.9
0°-90°	1891.1	65.0
90°-120°	217.1	7.5
90°-150°	733.7	25.2
90°-180°	1016.0	34.9
0°-180°	2907.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	0	3	7	8	9	3
95°	17	19	21	22	22	19
105°	65	66	68	68	69	69
115°	122	123	123	123	123	121
125°	179	180	180	178	177	160
135°	232	234	234	233	232	179
145°	282	283	284	283	282	176
155°	323	323	323	324	322	149
165°	352	351	351	352	351	99
175°	366	365	365	366	364	35
180°	367	367	367	367	367	

TEST NUMBER: P331917-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.0	12.9	12.6	12.4	12.2	12.1	12.2	12.2	12.3	12.4	12.3
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	7.0	7.4	7.8	8.3	8.7	9.1	9.6	10.1	10.6	11.1	11.3
95°	17.0	17.4	17.9	18.3	18.8	19.2	19.8	20.3	20.8	21.4	21.6
97.5°	30.2	30.5	30.9	31.2	31.6	31.9	32.3	32.6	33.0	33.3	33.7
100°	39.2	39.5	39.9	40.4	40.7	41.1	41.4	41.7	42.1	42.3	42.6
102.5°	49.6	49.8	50.0	50.2	50.5	50.8	51.2	51.7	52.1	52.5	52.7
105°	64.8	65.0	65.1	65.2	65.3	65.7	66.3	66.9	67.4	68.0	68.0
107.5°	82.6	82.7	82.8	82.8	82.9	83.0	83.2	83.5	83.7	84.0	84.1
110°	93.7	93.8	93.9	94.0	94.2	94.2	94.4	94.6	94.7	94.8	95.1

TEST NUMBER: P331917-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	105.2	105.3	105.3	105.4	105.5	105.5	105.6	105.6	105.6	105.7	105.9
115°	122.5	122.6	122.9	123.0	123.2	123.3	123.1	123.0	122.9	122.7	122.8
117.5°	139.8	140.0	140.1	140.2	140.4	140.3	140.1	140.0	139.8	139.7	139.7
120°	150.7	151.1	151.5	151.8	152.2	152.2	152.0	151.6	151.3	151.0	150.9
122.5°	162.0	162.2	162.6	162.8	163.1	163.1	163.0	162.8	162.7	162.5	162.3
125°	179.2	179.4	179.6	179.8	180.0	180.0	179.9	179.8	179.6	179.5	179.2
127.5°	195.1	195.5	195.9	196.3	196.7	196.9	196.7	196.6	196.5	196.3	196.0
130°	205.7	206.2	206.8	207.2	207.7	207.9	207.7	207.6	207.3	207.2	206.9
132.5°	216.3	216.9	217.4	217.8	218.3	218.6	218.4	218.3	218.1	218.0	217.7
135°	232.5	232.9	233.3	233.7	234.1	234.2	234.2	234.1	234.0	234.0	233.7
137.5°	247.5	247.9	248.1	248.4	248.7	249.0	249.2	249.3	249.5	249.6	249.4
140°	257.9	258.2	258.5	258.9	259.2	259.3	259.4	259.4	259.5	259.6	259.5
142.5°	267.3	267.7	268.0	268.3	268.6	268.8	269.0	269.0	269.1	269.3	269.2
145°	282.1	282.2	282.3	282.4	282.6	282.7	282.9	283.2	283.3	283.5	283.5
147.5°	295.0	295.2	295.5	295.7	295.9	296.1	296.3	296.4	296.6	296.9	296.9
150°	303.9	304.1	304.2	304.4	304.5	304.6	304.8	304.8	305.0	305.1	305.1
152.5°	311.4	311.5	311.7	311.9	312.1	312.2	312.3	312.3	312.4	312.5	312.6
155°	323.0	323.0	323.0	323.0	323.0	323.0	323.1	323.1	323.2	323.3	323.5
157.5°	332.9	332.8	332.7	332.6	332.6	332.6	332.6	332.6	332.7	332.8	333.0
160°	339.1	339.0	338.8	338.8	338.6	338.5	338.5	338.5	338.5	338.5	338.8
162.5°	344.6	344.5	344.3	344.1	343.9	343.9	343.9	344.0	344.1	344.1	344.4
165°	351.8	351.6	351.4	351.2	351.0	350.9	350.9	350.9	350.9	350.9	351.3
167.5°	357.5	357.3	357.0	356.7	356.4	356.4	356.4	356.4	356.5	356.6	356.9
170°	360.7	360.4	360.2	360.0	359.7	359.5	359.5	359.5	359.5	359.5	360.0
172.5°	363.3	363.0	362.7	362.5	362.2	362.1	362.1	362.1	362.1	362.1	362.5
175°	365.9	365.7	365.4	365.2	364.9	364.8	364.8	364.8	364.8	364.8	365.2
177.5°	367.0	366.8	366.6	366.4	366.2	366.1	366.1	366.1	366.1	366.1	366.4
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8

TEST NUMBER: P331917-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	12.2	12.2	12.1	12.1	12.1	12.1	12.2	12.2
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	11.5	11.7	11.9	12.0	11.9	11.8	11.7	11.7
95°	21.9	22.1	22.3	22.5	22.5	22.5	22.5	22.5
97.5°	33.9	34.2	34.6	34.7	34.7	34.7	34.6	34.6
100°	42.7	43.0	43.1	43.3	43.4	43.5	43.7	43.8
102.5°	52.9	53.1	53.2	53.3	53.3	53.3	53.2	53.2
105°	68.0	68.0	68.0	68.1	68.2	68.3	68.5	68.6
107.5°	84.4	84.5	84.8	84.9	84.8	84.7	84.6	84.5
110°	95.3	95.6	95.8	95.9	95.7	95.6	95.5	95.4

TEST NUMBER: P331917-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.2	106.6	106.9	107.0	107.0	107.0	106.9	106.9
115°	122.9	122.9	123.0	123.0	122.9	122.9	122.8	122.7
117.5°	139.7	139.7	139.7	139.5	139.3	139.2	139.0	138.8
120°	150.8	150.7	150.7	150.6	150.5	150.3	150.3	150.1
122.5°	162.2	162.0	161.8	161.7	161.5	161.3	161.1	160.9
125°	179.0	178.7	178.5	178.2	178.0	177.7	177.4	177.2
127.5°	195.6	195.3	194.9	194.5	194.3	194.0	193.7	193.4
130°	206.7	206.4	206.1	205.8	205.4	204.9	204.5	204.0
132.5°	217.4	217.0	216.8	216.5	216.1	215.7	215.4	215.1
135°	233.4	233.2	232.9	232.8	232.6	232.4	232.4	232.2
137.5°	249.2	248.9	248.6	248.3	248.1	247.9	247.6	247.4
140°	259.4	259.4	259.3	259.1	258.6	258.2	257.7	257.3
142.5°	269.1	269.0	269.0	268.8	268.5	268.2	267.7	267.4
145°	283.4	283.3	283.2	283.1	282.8	282.6	282.3	282.1
147.5°	296.9	296.9	296.9	296.6	296.3	295.9	295.5	295.1
150°	305.1	305.1	305.1	304.9	304.5	304.2	303.8	303.4
152.5°	312.7	312.8	312.9	312.7	312.4	312.1	311.8	311.4
155°	323.8	324.0	324.3	324.2	323.8	323.3	322.9	322.4
157.5°	333.3	333.6	333.9	333.8	333.5	333.1	332.7	332.4
160°	339.2	339.5	339.8	339.8	339.6	339.3	339.1	338.8
162.5°	344.7	345.0	345.4	345.3	344.9	344.5	344.1	343.6
165°	351.7	352.0	352.5	352.5	352.0	351.6	351.1	350.7
167.5°	357.3	357.8	358.2	358.2	357.8	357.3	356.9	356.6
170°	360.4	360.9	361.3	361.3	360.9	360.4	360.0	359.5
172.5°	362.9	363.3	363.7	363.7	363.2	362.8	362.3	361.9
175°	365.5	365.9	366.3	366.2	365.8	365.3	364.9	364.4
177.5°	366.7	367.0	367.3	367.3	367.0	366.6	366.2	365.8
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8

(END OF REPORT)